


INDUSTRIAL BELTS



Gates Industrial Belts (GIB)

NAPA now provides the convenience and support of over 11,000 industrial-application belts including PowerGrip®, Synchro Power®, Super HC®, PowerBand®, Predator®, Hi-Power®, Tri-Power®, Metric-Power®, PowerBack®, Power Curve®, Micro-V®, Multi-Speed, Power Round™, Easy-Splice and Polyflex® belts.

Table of Contents

Index.....	a1
Quick Select Product Guide	a2
Glossary	a7

Synchronous Belts

Eliminator Belts	1-7
PowerGrip GT2 Belts (2MR, 3MR).....	8-11
PowerGrip GT2 Belts (5MR)	12-13
PowerGrip GT2 Belts (8M, 14M).....	14-17
PowerGrip HTD Belts.....	18-25
PowerGrip Timing Belts	26-37
Cotton Cleaner Belts.....	38
PowerGrip GT2 Twin Power Belts (3MR, 5MR).....	39-40
PowerGrip GT2 Twin Power Belts (8M, 14M).....	41-42
PowerGrip HTD Twin Power Belts	43-44
PowerGrip Twin Power Timing Belts	45-51
Long Length PowerGrip Belting.....	52-54
Synchro-Power PolyUrethane Belts.....	55-83

Heavy Duty Belts

Super HC Beltx (3V,5V, 8V).....	84
Super HC Molded Notch Belts	85-86
Super HC PowerBand Belts.....	87-89
Super HC Molded Notch PowerBand Belts	90-91
Predator Belts	92-97
Hi-Power II V Belts	98-101
Hi-Power II PowerBand V-Belts	102-106
Tri-Power Molded Notch V-Belts.....	107
Metric Power V-Belts	108-111
Hi-Power II Dubl-V Belts	112-113
PowerBack Belts.....	114
Power Curve Belts	115
Micro-V Belts.....	116-117
Multi-Speed Belts.....	118-122
Nu-T-Link Belting	123
Easy-Splice Belting	124
Power Round Belts	125
Round Endless Belts.....	126-130

Light Duty Belts

Polyflex Belts.....	131-133
Polyflex JB Belts	134-140



**belts
hose**

Copyright 2009 Printed in U.S. of America
National Automotive Parts Association
2999 Circle 75 Parkway
Atlanta, GA 30339

Belts

DESCRIPTION	PAGE
Cotton Cleaner Belts (Special Pitch / Steel Tensile Timing Belts)	38
Easy-Splice V-Belting	124
Eliminator® Belts	1-4
Eliminator Competitive Crossover	5-7
Hi-Power® II Dubl-V Belts (AA, BB, CC, DD)	112-113
Hi-Power II PowerBand V-Belts (A, B, C, D)	102-106
Hi-Power II V-Belts (A, B, C, D, E)	98-101
Long-Length PowerGrip® GT®2 Belting	52
Long-Length PowerGrip HTD® Belting	53
Long-Length PowerGrip Timing Belting	54
Metric Power V-Belts	108-111
Micro-V® Belts (J, L, M)	116-117
Multi-Speed Belts (Variable Speed)	118-122
Nu-T-Link® Belting	123
Polyflex® Belts (3M, 5M, 7M, 11M)	131-133
Polyflex JB Belts (3MJB, 5MJB, 7MJB, 11MJB)	134-140
Power Curve™ Belts	115
Power Round™ Belts	125
PowerBack™ Belts	114
PowerGrip® GT®2 Belts – 2MR and 3MR	8-11
PowerGrip GT2 Belts – 5MR	12-13
PowerGrip GT2 Belts – 8M and 14M	14-17
PowerGrip GT2 Twin Power® Belts 3MR and 5MR	39-40
PowerGrip GT2 Twin Power Belts (8M, 14M)	41-42
PowerGrip HTD Belts (3M, 5M, 20M)	18-25
PowerGrip HTD Twin Power Belts (3M, 5M)	43-44
PowerGrip Timing Belts (MXL, XL, L, H, XH, XXH)	26-37
PowerGrip Twin Power Timing Belts (TPXL, TPL, TPH)	45-51
Predator® PowerBand Belts (CP, 3VP, 5VP, 8VP)	95-97
Predator Single Belts (AP, BP, CP, 5VP, 8VP, SPBP, SPCP)	92-94
Round Endless Belts (1/4", 5/16", 3/8", 7/16", 1/2", 9/16")	126-130
Super HC® Belts (3V, 5V, 8V)	84
Super HC Molded Notch Belts (3VX, 5VX)	85-86
Super HC Molded Notch PowerBand Belts (3VX, 5VX)	90-91
Super HC PowerBand Belts (3V, 5V, 8V)	87-89
Synchro-Power Polyurethane Belts	55-83
Tri-Power® Molded Notch V-Belts (AX, BX)	107



Use this Quick-Select Product Guide to determine the belt drive system that best meets your needs. For product details, follow the associated page number references to go directly to that section.

Gates Lifetime Warranty

Gates stands behind its customers and its products by offering one of the industry's best power transmission product warranties:


Gates power transmission products are guaranteed for the life of each applicable product to be free from defects in materials and workmanship or they will be replaced or repaired free of charge!

Synchronous Belt Quick-Select




PowerGrip® GT®2 Belts – 8M and 14M

Page 14



PowerGrip® GT®2 Twin Power® Belts – 8M and 14M

Page 41




PowerGrip® GT®2 Belts – 2MR and 3MR

Page 8



PowerGrip® GT®2 Belts – 5MR

Page 12




PowerGrip® GT®2 Twin Power® Belts – 3MR and 5MR

Page 39



Long-Length PowerGrip® GT®2 Belting

Page 52



PowerGrip® HTD® Belts

Page 18



PowerGrip® HTD® Twin Power® Belts


Page 43




Long-Length PowerGrip® HTD® Belting

Page 53


Quick-Select Product Guide



Synchronous Belt Quick-Select continued




PowerGrip® Timing Belts
Page 26




PowerGrip® Twin Power® Timing Belts
Page 45



Long-Length PowerGrip® Timing Belts
Page 54



Cotton Cleaner Belts
Page 38




Eliminator® Belts
Page 1
Designed to fit RPP® sprockets




Synchro-Power® Polyurethane Belts
Page 55



V-Belt Quick-Select



Super HC® Belts
Page 84




Super HC® PowerBand® Belts
Page 87




Super HC® Molded Notch Belts
Page 85



Super HC® Molded Notch PowerBand® Belts
Page 90




Predator® PowerBand® Belts
Page 95



Predator® Single Belts
Page 92




Hi-Power® II Belts
Page 98




Hi-Power® II PowerBand® Belts
Page 102



Tri-Power® Belts
Page 107



Hi-Power® II Dubl-V Belts
Page 112



Metric-Power V-Belts
Page 108



Power Curve® Belts
Page 115


Quick-Select Product Guide

V-Belt Quick-Select continued




PowerBack™ Belts

Page 114




Power Round™ Belts

Page 125




Round Endless Belts

Page 126




Micro-V® Belts

Page 116




Polyflex® Belts

Page 131



Polyflex® JB® Belts

Page 134



Multi-Speed Belts

Page 118



Nu-T-Link®

Page 123



Easy-Splice V-Belting

Page 124

Dimensions

Gates reserves the right to make changes in design or dimensions of standard products to improve their quality or to accommodate improved manufacturing techniques. All dimensions in this catalog are for reference only.

Weights

All weights are close approximations and may vary slightly from actual weights.

Aircraft Policy

WARNING! BE SAFE! Do not use Gates belts, pulleys or sprockets on aircraft propeller or rotor drive systems or in-flight accessory drives. Gates products are not designed or intended for aircraft use.

Glossary

Ordering Terminology

PBL — “Private Brand Label” of Gates standard line belts. Available upon customer request. PBL products are made-to-order and may require additional lead times and cost.

Standard/Non-Stock Belt Products — Products do not require minimum production quantities but may require production lead time and items are not returnable. Check with customer service for details.

Stock Belt Products — Products in this catalog are stock unless otherwise noted.

Belt Products Terminology

Aramid Tensile Members — Available in several stock lines and on an MTO basis. Also referred to as Kevlar® or Flexten®.

Arched Top — Construction feature that provides superior strength to prevent distortion of the tensile section.

Banded — Belts with a fabric cover over the belt body. Also referred to as wrapped or covered belts.

Bandless — Belts with no fabric cover. Also referred to as cut edge, raw edge or machined edge.

Bareback — Belts manufactured without rubber material being applied to the outside surface of the banded belt. Also known as low friction, dry cover or clutching cover.

Belt Body — The main part of any belt that generally surrounds, supports and protects the load-carrying tensile cords.

Carbon Tensile Member (U.S. Patent 5,807,194 & 5,112,282) — Currently available in Poly Chain® GT® Carbon™ belts. Gates provides the only belt on the market utilizing carbon fiber tensile in a dynamic application.

Compound — Mixtures of rubber, plastics and other materials that are used to form the body of the belt.

Concave Sides (U.S. Patent 1813698) — Construction that allows the belt to make uniform contact with sheave groove, thus distributing wear uniformly.

Datum Diameter — A system that defines specific sheave and belt dimensions, previously known as the pitch system (diameter or length) for classical belts and sheaves.

Effective Length (E.L.) — A standard length measurement that accounts for varying construction and manufacturing methods in the industry. The length is determined by adding the effective circumference to twice the measured center distance using sheaves and an applied tension specified by the RMA.

Eliminator® Belt — Gates trade name for a high-performance, polyurethane, synchronous belt designed to replace RPP® belts.

Flex Bonded Cord — Strong chemical bond between rubber body and tensile cord. Allows for absorption of bending stress and long service life. Avoids premature failure due to cord separation.

Flex-Weave® Cover — Patented nylon and cotton blended fabric construction that increases flexibility and reduces cover stress providing longer cover life and longer protection of belt core.

Gates Curves — Belts with this feature compensate for effects that occur when a V-belt bends in a sheave. Curved belts feature concave sides, radius relief and arched tops.

Hi-Power® II Belt — Gates trade name for belts commonly referred to as classical, wedge or conventional.

Idler — 1) A non-powered pulley, sheave, sprocket or wheel around which a belt travels. 2) A non-powered roll or rolls supporting a belt.

Metric-Power™ Belt — Gates trade name for molded notch, narrow and classical section V-belts in metric sizes.

Micro-V® Belt — Gates trade name for belts commonly referred to as V-ribbed, multi-rib and Poly-V.

Molded Notch Belts — Often referred to as cogged, notched or cut notch belts. Notches reduce bending stress.

Multi-Speed™ Belts — Gates trade name for products commonly referred to as variable speed, wide range variable speed, adjustable speed and variable pitch.

Oil and Heat Resistance (OHR) — Property of the belt that allows it to withstand the effects of oil, heat, sunlight, ozone, weather and aging.

Outside Circumference (O.C.) — The circumference (total length) measured around the outside of the belt, typically with a tape, while the belt is still on the drive. This measurement can be used to determine the closest belt length when a part number is not available.

Polyflex® Belt — a Gates trademark for a polyurethane V-belt that is often used in high precision drives, such as machine tools and small appliances.

Glossary



Polyflex® JB® Belt — a Gates trademark for two or more joined polyurethane V-belts.

PowerBack™ Belt — Gates trade name for a specialty construction V-belt with a flat back for driving roll-to-roll conveyor applications.

PowerBand® Belt — Gates trade name for two or more belts joined together at the top of the belt. It is also referred to as a joined or banded belt.

Power Curve™ Belt — Gates trade name for a special flexible construction V-belt for curved conveyor applications.

PowerGrip® Belt — Gates trade name for several synchronous product lines including timing, HTD®, GT®2 and Twin Power®.

PowerGrip® HTD®/GT®2 Belts — Gates trade name for a high-torque drive system with a curvilinear tooth profile. These belts are often referred to as Gilmer, timing, positive or synchronous belts. They are sometimes referred to, in error, as cogged or notched belts.

Predator® Belts — Gates trade name for the most aggressive PowerBand® V-belt made for shock loaded applications. Predator belt construction is available in narrow and classical profiles and single belt configuration.

Radius Relief — Construction that minimizes corner wear and works with concave sides to assure proper support of the belt.

Super HC®/Super HC® Molded Notch Belt — Gates trade name for a drive system commonly known as narrow or deep wedge.

Superior Length Stability — Assures V-belts require less re-tensioning and take-up during their service.

Synchronous — Generic term used for power transmission drive systems utilizing toothed belts in mesh with grooved pulleys or sprockets. These systems are also referred to as Gilmer or timing.

Tensile Cord — V-belts typically use special polyester cords, with aramid used in some specialty belts, such as Predator® and PowerRated® belts. Synchronous belts generally have fiberglass cords, except for the carbon fiber used in Poly Chain® GT® Carbon™ belts. Steel is rarely used, except in some special or Made-to-Order synchronous belts.

Tooth Facing — Specially woven and treated nylon fabric that reduces friction of the belt in the sprocket and resists abrasion and other tooth damage.

Tri-Power® Belts — Gates trade name for molded notch classical section or conventional belts.

Truncated Rib — Construction profile that provides improved crack resistance, higher load-carrying capacity and improved flex fatigue resistance.



Twin Power® Belts — Gates trade name for PowerGrip® rubber synchronous belts ideal for serpentine applications. Twin Power belts are specially made to handle the same load capacity on either side of the belt.

V80® — Gates trade name for V-belt matching system that meets RMA tolerances. Any V80® belt will match and perform with any other V80® belt of the same size and type.

The following Super HC®, Hi-Power® II and Tri-Power® belts are V80® belts: Individual V-Belts

B112PC-B500PC
XPZ604-SPZ3550
XPA630-SPA4500
XPB1250-SPB8000
XPC1800-SPC10600
10X530Li-10X1750Li
13X715Li-13X4000Li
17X875Li-17X8636Li

PowerBand® V-Belts

3VX250-3VX1400	A62-A180
3V800-3V1400	B62-B315
5VX500-5VX2000	C68-C420
5V670-5V3550	D144-D660

Power Transmission Metal Terminology

Bushings — A hub system that allows adaptation of sheaves, pulleys and sprockets to varying shaft sizes. Common bushing systems offered by Gates are QD® and Taper-Lock®.

Pulley — A common term that usually refers to sheaves, sprockets or pulleys. The term correctly used applies to metal used for PowerGrip® timing belts.

Sheaves — Metal products with “V” shaped grooves specially designed for various types of V-belts.

Sprockets — Metal products for high-torque synchronous power transmission systems, such as PowerGrip® GT®2 and Poly Chain® GT®2. Sprockets are specifically designed to transmit power with only the corresponding belt product line.



Eliminator® Belts

Gates Eliminator belts eliminate the competition.


It's a high-performance, polyurethane, synchronous belt designed to replace an RPP® belt of the same pitch, width and comparable length (within approximately +/- .5" on center distance maximum).

Markets/Applications

Any industrial applications utilizing RPP belts and sprockets, including Good Year® Blackhawk Pd™, Browning®, RPP Panther®, Carlisle/Dayco® RPP Panther Ultra and TB Wood's® QT Power Chain®.

Features/Advantages

- With durable **polyurethane construction** and robust **aramid tensile**, the Eliminator belt will last a minimum of two times longer than competitive RPP belts.
- The Eliminator **tooth profile** is designed to fit all RPP sprocket grooves, therefore it's not necessary to change sprockets, saving money on transaction costs and reducing downtime.
- **Green nylon tooth facing** reduces friction and provides durable wear surface for long life.



Notes

Eliminator belts are made to order. Minimum order quantities and manufacturing lead times may apply.

Eliminator part numbers are comprised of pitch, pitch length and width. For example; part number 1280-8M-12E denotes a 1280mm pitch length, 8mm pitch, 12mm width, and "E" for Eliminator.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of an Eliminator belt lies within the tensile member.

Product No. Series 9307

8mm Pitch

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Pitch Length (in.)	Belt Width (mm)	Belt Width (in.)	Wt. Ea. (Lbs.)
640-8M-12E	9307-0080	80	640	25.197	12	.472	.36
640-8M-22E	9307-1080	80	640	25.197	22	.866	.42
640-8M-35E	9307-2080	80	640	25.197	35	1.378	.68
640-8M-60E	9307-3080	80	640	25.197	60	2.362	2.19
720-8M-12E	9307-0090	90	720	28.346	12	.472	.37
720-8M-22E	9307-1090	90	720	28.346	22	.866	.44
720-8M-35E	9307-2090	90	720	28.346	35	1.378	.66
720-8M-60E	9307-3090	90	720	28.346	60	2.362	.84
800-8M-12E	9307-0100	100	800	31.496	12	.472	.37
800-8M-22E	9307-1100	100	800	31.496	22	.866	.46
800-8M-35E	9307-2100	100	800	31.496	35	1.378	.68
800-8M-60E	9307-3100	100	800	31.496	60	2.362	.89
896-8M-12E	9307-0112	112	896	35.276	12	.472	.39
896-8M-22E	9307-1112	112	896	35.276	22	.866	.48
896-8M-35E	9307-2112	112	896	35.276	35	1.378	.72
896-8M-60E	9307-3112	112	896	35.276	60	2.362	.95
960-8M-12E	9307-0120	120	960	37.795	12	.472	.89
960-8M-22E	9307-1120	120	960	37.795	22	.866	.99
960-8M-35E	9307-2120	120	960	37.795	35	1.378	1.22
960-8M-60E	9307-3120	120	960	37.795	60	2.362	1.47
1040-8M-12E	9307-0130	130	1040	40.945	12	.472	1.00
1040-8M-22E	9307-1130	130	1040	40.945	22	.866	1.01
1040-8M-35E	9307-2130	130	1040	40.945	35	1.378	1.25
1040-8M-60E	9307-3130	130	1040	40.945	60	2.362	1.52
1120-8M-12E	9307-0140	140	1120	44.094	12	.472	.91
1120-8M-22E	9307-1140	140	1120	44.094	22	.866	1.03
1120-8M-35E	9307-2140	140	1120	44.094	35	1.378	1.28
1120-8M-60E	9307-3140	140	1120	44.094	60	2.362	1.56



Eliminator® Belts

Product No. Series 9307 (continued)

8mm Pitch (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Pitch Length (In.)	Belt Width (mm)	Belt Width (In.)	Wt. Ea. (Lbs.)
1200-8M-12E	9307-0150	150	1200	47.244	12	.472	.92
1200-8M-22E	9307-1150	150	1200	47.244	22	.866	1.05
1200-8M-35E	9307-2150	150	1200	47.244	35	1.378	1.31
1200-8M-60E	9307-3150	150	1200	47.244	60	2.362	1.61
1224-8M-12E	9307-0153	153	1224	48.189	12	.472	.93
1224-8M-22E	9307-1153	153	1224	48.189	22	.866	1.05
1224-8M-35E	9307-2153	153	1224	48.189	35	1.378	1.32
1224-8M-60E	9307-3153	153	1224	48.189	60	2.362	1.63
1280-8M-12E	9307-0160	160	1280	50.394	12	.472	.93
1280-8M-22E	9307-1160	160	1280	50.394	22	.866	1.06
1280-8M-35E	9307-2160	160	1280	50.394	35	1.378	1.34
1280-8M-60E	9307-3160	160	1280	50.394	60	2.362	1.70
1440-8M-12E	9307-0180	180	1440	56.693	12	.472	.95
1440-8M-22E	9307-1180	180	1440	56.693	22	.866	1.10
1440-8M-35E	9307-2180	180	1440	56.693	35	1.378	1.39
1440-8M-60E	9307-3180	180	1440	56.693	60	2.362	1.76
1600-8M-12E	9307-0200	200	1600	62.992	12	.472	.97
1600-8M-22E	9307-1200	200	1600	62.992	22	.866	1.14
1600-8M-35E	9307-2200	200	1600	62.992	35	1.378	1.45
1600-8M-60E	9307-3200	200	1600	62.992	60	2.362	1.86
1760-8M-12E	9307-0220	220	1760	69.291	12	.472	.99
1760-8M-22E	9307-1220	220	1760	69.291	22	.866	1.17
1760-8M-35E	9307-2220	220	1760	69.291	35	1.378	1.51
1760-8M-60E	9307-3220	220	1760	69.291	60	2.362	1.95
1792-8M-12E	9307-0224	224	1792	70.551	12	.472	1.00
1792-8M-22E	9307-1224	224	1792	70.551	22	.866	1.18
1792-8M-35E	9307-2224	224	1792	70.551	35	1.378	1.52
1792-8M-60E	9307-3224	224	1792	70.551	60	2.362	1.97
2000-8M-12E	9307-0250	250	2000	78.740	12	.472	1.02
2000-8M-22E	9307-1250	250	2000	78.740	22	.866	1.22
2000-8M-35E	9307-2250	250	2000	78.740	35	1.378	1.59
2000-8M-60E	9307-3250	250	2000	78.740	60	2.362	2.10
2200-8M-12E	9307-0275	275	2200	86.614	12	.472	1.02
2200-8M-22E	9307-1275	275	2200	86.614	22	.866	.52
2200-8M-35E	9307-2275	275	2200	86.614	35	1.378	1.66
2200-8M-60E	9307-3275	275	2200	86.614	60	2.362	2.22
2400-8M-12E	9307-0300	300	2400	94.488	12	.472	1.07
2400-8M-22E	9307-1300	300	2400	94.488	22	.866	1.31
2400-8M-35E	9307-2300	300	2400	94.488	35	1.378	1.74
2400-8M-60E	9307-3300	300	2400	94.488	60	2.362	2.35
2600-8M-12E	9307-0325	325	2600	102.362	12	.472	1.09
2600-8M-22E	9307-1325	325	2600	102.362	22	.866	1.36
2600-8M-35E	9307-2325	325	2600	102.362	35	1.378	1.81
2600-8M-60E	9307-3325	325	2600	102.362	60	2.362	2.47
2800-8M-12E	9307-0350	350	2800	110.236	12	.472	1.12
2800-8M-22E	9307-1350	350	2800	110.236	22	.866	1.40
2800-8M-35E	9307-2350	350	2800	110.236	35	1.378	1.88
2800-8M-60E	9307-3350	350	2800	110.236	60	2.362	2.59
3048-8M-12E	9307-0381	381	3048	120.000	12	.472	1.15
3048-8M-22E	9307-1381	381	3048	120.000	22	.866	2.44
3048-8M-35E	9307-2381	381	3048	120.000	35	1.378	1.97
3048-8M-60E	9307-3381	381	3048	120.000	60	2.362	2.74
3280-8M-12E	9307-0410	410	3280	129.134	12	.472	2.16
3280-8M-22E	9307-1410	410	3280	129.134	22	.866	2.49
3280-8M-35E	9307-2410	410	3280	129.134	35	1.378	2.05
3280-8M-60E	9307-3410	410	3280	129.134	60	2.362	2.88
3600-8M-12E	9307-0450	450	3600	141.732	12	.472	2.20
3600-8M-22E	9307-1450	450	3600	141.732	22	.866	2.56
3600-8M-35E	9307-2450	450	3600	141.732	35	1.378	2.93
3600-8M-60E	9307-3450	450	3600	141.732	60	2.362	3.85



Product No. Series 9307 (continued)

8mm Pitch (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Pitch Length (In.)	Belt Width (mm)	Belt Width (In.)	Wt. Ea. (Lbs.)
4400-8M-12E	9307-0550	550	4400	173.228	12	.472	2.29
4400-8M-22E	9307-1550	550	4400	173.228	22	.866	2.74
4400-8M-35E	9307-2550	550	4400	173.228	35	1.378	3.22
4400-8M-60E	9307-3550	550	4400	173.228	60	2.362	4.34

14mm Pitch

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Pitch Length (In.)	Belt Width (mm)	Belt Width (In.)	Wt. Ea. (Lbs.)
994-14M-20E	9307-4071	71	994	39.130	20	.787	1.12
994-14M-42E	9307-5071	71	994	39.130	42	1.654	1.50
994-14M-65E	9307-6071	71	994	39.130	65	2.559	2.00
994-14M-90E	9307-7071	71	994	39.130	90	3.543	2.66
994-14M-120E	9307-8071	71	994	39.130	120	4.724	2.66
1190-14M-20E	9307-4085	85	1190	46.850	20	.787	1.19
1190-14M-42E	9307-5085	85	1190	46.850	42	1.654	1.74
1190-14M-65E	9307-6085	85	1190	46.850	65	2.559	2.21
1190-14M-90E	9307-7085	85	1190	46.850	90	3.543	2.97
1190-14M-120E	9307-8085	85	1190	46.850	120	4.724	3.58
1400-14M-20E	9307-4100	100	1400	55.118	20	.787	1.26
1400-14M-42E	9307-5100	100	1400	55.118	42	1.654	1.27
1400-14M-65E	9307-6100	100	1400	55.118	65	2.559	1.52
1400-14M-90E	9307-7100	100	1400	55.118	90	3.543	2.11
1400-14M-120E	9307-8100	100	1400	55.118	120	4.724	2.82
1610-14M-20E	9307-4115	115	1610	63.386	20	.787	2.31
1610-14M-42E	9307-5115	115	1610	63.386	42	1.654	2.82
1610-14M-65E	9307-6115	115	1610	63.386	65	2.559	2.64
1610-14M-90E	9307-7115	115	1610	63.386	90	3.543	4.44
1610-14M-120E	9307-8115	115	1610	63.386	120	4.724	5.27
1750-14M-20E	9307-4125	125	1750	68.898	20	.787	2.36
1750-14M-42E	9307-5125	125	1750	68.898	42	1.654	2.92
1750-14M-65E	9307-6125	125	1750	68.898	65	2.559	3.90
1750-14M-90E	9307-7125	125	1750	68.898	90	3.543	4.66
1750-14M-120E	9307-8125	125	1750	68.898	120	4.724	5.56
1890-14M-20E	9307-4135	135	1890	74.409	20	.787	2.41
1890-14M-42E	9307-5135	135	1890	74.409	42	1.654	3.02
1890-14M-65E	9307-6135	135	1890	74.409	65	2.559	4.06
1890-14M-90E	9307-7135	135	1890	74.409	90	3.543	4.88
1890-14M-120E	9307-8135	135	1890	74.409	120	4.724	5.85
2100-14M-20E	9307-4150	150	2100	82.677	20	.787	2.48
2100-14M-42E	9307-5150	150	2100	82.677	42	1.654	3.17
2100-14M-65E	9307-6150	150	2100	82.677	65	2.559	4.30
2100-14M-90E	9307-7150	150	2100	82.677	90	3.543	5.20
2100-14M-120E	9307-8150	150	2100	82.677	120	4.724	6.29
2310-14M-20E	9307-4165	165	2310	90.945	20	.787	2.55
2310-14M-42E	9307-5165	165	2310	90.945	42	1.654	3.33
2310-14M-65E	9307-6165	165	2310	90.945	65	2.559	4.53
2310-14M-90E	9307-7165	165	2310	90.945	90	3.543	5.53
2310-14M-120E	9307-8165	165	2310	90.945	120	4.724	6.72
2450-14M-20E	9307-4175	175	2450	96.457	20	.787	2.60
2450-14M-42E	9307-5175	175	2450	96.457	42	1.654	3.43
2450-14M-65E	9307-6175	175	2450	96.457	65	2.559	4.69
2450-14M-90E	9307-7175	175	2450	96.457	90	3.543	5.74
2450-14M-120E	9307-8175	175	2450	96.457	120	4.724	7.22
2590-14M-20E	9307-4185	185	2590	101.968	20	.787	2.65
2590-14M-42E	9307-5185	185	2590	101.968	42	1.654	3.53
2590-14M-65E	9307-6185	185	2590	101.968	65	2.559	4.85
2590-14M-90E	9307-7185	185	2590	101.968	90	3.543	5.96
2590-14M-120E	9307-8185	185	2590	101.968	120	4.724	7.30



Eliminator® Belts

Product No. Series 9307 (continued)

14mm Pitch (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Pitch Length (In.)	Belt Width (mm)	Belt Width (In.)	Wt. Ea. (Lbs.)
2800-14M-20E	9307-4200	200	2800	110.236	20	.787	2.72
2800-14M-42E	9307-5200	200	2800	110.236	42	1.654	3.68
2800-14M-65E	9307-6200	200	2800	110.236	65	2.559	5.08
2800-14M-90E	9307-7200	200	2800	110.236	90	3.543	6.29
2800-14M-120E	9307-8200	200	2800	110.236	120	4.724	7.73
3136-14M-20E	9307-4224	224	3136	123.465	20	.787	2.84
3136-14M-42E	9307-5224	224	3136	123.465	42	1.654	3.92
3136-14M-65E	9307-6224	224	3136	123.465	65	2.559	5.46
3136-14M-90E	9307-7224	224	3136	123.465	90	3.543	6.81
3136-14M-120E	9307-8224	224	3136	123.465	120	4.724	8.34
3360-14M-20E	9307-4240	240	3360	132.283	20	.787	2.91
3360-14M-42E	9307-5240	240	3360	132.283	42	1.654	4.09
3360-14M-65E	9307-6240	240	3360	132.283	65	2.559	5.71
3360-14M-90E	9307-7240	240	3360	132.283	90	3.543	7.16
3360-14M-120E	9307-8240	240	3360	132.283	120	4.724	8.89
3500-14M-20E	9307-4250	250	3500	137.795	20	.787	2.96
3500-14M-42E	9307-5250	250	3500	137.795	42	1.654	4.19
3500-14M-65E	9307-6250	250	3500	137.795	65	2.559	5.86
3500-14M-90E	9307-7250	250	3500	137.795	90	3.543	7.37
3500-14M-120E	9307-8250	250	3500	137.795	120	4.724	9.18
3850-14M-20E	9307-4275	275	3850	151.575	20	.787	3.08
3850-14M-42E	9307-5275	275	3850	151.575	42	1.654	4.44
3850-14M-65E	9307-6275	275	3850	151.575	65	2.559	6.26
3850-14M-90E	9307-7275	275	3850	151.575	90	3.543	7.92
3850-14M-120E	9307-8275	275	3850	151.575	120	4.724	9.91
4326-14M-20E	9307-4309	309	4326	170.315	20	.787	3.25
4326-14M-42E	9307-5309	309	4326	170.315	42	1.654	4.78
4326-14M-65E	9307-6309	309	4326	170.315	65	2.559	6.79
4326-14M-90E	9307-7309	309	4326	170.315	90	3.543	10.89
4326-14M-120E	9307-8309	309	4326	170.315	120	4.724	8.65



Eliminator® Competitive Crossover

Goodyear® BlackHawk Pd®	Carlisle/Dayco® Panther® Ultra	T.B. Woods® QT Power Chain®	Browning® RPP® Panther®	Gates Eliminator
480 8M BH 12	480PTH8M-12	480 8M 12W	480PTH8M-12	—
480 8M BH 22	480PTH8M-22	480 8M 22W	480PTH8M-22	—
480 8M BH 35	480PTH8M-35	480 8M 35W	480PTH8M-35	—
480 8M BH 60	480PTH8M-60	480 8M 60W	480PTH8M-60	—
560 8M BH 12	560PTH8M-12	560 8M 12W	560PTH8M-12	—
560 8M BH 22	560PTH8M-22	560 8M 22W	560PTH8M-22	—
560 8M BH 35	560PTH8M-35	560 8M 35W	560PTH8M-35	—
560 8M BH 60	560PTH8M-60	560 8M 60W	560PTH8M-60	—
600 8M BH 12	600PTH8M-12	600 8M 12W	600PTH8M-12	—
600 8M BH 22	600PTH8M-22	600 8M 22W	600PTH8M-22	—
600 8M BH 35	600PTH8M-35	600 8M 35W	600PTH8M-35	—
600 8M BH 60	600PTH8M-60	600 8M 60W	600PTH8M-60	—
640 8M BH 12	640PTH8M-12	640 8M 12W	640PTH8M-12	640-8M-12E
640 8M BH 22	640PTH8M-22	640 8M 22W	640PTH8M-22	640-8M-22E
640 8M BH 35	640PTH8M-35	640 8M 35W	640PTH8M-35	640-8M-35E
640 8M BH 60	640PTH8M-60	640 8M 60W	640PTH8M-60	640-8M-60E
720 8M BH 12	720PTH8M-12	720 8M 12W	720PTH8M-12	720-8M-12E
720 8M BH 22	720PTH8M-22	720 8M 22W	720PTH8M-22	720-8M-22E
720 8M BH 35	720PTH8M-35	720 8M 35W	720PTH8M-35	720-8M-35E
720 8M BH 60	720PTH8M-60	720 8M 60W	720PTH8M-60	720-8M-60E
800 8M BH 12	800PTH8M-12	800 8M 12W	800PTH8M-12	800-8M-12E
800 8M BH 22	800PTH8M-22	800 8M 22W	800PTH8M-22	800-8M-22E
800 8M BH 35	800PTH8M-35	800 8M 35W	800PTH8M-35	800-8M-35E
800 8M BH 60	800PTH8M-60	800 8M 60W	800PTH8M-60	800-8M-60E
880 8M BH 12	880PTH8M-12	880 8M 12W	880PTH8M-12	896-8M-12E
880 8M BH 22	880PTH8M-22	880 8M 22W	880PTH8M-22	896-8M-22E
880 8M BH 35	880PTH8M-35	880 8M 35W	880PTH8M-35	896-8M-35E
880 8M BH 60	880PTH8M-60	880 8M 60W	880PTH8M-60	896-8M-60E
960 8M BH 12	960PTH8M-12	960 8M 12W	960PTH8M-12	960-8M-12E
960 8M BH 22	960PTH8M-22	960 8M 22W	960PTH8M-22	960-8M-22E
960 8M BH 35	960PTH8M-35	960 8M 35W	960PTH8M-35	960-8M-35E
960 8M BH 60	960PTH8M-60	960 8M 60W	960PTH8M-60	960-8M-60E
1040 8M BH 12	1040PTH8M-12	1040 8M 12W	1040PTH8M-12	1040-8M-12E
1040 8M BH 22	1040PTH8M-22	1040 8M 22W	1040PTH8M-22	1040-8M-22E
1040 8M BH 35	1040PTH8M-35	1040 8M 35W	1040PTH8M-35	1040-8M-35E
1040 8M BH 60	1040PTH8M-60	1040 8M 60W	1040PTH8M-60	1040-8M-60E
1120 8M BH 12	1120PTH8M-12	1120 8M 12W	1120PTH8M-12	1120-8M-12E
1120 8M BH 22	1120PTH8M-22	1120 8M 22W	1120PTH8M-22	1120-8M-22E
1120 8M BH 35	1120PTH8M-35	1120 8M 35W	1120PTH8M-35	1120-8M-35E
1120 8M BH 60	1120PTH8M-60	1120 8M 60W	1120PTH8M-60	1120-8M-60E
1200 8M BH 12	1200PTH8M-12	1200 8M 12W	1200PTH8M-12	1200-8M-12E
1200 8M BH 22	1200PTH8M-22	1200 8M 22W	1200PTH8M-22	1200-8M-22E
1200 8M BH 35	1200PTH8M-35	1200 8M 35W	1200PTH8M-35	1200-8M-35E
1200 8M BH 60	1200PTH8M-60	1200 8M 60W	1200PTH8M-60	1200-8M-60E
—	1224PTH8M-12	—	1224PTH8M-12	1224-8M-12E
—	1224PTH8M-22	—	1224PTH8M-22	1224-8M-22E
—	1224PTH8M-35	—	1224PTH8M-35	1224-8M-35E
—	1224PTH8M-60	—	1224PTH8M-60	1224-8M-60E
1280 8M BH 12	1280PTH8M-12	1280 8M 12W	1280PTH8M-12	1280-8M-12E
1280 8M BH 22	1280PTH8M-22	1280 8M 22W	1280PTH8M-22	1280-8M-22E
1280 8M BH 35	1280PTH8M-35	1280 8M 35W	1280PTH8M-35	1280-8M-35E
1280 8M BH 60	1280PTH8M-60	1280 8M 60W	1280PTH8M-60	1280-8M-60E
1440 8M BH 12	1440PTH8M-12	1440 8M 12W	1440PTH8M-12	1440-8M-12E
1440 8M BH 22	1440PTH8M-22	1440 8M 22W	1440PTH8M-22	1440-8M-22E
1440 8M BH 35	1440PTH8M-35	1440 8M 35W	1440PTH8M-35	1440-8M-35E
1440 8M BH 60	1440PTH8M-60	1440 8M 60W	1440PTH8M-60	1440-8M-62E
1600 8M BH 12	1600PTH8M-12	1600 8M 12W	1600PTH8M-12	1600-8M-12E
1600 8M BH 22	1600PTH8M-22	1600 8M 22W	1600PTH8M-22	1600-8M-22E
1600 8M BH 35	1600PTH8M-35	1600 8M 35W	1600PTH8M-35	1600-8M-35E
1600 8M BH 60	1600PTH8M-60	1600 8M 60W	1600PTH8M-60	1600-8M-60E
1760 8M BH 12	1760PTH8M-12	1760 8M 12W	1760PTH8M-12	1760-8M-12E
1760 8M BH 22	1760PTH8M-22	1760 8M 22W	1760PTH8M-22	1760-8M-22E
1760 8M BH 35	1760PTH8M-35	1760 8M 35W	1760PTH8M-35	1760-8M-35E
1760 8M BH 60	1760PTH8M-60	1760 8M 60W	1760PTH8M-60	1760-8M-60E



Eliminator® Competitive Crossover

Goodyear® BlackHawk Pd®	Carlisle/Dayco® Panther® Ultra	T.B. Woods® QT Power Chain®	Browning® RPP® Panther®	Gates Eliminator
1800 8M BH 12	1800PTH8M-12	1800 8M 12W	1800PTH8M-12	1792-8M-12E
1800 8M BH 22	1800PTH8M-22	1800 8M 22W	1800PTH8M-22	1792-8M-22E
1800 8M BH 35	1800PTH8M-35	1800 8M 35W	1800PTH8M-35	1792-8M-35E
1800 8M BH 60	1800PTH8M-60	1800 8M 60W	1800PTH8M-60	1792-8M-60E
2000 8M BH 12	2000PTH8M-12	2000 8M 12W	2000PTH8M-12	2000-8M-12E
2000 8M BH 22	2000PTH8M-22	2000 8M 22W	2000PTH8M-22	2000-8M-22E
2000 8M BH 35	2000PTH8M-35	2000 8M 35W	2000PTH8M-35	2000-8M-35E
2000 8M BH 60	2000PTH8M-60	2000 8M 60W	2000PTH8M-60	2000-8M-60E
—	2200PTH8M-12	2200 8M 12W	2200PTH8M-12	2200-8M-12E
—	2200PTH8M-22	2200 8M 22W	2200PTH8M-22	2200-8M-22E
—	2200PTH8M-35	2200 8M 35W	2200PTH8M-35	2200-8M-35E
—	2200PTH8M-60	2200 8M 60W	2200PTH8M-60	2200-8M-60E
2400 8M BH 12	2400PTH8M-12	2400 8M 12W	2400PTH8M-12	2400-8M-12E
2400 8M BH 22	2400PTH8M-22	2400 8M 22W	2400PTH8M-22	2400-8M-22E
2400 8M BH 35	2400PTH8M-35	2400 8M 35W	2400PTH8M-35	2400-8M-35E
2400 8M BH 60	2400PTH8M-60	2400 8M 60W	2400PTH8M-60	2400-8M-60E
2600 8M BH 12	2600PTH8M-12	2600 8M 12W	2600PTH8M-12	2600-8M-12E
2600 8M BH 22	2600PTH8M-22	2600 8M 22W	2600PTH8M-22	2600-8M-22E
2600 8M BH 35	2600PTH8M-35	2600 8M 35W	2600PTH8M-35	2600-8M-35E
2600 8M BH 60	2600PTH8M-60	2600 8M 60W	2600PTH8M-60	2600-8M-60E
2800 8M BH 12	2800PTH8M-12	2800 8M 12W	2800PTH8M-12	2800-8M-12E
2800 8M BH 22	2800PTH8M-22	2800 8M 22W	2800PTH8M-22	2800-8M-22E
2800 8M BH 35	2800PTH8M-35	2800 8M 35W	2800PTH8M-35	2800-8M-35E
2800 8M BH 60	2800PTH8M-60	2800 8M 60W	2800PTH8M-60	2800-8M-60E
3048 8M BH 12	3048PTH8M-12	3048 8M 12W	3048PTH8M-12	3048-8M-12E
3048 8M BH 22	3048PTH8M-22	3048 8M 22W	3048PTH8M-22	3048-8M-22E
3048 8M BH 35	3048PTH8M-35	3048 8M 35W	3048PTH8M-35	3048-8M-35E
3048 8M BH 60	3048PTH8M-60	3048 8M 60W	3048PTH8M-60	3048-8M-60E
3280 8M BH 12	3280PTH8M-12	3280 8M 12W	3280PTH8M-12	3280-8M-12E
3280 8M BH 22	3280PTH8M-22	3280 8M 22W	3280PTH8M-22	3280-8M-22E
3280 8M BH 35	3280PTH8M-35	3280 8M 35W	3280PTH8M-35	3280-8M-35E
3280 8M BH 60	3280PTH8M-60	3280 8M 60W	3280PTH8M-60	3280-8M-60E
3600 8M BH 12	3600PTH8M-12	3600 8M 12W	3600PTH8M-12	3600-8M-12E
3600 8M BH 22	3600PTH8M-22	3600 8M 22W	3600PTH8M-22	3600-8M-22E
3600 8M BH 35	3600PTH8M-35	3600 8M 35W	3600PTH8M-35	3600-8M-35E
3600 8M BH 60	3600PTH8M-60	3600 8M 60W	3600PTH8M-60	3600-8M-60E
4400 8M BH 12	4400PTH8M-12	4400 8M 12W	4400PTH8M-12	4400-8M-12E
4400 8M BH 22	4400PTH8M-22	4400 8M 22W	4400PTH8M-22	4400-8M-22E
4400 8M BH 35	4400PTH8M-35	4400 8M 35W	4400PTH8M-35	4400-8M-35E
4400 8M BH 60	4400PTH8M-60	4400 8M 60W	4400PTH8M-60	4400-8M-60E
966 14M BH 20	966PTH14M-20	966 14M 20W	966PTH14M-20	994-14M-20E
966 14M BH 42	966PTH14M-42	966 14M 42W	966PTH14M-42	994-14M-42E
966 14M BH 65	966PTH14M-65	966 14M 65W	966PTH14M-65	994-14M-65E
966 14M BH 90	966PTH14M-90	966 14M 90W	966PTH14M-90	994-14M-90E
966 14M BH 120	966PTH14M-120	966 14M 120W	966PTH14M-120	994-14M-120E
1190 14M BH 20	1190PTH14M-20	1190 14M 20W	1190PTH14M-20	1190-14M-20E
1190 14M BH 42	1190PTH14M-42	1190 14M 42W	1190PTH14M-42	1190-14M-42E
1190 14M BH 65	1190PTH14M-65	1190 14M 65W	1190PTH14M-65	1190-14M-65E
1190 14M BH 90	1190PTH14M-90	1190 14M 90W	1190PTH14M-90	1190-14M-90E
1190 14M BH 120	1190PTH14M-120	1190 14M 120W	1190PTH14M-120	1190-14M-120E
1400 14M BH 20	1400PTH14M-20	1400 14M 20W	1400PTH14M-20	1400-14M-20E
1400 14M BH 42	1400PTH14M-42	1400 14M 42W	1400PTH14M-42	1400-14M-42E
1400 14M BH 65	1400PTH14M-65	1400 14M 65W	1400PTH14M-65	1400-14M-65E
1400 14M BH 90	1400PTH14M-90	1400 14M 90W	1400PTH14M-90	1400-14M-90E
1400 14M BH 120	1400PTH14M-120	1400 14M 120W	1400PTH14M-120	1400-14M-120E
1610 14M BH 20	1610PTH14M-20	1610 14M 20W	1610PTH14M-20	1610-14M-20E
1610 14M BH 42	1610PTH14M-42	1610 14M 42W	1610PTH14M-42	1610-14M-42E
1610 14M BH 65	1610PTH14M-65	1610 14M 65W	1610PTH14M-65	1610-14M-65E
1610 14M BH 90	1610PTH14M-90	1610 14M 90W	1610PTH14M-90	1610-14M-90E
1610 14M BH 120	1610PTH14M-120	1610 14M 120W	1610PTH14M-120	1610-14M-120E
1778 14M BH 20	1778PTH14M-20	1778 14M 20W	1778PTH14M-20	1750-14M-20E
1778 14M BH 42	1778PTH14M-42	1778 14M 42W	1778PTH14M-42	1750-14M-42E
1778 14M BH 65	1778PTH14M-65	1778 14M 65W	1778PTH14M-65	1750-14M-65E
1778 14M BH 90	1778PTH14M-90	1778 14M 90W	1778PTH14M-90	1750-14M-90E
1778 14M BH 120	1778PTH14M-120	1778 14M 120W	1778PTH14M-120	1750-14M-120E



Eliminator® Competitive Crossover

Goodyear® BlackHawk Pd®	Carlisle/Dayco® Panther® Ultra	T.B. Woods® QT Power Chain®	Browning® RPP® Panther®	Gates Eliminator
1890 14M BH 20	1890PTH14M-20	1890 14M 20W	1890PTH14M-20	1890-14M-20E
1890 14M BH 42	1890PTH14M-42	1890 14M 42W	1890PTH14M-42	1890-14M-42E
1890 14M BH 65	1890PTH14M-65	1890 14M 65W	1890PTH14M-65	1890-14M-65E
1890 14M BH 90	1890PTH14M-90	1890 14M 90W	1890PTH14M-90	1890-14M-90E
1890 14M BH 120	1890PTH14M-120	1890 14M 120W	1890PTH14M-120	1890-14M-120E
2100 14M BH 20	2100PTH14M-20	2100 14M 20W	2100PTH14M-20	2100-14M-20E
2100 14M BH 42	2100PTH14M-42	2100 14M 42W	2100PTH14M-42	2100-14M-42E
2100 14M BH 65	2100PTH14M-65	2100 14M 65W	2100PTH14M-65	2100-14M-65E
2100 14M BH 90	2100PTH14M-90	2100 14M 90W	2100PTH14M-90	2100-14M-90E
2100 14M BH 120	2100PTH14M-120	2100 14M 120W	2100PTH14M-120	2100-14M-120E
2310 14M BH 20	2310PTH14M-20	2310 14M 20W	2310PTH14M-20	2310-14M-20E
2310 14M BH 42	2310PTH14M-42	2310 14M 42W	2310PTH14M-42	2310-14M-42E
2310 14M BH 65	2310PTH14M-65	2310 14M 65W	2310PTH14M-65	2310-14M-65E
2310 14M BH 90	2310PTH14M-90	2310 14M 90W	2310PTH14M-90	2310-14M-90E
2310 14M BH 120	2310PTH14M-120	2310 14M 120W	2310PTH14M-120	2310-14M-120E
2450 14M BH 20	2450PTH14M-20	2450 14M 20W	2450PTH14M-20	2450-14M-20E
2450 14M BH 42	2450PTH14M-42	2450 14M 42W	2450PTH14M-42	2450-14M-42E
2450 14M BH 65	2450PTH14M-65	2450 14M 65W	2450PTH14M-65	2450-14M-65E
2450 14M BH 90	2450PTH14M-90	2450 14M 90W	2450PTH14M-90	2450-14M-90E
2450 14M BH 120	2450PTH14M-120	2450 14M 120W	2450PTH14M-120	2450-14M-120E
2590 14M BH 20	2590PTH14M-20	2590 14M 20W	2590PTH14M-20	2590-14M-20E
2590 14M BH 42	2590PTH14M-42	2590 14M 42W	2590PTH14M-42	2590-14M-42E
2590 14M BH 65	2590PTH14M-65	2590 14M 65W	2590PTH14M-65	2590-14M-65E
2590 14M BH 90	2590PTH14M-90	2590 14M 90W	2590PTH14M-90	2590-14M-90E
2590 14M BH 120	2590PTH14M-120	2590 14M 120W	2590PTH14M-120	2590-14M-120E
2800 14M BH 20	2800PTH14M-20	2800 14M 20W	2800PTH14M-20	2800-14M-20E
2800 14M BH 42	2800PTH14M-42	2800 14M 42W	2800PTH14M-42	2800-14M-42E
2800 14M BH 65	2800PTH14M-65	2800 14M 65W	2800PTH14M-65	2800-14M-65E
2800 14M BH 90	2800PTH14M-90	2800 14M 90W	2800PTH14M-90	2800-14M-90E
2800 14M BH 120	2800PTH14M-120	2800 14M 120W	2800PTH14M-120	2800-14M-125E
3150 14M BH 20	3150PTH14M-20	3150 14M 20W	3150PTH14M-20	3136-14M-20E
3150 14M BH 42	3150PTH14M-42	3150 14M 42W	3150PTH14M-42	3136-14M-42E
3150 14M BH 65	3150PTH14M-65	3150 14M 65W	3150PTH14M-65	3136-14M-65E
3150 14M BH 90	3150PTH14M-90	3150 14M 90W	3150PTH14M-90	3136-14M-90E
3150 14M BH 120	3150PTH14M-120	3150 14M 120W	3150PTH14M-120	3136-14M-120E
3360 14M BH 20	3360PTH14M-20	3360 14M 20W	3360PTH14M-20	3360-14M-20E
3360 14M BH 42	3360PTH14M-42	3360 14M 42W	3360PTH14M-42	3360-14M-42E
3360 14M BH 65	3360PTH14M-65	3360 14M 65W	3360PTH14M-65	3360-14M-65E
3360 14M BH 90	3360PTH14M-90	3360 14M 90W	3360PTH14M-90	3360-14M-90E
3360 14M BH 120	3360PTH14M-120	3360 14M 120W	3360PTH14M-120	3360-14M-120E
3500 14M BH 20	3500PTH14M-20	3500 14M 20W	3500PTH14M-20	3500-14M-20E
3500 14M BH 42	3500PTH14M-42	3500 14M 42W	3500PTH14M-42	3500-14M-42E
3500 14M BH 65	3500PTH14M-65	3500 14M 65W	3500PTH14M-65	3500-14M-65E
3500 14M BH 90	3500PTH14M-90	3500 14M 90W	3500PTH14M-90	3500-14M-90E
3500 14M BH 120	3500PTH14M-120	3500 14M 120W	3500PTH14M-120	3500-14M-120E
3850 14M BH 20	3850PTH14M-20	3850 14M 20W	3850PTH14M-20	3850-14M-20E
3850 14M BH 42	3850PTH14M-42	3850 14M 42W	3850PTH14M-42	3850-14M-42E
3850 14M BH 65	3850PTH14M-65	3850 14M 65W	3850PTH14M-65	3850-14M-65E
3850 14M BH 90	3850PTH14M-90	3850 14M 90W	3850PTH14M-90	3850-14M-90E
3850 14M BH 120	3850PTH14M-120	3850 14M 120W	3850PTH14M-120	3850-14M-120E
4326 14M BH 20	4326PTH14M-20	4326 14M 20W	4326PTH14M-20	4326-14M-20E
4326 14M BH 42	4326PTH14M-42	4326 14M 42W	4326PTH14M-42	4326-14M-42E
4326 14M BH 65	4326PTH14M-65	4326 14M 65W	4326PTH14M-65	4326-14M-65E
4326 14M BH 90	4326PTH14M-90	4326 14M 90W	4326PTH14M-90	4326-14M-90E
4326 14M BH 120	4326PTH14M-120	4326 14M 120W	4326PTH14M-120	4326-14M-120E
4578 14M BH 20	4578PTH14M-20	4578 14M 20W	4578PTH14M-20	—
4578 14M BH 42	4578PTH14M-42	4578 14M 42W	4578PTH14M-42	—
4578 14M BH 65	4578PTH14M-65	4578 14M 65W	4578PTH14M-65	—
4578 14M BH 90	4578PTH14M-90	4578 14M 90W	4578PTH14M-90	—
4578 14M BH 120	4578PTH14M-120	4578 14M 120W	4578PTH14M-120	—
4956 14M BH 20	4956PTH14M-20	4956 14M 20W	4956PTH14M-20	—
4956 14M BH 42	4956PTH14M-42	4956 14M 42W	4956PTH14M-42	—
4956 14M BH 65	4956PTH14M-65	4956 14M 65W	4956PTH14M-65	—
4956 14M BH 90	4956PTH14M-90	4956 14M 90W	4956PTH14M-90	—
4956 14M BH 120	4956PTH14M-120	4956 14M 120W	4956PTH14M-120	—



PowerGrip® GT®2 Belts - 2MR and 3MR


The PowerGrip GT2 belt has twice the load carrying capacity of its predecessor HTD®. In addition, less width is required compared to HTD, allowing lighter, more compact drives.

Markets/Applications

PowerGrip GT2 belts are suitable for many applications including data storage, machine tool, hand power tools, postage handling, DC Stepper/Servo, food processors, office machines, centrifuges, money handling, medical diagnostic, sewing machines, ticket dispensers, robotics, vending machines and vacuum cleaners.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Gates **patented tooth profile** is designed for use with a specific sprocket groove-belt tooth combination increases capacity, while improving registration.
- PowerGrip GT2 greatly exceeds HTD in tooth ratchet resistance.
- Eliminates lubrication and re-tensioning reduce maintenance and labor as compared to roller chain drives.
- PowerGrip GT2 belt/sprocket combinations match or exceed the positional accuracy of PowerGrip Timing belt/pulley systems.



Recommended Sprockets

PowerGrip GT2 Sprockets

Notes

PowerGrip GT2 part numbers are comprised of pitch, pitch length and width. For example; part number 2MR-100-04 denotes a 2mm pitch, 100mm pitch length and 4mm width.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of a PowerGrip GT2 belt lies within the tensile member.

Product No. Series 9390

2MR Pitch — 4mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-100-04	9390-0050	50	3.94	.01
2MR-112-04	9390-0056	56	4.41	.01
2MR-124-04	9390-0062	62	4.88	.01
2MR-126-04	9390-0063	63	4.96	.01
2MR-134-04	9390-0067	67	5.28	.01
2MR-136-04	9390-0068	68	5.35	.01
2MR-140-04	9390-0070	70	5.51	.05
2MR-152-04	9390-0076	76	5.98	.01
2MR-158-04	9390-0079	79	6.22	.01
2MR-160-04	9390-0080	80	6.30	.01
2MR-164-04	9390-0082	82	6.46	.01
2MR-166-04	9390-0083	83	6.54	.01
2MR-168-04	9390-0084	84	6.61	.01
2MR-172-04	9390-0086	86	6.77	.01
2MR-180-04	9390-0090	90	7.09	.01
2MR-186-04	9390-0093	93	7.32	.01
2MR-192-04	9390-0096	96	7.56	.01
2MR-200-04	9390-0100	100	7.87	.01
2MR-202-04	9390-0101	101	7.95	.01
2MR-210-04	9390-0105	105	8.27	.01
2MR-212-04	9390-0106	106	8.35	.01
2MR-216-04	9390-0108	108	8.50	.01
2MR-220-04	9390-0110	110	8.66	.01
2MR-232-04	9390-0116	116	9.13	.01
2MR-236-04	9390-0118	118	9.29	.01
2MR-240-04	9390-0120	120	9.45	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-250-04	9390-0125	125	9.84	.01
2MR-252-04	9390-0126	126	9.92	.01
2MR-258-04	9390-0129	129	10.16	.01
2MR-278-04	9390-0139	139	10.94	.01
2MR-280-04	9390-0140	140	11.02	.01
2MR-300-04	9390-0150	150	11.81	.01
2MR-320-04	9390-0160	160	12.60	.01
2MR-322-04	9390-0161	161	12.68	.01
2MR-332-04	9390-0166	166	13.07	.01
2MR-346-04	9390-0173	173	13.62	.01
2MR-350-04	9390-0175	175	13.78	.01
2MR-364-04	9390-0182	182	14.33	.01
2MR-370-04	9390-0185	185	14.57	.01
2MR-380-04	9390-0190	190	14.96	.01
2MR-386-04	9390-0193	193	15.20	.01
2MR-400-04	9390-0200	200	15.75	.01
2MR-406-04	9390-0203	203	15.98	.01
2MR-420-04	9390-0210	210	16.54	.01
2MR-456-04	9390-0228	228	17.95	.01
2MR-470-04	9390-0235	235	18.50	.01
2MR-474-04	9390-0237	237	18.66	.01
2MR-488-04	9390-0244	244	19.21	.01
2MR-504-04	9390-0252	252	19.84	.01
2MR-528-04	9390-0264	264	20.79	.01
2MR-552-04	9390-0276	276	21.73	.01
2MR-576-04	9390-0288	288	22.68	.01

PowerGrip® GT®2 Belts - 2MR and 3MR

Product No. Series 9390 (continued)

2MR Pitch — 4mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-600-04	9390-0300	300	23.62	.01
2MR-640-04	9390-0320	320	25.20	.02
2MR-696-04	9390-0348	348	27.40	.02

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-744-04	9390-0372	372	29.29	.02
2MR-848-04	9390-0424	424	33.39	.02
2MR-1164-04	9390-0582	582	45.83	.03

2MR Pitch — 6mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-100-06	9390-1050	50	3.94	.05
2MR-112-06	9390-1056	56	4.41	.05
2MR-124-06	9390-1062	62	4.88	.01
2MR-126-06	9390-1063	63	4.96	.01
2MR-134-06	9390-1067	67	5.28	.01
2MR-136-06	9390-1068	68	5.35	.01
2MR-140-06	9390-1070	70	5.51	.05
2MR-152-06	9390-1076	76	5.98	.01
2MR-158-06	9390-1079	79	6.22	.01
2MR-160-06	9390-1080	80	6.30	.01
2MR-164-06	9390-1082	82	6.46	.01
2MR-166-06	9390-1083	83	6.54	.01
2MR-168-06	9390-1084	84	6.61	.01
2MR-172-06	9390-1086	86	6.77	.01
2MR-180-06	9390-1090	90	7.09	.01
2MR-186-06	9390-1093	93	7.32	.01
2MR-192-06	9390-1096	96	7.56	.01
2MR-200-06	9390-1100	100	7.87	.01
2MR-202-06	9390-1101	101	7.95	.01
2MR-210-06	9390-1105	105	8.27	.01
2MR-212-06	9390-1106	106	8.35	.01
2MR-216-06	9390-1108	108	8.50	.01
2MR-220-06	9390-1110	110	8.66	.01
2MR-232-06	9390-1116	116	9.13	.05
2MR-236-06	9390-1118	118	9.29	.01
2MR-240-06	9390-1120	120	9.45	.01
2MR-250-06	9390-1125	125	9.84	.01
2MR-252-06	9390-1126	126	9.92	.01
2MR-258-06	9390-1129	129	10.16	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-278-06	9390-1139	139	10.94	.01
2MR-280-06	9390-1140	140	11.02	.01
2MR-300-06	9390-1150	150	11.81	.01
2MR-320-06	9390-1160	160	12.60	.01
2MR-322-06	9390-1161	161	12.68	.01
2MR-332-06	9390-1166	166	13.07	.02
2MR-346-06	9390-1173	173	13.62	.01
2MR-350-06	9390-1175	175	13.78	.01
2MR-364-06	9390-1182	182	14.33	.01
2MR-370-06	9390-1185	185	14.57	.01
2MR-380-06	9390-1190	190	14.96	.01
2MR-386-06	9390-1193	193	15.20	.01
2MR-400-06	9390-1200	200	15.75	.01
2MR-406-06	9390-1203	203	15.98	.01
2MR-420-06	9390-1210	210	16.54	.01
2MR-456-06	9390-1228	228	17.95	.01
2MR-470-06	9390-1235	235	18.50	.01
2MR-474-06	9390-1237	237	18.66	.01
2MR-488-06	9390-1244	244	19.21	.01
2MR-504-06	9390-1252	252	19.84	.01
2MR-528-06	9390-1264	264	20.79	.02
2MR-552-06	9390-1276	276	21.73	.01
2MR-576-06	9390-1288	288	22.68	.02
2MR-600-06	9390-1300	300	23.62	.02
2MR-640-06	9390-1320	320	25.20	.01
2MR-696-06	9390-1348	348	27.40	.01
2MR-744-06	9390-1372	372	29.29	.03
2MR-848-06	9390-1424	424	33.39	.03
2MR-1164-06	9390-1582	582	45.83	.04

2MR Pitch — 9mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-100-09	9390-2050	50	3.94	.05
2MR-112-09	9390-2056	56	4.41	.05
2MR-124-09	9390-2062	62	4.88	.01
2MR-126-09	9390-2063	63	4.96	.01
2MR-134-09	9390-2067	67	5.28	.01
2MR-136-09	9390-2068	68	5.35	.01
2MR-140-09	9390-2070	70	5.51	.01
2MR-152-09	9390-2076	76	5.98	.01
2MR-158-09	9390-2079	79	6.22	.01
2MR-160-09	9390-2080	80	6.30	.01
2MR-164-09	9390-2082	82	6.46	.01
2MR-166-09	9390-2083	83	6.54	.01
2MR-168-09	9390-2084	84	6.61	.01
2MR-172-09	9390-2086	86	6.77	.01
2MR-180-09	9390-2090	90	7.09	.01
2MR-186-09	9390-2093	93	7.32	.01
2MR-192-09	9390-2096	96	7.56	.01
2MR-200-09	9390-2100	100	7.87	.01
2MR-202-09	9390-2101	101	7.95	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-210-09	9390-2105	105	8.27	.01
2MR-212-09	9390-2106	106	8.35	.01
2MR-216-09	9390-2108	108	8.50	.01
2MR-220-09	9390-2110	110	8.66	.01
2MR-232-09	9390-2116	116	9.13	.01
2MR-236-09	9390-2118	118	9.29	.01
2MR-240-09	9390-2120	120	9.45	.01
2MR-250-09	9390-2125	125	9.84	.01
2MR-252-09	9390-2126	126	9.92	.01
2MR-258-09	9390-2129	129	10.16	.01
2MR-278-09	9390-2139	139	10.94	.01
2MR-280-09	9390-2140	140	11.02	.01
2MR-300-09	9390-2150	150	11.81	.01
2MR-320-09	9390-2160	160	12.60	.01
2MR-322-09	9390-2161	161	12.68	.01
2MR-332-09	9390-2166	166	13.07	.01
2MR-346-09	9390-2173	173	13.62	.01
2MR-350-09	9390-2175	175	13.78	.01
2MR-364-09	9390-2182	182	14.33	.02



PowerGrip® GT®2 Belts - 2MR and 3MR

Product No. Series 9390 (continued)

2MR Pitch — 9mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-370-09	9390-2185	185	14.57	.01
2MR-380-09	9390-2190	190	14.96	.02
2MR-386-09	9390-2193	193	15.20	.01
2MR-400-09	9390-2200	200	15.75	.01
2MR-406-09	9390-2203	203	15.98	.02
2MR-420-09	9390-2210	210	16.54	.02
2MR-456-09	9390-2228	228	17.95	.01
2MR-470-09	9390-2235	235	18.50	.02
2MR-474-09	9390-2237	237	18.66	.02
2MR-488-09	9390-2244	244	19.21	.02

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2MR-504-09	9390-2252	252	19.84	.02
2MR-528-09	9390-2264	264	20.79	.03
2MR-552-09	9390-2276	276	21.73	.03
2MR-576-09	9390-2288	288	22.68	.01
2MR-600-09	9390-2300	300	23.62	.03
2MR-640-09	9390-2320	320	25.20	.02
2MR-696-09	9390-2348	348	27.40	.02
2MR-744-09	9390-2372	372	29.29	.02
2MR-848-09	9390-2424	424	33.39	.04
2MR-1164-09	9390-2582	582	45.83	.04

3MR Pitch — 6mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-99-06	9390-3033	33	3.90	.01
3MR-111-06	9390-3037	37	4.37	.01
3MR-123-06	9390-3041	41	4.84	.01
3MR-129-06	9390-3043	43	5.08	.01
3MR-159-06	9390-3053	53	6.26	.01
3MR-165-06	9390-3055	55	6.50	.05
3MR-180-06	9390-3060	60	7.09	.01
3MR-183-06	9390-3061	61	7.20	.01
3MR-189-06	9390-3063	63	7.44	.01
3MR-201-06	9390-3067	67	7.91	.01
3MR-219-06	9390-3073	73	8.62	.01
3MR-225-06	9390-3075	75	8.86	.01
3MR-240-06	9390-3080	80	9.45	.01
3MR-243-06	9390-3081	81	9.57	.01
3MR-255-06	9390-3085	85	10.04	.01
3MR-267-06	9390-3089	89	10.51	.01
3MR-282-06	9390-3094	94	11.10	.01
3MR-291-06	9390-3097	97	11.46	.01
3MR-300-06	9390-3100	100	11.81	.01
3MR-339-06	9390-3113	113	13.35	.01
3MR-348-06	9390-3116	116	13.70	.01
3MR-357-06	9390-3119	119	14.06	.01
3MR-360-06	9390-3120	120	14.17	.01
3MR-375-06	9390-3125	125	14.76	.01
3MR-393-06	9390-3131	131	15.47	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-414-06	9390-3138	138	16.30	.02
3MR-420-06	9390-3140	140	16.54	.01
3MR-447-06	9390-3149	149	17.60	.01
3MR-450-06	9390-3150	150	17.72	.01
3MR-474-06	9390-3158	158	18.66	.02
3MR-480-06	9390-3160	160	18.90	.02
3MR-483-06	9390-3161	161	19.02	.02
3MR-489-06	9390-3163	163	19.25	.02
3MR-504-06	9390-3168	168	19.84	.02
3MR-537-06	9390-3179	179	21.14	.02
3MR-552-06	9390-3184	184	21.73	.02
3MR-564-06	9390-3188	188	22.20	.02
3MR-600-06	9390-3200	200	23.62	.02
3MR-630-06	9390-3210	210	24.80	.05
3MR-684-06	9390-3228	228	26.93	.02
3MR-735-06	9390-3245	245	28.94	.02
3MR-750-06	9390-3250	250	29.53	.02
3MR-786-06	9390-3262	262	30.94	.03
3MR-840-06	9390-3280	280	33.07	.03
3MR-945-06	9390-3315	315	37.20	.04
3MR-1050-06	9390-3350	350	41.34	.04
3MR-1080-06	9390-3360	360	42.52	.02
3MR-1536-06	9390-3512	512	60.47	.06
3MR-1587-06	9390-3529	529	62.48	.06
3MR-2061-06	9390-3687	687	81.14	.07

3MR Pitch — 9mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-99-09	9390-4033	33	3.90	.01
3MR-111-09	9390-4037	37	4.37	.01
3MR-123-09	9390-4041	41	4.84	.01
3MR-129-09	9390-4043	43	5.08	.01
3MR-159-09	9390-4053	53	6.26	.01
3MR-165-09	9390-4055	55	6.50	.05
3MR-180-09	9390-4060	60	7.09	.01
3MR-183-09	9390-4061	61	7.20	.01
3MR-189-09	9390-4063	63	7.44	.01
3MR-201-09	9390-4067	67	7.91	.01
3MR-219-09	9390-4073	73	8.62	.01
3MR-225-09	9390-4075	75	8.86	.01
3MR-240-09	9390-4080	80	9.45	.01
3MR-243-09	9390-4081	81	9.57	.01
3MR-255-09	9390-4085	85	10.04	.01
3MR-267-09	9390-4089	89	10.51	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-282-09	9390-4094	94	11.10	.01
3MR-291-09	9390-4097	97	11.46	.01
3MR-300-09	9390-4100	100	11.81	.01
3MR-339-09	9390-4113	113	13.35	.01
3MR-348-09	9390-4116	116	13.70	.01
3MR-357-09	9390-4119	119	14.06	.02
3MR-360-09	9390-4120	120	14.17	.01
3MR-375-09	9390-4125	125	14.76	.01
3MR-393-09	9390-4131	131	15.47	.02
3MR-414-09	9390-4138	138	16.30	.02
3MR-420-09	9390-4140	140	16.54	.02
3MR-447-09	9390-4149	149	17.60	.02
3MR-450-09	9390-4150	150	17.72	.02
3MR-474-09	9390-4158	158	18.66	.02
3MR-480-09	9390-4160	160	18.90	.02
3MR-483-09	9390-4161	161	19.02	.02



PowerGrip® GT®2 Belts - 2MR and 3MR

Product No. Series 9390 (continued)

3MR Pitch — 9mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-489-09	9390-4163	163	19.25	.02
3MR-504-09	9390-4168	168	19.84	.03
3MR-537-09	9390-4179	179	21.14	.02
3MR-552-09	9390-4184	184	21.73	.02
3MR-564-09	9390-4188	188	22.20	.02
3MR-600-09	9390-4200	200	23.62	.03
3MR-630-09	9390-4210	210	24.80	.03
3MR-684-09	9390-4228	228	26.93	.03
3MR-735-09	9390-4245	245	28.94	.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-750-09	9390-4250	250	29.53	.04
3MR-786-09	9390-4262	262	30.94	.04
3MR-840-09	9390-4280	280	33.07	.04
3MR-945-09	9390-4315	315	37.20	.04
3MR-1050-09	9390-4350	350	41.34	.05
3MR-1080-09	9390-4360	360	42.52	.05
3MR-1536-09	9390-4512	512	60.47	.07
3MR-1587-09	9390-4529	529	62.48	.08
3MR-2061-09	9390-4687	687	81.14	.10

3MR Pitch — 15mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-99-15	9390-5033	33	3.90	.01
3MR-111-15	9390-5037	37	4.37	.01
3MR-123-15	9390-5041	41	4.84	.01
3MR-129-15	9390-5043	43	5.08	.02
3MR-159-15	9390-5053	53	6.26	.02
3MR-165-15	9390-5055	55	6.50	.01
3MR-180-15	9390-5060	60	7.09	.02
3MR-183-15	9390-5061	61	7.20	.02
3MR-189-15	9390-5063	63	7.44	.01
3MR-201-15	9390-5067	67	7.91	.02
3MR-219-15	9390-5073	73	8.62	.01
3MR-225-15	9390-5075	75	8.86	.05
3MR-240-15	9390-5080	80	9.45	.02
3MR-243-15	9390-5081	81	9.57	.02
3MR-255-15	9390-5085	85	10.04	.02
3MR-267-15	9390-5089	89	10.51	.02
3MR-282-15	9390-5094	94	11.10	.02
3MR-291-15	9390-5097	97	11.46	.02
3MR-300-15	9390-5100	100	11.81	.02
3MR-339-15	9390-5113	113	13.35	.03
3MR-348-15	9390-5116	116	13.70	.03
3MR-357-15	9390-5119	119	14.06	.03
3MR-360-15	9390-5120	120	14.17	.03
3MR-375-15	9390-5125	125	14.76	.03
3MR-393-15	9390-5131	131	15.47	.03

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3MR-414-15	9390-5138	138	16.30	.04
3MR-420-15	9390-5140	140	16.54	.04
3MR-447-15	9390-5149	149	17.60	.04
3MR-450-15	9390-5150	150	17.72	.05
3MR-474-15	9390-5158	158	18.66	.04
3MR-480-15	9390-5160	160	18.90	.03
3MR-483-15	9390-5161	161	19.02	.04
3MR-489-15	9390-5163	163	19.25	.04
3MR-504-15	9390-5168	168	19.84	.04
3MR-537-15	9390-5179	179	21.14	.04
3MR-552-15	9390-5184	184	21.73	.04
3MR-564-15	9390-5188	188	22.20	.04
3MR-600-15	9390-5200	200	23.62	.05
3MR-630-15	9390-5210	210	24.80	.06
3MR-684-15	9390-5228	228	26.93	.06
3MR-735-15	9390-5245	245	28.94	.07
3MR-750-15	9390-5250	250	29.53	.06
3MR-786-15	9390-5262	262	30.94	.06
3MR-840-15	9390-5280	280	33.07	.03
3MR-945-15	9390-5315	315	37.20	.10
3MR-1050-15	9390-5350	350	41.34	.20
3MR-1080-15	9390-5360	360	42.52	.10
3MR-1536-15	9390-5512	512	60.47	.16
3MR-1587-15	9390-5529	529	62.48	.15
3MR-2061-15	9390-5687	687	81.14	.20



PowerGrip® GT®2 Belts - 5MR

The highest density 5mm rubber belt, the PowerGrip GT2 belt has twice the load carrying capacity of its predecessor HTD®. In addition, less width is required compared to HTD, allowing lighter, more compact drives.

Markets/Applications

PowerGrip GT2 belts are suitable for many applications such as HVAC, office machines, machine tools, hand power tools, postage handling, spindle drives, food processors, sewing machines, robotics, linear and light package conveyor.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Gates **patented tooth profile** is designed for use with a specific sprocket groove-belt tooth combination increases capacity, while improving registration.
- PowerGrip GT2 has more tooth ratchet resistance than HTD.
- Eliminates lubrication and re-tensioning reduce maintenance and labor as compared to roller chain drives.
- PowerGrip GT2 belt/sprocket combinations match or exceed the positional accuracy of PowerGrip Timing belt/pulley systems.


Recommended Sprockets

PowerGrip GT2 and Poly Chain™ GT®

Notes

PowerGrip GT2 part numbers are comprised of pitch, pitch length and width. For example; part number 5MR-400-09 denotes a 5mm pitch, 400mm pitch length and 9mm width.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of a PowerGrip GT2 belt lies within the tensile member.



Product No. Series 9390

5MR Pitch — 9mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-300-09	9390-6060	60	11.81	.02
5MR-355-09	9390-6071	71	13.98	.02
5MR-375-09	9390-6075	75	14.76	.01
5MR-400-09	9390-6080	80	15.75	.03
5MR-405-09	9390-6081	81	15.95	.03
5MR-425-09	9390-6085	85	16.73	.04
5MR-450-09	9390-6090	90	17.72	.03
5MR-500-09	9390-6100	100	19.69	.04
5MR-535-09	9390-6107	107	21.06	.04
5MR-565-09	9390-6113	113	22.24	.04
5MR-575-09	9390-6115	115	22.64	.04
5MR-580-09	9390-6116	116	22.83	.05
5MR-600-09	9390-6120	120	23.62	.05
5MR-625-09	9390-6125	125	24.61	.05
5MR-650-09	9390-6130	130	25.59	.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-700-09	9390-6140	140	27.56	.05
5MR-750-09	9390-6150	150	29.53	.06
5MR-800-09	9390-6160	160	31.50	.06
5MR-815-09	9390-6163	163	32.09	.07
5MR-850-09	9390-6170	170	33.46	.06
5MR-900-09	9390-6180	180	35.43	.07
5MR-1000-09	9390-6200	200	39.37	.07
5MR-1150-09	9390-6230	230	45.28	.06
5MR-1300-09	9390-6260	260	51.18	.10
5MR-1450-09	9390-6290	290	57.09	.10
5MR-1600-09	9390-6320	320	62.99	.12
5MR-1720-09	9390-6344	344	67.72	.12
5MR-1755-09	9390-6351	351	69.09	.10
5MR-2100-09	9390-6420	420	82.67	.17

5MR Pitch — 15mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-300-15	9390-7060	60	11.81	.04
5MR-355-15	9390-7071	71	13.98	.04
5MR-375-15	9390-7075	75	14.76	.05
5MR-400-15	9390-7080	80	15.75	.05
5MR-405-15	9390-7081	81	15.95	.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-425-15	9390-7085	85	16.73	.05
5MR-450-15	9390-7090	90	17.72	.06
5MR-500-15	9390-7100	100	19.69	.05
5MR-535-15	9390-7107	107	21.06	.07
5MR-565-15	9390-7113	113	22.24	.07

PowerGrip® GT®2 Belts - 5MR

Product No. Series 9390 (continued)

5MR Pitch — 15mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-575-15	9390-7115	115	22.64	.06
5MR-580-15	9390-7116	116	22.83	.07
5MR-600-15	9390-7120	120	23.62	.07
5MR-625-15	9390-7125	125	24.61	.07
5MR-650-15	9390-7130	130	25.59	.10
5MR-700-15	9390-7140	140	27.56	.10
5MR-750-15	9390-7150	150	29.53	.10
5MR-800-15	9390-7160	160	31.50	.10
5MR-815-15	9390-7163	163	32.09	.10
5MR-850-15	9390-7170	170	33.46	.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-900-15	9390-7180	180	35.43	.10
5MR-1000-15	9390-7200	200	39.37	.10
5MR-1150-15	9390-7230	230	45.28	.15
5MR-1300-15	9390-7260	260	51.18	.17
5MR-1450-15	9390-7290	290	57.09	.01
5MR-1600-15	9390-7320	320	62.99	.20
5MR-1720-15	9390-7344	344	67.72	.20
5MR-1755-15	9390-7351	351	69.09	.25
5MR-2100-15	9390-7420	420	82.68	.27

5MR Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-300-25	9390-8060	60	11.81	.07
5MR-355-25	9390-8071	71	13.98	.07
5MR-375-25	9390-8075	75	14.76	.07
5MR-400-25	9390-8080	80	15.75	.07
5MR-405-25	9390-8081	81	5.95	.10
5MR-425-25	9390-8085	85	16.73	.07
5MR-450-25	9390-8090	90	17.72	.10
5MR-500-25	9390-8100	100	19.69	.10
5MR-535-25	9390-8107	107	21.06	.10
5MR-565-25	9390-8113	113	22.24	.10
5MR-575-25	9390-8115	115	22.64	.10
5MR-580-25	9390-8116	116	22.83	.10
5MR-600-25	9390-8120	120	23.62	.10
5MR-625-25	9390-8125	125	24.61	.10
5MR-650-25	9390-8130	130	25.59	.15

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5MR-700-25	9390-8140	140	27.56	.10
5MR-750-25	9390-8150	150	29.53	.15
5MR-800-25	9390-8160	160	31.50	.15
5MR-815-25	9390-8163	163	32.09	.20
5MR-850-25	9390-8170	170	33.46	.20
5MR-900-25	9390-8180	180	35.43	.20
5MR-1000-25	9390-8200	200	39.37	.20
5MR-1150-25	9390-8230	230	45.28	.25
5MR-1300-25	9390-8260	260	51.18	.30
5MR-1450-25	9390-8290	290	57.09	.35
5MR-1600-25	9390-8320	320	62.99	.40
5MR-1720-25	9390-8344	344	67.72	.35
5MR-1755-25	9390-8351	351	69.09	.40
5MR-2100-25	9390-8420	420	82.68	.53



PowerGrip® GT®2 Belts - 8M and 14M

Reduce both acquisition costs and transaction costs by designing with PowerGrip GT2. The PowerGrip GT2 belt has two times the rating of competitive RPP® belts, and its predecessors PowerGrip GT and HTD® belts. PowerGrip GT2 drive systems offer the largest selection of belts and sprockets in the industry. At reduced widths, PowerGrip GT2 belts can be used as a direct replacement for most 1.0 and 1.5 rated 8mm and 14mm pitch rubber curvilinear synchronous belts.

Markets/Applications

PowerGrip GT2 belts are suitable for many applications such as HVAC, textile, printing, machine tools, food processing, conveyors, packaging, agriculture, pumps, compressors, centrifuges, laundry, pulp and paper.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Gates **patented tooth profile** is designed for use with a specific sprocket groove profile. The sprocket groove-belt tooth combination increases capacity, while improving registration.
- PowerGrip GT2 has more tooth ratchet resistance than HTD
- Eliminates lubrication and re-tensioning reduce maintenance and labor as compared to roller chain drives.
- PowerGrip GT2 ACHE belts are available in 14mm pitch. A single twist cord helps prevent the belt from moving downward on vertical shaft ACHE applications.

Recommended Sprockets


PowerGrip GT2 Sprockets

Notes

PowerGrip GT2 part numbers are comprised of pitch, pitch length and width. For example; part number 3150-14MGT-55 denotes a 3150mm pitch length, 14mm pitch and 55mm width.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of a PowerGrip GT2 belt lies within the tensile member.

WARNING: New drive designs must use the PowerGrip GT2 sprockets, because of the high torque capacity of PowerGrip GT2 belts. Do not use HTD or RPP® profile sprockets in new designs. PowerGrip GT2 belts can be used on existing HTD or HT100® sprockets as replacement belts, usually at the next narrowest width.



Product No. Series 9207

8mm Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
384-8MGT-12	9207-1200	48	15.12	.05
480-8MGT-12	9207-1201	60	18.90	.10
560-8MGT-12	9207-1202	70	22.05	.10
600-8MGT-12	9207-1203	75	23.62	.10
640-8MGT-12	9207-1204	80	25.20	.10
720-8MGT-12	9207-1205	90	28.35	.10
800-8MGT-12	9207-1206	100	31.50	.10
840-8MGT-12	9207-1207	105	33.07	.15
880-8MGT-12	9207-1208	110	34.65	.15
920-8MGT-12	9207-1209	115	36.22	.10
960-8MGT-12	9207-1210	120	37.80	.10
1040-8MGT-12	9207-1211	130	40.94	.15
1064-8MGT-12	9207-1212	133	41.89	.15
1104-8MGT-12	9207-1213	138	43.46	.15
1120-8MGT-12	9207-1214	140	44.09	.15
1160-8MGT-12	9207-1215	145	45.67	.15

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1200-8MGT-12	9207-1216	150	47.24	.20
1224-8MGT-12	9207-1217	153	48.19	.20
1280-8MGT-12	9207-1218	160	50.39	.20
1440-8MGT-12	9207-1219	180	56.69	.20
1512-8MGT-12	9207-1220	189	59.53	.25
1584-8MGT-12	9207-1221	198	62.36	.25
1600-8MGT-12	9207-1222	200	62.99	.25
1760-8MGT-12	9207-1223	220	69.29	.25
1800-8MGT-12	9207-1224	225	70.87	.25
2000-8MGT-12	9207-1225	250	78.74	.25
2200-8MGT-12	9207-1226	275	86.61	.25
2400-8MGT-12	9207-1227	300	94.49	.30
2600-8MGT-12	9207-1228	325	102.36	.35
2800-8MGT-12	9207-1229	350	110.24	.35
3280-8MGT-12	9207-1230	410	129.13	.35

PowerGrip® GT®2 Belts - 8M and 14M

Product No. Series 9207 (continued)

8mm Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
384-8MGT-20	9207-1021	48	15.12	.09
480-8MGT-20	9207-0001	60	18.90	.10
560-8MGT-20	9207-0005	70	22.05	.15
600-8MGT-20	9207-0009	75	23.62	.15
640-8MGT-20	9207-0013	80	25.20	.15
720-8MGT-20	9207-0017	90	28.35	.20
800-8MGT-20	9207-0021	100	31.50	.20
840-8MGT-20	9207-1025	105	33.07	.20
880-8MGT-20	9207-0025	110	34.65	.20
920-8MGT-20	9207-1001	115	36.22	.15
960-8MGT-20	9207-0029	120	37.80	.20
1040-8MGT-20	9207-0033	130	40.94	.25
1064-8MGT-20	9207-1005	133	41.89	.25
1104-8MGT-20	9207-1037	138	43.46	.31
1120-8MGT-20	9207-0037	140	44.09	.30
1160-8MGT-20	9207-1009	145	45.67	.25
1200-8MGT-20	9207-0041	150	47.24	.30

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1224-8MGT-20	9207-1029	153	48.19	.30
1280-8MGT-20	9207-0045	160	50.39	.30
1440-8MGT-20	9207-0049	180	56.69	.35
1512-8MGT-20	9207-1013	189	59.53	.37
1584-8MGT-20	9207-1017	198	62.36	4.25
1600-8MGT-20	9207-0053	200	62.99	.40
1760-8MGT-20	9207-0057	220	69.29	.45
1800-8MGT-20	9207-0061	225	70.87	.45
2000-8MGT-20	9207-0065	250	78.74	.45
2200-8MGT-20	9207-1033	275	86.62	.55
2400-8MGT-20	9207-0069	300	94.49	.60
2600-8MGT-20	9207-0077	325	102.36	.65
2800-8MGT-20	9207-0073	350	110.24	.70
3048-8MGT-20	9207-0081	381	120.00	.75
3280-8MGT-20	9207-0085	410	129.13	.80
3600-8MGT-20	9207-0089	450	141.73	.95
4400-8MGT-20	9207-0093	550	173.23	1.15

8mm Pitch — 30mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
384-8MGT-30	9207-1022	48	15.12	.15
480-8MGT-30	9207-0002	60	18.90	.20
560-8MGT-30	9207-0006	70	22.05	.20
600-8MGT-30	9207-0010	75	23.62	.21
640-8MGT-30	9207-0014	80	25.20	.20
720-8MGT-30	9207-0018	90	28.35	.25
800-8MGT-30	9207-0022	100	31.50	.25
840-8MGT-30	9207-1026	105	33.07	.30
880-8MGT-30	9207-0026	110	34.65	.30
920-8MGT-30	9207-1002	115	36.22	.35
960-8MGT-30	9207-0030	120	37.80	.35
1040-8MGT-30	9207-0034	130	40.94	.35
1064-8MGT-30	9207-1006	133	41.89	.40
1104-8MGT-30	9207-1038	138	43.46	.46
1120-8MGT-30	9207-0038	140	44.09	.40
1160-8MGT-30	9207-1010	145	45.67	.45
1200-8MGT-30	9207-0042	150	47.24	.45

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1224-8MGT-30	9207-1030	153	48.19	.45
1280-8MGT-30	9207-0046	160	50.39	.45
1440-8MGT-30	9207-0050	180	56.69	.55
1512-8MGT-30	9207-1014	189	59.53	.50
1584-8MGT-30	9207-1018	198	62.36	.60
1600-8MGT-30	9207-0054	200	62.99	.60
1760-8MGT-30	9207-0058	220	69.29	.65
1800-8MGT-30	9207-0062	225	70.87	.65
2000-8MGT-30	9207-0066	250	78.74	.70
2200-8MGT-30	9207-1034	275	86.61	.80
2400-8MGT-30	9207-0070	300	94.49	.85
2600-8MGT-30	9207-0078	325	102.36	1.00
2800-8MGT-30	9207-0074	350	110.24	1.00
3048-8MGT-30	9207-0082	381	120.00	1.20
3280-8MGT-30	9207-0086	410	129.13	1.25
3600-8MGT-30	9207-0090	450	141.73	1.11
4400-8MGT-30	9207-0094	550	173.23	1.70

8mm Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
384-8MGT-50	9207-1023	48	15.12	.20
480-8MGT-50	9207-0003	60	18.90	.30
560-8MGT-50	9207-0007	70	22.05	.30
600-8MGT-50	9207-0011	75	23.62	.35
640-8MGT-50	9207-0015	80	25.20	.40
720-8MGT-50	9207-0019	90	28.35	.45
800-8MGT-50	9207-0023	100	31.50	.50
840-8MGT-50	9207-1027	105	33.07	.50
880-8MGT-50	9207-0027	110	34.65	.55
920-8MGT-50	9207-1003	115	36.22	.60
960-8MGT-50	9207-0031	120	37.80	.60
1040-8MGT-50	9207-0035	130	40.94	.65
1064-8MGT-50	9207-1007	133	41.89	.65
1104-8MGT-50	9207-1039	138	43.46	.65
1120-8MGT-50	9207-0039	140	44.09	.65
1160-8MGT-50	9207-1011	145	45.67	.70
1200-8MGT-50	9207-0043	150	47.24	.75

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1224-8MGT-50	9207-1031	153	48.19	.75
1280-8MGT-50	9207-0047	160	50.39	.75
1440-8MGT-50	9207-0051	180	56.69	.90
1512-8MGT-50	9207-1015	189	59.53	1.00
1584-8MGT-50	9207-1019	198	62.36	1.00
1600-8MGT-50	9207-0055	200	62.99	1.00
1760-8MGT-50	9207-0059	220	69.29	1.10
1800-8MGT-50	9207-0063	225	70.87	1.10
2000-8MGT-50	9207-0067	250	78.74	1.30
2200-8MGT-50	9207-1035	275	86.61	1.35
2400-8MGT-50	9207-0071	300	94.49	1.50
2600-8MGT-50	9207-0079	325	102.36	1.60
2800-8MGT-50	9207-0075	350	110.24	1.70
3048-8MGT-50	9207-0083	381	120.00	1.90
3280-8MGT-50	9207-0087	410	129.13	2.00
3600-8MGT-50	9207-0091	450	141.73	2.35
4400-8MGT-50	9207-0095	550	173.23	2.75



PowerGrip® GT®2 Belts - 8M and 14M

Product No. Series 9207 (continued)

8mm Pitch — 85mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
384-8MGT-85	9207-1024	48	15.12	.40
480-8MGT-85	9207-0004	60	18.90	.50
560-8MGT-85	9207-0008	70	22.05	.55
600-8MGT-85	9207-0012	75	23.62	.65
640-8MGT-85	9207-0016	80	25.20	.70
720-8MGT-85	9207-0020	90	28.35	.75
800-8MGT-85	9207-0024	100	31.50	.85
840-8MGT-85	9207-1028	105	33.07	.90
880-8MGT-85	9207-0028	110	34.65	.95
920-8MGT-85	9207-1004	115	36.22	1.00
960-8MGT-85	9207-0032	120	37.80	.95
1040-8MGT-85	9207-0036	130	40.94	1.10
1064-8MGT-85	9207-1008	133	41.89	1.05
1104-8MGT-85	9207-1040	138	43.46	1.30
1120-8MGT-85	9207-0040	140	44.09	2.85
1160-8MGT-85	9207-1012	146	45.83	2.20
1200-8MGT-85	9207-0044	150	47.24	1.25

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1224-8MGT-85	9207-1032	153	48.19	1.30
1280-8MGT-85	9207-0048	160	50.39	1.31
1440-8MGT-85	9207-0052	180	56.69	1.55
1512-8MGT-85	9207-1016	189	59.53	1.60
1584-8MGT-85	9207-1020	198	62.36	1.65
1600-8MGT-85	9207-0056	200	62.99	1.75
1760-8MGT-85	9207-0060	220	69.29	1.90
1800-8MGT-85	9207-0064	225	70.87	1.95
2000-8MGT-85	9207-0068	250	78.74	2.10
2200-8MGT-85	9207-1036	275	86.61	2.30
2400-8MGT-85	9207-0072	300	94.49	2.45
2600-8MGT-85	9207-0080	325	102.36	2.65
2800-8MGT-85	9207-0076	350	110.24	3.05
3048-8MGT-85	9207-0084	381	120.00	3.35
3280-8MGT-85	9207-0088	410	129.13	3.65
3600-8MGT-85	9207-0092	450	141.73	3.90
4400-8MGT-85	9207-0096	550	173.23	4.80

14mm Pitch — 40mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
966-14MGT-40	9207-0100	69	38.03	1.30
1190-14MGT-40	9207-0105	85	46.85	1.50
1400-14MGT-40	9207-0110	100	55.12	1.65
1610-14MGT-40	9207-0115	115	63.39	1.85
1778-14MGT-40	9207-0120	127	70.00	1.95
1890-14MGT-40	9207-0125	135	74.41	2.05
2100-14MGT-40	9207-0130	150	82.68	2.35
2310-14MGT-40	9207-0135	165	90.94	2.45
2450-14MGT-40	9207-0140	175	96.46	2.55
2590-14MGT-40	9207-0145	185	101.97	2.65
2800-14MGT-40	9207-0150	200	110.24	2.80

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3150-14MGT-40	9207-0155	225	124.02	3.10
3360-14MGT-40	9207-0180	240	132.28	3.80
3500-14MGT-40	9207-0160	250	137.80	4.00
3850-14MGT-40	9207-0165	275	151.57	4.20
4326-14MGT-40	9207-0170	309	170.31	4.50
4578-14MGT-40	9207-0175	327	180.24	4.85
4956-14MGT-40	9207-0185	354	195.12	5.15
5320-14MGT-40	9207-0190	380	209.45	5.50
5740-14MGT-40	9207-0195	410	225.98	5.75
6160-14MGT-40	9207-0200	440	242.52	5.00
6860-14MGT-40	9207-0205	490	270.08	5.56

14mm Pitch — 55mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
966-14MGT-55	9207-0101	69	38.03	1.65
1190-14MGT-55	9207-0106	85	46.85	1.90
1400-14MGT-55	9207-0111	100	55.12	2.10
1610-14MGT-55	9207-0116	115	63.39	2.35
1778-14MGT-55	9207-0121	127	70.00	2.55
1890-14MGT-55	9207-0126	135	74.41	3.20
2100-14MGT-55	9207-0131	150	82.68	2.95
2310-14MGT-55	9207-0136	165	90.94	3.15
2450-14MGT-55	9207-0141	175	96.46	3.35
2590-14MGT-55	9207-0146	185	101.97	3.50
2800-14MGT-55	9207-0151	200	110.24	3.70

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3150-14MGT-55	9207-0156	225	124.02	5.00
3360-14MGT-55	9207-0181	240	132.28	4.95
3500-14MGT-55	9207-0161	250	137.80	5.00
3850-14MGT-55	9207-0166	275	151.57	5.75
4326-14MGT-55	9207-0171	309	170.31	5.95
4578-14MGT-55	9207-0176	327	180.24	6.20
4956-14MGT-55	9207-0186	354	195.12	6.50
5320-14MGT-55	9207-0191	380	209.45	6.95
5740-14MGT-55	9207-0196	410	225.98	7.50
6160-14MGT-55	9207-0201	440	242.52	7.10
6860-14MGT-55	9207-0206	490	270.08	8.75

14mm Pitch — 85mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
966-14MGT-85	9207-0102	69	38.03	3.10
1190-14MGT-85	9207-0107	85	46.85	3.35
1400-14MGT-85	9207-0112	100	55.12	3.75
1610-14MGT-85	9207-0117	115	63.39	2.76
1778-14MGT-85	9207-0122	127	70.00	4.50
1890-14MGT-85	9207-0127	135	74.41	4.65
2100-14MGT-85	9207-0132	150	82.68	3.61

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2310-14MGT-85	9207-0137	165	90.94	5.40
2450-14MGT-85	9207-0142	175	96.46	5.70
2590-14MGT-85	9207-0147	185	101.97	5.85
2800-14MGT-85	9207-0152	200	110.24	6.20
3150-14MGT-85	9207-0157	225	124.02	6.90
3360-14MGT-85	9207-0182	240	132.28	7.40
3500-14MGT-85	9207-0162	250	137.80	7.40



PowerGrip® GT®2 Belts - 8M and 14M

Product No. Series 9207 (continued)

14mm Pitch — 85mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3850-14MGT-85	9207-0167	275	151.57	8.00
4326-14MGT-85	9207-0172	309	170.31	8.50
4578-14MGT-85	9207-0177	327	180.24	9.35
4956-14MGT-85	9207-0187	354	195.12	9.85

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5320-14MGT-85	9207-0192	380	209.45	10.45
5740-14MGT-85	9207-0197	410	225.98	11.35
6160-14MGT-85	9207-0202	440	242.52	12.10
6860-14MGT-85	9207-0207	490	270.08	14.30

14mm Pitch — 115mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
966-14MGT-115	9207-0103	69	38.03	2.20
1190-14MGT-115	9207-0108	85	46.85	2.75
1400-14MGT-115	9207-0113	100	55.12	4.65
1610-14MGT-115	9207-0118	115	63.39	5.15
1778-14MGT-115	9207-0123	127	70.00	5.55
1890-14MGT-115	9207-0128	135	74.41	5.90
2100-14MGT-115	9207-0133	150	82.68	6.25
2310-14MGT-115	9207-0138	165	90.94	7.40
2450-14MGT-115	9207-0143	175	96.46	7.25
2590-14MGT-115	9207-0148	185	101.97	7.45
2800-14MGT-115	9207-0153	200	110.24	8.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3150-14MGT-115	9207-0158	225	124.02	8.75
3360-14MGT-115	9207-0183	240	132.28	9.10
3500-14MGT-115	9207-0163	250	137.80	10.00
3850-14MGT-115	9207-0168	275	151.57	8.97
4326-14MGT-115	9207-0173	309	170.31	11.55
4578-14MGT-115	9207-0178	327	180.24	12.10
4956-14MGT-115	9207-0188	354	195.12	13.00
5320-14MGT-115	9207-0193	380	209.45	14.55
5740-14MGT-115	9207-0198	410	225.98	13.39
6160-14MGT-115	9207-0203	440	242.52	16.84
6860-14MGT-115	9207-0208	490	270.08	17.30

14mm Pitch — 170mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
966-14MGT-170	9207-0104	69	38.03	3.30
1190-14MGT-170	9207-0109	85	46.85	4.08
1400-14MGT-170	9207-0114	100	55.12	5.10
1610-14MGT-170	9207-0119	115	63.39	5.55
1778-14MGT-170	9207-0124	127	70.00	1.30
1890-14MGT-170	9207-0129	135	74.41	9.25
2100-14MGT-170	9207-0134	150	82.68	7.35
2310-14MGT-170	9207-0139	165	90.94	8.05
2450-14MGT-170	9207-0144	175	96.46	8.43
2590-14MGT-170	9207-0149	185	101.97	8.45
2800-14MGT-170	9207-0154	200	110.24	12.75

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3150-14MGT-170	9207-0159	225	124.02	13.80
3360-14MGT-170	9207-0184	240	132.28	11.75
3500-14MGT-170	9207-0164	250	137.80	15.20
3850-14MGT-170	9207-0169	275	151.57	16.20
4326-14MGT-170	9207-0174	309	170.31	15.15
4578-14MGT-170	9207-0179	327	180.24	18.40
4956-14MGT-170	9207-0189	354	195.12	.25
5320-14MGT-170	9207-0194	380	209.45	21.10
5740-14MGT-170	9207-0199	410	225.98	21.12
6160-14MGT-170	9207-0204	440	242.52	22.67
6860-14MGT-170	9207-0209	490	270.08	23.66

14mm Pitch PowerGrip® GT®2 ACHE Belts — 40, 55 and 85mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3150-14MGT-40F	9207-0589	225	124.01	3.65
3150-14MGT-55F	9207-0593	225	124.01	4.85
3150-14MGT-85F	9207-0597	225	124.01	5.82
3360-14MGT-40F	9207-0590	240	132.28	4.10
3360-14MGT-55F	9207-0594	240	132.28	2.35
3360-14MGT-85F	9207-0598	240	132.28	7.25

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
3500-14MGT-40F	9207-0591	250	137.79	3.90
3500-14MGT-55F	9207-0595	250	137.79	5.35
3500-14MGT-85F	9207-0599	250	137.79	7.60
3850-14MGT-40F	9207-0592	275	151.57	4.55
3850-14MGT-55F	9207-0596	275	151.57	5.40
3850-14MGT-85F	9207-0600	275	151.57	7.85



PowerGrip® HTD® Belts

PowerGrip HTD belts have a larger, more robust tooth profile for increased capacity, as compared to timing belts.

Markets/Applications

PowerGrip HTD belts are suitable for many applications including data storage, hand power tools, postage handling, food processors, office machines, centrifuges, money handling, medical diagnostic, sewing machines, ticket dispensers, robotics, vending machines and vacuum cleaners.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Thirty percent increase in horsepower ratings, as compared to traditional timing belts.
- Eliminates lubrication and re-tensioning to reduce maintenance and labor required on drives.


Recommended Sprockets

PowerGrip HTD Sprockets

Notes

PowerGrip HTD part numbers are comprised of pitch, pitch length and width. For example; part number 900-3M-15 denotes a 900mm pitch length, 3mm pitch and 15mm width.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of a PowerGrip HTD belt lies within the tensile member.



Product No. Series 9293

3mm Pitch — 6mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
87-3M-06	9293-2000	29	3.43	.01
102-3M-06	9293-2001	34	4.02	.01
105-3M-06	9293-2002	35	4.13	.01
111-3M-06	9293-2003	37	4.37	.01
123-3M-06	9293-2004	41	4.84	.01
144-3M-06	9293-2005	48	5.67	.01
147-3M-06	9293-2006	49	5.79	.01
150-3M-06	9293-0300	50	5.91	.01
156-3M-06	9293-2007	52	6.14	.01
159-3M-06	9293-0301	53	6.26	.01
165-3M-06	9293-2008	55	6.50	.01
168-3M-06	9293-0302	56	6.61	.01
174-3M-06	9293-2009	58	6.85	.01
177-3M-06	9293-0303	59	6.97	.01
180-3M-06	9293-2010	60	7.09	.01
183-3M-06	9293-2011	61	7.20	.01
189-3M-06	9293-0304	63	7.44	.01
195-3M-06	9293-2012	65	7.68	.01
201-3M-06	9293-0305	67	7.91	.01
204-3M-06	9293-2013	68	8.03	.01
207-3M-06	9293-2014	69	8.15	.01
213-3M-06	9293-0306	71	8.39	.00
216-3M-06	9293-2015	72	8.50	.01
222-3M-06	9293-2016	74	8.74	.01
225-3M-06	9293-0307	75	8.86	.01
228-3M-06	9293-2017	76	8.98	.01
234-3M-06	9293-2018	78	9.21	.01
237-3M-06	9293-2019	79	9.33	.01
240-3M-06	9293-0308	80	9.45	.01
246-3M-06	9293-2020	82	9.69	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
252-3M-06	9293-0309	84	9.92	.01
255-3M-06	9293-0310	85	10.04	.01
258-3M-06	9293-2021	86	10.16	.01
261-3M-06	9293-2022	87	10.28	.01
264-3M-06	9293-2023	88	10.39	.01
267-3M-06	9293-0311	89	10.51	.01
276-3M-06	9293-2024	92	10.87	.01
282-3M-06	9293-2025	94	11.10	.01
285-3M-06	9293-0312	95	11.22	.01
288-3M-06	9293-2026	96	11.34	.01
291-3M-06	9293-2027	97	11.46	.01
297-3M-06	9293-2028	99	11.69	.01
300-3M-06	9293-0313	100	11.81	.01
312-3M-06	9293-0314	104	12.28	.01
315-3M-06	9293-2029	105	12.40	.01
318-3M-06	9293-0315	106	12.52	.01
324-3M-06	9293-2030	108	12.76	.01
330-3M-06	9293-2031	110	12.99	.01
333-3M-06	9293-2032	111	13.11	.01
336-3M-06	9293-2033	112	13.23	.01
339-3M-06	9293-0316	113	13.35	.01
345-3M-06	9293-2034	115	13.58	.01
357-3M-06	9293-0317	119	14.06	.01
360-3M-06	9293-2035	120	14.17	.01
363-3M-06	9293-0318	121	14.29	.01
366-3M-06	9293-2036	122	14.41	.01
369-3M-06	9293-2037	123	14.53	.01
381-3M-06	9293-2038	127	15.00	.01
384-3M-06	9293-0319	128	15.12	.02
387-3M-06	9293-2039	129	15.24	.02



Product No. Series 9293 (continued)

3mm Pitch — 6mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
390-3M-06	9293-0320	130	15.35	.01
396-3M-06	9293-2040	132	15.59	.02
399-3M-06	9293-0321	133	15.71	.01
405-3M-06	9293-2041	135	15.94	.02
411-3M-06	9293-2042	137	16.18	.01
417-3M-06	9293-2043	139	16.42	.02
420-3M-06	9293-0322	140	16.54	.01
426-3M-06	9293-2044	142	16.77	.01
432-3M-06	9293-2045	144	17.01	.01
435-3M-06	9293-2046	145	17.13	.02
438-3M-06	9293-2047	146	17.24	.02
444-3M-06	9293-2048	148	17.48	.02
447-3M-06	9293-0323	149	17.60	.01
459-3M-06	9293-2049	153	18.07	.01
468-3M-06	9293-2050	156	18.43	.01
471-3M-06	9293-2051	157	18.54	.01
474-3M-06	9293-0324	158	18.66	.01
480-3M-06	9293-2052	160	18.90	.02
486-3M-06	9293-0325	162	19.13	.01
489-3M-06	9293-2053	163	19.25	.02
492-3M-06	9293-2054	164	19.37	.02
501-3M-06	9293-0326	167	19.72	.01
510-3M-06	9293-2055	170	20.08	.02
513-3M-06	9293-0327	171	20.20	.01
519-3M-06	9293-2056	173	20.43	.02
525-3M-06	9293-2057	175	20.67	.02
528-3M-06	9293-2058	176	20.79	.02
531-3M-06	9293-0328	177	20.91	.02
537-3M-06	9293-2059	179	21.14	.02
558-3M-06	9293-2060	186	21.97	.01
564-3M-06	9293-0329	188	22.20	.02
570-3M-06	9293-2061	190	22.44	.02
576-3M-06	9293-2062	192	22.68	.02
585-3M-06	9293-2063	195	23.03	.02
591-3M-06	9293-2064	197	23.27	.02
597-3M-06	9293-0330	199	23.50	.02
600-3M-06	9293-2065	200	23.62	.02
606-3M-06	9293-2066	202	23.86	.02
609-3M-06	9293-2067	203	23.98	.02
612-3M-06	9293-2068	204	24.09	.02
627-3M-06	9293-2069	209	24.69	.02

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
633-3M-06	9293-0331	211	24.92	.02
639-3M-06	9293-2070	213	25.16	.03
645-3M-06	9293-2071	215	25.39	.02
648-3M-06	9293-2072	216	25.51	.03
654-3M-06	9293-2073	218	25.75	.03
657-3M-06	9293-2074	219	25.87	.03
663-3M-06	9293-2075	221	26.10	.02
669-3M-06	9293-0332	223	26.34	.02
684-3M-06	9293-2076	228	26.93	.03
687-3M-06	9293-2077	229	27.05	.02
696-3M-06	9293-2078	232	27.40	.03
711-3M-06	9293-0333	237	27.99	.02
735-3M-06	9293-2079	245	28.94	.03
738-3M-06	9293-2080	246	29.06	.03
753-3M-06	9293-0334	251	29.65	.02
795-3M-06	9293-0335	265	31.30	.02
822-3M-06	9293-2081	274	32.36	.03
837-3M-06	9293-2082	279	32.95	.03
843-3M-06	9293-0336	281	33.19	.02
873-3M-06	9293-2083	291	34.37	.04
882-3M-06	9293-0337	294	34.72	.03
891-3M-06	9293-2084	297	35.08	.03
900-3M-06	9293-2085	300	35.43	.03
915-3M-06	9293-2086	305	36.02	.03
945-3M-06	9293-0338	315	37.20	.03
951-3M-06	9293-2087	317	37.44	.04
981-3M-06	9293-2088	327	38.62	.04
1002-3M-06	9293-0339	334	39.45	.03
1026-3M-06	9293-2089	342	40.39	.04
1035-3M-06	9293-2090	345	40.75	.03
1062-3M-06	9293-0340	354	41.81	.03
1125-3M-06	9293-0341	375	44.29	.04
1155-3M-06	9293-2091	385	45.47	.04
1191-3M-06	9293-0342	397	46.89	.04
1263-3M-06	9293-0343	421	49.72	.04
1500-3M-06	9293-2092	500	59.06	.05
1512-3M-06	9293-2093	504	59.53	.05
1587-3M-06	9293-2094	529	62.48	.07
1956-3M-06	9293-2095	652	77.01	.08
2004-3M-06	9293-2096	668	78.90	.06

3mm Pitch — 9mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
87-3M-09	9293-2200	29	3.43	.01
102-3M-09	9293-2201	34	4.02	.01
105-3M-09	9293-2202	35	4.13	.01
111-3M-09	9293-2203	37	4.37	.01
123-3M-09	9293-2204	41	4.84	.01
144-3M-09	9293-2205	48	5.67	.01
147-3M-09	9293-2206	49	5.79	.01
150-3M-09	9293-0344	50	5.91	.01
156-3M-09	9293-2207	52	6.14	.01
159-3M-09	9293-0345	53	6.26	.01
165-3M-09	9293-2208	55	6.50	.01
168-3M-09	9293-0346	56	6.61	.01
174-3M-09	9293-2209	58	6.85	.01
177-3M-09	9293-0347	59	6.97	.01
180-3M-09	9293-2210	60	7.09	.01
183-3M-09	9293-2211	61	7.20	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
189-3M-09	9293-0348	63	7.44	.01
195-3M-09	9293-2212	65	7.68	.01
201-3M-09	9293-0349	67	7.91	.01
204-3M-09	9293-2213	68	8.03	.01
207-3M-09	9293-2214	69	8.15	.01
213-3M-09	9293-0350	71	8.39	.01
216-3M-09	9293-2215	72	8.50	.01
222-3M-09	9293-2216	74	8.74	.01
225-3M-09	9293-0351	75	8.86	.01
228-3M-09	9293-2217	76	8.98	.01
234-3M-09	9293-2218	78	9.21	.01
237-3M-09	9293-2219	79	9.33	.01
240-3M-09	9293-0352	80	9.45	.01
246-3M-09	9293-2220	82	9.69	.01
252-3M-09	9293-0353	84	9.92	.01
255-3M-09	9293-0354	85	10.04	.01



PowerGrip® HTD® Belts

Product No. Series 9293 (continued)

3mm Pitch — 9mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
258-3M-09	9293-2221	86	10.16	.02
261-3M-09	9293-2222	87	10.28	.01
264-3M-09	9293-2223	88	10.39	.01
267-3M-09	9293-0355	89	10.51	.01
276-3M-09	9293-2224	92	10.87	.01
282-3M-09	9293-2225	94	11.10	.01
285-3M-09	9293-0356	95	11.22	.01
288-3M-09	9293-2226	96	11.34	.02
291-3M-09	9293-2227	97	11.46	.01
297-3M-09	9293-2228	99	11.69	.02
300-3M-09	9293-0357	100	11.81	.01
312-3M-09	9293-0358	104	12.28	.01
315-3M-09	9293-2229	105	12.40	.01
318-3M-09	9293-0359	106	12.52	.02
324-3M-09	9293-2230	108	12.76	.01
330-3M-09	9293-2231	110	12.99	.01
333-3M-09	9293-2232	111	13.11	.01
336-3M-09	9293-2233	112	13.23	.01
339-3M-09	9293-0360	113	13.35	.01
345-3M-09	9293-2234	115	13.58	.02
357-3M-09	9293-0361	119	14.06	.01
360-3M-09	9293-2235	120	14.17	.02
363-3M-09	9293-0362	121	14.29	.01
366-3M-09	9293-2236	122	14.41	.02
369-3M-09	9293-2237	123	14.53	.01
381-3M-09	9293-2238	127	15.00	.01
384-3M-09	9293-0363	128	15.12	.20
387-3M-09	9293-2239	129	15.24	.02
390-3M-09	9293-0364	130	15.35	.01
396-3M-09	9293-2240	132	15.59	.02
399-3M-09	9293-0365	133	15.71	.02
405-3M-09	9293-2241	135	15.94	.02
411-3M-09	9293-2242	137	16.18	.02
417-3M-09	9293-2243	139	16.42	.01
420-3M-09	9293-0366	140	16.54	.02
426-3M-09	9293-2244	142	16.77	.02
432-3M-09	9293-2245	144	17.01	.01
435-3M-09	9293-2246	145	17.13	.02
438-3M-09	9293-2247	146	17.24	.03
444-3M-09	9293-2248	148	17.48	.03
447-3M-09	9293-0367	149	17.60	.02
459-3M-09	9293-2249	153	18.07	.02
468-3M-09	9293-2250	156	18.43	.02
471-3M-09	9293-2251	157	18.54	.02
474-3M-09	9293-0368	158	18.66	.02
480-3M-09	9293-2252	160	18.90	.02
486-3M-09	9293-0369	162	19.13	.02
489-3M-09	9293-2253	163	19.25	.02
492-3M-09	9293-2254	164	19.37	.03
501-3M-09	9293-0370	167	19.72	.02
510-3M-09	9293-2255	170	20.08	.02
513-3M-09	9293-0371	171	20.20	.02
519-3M-09	9293-2256	173	20.43	.03
525-3M-09	9293-2257	175	20.67	.02
528-3M-09	9293-2258	176	20.79	.03

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
531-3M-09	9293-0372	177	20.91	.02
537-3M-09	9293-2259	179	21.14	.02
558-3M-09	9293-2260	186	21.97	.02
564-3M-09	9293-0373	188	22.20	.03
570-3M-09	9293-2261	190	22.44	.03
576-3M-09	9293-2262	192	22.68	.03
585-3M-09	9293-2263	195	23.03	.03
591-3M-09	9293-2264	197	23.27	.03
597-3M-09	9293-0374	199	23.50	.02
600-3M-09	9293-2265	200	23.62	.03
606-3M-09	9293-2266	202	23.86	.04
609-3M-09	9293-2267	203	23.98	.04
612-3M-09	9293-2268	204	24.09	.04
627-3M-09	9293-2269	209	24.69	.04
633-3M-09	9293-0375	211	24.92	.03
639-3M-09	9293-2270	213	25.16	.04
645-3M-09	9293-2271	215	25.39	.03
648-3M-09	9293-2272	216	25.51	.04
654-3M-09	9293-2273	218	25.75	.04
657-3M-09	9293-2274	219	25.87	.04
663-3M-09	9293-2275	221	26.10	.03
669-3M-09	9293-0376	223	26.34	.03
684-3M-09	9293-2276	228	26.93	.03
687-3M-09	9293-2277	229	27.05	.04
696-3M-09	9293-2278	232	27.40	.03
711-3M-09	9293-0377	237	27.99	.03
735-3M-09	9293-2279	245	28.94	.04
738-3M-09	9293-2280	246	29.06	.04
753-3M-09	9293-0378	251	29.65	.03
795-3M-09	9293-0379	265	31.30	.04
822-3M-09	9293-2281	274	32.36	.05
837-3M-09	9293-2282	279	32.95	.05
843-3M-09	9293-0380	281	33.19	.04
873-3M-09	9293-2283	291	34.37	.05
882-3M-09	9293-0381	294	34.72	.04
891-3M-09	9293-2284	297	35.08	.06
900-3M-09	9293-2285	300	35.43	.04
915-3M-09	9293-2286	305	36.02	.05
945-3M-09	9293-0382	315	37.20	.05
951-3M-09	9293-2287	317	37.44	.06
981-3M-09	9293-2288	327	38.62	.05
1002-3M-09	9293-0383	334	39.45	.04
1026-3M-09	9293-2289	342	40.39	.06
1035-3M-09	9293-2290	345	40.75	.05
1062-3M-09	9293-0384	354	41.81	.05
1125-3M-09	9293-0385	375	44.29	.06
1155-3M-09	9293-2291	385	45.47	.07
1191-3M-09	9293-0386	397	46.89	.06
1263-3M-09	9293-0387	421	49.72	.07
1500-3M-09	9293-2292	500	59.06	.07
1512-3M-09	9293-2293	504	59.53	.08
1587-3M-09	9293-2294	529	62.48	.08
1956-3M-09	9293-2295	652	77.01	.13
2004-3M-09	9293-2296	668	78.90	.14

3mm Pitch — 15mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
87-3M-15	9293-2400	29	3.43	.01
102-3M-15	9293-2401	34	4.02	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
105-3M-15	9293-2402	35	4.13	.01
111-3M-15	9293-2403	37	4.37	.01



Product No. Series 9293 (continued)

3mm Pitch — 15mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
123-3M-15	9293-2404	41	4.84	.01
144-3M-15	9293-2405	48	5.67	.01
147-3M-15	9293-2406	49	5.79	.01
150-3M-15	9293-0388	50	5.91	.02
156-3M-15	9293-2407	52	6.14	.02
159-3M-15	9293-0389	53	6.26	.02
165-3M-15	9293-2408	55	6.50	.02
168-3M-15	9293-0390	56	6.61	.01
174-3M-15	9293-2409	58	6.85	.01
177-3M-15	9293-0391	59	6.97	.02
180-3M-15	9293-2410	60	7.09	.02
183-3M-15	9293-2411	61	7.20	.02
189-3M-15	9293-0392	63	7.44	.02
195-3M-15	9293-2412	65	7.68	.02
201-3M-15	9293-0393	67	7.91	.01
204-3M-15	9293-2413	68	8.03	.02
207-3M-15	9293-2414	69	8.15	.01
213-3M-15	9293-0394	71	8.39	.01
216-3M-15	9293-2415	72	8.50	.02
222-3M-15	9293-2416	74	8.74	.02
225-3M-15	9293-0395	75	8.86	.01
228-3M-15	9293-2417	76	8.98	.02
234-3M-15	9293-2418	78	9.21	.02
237-3M-15	9293-2419	79	9.33	.02
240-3M-15	9293-0396	80	9.45	.02
246-3M-15	9293-2420	82	9.69	.02
252-3M-15	9293-0397	84	9.92	.02
255-3M-15	9293-0398	85	10.04	.02
258-3M-15	9293-2421	86	10.16	.03
261-3M-15	9293-2422	87	10.28	.03
264-3M-15	9293-2423	88	10.39	.02
267-3M-15	9293-0399	89	10.51	.02
276-3M-15	9293-2424	92	10.87	.02
282-3M-15	9293-2425	94	11.10	.02
285-3M-15	9293-0400	95	11.22	.02
288-3M-15	9293-2426	96	11.34	.03
291-3M-15	9293-2427	97	11.46	.02
297-3M-15	9293-2428	99	11.69	.03
300-3M-15	9293-0401	100	11.81	.02
312-3M-15	9293-0402	104	12.28	.02
315-3M-15	9293-2429	105	12.40	.03
318-3M-15	9293-0403	106	12.52	.02
324-3M-15	9293-2430	108	12.76	.03
330-3M-15	9293-2431	110	12.99	.03
333-3M-15	9293-2432	111	13.11	.03
336-3M-15	9293-2433	112	13.23	.03
339-3M-15	9293-0404	113	13.35	.02
345-3M-15	9293-2434	115	13.58	.03
357-3M-15	9293-0405	119	14.06	.02
360-3M-15	9293-2435	120	14.17	.03
363-3M-15	9293-0406	121	14.29	.03
366-3M-15	9293-2436	122	14.41	.04
369-3M-15	9293-2437	123	14.53	.04
381-3M-15	9293-2438	127	15.00	.03
384-3M-15	9293-0407	128	15.12	.03
387-3M-15	9293-2439	129	15.24	.03
390-3M-15	9293-0408	130	15.35	.03
396-3M-15	9293-2440	132	15.59	.04
399-3M-15	9293-0409	133	15.71	.03
405-3M-15	9293-2441	135	15.94	.04
411-3M-15	9293-2442	137	16.18	.04
417-3M-15	9293-2443	139	16.42	.04

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
420-3M-15	9293-0410	140	16.54	.03
426-3M-15	9293-2444	142	16.77	.04
432-3M-15	9293-2445	144	17.01	.04
435-3M-15	9293-2446	145	17.13	.04
438-3M-15	9293-2447	146	17.24	.03
444-3M-15	9293-2448	148	17.48	.04
447-3M-15	9293-0411	149	17.60	.04
459-3M-15	9293-2449	153	18.07	.04
468-3M-15	9293-2450	156	18.43	.05
471-3M-15	9293-2451	157	18.54	.05
474-3M-15	9293-0412	158	18.66	.03
480-3M-15	9293-2452	160	18.90	.04
486-3M-15	9293-0413	162	19.13	.05
489-3M-15	9293-2453	164	19.25	.05
492-3M-15	9293-2454	164	19.37	.05
501-3M-15	9293-0414	167	19.72	.04
510-3M-15	9293-2455	170	20.08	.05
513-3M-15	9293-0415	171	20.20	.04
519-3M-15	9293-2456	173	20.43	.05
525-3M-15	9293-2457	175	20.67	.05
528-3M-15	9293-2458	176	20.79	.05
531-3M-15	9293-0416	177	20.91	.04
537-3M-15	9293-2459	179	21.14	.05
558-3M-15	9293-2460	186	21.97	.05
564-3M-15	9293-0417	188	22.20	.04
570-3M-15	9293-2461	190	22.44	.05
576-3M-15	9293-2462	192	22.68	.05
585-3M-15	9293-2463	195	23.03	.05
591-3M-15	9293-2464	197	23.27	.06
597-3M-15	9293-0418	199	23.50	.05
600-3M-15	9293-2465	200	23.62	.05
606-3M-15	9293-2466	202	23.86	.06
609-3M-15	9293-2467	203	23.98	.06
612-3M-15	9293-2468	204	24.09	.06
627-3M-15	9293-2469	209	24.69	.06
633-3M-15	9293-0419	211	24.92	.05
639-3M-15	9293-2470	213	25.16	.06
645-3M-15	9293-2471	215	25.39	.06
648-3M-15	9293-2472	216	25.51	.06
654-3M-15	9293-2473	218	25.75	.06
657-3M-15	9293-2474	219	25.87	.06
663-3M-15	9293-2475	221	26.10	.06
669-3M-15	9293-0420	223	26.34	.05
684-3M-15	9293-2476	228	26.93	.07
687-3M-15	9293-2477	229	27.05	.07
696-3M-15	9293-2478	232	27.40	.05
711-3M-15	9293-0421	237	27.99	.05
735-3M-15	9293-2479	245	28.94	.07
738-3M-15	9293-2480	246	29.06	.07
753-3M-15	9293-0422	251	29.65	.06
795-3M-15	9293-0423	265	31.30	.06
822-3M-15	9293-2481	274	32.36	.08
837-3M-15	9293-2482	279	32.95	.08
843-3M-15	9293-0424	281	33.19	.06
873-3M-15	9293-2483	291	34.37	.09
882-3M-15	9293-0425	294	34.72	.10
891-3M-15	9293-2484	297	35.08	.10
900-3M-15	9293-2485	300	35.43	.10
915-3M-15	9293-2486	305	36.02	.10
945-3M-15	9293-0426	315	37.20	.10
951-3M-15	9293-2487	317	37.44	.10
981-3M-15	9293-2488	327	38.62	.10



PowerGrip® HTD® Belts

Product No. Series 9293 (continued)

3mm Pitch — 15mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1002-3M-15	9293-0427	334	39.45	.09
1026-3M-15	9293-2489	342	40.39	.11
1035-3M-15	9293-2490	345	40.75	.11
1062-3M-15	9293-0428	354	41.81	.11
1125-3M-15	9293-0429	375	44.29	.10
1155-3M-15	9293-2491	385	40.47	.12
1191-3M-15	9293-0430	397	46.89	.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1263-3M-15	9293-0431	421	49.72	.13
1500-3M-15	9293-2492	500	59.06	.14
1512-3M-15	9293-2493	504	59.53	.15
1587-3M-15	9293-2494	529	62.48	.17
1956-3M-15	9293-2495	652	77.01	.19
2004-3M-15	9293-2496	668	78.90	.19

5mm Pitch — 9mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
200-5M-09	9293-2600	40	7.87	.01
240-5M-09	9293-2601	48	9.45	.02
260-5M-09	9293-2602	52	10.24	.01
270-5M-09	9293-2603	54	10.63	.02
285-5M-09	9293-2604	57	11.22	.02
300-5M-09	9293-2605	60	11.81	.02
310-5M-09	9293-2606	62	12.20	.02
320-5M-09	9293-2607	64	12.60	.02
350-5M-09	9293-0500	70	13.78	.03
375-5M-09	9293-0501	75	14.76	.03
400-5M-09	9293-0502	80	15.75	.03
415-5M-09	9293-2608	83	16.34	.03
425-5M-09	9293-0503	85	16.73	.03
450-5M-09	9293-0504	90	17.72	.03
460-5M-09	9293-2609	92	18.11	.03
475-5M-09	9293-0505	95	18.70	.03
480-5M-09	9293-2610	96	18.90	.04
495-5M-09	9293-2611	99	19.49	.03
500-5M-09	9293-0506	100	19.69	.03
520-5M-09	9293-2612	104	20.47	.04
535-5M-09	9293-0507	107	21.06	.04
555-5M-09	9293-2613	111	21.85	.04
565-5M-09	9293-0508	113	22.24	.05
580-5M-09	9293-2614	116	22.83	.04
585-5M-09	9293-2615	117	23.03	.04
600-5M-09	9293-0509	120	23.62	.04
615-5M-09	9293-2616	123	24.21	.05
635-5M-09	9293-0510	127	25.00	.05
655-5M-09	9293-2617	131	25.79	.05
665-5M-09	9293-2618	133	26.18	.04
670-5M-09	9293-0511	134	26.38	.05
680-5M-09	9293-2619	136	26.77	.05
685-5M-09	9293-2620	137	26.97	.05
695-5M-09	9293-2621	139	27.36	.05
710-5M-09	9293-0512	142	27.95	.05
740-5M-09	9293-0513	148	29.13	.05
745-5M-09	9293-2622	149	29.33	.07
765-5M-09	9293-2623	153	30.12	.06
790-5M-09	9293-2624	158	31.10	.06

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
800-5M-09	9293-0514	160	31.50	.06
830-5M-09	9293-2625	166	32.68	.06
835-5M-09	9293-2626	167	32.87	.06
850-5M-09	9293-0515	170	33.46	.07
870-5M-09	9293-2627	174	34.25	.06
890-5M-09	9293-0516	178	35.04	.07
925-5M-09	9293-2628	185	36.42	.07
950-5M-09	9293-0517	190	37.40	.07
975-5M-09	9293-2629	195	38.39	.07
985-5M-09	9293-2630	197	38.78	.07
1000-5M-09	9293-0518	200	39.37	.08
1050-5M-09	9293-0519	210	41.34	.08
1115-5M-09	9293-2631	223	43.90	.08
1125-5M-09	9293-0520	225	44.29	.09
1195-5M-09	9293-0521	239	47.05	.09
1250-5M-09	9293-2632	250	49.21	.09
1270-5M-09	9293-0522	254	50.00	.12
1295-5M-09	9293-2633	259	50.98	.12
1375-5M-09	9293-2634	275	54.13	.11
1420-5M-09	9293-0523	284	55.91	.11
1575-5M-09	9293-2635	315	62.01	.13
1595-5M-09	9293-0524	319	62.80	.11
1635-5M-09	9293-2636	327	64.37	.13
1690-5M-09	9293-0525	338	66.54	.13
1720-5M-09	9293-2637	344	67.72	.16
1790-5M-09	9293-0526	358	70.47	.15
1800-5M-09	9293-2638	360	70.87	.17
1895-5M-09	9293-0527	379	74.61	.15
1945-5M-09	9293-2639	389	76.57	.18
1980-5M-09	9293-2640	396	77.95	.15
2000-5M-09	9293-0528	400	78.74	.15
2110-5M-09	9293-2641	422	83.07	.20
2250-5M-09	9293-0529	450	88.58	.15
2525-5M-09	9293-0530	505	99.40	.20
2760-5M-09	9293-2642	552	108.66	.28
3120-5M-09	9293-2643	624	122.83	.15
3170-5M-09	9293-2644	634	124.80	.34
3430-5M-09	9293-2645	686	135.04	.36
3800-5M-09	9293-2646	760	149.61	.30

5mm Pitch — 15mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
200-5M-15	9293-2700	40	7.87	.02
240-5M-15	9293-2701	48	9.45	.03
260-5M-15	9293-2702	52	10.24	.03
270-5M-15	9293-2703	54	10.63	.03
285-5M-15	9293-2704	57	11.22	.03

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
300-5M-15	9293-2705	60	11.81	.03
310-5M-15	9293-2706	62	12.20	.04
320-5M-15	9293-2707	64	12.60	.04
350-5M-15	9293-0531	70	13.78	.04
375-5M-15	9293-0532	75	14.76	.05



Product No. Series 9293 (continued)

5mm Pitch — 15mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
400-5M-15	9293-0533	80	15.75	.05
415-5M-15	9293-2708	83	16.34	.05
425-5M-15	9293-0534	85	16.73	.04
450-5M-15	9293-0535	90	17.72	.06
460-5M-15	9293-2709	92	18.11	.06
475-5M-15	9293-0536	95	18.70	.06
480-5M-15	9293-2710	96	18.90	.06
495-5M-15	9293-2711	99	19.49	.06
500-5M-15	9293-0537	100	19.69	.05
520-5M-15	9293-2712	104	20.47	.07
535-5M-15	9293-0538	107	21.06	.05
555-5M-15	9293-2713	111	21.85	.05
565-5M-15	9293-0539	113	22.24	.07
580-5M-15	9293-2714	116	22.83	.07
585-5M-15	9293-2715	117	23.03	.08
600-5M-15	9293-0540	120	23.62	.07
615-5M-15	9293-2716	123	24.21	.07
635-5M-15	9293-0541	127	25.00	.07
655-5M-15	9293-2717	131	25.79	.08
665-5M-15	9293-2718	133	26.18	.07
670-5M-15	9293-0542	134	26.38	.07
680-5M-15	9293-2719	136	26.77	.09
685-5M-15	9293-2720	137	26.97	.10
695-5M-15	9293-2721	139	27.36	.08
710-5M-15	9293-0543	142	27.95	.10
740-5M-15	9293-0544	148	29.13	.15
745-5M-15	9293-2722	149	29.33	.09
765-5M-15	9293-2723	153	30.12	.07
790-5M-15	9293-2724	158	31.10	.10
800-5M-15	9293-0545	160	31.50	.10
830-5M-15	9293-2725	166	32.68	.10
835-5M-15	9293-2726	167	32.87	.10
850-5M-15	9293-0546	170	33.46	.10
870-5M-15	9293-2727	174	34.25	.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
890-5M-15	9293-0547	178	35.04	.10
925-5M-15	9293-2728	185	36.42	.10
950-5M-15	9293-0548	190	37.40	.10
975-5M-15	9293-2729	195	38.39	.10
985-5M-15	9293-2730	197	38.78	.10
1000-5M-15	9293-0549	200	39.37	.12
1050-5M-15	9293-0550	210	41.34	.12
1115-5M-15	9293-2731	223	43.90	.16
1125-5M-15	9293-0551	225	44.29	.12
1195-5M-15	9293-0552	239	47.05	.15
1250-5M-15	9293-2732	250	49.21	.30
1270-5M-15	9293-0553	254	50.00	.15
1295-5M-15	9293-2733	259	50.98	.10
1375-5M-15	9293-2734	275	54.13	.15
1420-5M-15	9293-0554	284	55.91	.15
1575-5M-15	9293-2735	315	62.01	.15
1595-5M-15	9293-0555	319	62.80	.15
1635-5M-15	9293-2736	327	64.37	.25
1690-5M-15	9293-0556	338	66.54	.20
1720-5M-15	9293-2737	344	67.72	.27
1790-5M-15	9293-0557	358	70.47	.20
1800-5M-15	9293-2738	360	70.87	.20
1895-5M-15	9293-0558	379	74.61	.20
1945-5M-15	9293-2739	389	76.57	.30
1980-5M-15	9293-2740	396	77.95	.25
2000-5M-15	9293-0559	400	78.74	.25
2110-5M-15	9293-2741	422	83.07	.30
2250-5M-15	9293-0560	450	88.58	.30
2525-5M-15	9293-0561	505	99.40	.30
2760-5M-15	9293-2742	552	108.66	.35
3120-5M-15	9293-2743	624	122.83	.40
3170-5M-15	9293-2744	634	124.80	.56
3430-5M-15	9293-2745	686	135.04	.40
3800-5M-15	9293-2746	760	149.61	.50

5mm Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
200-5M-25	9293-2800	40	7.87	.04
240-5M-25	9293-2801	48	9.45	.05
260-5M-25	9293-2802	52	10.24	.05
270-5M-25	9293-2803	54	10.63	.06
285-5M-25	9293-2804	57	11.22	.06
300-5M-25	9293-2805	60	11.81	.06
310-5M-25	9293-2806	62	12.20	.47
320-5M-25	9293-2807	64	12.60	.05
350-5M-25	9293-0562	70	13.78	.07
375-5M-25	9293-0563	75	14.76	.07
400-5M-25	9293-0564	80	15.75	.07
415-5M-25	9293-2808	83	16.34	.10
425-5M-25	9293-0565	85	16.73	.07
450-5M-25	9293-0566	90	17.72	.20
460-5M-25	9293-2809	92	18.11	.10
475-5M-25	9293-0567	95	18.70	.10
480-5M-25	9293-2810	96	18.90	.10
495-5M-25	9293-2811	99	19.49	.10
500-5M-25	9293-0568	100	19.69	.10
520-5M-25	9293-2812	104	20.47	.10
535-5M-25	9293-0569	107	21.06	.10
555-5M-25	9293-2813	111	21.85	.10
565-5M-25	9293-0570	113	22.24	.15

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
580-5M-25	9293-2814	116	22.83	.10
585-5M-25	9293-2815	117	23.03	.10
600-5M-25	9293-0571	120	23.62	.15
615-5M-25	9293-2816	123	24.21	.10
635-5M-25	9293-0572	127	25.00	.15
655-5M-25	9293-2817	131	25.79	.15
665-5M-25	9293-2818	133	26.18	.15
670-5M-25	9293-0573	134	26.38	.10
680-5M-25	9293-2819	136	26.77	.10
685-5M-25	9293-2820	137	26.97	.17
695-5M-25	9293-2821	139	27.36	.15
710-5M-25	9293-0574	142	27.95	.15
740-5M-25	9293-0575	148	29.13	.10
745-5M-25	9293-2822	149	29.33	.15
765-5M-25	9293-2823	153	30.12	.15
790-5M-25	9293-2824	158	31.10	.15
800-5M-25	9293-0576	160	31.50	.20
830-5M-25	9293-2825	166	32.68	.15
835-5M-25	9293-2826	167	32.87	.15
850-5M-25	9293-0577	170	33.46	.15
870-5M-25	9293-2827	174	34.25	.20
890-5M-25	9293-0578	178	35.04	.20
925-5M-25	9293-2828	185	36.42	.15



PowerGrip® HTD® Belts

Product No. Series 9293 (continued)

5mm Pitch — 25mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
950-5M-25	9293-0579	190	37.40	.20
975-5M-25	9293-2829	195	38.39	.24
985-5M-25	9293-2830	197	38.78	.20
1000-5M-25	9293-0580	200	39.37	.15
1050-5M-25	9293-0581	210	41.34	.25
1115-5M-25	9293-2831	223	43.90	.25
1125-5M-25	9293-0582	225	44.29	.25
1195-5M-25	9293-0583	239	47.05	.25
1250-5M-25	9293-2832	250	49.21	.25
1270-5M-25	9293-0584	254	50.00	.25
1295-5M-25	9293-2833	259	50.98	.30
1375-5M-25	9293-2834	275	54.13	.30
1420-5M-25	9293-0585	284	55.91	.30
1575-5M-25	9293-2835	315	62.01	.35
1595-5M-25	9293-0586	319	62.84	.35
1635-5M-25	9293-2836	327	64.37	.50

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1690-5M-25	9293-0587	338	66.54	.35
1720-5M-25	9293-2837	344	67.72	.45
1790-5M-25	9293-0588	358	70.47	.40
1800-5M-25	9293-2838	360	70.87	.40
1895-5M-25	9293-0589	379	74.61	.40
1945-5M-25	9293-2839	389	76.57	.40
1980-5M-25	9293-2840	396	77.95	.45
2000-5M-25	9293-0590	400	78.74	.45
2110-5M-25	9293-2841	422	83.07	.45
2250-5M-25	9293-0591	450	88.58	.50
2525-5M-25	9293-0592	505	99.40	.55
2760-5M-25	9293-2842	552	108.66	.60
3120-5M-25	9293-2843	624	122.83	.74
3170-5M-25	9293-2844	634	124.80	.70
3430-5M-25	9293-2845	686	135.04	.92
3800-5M-25	9293-2846	760	149.61	1.08

20mm Pitch — 115mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2000-20M-115	9293-0700	100	78.74	8.50
2500-20M-115	9293-0702	125	98.43	9.40
3400-20M-115	9293-0703	170	133.86	12.30
3800-20M-115	9293-0704	190	149.61	13.70
4200-20M-115	9293-0705	210	165.35	15.00
4600-20M-115	9293-0706	230	181.10	16.30
5000-20M-115	9293-0707	250	196.85	21.89
5200-20M-115	9293-0708	260	204.72	22.76

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5400-20M-115	9293-0709	270	212.60	24.00
5600-20M-115	9293-0710	280	220.47	19.75
5800-20M-115	9293-0711	290	228.35	21.30
6000-20M-115	9293-0775	300	236.22	26.28
6200-20M-115	9293-0712	310	244.09	21.45
6400-20M-115	9293-0713	320	251.97	22.25
6600-20M-115	9293-0714	330	259.84	29.25

20mm Pitch — 170mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2000-20M-170	9293-0715	100	78.74	13.10
2500-20M-170	9293-0717	125	98.43	14.65
3400-20M-170	9293-0718	170	133.86	19.00
3800-20M-170	9293-0719	190	149.61	21.00
4200-20M-170	9293-0720	210	165.35	27.16
4600-20M-170	9293-0721	230	181.10	24.55
5000-20M-170	9293-0722	250	196.85	25.55
5200-20M-170	9293-0723	260	204.72	25.27

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5400-20M-170	9293-0724	270	212.60	34.95
5600-20M-170	9293-0725	280	220.47	28.70
5800-20M-170	9293-0726	290	228.35	37.54
6000-20M-170	9293-0776	300	236.22	31.95
6200-20M-170	9293-0727	310	244.09	40.14
6400-20M-170	9293-0728	320	251.97	41.44
6600-20M-170	9293-0729	330	259.84	42.73

20mm Pitch — 230mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2000-20M-230	9293-0730	100	78.74	17.44
2500-20M-230	9293-0732	125	98.43	21.83
3400-20M-230	9293-0733	170	133.86	25.50
3800-20M-230	9293-0734	190	149.61	33.24
4200-20M-230	9293-0735	210	165.35	30.25
4600-20M-230	9293-0736	230	181.10	40.26
5000-20M-230	9293-0737	250	196.85	43.77
5200-20M-230	9293-0738	260	204.72	36.40

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5400-20M-230	9293-0739	270	212.60	47.28
5600-20M-230	9293-0740	280	220.47	49.04
5800-20M-230	9293-0741	290	228.35	50.79
6000-20M-230	9293-0777	300	236.22	52.55
6200-20M-230	9293-0742	310	244.09	54.31
6400-20M-230	9293-0743	320	251.97	56.06
6600-20M-230	9293-0744	330	259.84	57.82



Product No. Series 9293 (continued)

20mm Pitch — 290mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2000-20M-290	9293-0745	100	78.74	21.99
2500-20M-290	9293-0747	125	98.43	27.52
3400-20M-290	9293-0748	170	133.86	37.48
3800-20M-290	9293-0749	190	149.61	41.91
4200-20M-290	9293-0750	210	165.35	46.34
4600-20M-290	9293-0751	230	181.10	50.76
5000-20M-290	9293-0752	250	196.85	55.19
5200-20M-290	9293-0753	260	204.72	57.40

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5400-20M-290	9293-0754	270	212.60	59.62
5600-20M-290	9293-0755	280	220.47	61.83
5800-20M-290	9293-0756	290	228.35	64.05
6000-20M-290	9293-0778	300	236.22	66.26
6200-20M-290	9293-0757	310	244.09	68.47
6400-20M-290	9293-0758	320	251.97	70.69
6600-20M-290	9293-0759	330	259.84	72.90

20mm Pitch — 340mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
2000-20M-340	9293-0760	100	78.74	25.78
2500-20M-340	9293-0762	125	98.43	32.27
3400-20M-340	9293-0763	170	133.86	43.94
3800-20M-340	9293-0764	190	149.61	49.13
4200-20M-340	9293-0765	210	165.35	54.33
4600-20M-340	9293-0766	230	181.10	59.52
5000-20M-340	9293-0767	250	196.85	64.71
5200-20M-340	9293-0768	260	204.72	67.30

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
5400-20M-340	9293-0769	270	212.60	69.90
5600-20M-340	9293-0770	280	220.47	72.49
5800-20M-340	9293-0771	290	228.35	75.09
6000-20M-340	9293-0779	300	236.22	77.68
6200-20M-340	9293-0772	310	244.09	80.28
6400-20M-340	9293-0773	320	251.97	82.87
6600-20M-340	9293-0774	330	259.84	85.47

PowerGrip® Timing Belts

The trapezoidal tooth profile this belt well suited for use in positioning applications.

Markets/Applications

PowerGrip Timing belts are suitable for office machines, machine tools, postage equipment, sewing machines, vending machines, agriculture, outdoor power equipment, food processing, HVAC, oil fields, wood, paper, sand and gravel applications.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Eliminates lubrication and re-tensioning to reduce maintenance and labor required on drives.



Recommended Pulleys—PowerGrip Timing Pulleys

Notes

Gates PowerGrip Timing belts are measured by:

Length — The length of a PowerGrip Timing Belts is shown in the first part of the belt designation. The first number is the pitch length in tenths of an inch. A 300L075 has a 30.0" pitch length.

Pitch — The pitch is the distance from center to center of the teeth (in inches). It is shown in the second part of the belt designation by a letter or letters. Part number 300L075 has a .375" pitch. The letters correspond to pitches as follows:

MXL = Mini Extra Light = 0.080" pitch;

XL = Extra Light = 0.200" pitch;

L = Light = 0.375" pitch;

H = Heavy = 0.500" pitch;

XH = Extra Heavy = 0.875" pitch;

XXH = Double Extra Heavy = 1.250" pitch.

Width — The width is shown in the last part of the belt designation. Part number 300L075 is .75" wide.

Product No. Series 9257

2/25" Pitch (.080"/MXL) — 1/8" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
32MXL012	9257-0129	40	3.20	.01
34MXL012	9257-0130	42	3.36	.01
36MXL012	9257-0119	45	3.60	.01
38MXL012	9257-0131	47	3.76	.01
40MXL012	9257-0120	50	4.00	.01
43MXL012	9257-0132	54	4.32	.01
44MXL012	9257-0121	55	4.40	.01
45MXL012	9257-0133	56	4.48	.01
47MXL012	9257-0134	59	4.72	.01
48MXL012	9257-0122	60	4.80	.01
51MXL012	9257-0135	64	5.12	.01
52MXL012	9257-0136	65	5.20	.01
53MXL012	9257-0137	67	5.36	.01
54MXL012	9257-0138	68	5.44	.01
56MXL012	9257-0104	70	5.60	.01
57MXL012	9257-0139	71	5.68	.01
58MXL012	9257-0140	72	5.76	.01
59MXL012	9257-0141	74	5.92	.01
61MXL012	9257-0142	76	6.08	.01
62MXL012	9257-0143	77	6.16	.01
63MXL012	9257-0144	79	6.32	.01
64MXL012	9257-0105	80	6.40	.01
66MXL012	9257-0145	83	6.64	.01
68MXL012	9257-0123	85	6.80	.01
69MXL012	9257-0146	87	6.96	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
70MXL012	9257-0147	88	7.04	.01
72MXL012	9257-0106	90	7.20	.01
74MXL012	9257-0148	92	7.36	.01
75MXL012	9257-0149	94	7.52	.01
76MXL012	9257-0124	95	7.60	.01
80MXL012	9257-0107	100	8.00	.01
81MXL012	9257-0150	102	8.16	.01
82MXL012	9257-0151	103	8.24	.01
84MXL012	9257-0152	106	8.48	.01
85MXL012	9257-0153	107	8.56	.01
86MXL012	9257-0154	108	8.64	.01
87MXL012	9257-0155	109	8.72	.01
88MXL012	9257-0108	110	8.80	.01
90MXL012	9257-0156	112	8.96	.01
91MXL012	9257-0157	114	9.12	.01
96MXL012	9257-0100	120	9.60	.01
98MXL012	9257-0158	123	9.84	.01
100MXL012	9257-0159	125	10.00	.01
101MXL012	9257-0160	126	10.08	.01
104MXL012	9257-0109	130	10.40	.01
106MXL012	9257-0161	132	10.56	.01
112MXL012	9257-0110	140	11.20	.01
115MXL012	9257-0162	144	11.52	.01
120MXL012	9257-0111	150	12.00	.01
122MXL012	9257-0163	153	12.24	.01



Product No. Series 9257 (continued)

2/25" Pitch (.080"/MXL) — 1/8" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
124MXL012	9257-0164	155	12.40	.01
132MXL012	9257-0125	165	13.20	.01
133MXL012	9257-0165	166	13.28	.01
136MXL012	9257-0166	170	13.60	.01
140MXL012	9257-0112	175	14.00	.01
147MXL012	9257-0167	184	14.72	.01
152MXL012	9257-0126	190	15.20	.01
156MXL012	9257-0168	195	15.60	.01
160MXL012	9257-0113	200	16.00	.01
166MXL012	9257-0169	208	16.64	.01
168MXL012	9257-0127	210	16.80	.01
170MXL012	9257-0170	212	16.96	.01
177MXL012	9257-0171	221	17.68	.01
178MXL012	9257-0172	222	17.76	.01
180MXL012	9257-0114	225	18.00	.01
184MXL012	9257-0173	230	18.40	.01
196MXL012	9257-0174	245	19.60	.01
198MXL012	9257-0175	248	19.84	.01
200MXL012	9257-0115	250	20.00	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
208MXL012	9257-0116	260	20.80	.01
212MXL012	9257-0176	265	21.20	.01
224MXL012	9257-0177	280	22.40	.01
236MXL012	9257-0128	295	23.60	.01
240MXL012	9257-0117	300	24.00	.01
252MXL012	9257-0178	315	25.20	.01
278MXL012	9257-0179	347	27.76	.01
297MXL012	9257-0180	371	29.68	.01
298MXL012	9257-0181	372	29.76	.01
320MXL012	9257-0118	400	32.00	.00
330MXL012	9257-0182	412	32.96	.01
339MXL012	9257-0183	424	33.92	.01
347MXL012	9257-0184	434	34.72	.01
348MXL012	9257-0185	435	34.80	.01
390MXL012	9257-0186	487	38.96	.01
398MXL012	9257-0187	498	39.84	.01
480MXL012	9257-0188	600	48.00	.01
490MXL012	9257-0189	612	48.96	.01
518MXL012	9257-0190	648	51.84	.01

2/25" Pitch (.080"/MXL) — 3/16" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
32MXL019	9257-0229	40	3.20	.01
34MXL019	9257-0230	42	3.36	.01
36MXL019	9257-0219	45	3.60	.01
38MXL019	9257-0231	47	3.76	.01
40MXL019	9257-0220	50	4.00	.01
43MXL019	9257-0232	54	4.32	.01
44MXL019	9257-0221	55	4.40	.01
45MXL019	9257-0233	56	4.48	.01
47MXL019	9257-0234	59	4.72	.01
48MXL019	9257-0222	60	4.80	.01
51MXL019	9257-0235	64	5.12	.01
52MXL019	9257-0236	65	5.20	.01
53MXL019	9257-0237	67	5.36	.01
54MXL019	9257-0238	68	5.44	.01
56MXL019	9257-0204	70	5.60	.01
57MXL019	9257-0239	71	5.68	.01
58MXL019	9257-0240	72	5.76	.01
59MXL019	9257-0241	74	5.92	.01
61MXL019	9257-0242	76	6.08	.01
62MXL019	9257-0243	77	6.16	.01
63MXL019	9257-0244	79	6.32	.01
64MXL019	9257-0205	80	6.40	.01
66MXL019	9257-0245	83	6.64	.01
68MXL019	9257-0223	85	6.80	.01
69MXL019	9257-0246	87	6.96	.01
70MXL019	9257-0247	88	7.04	.01
72MXL019	9257-0206	90	7.20	.01
74MXL019	9257-0248	92	7.36	.01
75MXL019	9257-0249	94	7.52	.01
76MXL019	9257-0224	95	7.60	.01
80MXL019	9257-0207	100	8.00	.01
81MXL019	9257-0250	102	8.16	.00
82MXL019	9257-0251	103	8.24	.01
84MXL019	9257-0252	106	8.48	.01
85MXL019	9257-0253	107	8.56	.00
86MXL019	9257-0254	108	8.64	.01
87MXL019	9257-0255	109	8.72	.01
88MXL019	9257-0208	110	8.80	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
90MXL019	9257-0256	112	8.96	.01
91MXL019	9257-0257	114	9.12	.01
96MXL019	9257-0200	120	9.60	.01
98MXL019	9257-0258	123	9.84	.01
100MXL019	9257-0259	125	10.00	.01
101MXL019	9257-0260	126	10.08	.01
104MXL019	9257-0209	130	10.40	.01
106MXL019	9257-0261	132	10.56	.01
112MXL019	9257-0210	140	11.20	.01
115MXL019	9257-0262	144	11.52	.01
120MXL019	9257-0211	150	12.00	.01
122MXL019	9257-0263	153	12.24	.01
124MXL019	9257-0264	155	12.40	.01
132MXL019	9257-0225	165	13.20	.01
133MXL019	9257-0265	166	13.28	.01
136MXL019	9257-0266	170	13.60	.01
140MXL019	9257-0212	175	14.00	.01
147MXL019	9257-0267	184	14.72	.01
152MXL019	9257-0226	190	15.20	.01
156MXL019	9257-0268	195	15.60	.01
160MXL019	9257-0213	200	16.00	.00
166MXL019	9257-0269	208	16.64	.01
168MXL019	9257-0227	210	16.80	.01
170MXL019	9257-0270	212	16.96	.01
177MXL019	9257-0271	221	17.68	.01
178MXL019	9257-0272	222	17.76	.01
180MXL019	9257-0214	225	18.00	.01
184MXL019	9257-0273	230	18.40	.01
196MXL019	9257-0274	245	19.60	.01
198MXL019	9257-0275	248	19.84	.01
200MXL019	9257-0215	250	20.00	.01
208MXL019	9257-0216	260	20.80	.01
212MXL019	9257-0276	265	21.20	.01
224MXL019	9257-0277	280	22.40	.01
236MXL019	9257-0228	295	23.60	.01
240MXL019	9257-0217	300	24.00	.01
252MXL019	9257-0278	315	25.20	.01
278MXL019	9257-0279	347	27.76	.01



PowerGrip® Timing Belts

Product No. Series 9257 (continued)

2/25" Pitch (.080"/MXL) — 3/16" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
297MXL019	9257-0280	371	29.68	.01
298MXL019	9257-0281	372	29.76	.01
320MXL019	9257-0218	400	32.00	.01
330MXL019	9257-0282	412	32.96	.01
339MXL019	9257-0283	424	33.92	.02
347MXL019	9257-0284	434	34.72	.02

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
348MXL019	9257-0285	435	34.80	.02
390MXL019	9257-0286	487	38.96	.02
398MXL019	9257-0287	498	39.84	.02
480MXL019	9257-0288	600	48.00	.02
490MXL019	9257-0289	612	48.96	.02
518MXL019	9257-0290	648	51.84	.02

2/25" Pitch (.080"/MXL) — 1/4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
32MXL025	9257-0329	40	3.20	.01
34MXL025	9257-0330	42	3.36	.01
36MXL025	9257-0319	45	3.60	.01
38MXL025	9257-0331	47	3.76	.01
40MXL025	9257-0320	50	4.00	.01
43MXL025	9257-0332	54	4.32	.01
44MXL025	9257-0321	55	4.40	.00
45MXL025	9257-0333	56	4.48	.01
47MXL025	9257-0334	59	4.72	.01
48MXL025	9257-0322	60	4.80	.01
51MXL025	9257-0335	64	5.12	.01
52MXL025	9257-0336	65	5.20	.01
53MXL025	9257-0337	67	5.36	.01
54MXL025	9257-0338	68	5.44	.01
56MXL025	9257-0304	70	5.60	.01
57MXL025	9257-0339	71	5.68	.01
58MXL025	9257-0340	72	5.76	.01
59MXL025	9257-0341	74	5.92	.01
61MXL025	9257-0342	76	6.08	.01
62MXL025	9257-0343	77	6.16	.01
63MXL025	9257-0344	79	6.32	.01
64MXL025	9257-0305	80	6.40	.01
66MXL025	9257-0345	83	6.64	.01
68MXL025	9257-0323	85	6.80	.01
69MXL025	9257-0346	87	6.96	.01
70MXL025	9257-0347	88	7.04	.01
72MXL025	9257-0306	90	7.20	.01
74MXL025	9257-0348	92	7.36	.01
75MXL025	9257-0349	94	7.52	.01
76MXL025	9257-0324	95	7.60	.01
80MXL025	9257-0307	100	8.00	.01
81MXL025	9257-0350	102	8.16	.01
82MXL025	9257-0351	103	8.24	.01
84MXL025	9257-0352	106	8.48	.01
85MXL025	9257-0353	107	8.56	.01
86MXL025	9257-0354	108	8.64	.01
87MXL025	9257-0355	109	8.72	.01
88MXL025	9257-0308	110	8.80	.01
90MXL025	9257-0356	112	8.96	.01
91MXL025	9257-0357	114	9.12	.01
96MXL025	9257-0300	120	9.60	.01
98MXL025	9257-0358	123	9.84	.01
100MXL025	9257-0359	125	10.00	.01
101MXL025	9257-0360	126	10.08	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
104MXL025	9257-0309	130	10.40	.01
106MXL025	9257-0361	132	10.56	.01
112MXL025	9257-0310	140	11.20	.01
115MXL025	9257-0362	144	11.52	.01
120MXL025	9257-0311	150	12.00	.01
122MXL025	9257-0363	153	12.24	.01
124MXL025	9257-0364	155	12.40	.01
132MXL025	9257-0325	165	13.20	.01
133MXL025	9257-0365	166	13.28	.01
136MXL025	9257-0366	170	13.60	.01
140MXL025	9257-0312	175	14.00	.00
147MXL025	9257-0367	184	14.72	.01
152MXL025	9257-0326	190	15.20	.00
156MXL025	9257-0368	195	15.60	.01
160MXL025	9257-0313	200	16.00	.00
166MXL025	9257-0369	208	16.64	.01
168MXL025	9257-0327	210	16.80	.00
170MXL025	9257-0370	212	16.96	.01
177MXL025	9257-0371	221	17.68	.01
178MXL025	9257-0372	222	17.76	.01
180MXL025	9257-0314	225	18.00	.01
184MXL025	9257-0373	230	18.40	.01
196MXL025	9257-0374	245	19.60	.01
198MXL025	9257-0375	248	19.84	.01
200MXL025	9257-0315	250	20.00	.00
208MXL025	9257-0316	260	20.80	.01
212MXL025	9257-0376	265	21.20	.01
224MXL025	9257-0377	280	22.40	.01
236MXL025	9257-0328	295	23.60	.02
240MXL025	9257-0317	300	24.00	.01
252MXL025	9257-0378	315	25.20	.01
278MXL025	9257-0379	347	27.76	.01
297MXL025	9257-0380	371	29.68	.01
298MXL025	9257-0381	372	29.76	.01
320MXL025	9257-0318	400	32.00	.02
330MXL025	9257-0382	412	32.96	.02
339MXL025	9257-0383	424	33.92	.02
347MXL025	9257-0384	434	34.72	.02
348MXL025	9257-0385	435	34.80	.01
390MXL025	9257-0386	487	38.96	.02
398MXL025	9257-0387	498	39.84	.02
480MXL025	9257-0388	600	48.00	.02
490MXL025	9257-0389	612	48.96	.02
518MXL025	9257-0390	648	51.84	.02



Product No. Series 9257 (continued)

1/5" Pitch (.200"/XL) — 1/4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)	Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
42XL025	9257-1141	21	4.20	.01	178XL025	9257-1190	89	17.80	.02
50XL025	9257-1121	25	5.00	.01	180XL025	9257-1112	90	18.00	.01
54XL025	9257-1142	27	5.40	.01	182XL025	9257-1191	91	18.20	.02
56XL025	9257-1143	28	5.60	.01	184XL025	9257-1192	92	18.40	.02
58XL025	9257-1144	29	5.80	.01	186XL025	9257-1193	93	18.60	.02
60XL025	9257-1100	30	6.00	.01	188XL025	9257-1194	94	18.80	.01
62XL025	9257-1145	31	6.20	.01	190XL025	9257-1113	95	19.00	.01
64XL025	9257-1146	32	6.40	.01	192XL025	9257-1195	96	19.20	.01
66XL025	9257-1147	33	6.60	.01	194XL025	9257-1196	97	19.40	.02
68XL025	9257-1148	34	6.80	.01	200XL025	9257-1114	100	20.00	.01
70XL025	9257-1101	35	7.00	.01	202XL025	9257-1197	101	20.20	.01
72XL025	9257-1149	36	7.20	.01	204XL025	9257-1198	102	20.40	.01
74XL025	9257-1150	37	7.40	.01	206XL025	9257-1199	103	20.60	.01
76XL025	9257-1151	38	7.60	.01	210XL025	9257-1115	105	21.00	.01
78XL025	9257-1152	39	7.80	.01	212XL025	9257-8100	106	21.20	.02
80XL025	9257-1102	40	8.00	.01	214XL025	9257-8101	107	21.40	.02
82XL025	9257-1153	41	8.20	.01	218XL025	9257-8102	109	21.80	.02
84XL025	9257-1154	42	8.40	.01	220XL025	9257-1116	110	22.00	.01
86XL025	9257-1155	43	8.60	.01	222XL025	9257-8103	111	22.20	.02
88XL025	9257-1156	44	8.80	.01	226XL025	9257-8104	113	22.60	.01
90XL025	9257-1103	45	9.00	.01	228XL025	9257-8105	114	22.80	.01
92XL025	9257-1157	46	9.20	.01	230XL025	9257-1117	115	23.00	.01
94XL025	9257-1158	47	9.40	.01	232XL025	9257-8106	116	23.20	.01
96XL025	9257-1159	48	9.60	.01	234XL025	9257-8107	117	23.40	.02
98XL025	9257-1160	49	9.80	.01	236XL025	9257-8108	118	23.60	.02
100XL025	9257-1104	50	10.00	.01	240XL025	9257-1118	120	24.00	.02
102XL025	9257-1161	51	10.20	.01	244XL025	9257-8109	122	24.40	.01
106XL025	9257-1162	53	10.60	.01	246XL025	9257-8110	123	24.60	.02
108XL025	9257-1163	54	10.80	.01	250XL025	9257-1119	125	25.00	.02
110XL025	9257-1105	55	11.00	.01	254XL025	9257-8111	127	25.40	.01
112XL025	9257-1164	56	11.20	.01	258XL025	9257-8112	129	25.80	.02
114XL025	9257-1165	57	11.40	.01	260XL025	9257-1120	130	26.00	.20
116XL025	9257-1166	58	11.60	.01	262XL025	9257-8113	131	26.20	.02
120XL025	9257-1106	60	12.00	.01	264XL025	9257-8114	132	26.40	.01
122XL025	9257-1167	61	12.20	.01	266XL025	9257-8115	133	26.60	.02
124XL025	9257-1168	62	12.40	.01	268XL025	9257-8116	134	26.80	.02
126XL025	9257-1169	63	12.60	.01	274XL025	9257-8117	137	27.40	.02
128XL025	9257-1170	64	12.80	.01	280XL025	9257-1122	140	28.00	.02
130XL025	9257-1107	65	13.00	.01	286XL025	9257-8118	143	28.60	.03
132XL025	9257-1171	66	13.20	.01	290XL025	9257-1123	145	29.00	.02
134XL025	9257-1172	67	13.40	.01	296XL025	9257-8119	148	29.60	.01
136XL025	9257-1173	68	13.60	.01	300XL025	9257-1124	150	30.00	.02
138XL025	9257-1174	69	13.80	.01	306XL025	9257-8120	153	30.60	.03
140XL025	9257-1108	70	14.00	.01	310XL025	9257-1125	155	31.00	.02
142XL025	9257-1175	71	14.20	.01	316XL025	9257-8121	158	31.60	.03
144XL025	9257-1176	72	14.40	.01	320XL025	9257-8122	160	32.00	.02
146XL025	9257-1177	73	14.60	.01	322XL025	9257-8123	161	32.20	.03
148XL025	9257-1178	74	14.80	.01	330XL025	9257-1126	165	33.00	.02
150XL025	9257-1109	75	15.00	.01	338XL025	9257-8124	169	33.80	.03
152XL025	9257-1179	76	15.20	.01	340XL025	9257-1127	170	34.00	.02
154XL025	9257-1180	77	15.40	.01	344XL025	9257-8125	172	34.40	.03
156XL025	9257-1181	78	15.60	.01	348XL025	9257-8126	174	34.80	.04
158XL025	9257-1182	79	15.80	.01	350XL025	9257-1128	175	35.00	.03
160XL025	9257-1110	80	16.00	.01	362XL025	9257-8127	181	36.20	.01
162XL025	9257-1183	81	16.20	.01	370XL025	9257-1129	185	37.00	.03
164XL025	9257-1184	82	16.40	.01	380XL025	9257-1130	190	38.00	.02
166XL025	9257-1185	83	16.60	.01	384XL025	9257-8128	192	38.40	.04
168XL025	9257-1186	84	16.80	.01	390XL025	9257-1131	195	39.00	.03
170XL025	9257-1111	85	17.00	.01	400XL025	9257-1132	200	40.00	.03
172XL025	9257-1187	86	17.20	.02	412XL025	9257-8129	206	41.20	.01
174XL025	9257-1188	87	17.40	.02	420XL025	9257-1133	210	42.00	.03
176XL025	9257-1189	88	17.60	.01	424XL025	9257-8130	212	42.40	.05



PowerGrip® Timing Belts

Product No. Series 9257 (continued)

1/5" Pitch (.200"/XL) — 1/4" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
432XL025	9257-8131	216	43.20	.05
438XL025	9257-8132	219	43.80	.04
444XL025	9257-8133	222	44.40	.05
450XL025	9257-1134	225	45.00	.05
454XL025	9257-8134	227	45.40	.05
460XL025	9257-1135	230	46.00	.03
468XL025	9257-8135	234	46.80	.05
480XL025	9257-1136	240	48.00	.01
492XL025	9257-8136	246	49.20	.04
498XL025	9257-8137	249	49.80	.05
500XL025	9257-1137	250	50.00	.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
506XL025	9257-8138	253	50.60	.04
524XL025	9257-8139	262	52.40	.04
570XL025	9257-1138	285	57.00	.05
580XL025	9257-8140	290	58.00	.05
592XL025	9257-8141	296	59.20	.05
612XL025	9257-8142	306	61.20	.05
630XL025	9257-1139	315	63.00	.05
672XL025	9257-8143	336	67.20	.04
690XL025	9257-8144	345	69.00	.04
770XL025	9257-1140	385	77.00	.06
850XL025	9257-8145	425	85.00	.06

1/5" Pitch (.200"/XL) — 3/8" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
42XL037	9257-1341	21	4.20	.01
50XL037	9257-1321	25	5.00	.01
54XL037	9257-1342	27	5.40	.01
56XL037	9257-1343	28	5.60	.01
58XL037	9257-1344	29	5.80	.01
60XL037	9257-1300	30	6.00	.01
62XL037	9257-1345	31	6.20	.01
64XL037	9257-1346	32	6.40	.01
66XL037	9257-1347	33	6.60	.01
68XL037	9257-1348	34	6.80	.01
70XL037	9257-1301	35	7.00	.01
72XL037	9257-1349	36	7.20	.01
74XL037	9257-1350	37	7.40	.01
76XL037	9257-1351	38	7.60	.01
78XL037	9257-1352	39	7.80	.01
80XL037	9257-1302	40	8.00	.01
82XL037	9257-1353	41	8.20	.01
84XL037	9257-1354	42	8.40	.01
86XL037	9257-1355	43	8.60	.01
88XL037	9257-1356	44	8.80	.01
90XL037	9257-1303	45	9.00	.01
92XL037	9257-1357	46	9.20	.01
94XL037	9257-1358	47	9.40	.01
96XL037	9257-1359	48	9.60	.01
98XL037	9257-1360	49	9.80	.01
100XL037	9257-1304	50	10.00	.01
102XL037	9257-1361	51	10.20	.01
106XL037	9257-1362	53	10.60	.01
108XL037	9257-1363	54	10.80	.01
110XL037	9257-1305	55	11.00	.01
112XL037	9257-1364	56	11.20	.01
114XL037	9257-1365	57	11.40	.01
116XL037	9257-1366	58	11.60	.01
120XL037	9257-1306	60	12.00	.01
122XL037	9257-1367	61	12.20	.01
124XL037	9257-1368	62	12.40	.01
126XL037	9257-1369	63	12.60	.01
128XL037	9257-1370	64	12.80	.01
130XL037	9257-1307	65	13.00	.01
132XL037	9257-1371	66	13.20	.01
134XL037	9257-1372	67	13.40	.01
136XL037	9257-1373	68	13.60	.01
138XL037	9257-1374	69	13.80	.01
140XL037	9257-1308	70	14.00	.02
142XL037	9257-1375	71	14.20	.01
144XL037	9257-1376	72	14.40	.01

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
146XL037	9257-1377	73	14.60	.01
148XL037	9257-1378	74	14.80	.02
150XL037	9257-1309	75	15.00	.01
152XL037	9257-1379	76	15.20	.02
154XL037	9257-1380	77	15.40	.02
156XL037	9257-1381	78	15.60	.01
158XL037	9257-1382	79	15.80	.02
160XL037	9257-1310	80	16.00	.02
162XL037	9257-1383	81	16.20	.02
164XL037	9257-1384	82	16.40	.01
166XL037	9257-1385	83	16.60	.01
168XL037	9257-1386	84	16.80	.02
170XL037	9257-1311	85	17.00	.02
172XL037	9257-1387	86	17.20	.01
174XL037	9257-1388	87	17.40	.02
176XL037	9257-1389	88	17.60	.02
178XL037	9257-1390	89	17.80	.02
180XL037	9257-1312	90	18.00	.02
182XL037	9257-1391	91	18.20	.02
184XL037	9257-1392	92	18.40	.02
186XL037	9257-1393	93	18.60	.02
188XL037	9257-1394	94	18.80	.02
190XL037	9257-1313	95	19.00	.02
192XL037	9257-1395	96	19.20	.01
194XL037	9257-1396	97	19.40	.01
200XL037	9257-1314	100	20.00	.02
202XL037	9257-1397	101	20.20	.02
204XL037	9257-1398	102	20.40	.03
206XL037	9257-1399	103	20.60	.02
210XL037	9257-1315	105	21.00	.02
212XL037	9257-8300	106	21.20	.02
214XL037	9257-8301	107	21.40	.02
218XL037	9257-8302	109	21.80	.03
220XL037	9257-1316	110	22.00	.02
222XL037	9257-8303	111	22.20	.02
226XL037	9257-8304	113	22.60	.03
228XL037	9257-8305	114	22.80	.02
230XL037	9257-1317	115	23.00	.02
232XL037	9257-8306	116	23.20	.03
234XL037	9257-8307	117	23.40	.03
236XL037	9257-8308	118	23.60	.03
240XL037	9257-1318	120	24.00	.02
244XL037	9257-8309	122	24.40	.03
246XL037	9257-8310	123	24.60	.03
250XL037	9257-1319	125	25.00	.03
254XL037	9257-8311	127	25.40	.20



Product No. Series 9257 (continued)

1/5" Pitch (.200"/XL) — 3/8" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
258XL037	9257-8312	129	25.80	.20
260XL037	9257-1320	130	26.00	.03
262XL037	9257-8313	131	26.20	.20
264XL037	9257-8314	132	26.40	.20
266XL037	9257-8315	133	26.60	.20
268XL037	9257-8316	134	26.80	.03
274XL037	9257-8317	137	27.40	.03
280XL037	9257-1322	140	28.00	.03
286XL037	9257-8318	143	28.60	.03
290XL037	9257-1323	145	29.00	.03
296XL037	9257-8319	148	29.60	.03
300XL037	9257-1324	150	30.00	.03
306XL037	9257-8320	153	30.60	.25
310XL037	9257-1325	155	31.00	.03
316XL037	9257-8321	158	31.60	.03
320XL037	9257-8322	160	32.00	.04
322XL037	9257-8323	161	32.20	.04
330XL037	9257-1326	165	33.00	.04
338XL037	9257-8324	169	33.80	.25
340XL037	9257-1327	170	34.00	.04
344XL037	9257-8325	172	34.40	.05
348XL037	9257-8326	174	34.80	.04
350XL037	9257-1328	175	35.00	.03
362XL037	9257-8327	181	36.20	.04
370XL037	9257-1329	185	37.00	.05
380XL037	9257-1330	190	38.00	.04
384XL037	9257-8328	192	38.40	.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
390XL037	9257-1331	195	39.00	.05
400XL037	9257-1332	200	40.00	.03
412XL037	9257-8329	206	41.20	.05
420XL037	9257-1333	210	42.00	.05
424XL037	9257-8330	212	42.40	.05
432XL037	9257-8331	216	43.20	.05
438XL037	9257-8332	219	43.80	.05
444XL037	9257-8333	222	44.40	.05
450XL037	9257-1334	225	45.00	.04
454XL037	9257-8334	227	45.40	.06
460XL037	9257-1335	230	46.00	.05
468XL037	9257-8335	234	46.80	.06
480XL037	9257-1336	240	48.00	.06
492XL037	9257-8336	246	49.20	.06
498XL037	9257-8337	249	49.80	.06
500XL037	9257-1337	250	50.00	.05
506XL037	9257-8338	253	50.60	.08
524XL037	9257-8339	262	52.40	.06
570XL037	9257-1338	285	57.00	.05
580XL037	9257-8340	290	58.00	.07
592XL037	9257-8341	296	59.20	.06
612XL037	9257-8342	306	61.20	.08
630XL037	9257-1339	315	63.00	.10
672XL037	9257-8343	336	67.20	.10
690XL037	9257-8344	345	69.00	.10
770XL037	9257-1340	385	77.00	.10
850XL037	9257-8345	425	85.00	.09

3/8" Pitch (.375"/L) — 1/2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
124L050	9257-2100	33	12.38	.02
135L050	9257-2120	36	13.50	.03
150L050	9257-2101	40	15.00	.03
154L050	9257-2127	41	15.38	.04
158L050	9257-2128	42	15.75	.04
165L050	9257-2121	44	16.50	.04
173L050	9257-2129	46	17.25	.04
176L050	9257-7133	47	17.63	.04
187L050	9257-2102	50	18.75	.04
195L050	9257-2122	52	19.50	.04
199L050	9257-7134	53	19.88	.05
203L050	9257-7135	54	20.25	.04
210L050	9257-2103	56	21.00	.04
218L050	9257-7136	58	21.75	.05
225L050	9257-2104	60	22.50	.05
240L050	9257-2105	64	24.00	.05
248L050	9257-7137	66	24.75	.01
255L050	9257-2106	68	25.50	.06
263L050	9257-7138	70	26.25	.06
270L050	9257-2107	72	27.00	.06
285L050	9257-2108	76	28.50	.05
300L050	9257-2109	80	30.00	.07
315L050	9257-2123	84	31.50	.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
322L050	9257-2110	86	32.25	.07
345L050	9257-2111	92	34.50	.07
367L050	9257-2112	98	36.75	.08
375L050	9257-7139	100	37.50	.08
390L050	9257-2113	104	39.00	.09
420L050	9257-2114	112	42.00	.10
446L050	9257-7140	119	44.63	.15
450L050	9257-2115	120	45.00	.10
480L050	9257-2116	128	48.00	.10
510L050	9257-2117	136	51.00	.12
540L050	9257-2118	144	54.00	.10
566L050	9257-7141	151	56.63	.15
570L050	9257-7142	152	57.00	.14
581L050	9257-7143	155	58.13	.13
600L050	9257-2119	160	60.00	.16
630L050	9257-7144	168	63.00	.10
660L050	9257-2124	176	66.00	.15
720L050	9257-7145	192	72.00	.15
731L050	9257-7146	195	73.13	.18
817L050	9257-2125	218	81.75	.20
900L050	9257-2126	240	90.00	.20
915L050	9257-7147	244	91.50	.25
945L050	9257-7148	252	94.50	.25



PowerGrip® Timing Belts

Product No. Series 9257 (continued)

3/8" Pitch (.375"/L) — 3/4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
124L075	9257-2200	33	12.38	.04
135L075	9257-2220	36	13.50	.20
150L075	9257-2201	40	15.00	.05
154L075	9257-2227	41	15.38	.05
158L075	9257-2228	42	15.75	.05
165L075	9257-2221	44	16.50	.05
173L075	9257-2229	46	17.25	.05
176L075	9257-7233	47	17.63	.07
187L075	9257-2202	50	18.75	.06
195L075	9257-2222	52	19.50	.06
199L075	9257-7234	53	19.88	.08
203L075	9257-7235	54	20.25	.07
210L075	9257-2203	56	21.00	.07
218L075	9257-7236	58	21.75	.07
225L075	9257-2204	60	22.50	.06
240L075	9257-2205	64	24.00	.06
248L075	9257-7237	66	24.75	.10
255L075	9257-2206	68	25.50	.09
263L075	9257-7238	70	26.25	.07
270L075	9257-2207	72	27.00	.07
285L075	9257-2208	76	28.50	.10
300L075	9257-2209	80	30.00	.07
315L075	9257-2223	84	31.50	.11

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
322L075	9257-2210	86	32.25	.10
345L075	9257-2211	92	34.50	.10
367L075	9257-2212	98	36.75	.12
375L075	9257-7239	100	37.50	.20
390L075	9257-2213	104	39.00	.12
420L075	9257-2214	112	42.00	.15
446L075	9257-7240	119	44.63	.17
450L075	9257-2215	120	45.00	.15
480L075	9257-2216	128	48.00	.15
510L075	9257-2217	136	51.00	.15
540L075	9257-2218	144	54.00	.15
566L075	9257-7241	151	56.63	.22
570L075	9257-7242	152	57.00	.23
581L075	9257-7243	155	58.13	.24
600L075	9257-2219	160	60.00	.20
630L075	9257-7244	168	63.00	.25
660L075	9257-2224	176	66.00	.20
720L075	9257-7245	192	72.00	.30
731L075	9257-7246	195	73.13	.30
817L075	9257-2225	218	81.75	.25
900L075	9257-2226	240	90.00	.40
915L075	9257-7247	244	91.50	.41
945L075	9257-7248	252	94.50	.45

3/8" Pitch (.375"/L) — 1" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
124L100	9257-2300	33	12.38	.05
135L100	9257-2320	36	13.50	.05
150L100	9257-2301	40	15.00	.08
154L100	9257-2327	41	15.38	.10
158L100	9257-2328	42	15.75	.08
165L100	9257-2321	44	16.50	.06
173L100	9257-2329	46	17.25	.09
176L100	9257-7333	47	17.63	.09
187L100	9257-2302	50	18.75	.02
195L100	9257-2322	52	19.50	.10
199L100	9257-7334	53	19.88	.10
203L100	9257-7335	54	20.25	.20
210L100	9257-2303	56	21.00	.10
218L100	9257-7336	58	21.75	.20
225L100	9257-2304	60	22.50	.10
240L100	9257-2305	64	24.00	.10
248L100	9257-7337	66	24.75	.10
255L100	9257-2306	68	25.50	.11
263L100	9257-7338	70	26.25	.15
270L100	9257-2307	72	27.00	.10
285L100	9257-2308	76	28.50	.11
300L100	9257-2309	80	30.00	.13
315L100	9257-2323	84	31.50	.15

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
322L100	9257-2310	86	32.25	.12
345L100	9257-2311	92	34.50	.50
367L100	9257-2312	98	36.75	.15
375L100	9257-7339	100	37.50	.16
390L100	9257-2313	104	39.00	.18
420L100	9257-2314	112	42.00	.20
446L100	9257-7340	119	44.63	.20
450L100	9257-2315	120	45.00	.20
480L100	9257-2316	128	48.00	.20
510L100	9257-2317	136	51.00	.25
540L100	9257-2318	144	54.00	.25
566L100	9257-7341	151	56.63	.30
570L100	9257-7342	152	57.00	.30
581L100	9257-7343	155	58.13	.31
600L100	9257-2319	160	60.00	.25
630L100	9257-7344	168	63.00	.30
660L100	9257-2324	176	66.00	.30
720L100	9257-7345	192	72.00	.35
731L100	9257-7346	195	73.13	.41
817L100	9257-2325	218	81.75	.35
900L100	9257-2326	240	90.00	.35
915L100	9257-7347	244	91.50	.60
945L100	9257-7348	252	94.50	.64

1/2" Pitch (.500"/H) — 3/4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
210H075	9257-3125	42	21.00	.08
220H075	9257-3126	44	22.00	.08
225H075	9257-3145	45	22.50	.08
230H075	9257-3127	46	23.00	.20
240H075	9257-3100	48	24.00	.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
270H075	9257-3101	54	27.00	.12
300H075	9257-3102	60	30.00	.10
310H075	9257-3146	62	31.00	.14
315H075	9257-3147	63	31.50	.15
320H075	9257-3128	64	32.00	.12



Product No. Series 9257 (continued)

1/2" Pitch (.500"/H) — 3/4" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
330H075	9257-3103	66	33.00	.15
340H075	9257-3129	68	34.00	.12
350H075	9257-3130	70	35.00	.15
360H075	9257-3104	72	36.00	.10
370H075	9257-3131	74	37.00	.15
390H075	9257-3105	78	39.00	.10
400H075	9257-3132	80	40.00	.20
410H075	9257-3133	82	41.00	.15
415H075	9257-3148	83	41.50	.19
420H075	9257-3106	84	42.00	.10
445H075	9257-3149	89	44.50	.15
450H075	9257-3107	90	45.00	.15
455H075	9257-8150	91	45.50	.20
465H075	9257-8151	93	46.50	.21
480H075	9257-3108	96	48.00	.20
490H075	9257-3134	98	49.00	.15
495H075	9257-8152	99	49.50	.23
510H075	9257-3109	102	51.00	.20
525H075	9257-8153	105	52.50	.24
540H075	9257-3110	108	54.00	.20
555H075	9257-8154	111	55.50	.26
560H075	9257-3135	112	56.00	.20
570H075	9257-3111	114	57.00	.20
585H075	9257-3136	117	58.50	.25
600H075	9257-3112	120	60.00	.20
605H075	9257-8155	121	60.50	.28
630H075	9257-3113	126	63.00	.25
645H075	9257-3137	129	64.50	.30
655H075	9257-8156	131	65.50	.31
660H075	9257-3114	132	66.00	.25
670H075	9257-8157	134	67.00	1.22

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
700H075	9257-3115	140	70.00	.25
730H075	9257-3138	146	73.00	.30
750H075	9257-3116	150	75.00	.30
775H075	9257-8158	155	77.50	.36
780H075	9257-3139	156	78.00	.35
800H075	9257-3117	160	80.00	.35
810H075	9257-8159	162	81.00	.37
820H075	9257-3140	164	82.00	.38
840H075	9257-3141	168	84.00	.40
850H075	9257-3118	170	85.00	.35
900H075	9257-3119	180	90.00	.40
950H075	9257-8160	190	95.00	.44
960H075	9257-3142	192	96.00	.45
1000H075	9257-3120	200	100.00	.45
1100H075	9257-3121	220	110.00	.45
1140H075	9257-3143	228	114.00	.50
1180H075	9257-8161	236	118.00	.55
1250H075	9257-3122	250	125.00	.45
1325H075	9257-8162	265	132.50	.60
1350H075	9257-8163	270	135.00	.55
1365H075	9257-8164	273	136.50	.62
1400H075	9257-3123	280	140.00	.55
1510H075	9257-8165	302	151.00	.69
1550H075	9257-3144	310	155.00	.70
1645H075	9257-8166	329	164.50	.78
1680H075	9257-8167	336	168.00	.81
1700H075	9257-3124	340	170.00	.70
2090H075	9257-8168	418	209.00	.95
2100H075	9257-8169	420	210.00	1.06
2120H075	9257-8170	424	212.00	1.10
2330H075	9257-8171	466	233.00	1.14

1/2" Pitch (.500"/H) — 1" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
210H100	9257-3225	42	21.00	.10
220H100	9257-3226	44	22.00	.10
225H100	9257-3245	45	22.50	.11
230H100	9257-3227	46	23.00	.12
240H100	9257-3200	48	24.00	.10
270H100	9257-3201	54	27.00	.10
300H100	9257-3202	60	30.00	.10
310H100	9257-3246	62	31.00	.75
315H100	9257-3247	63	31.50	.15
320H100	9257-3228	64	32.00	.17
330H100	9257-3203	66	33.00	.15
340H100	9257-3229	68	34.00	.17
350H100	9257-3230	70	35.00	.15
360H100	9257-3204	72	36.00	.19
370H100	9257-3231	74	37.00	.15
390H100	9257-3205	78	39.00	.15
400H100	9257-3232	80	40.00	.15
410H100	9257-3233	82	41.00	.15
415H100	9257-3248	83	41.50	.26
420H100	9257-3206	84	42.00	.20
445H100	9257-3249	89	44.50	.25
450H100	9257-3207	90	45.00	.10
455H100	9257-8250	91	45.50	.25
465H100	9257-8251	93	46.50	.25
480H100	9257-3208	96	48.00	.20
490H100	9257-3234	98	49.00	.25

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
495H100	9257-8252	99	49.50	.20
510H100	9257-3209	102	51.00	.20
525H100	9257-8253	105	52.50	.30
540H100	9257-3210	108	54.00	.25
555H100	9257-8254	111	55.50	.30
560H100	9257-3235	112	56.00	.30
570H100	9257-3211	114	57.00	.30
585H100	9257-3236	117	58.50	.30
600H100	9257-3212	120	60.00	.30
605H100	9257-8255	121	60.50	.35
630H100	9257-3213	126	63.00	.33
645H100	9257-3237	129	64.50	.35
655H100	9257-8256	131	65.50	.41
660H100	9257-3214	132	66.00	.35
670H100	9257-8257	134	67.00	.40
700H100	9257-3215	140	70.00	.40
730H100	9257-3238	146	73.00	.40
750H100	9257-3216	150	75.00	.40
775H100	9257-8258	155	77.50	.50
780H100	9257-3239	156	78.00	.40
800H100	9257-3217	160	80.00	.44
810H100	9257-8259	162	81.00	.52
820H100	9257-3240	164	82.00	.40
840H100	9257-3241	168	84.00	.40
850H100	9257-3218	170	85.00	.45
900H100	9257-3219	180	90.00	.56



PowerGrip® Timing Belts

Product No. Series 9257 (continued)

1/2" Pitch (.500"/H) — 1" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
950H100	9257-8260	190	95.00	.60
960H100	9257-3242	192	96.00	.58
1000H100	9257-3220	200	100.00	.45
1100H100	9257-3221	220	110.00	.55
1140H100	9257-3243	228	114.00	.60
1180H100	9257-8261	236	118.00	.75
1250H100	9257-3222	250	125.00	.65
1325H100	9257-8262	265	132.50	.80
1350H100	9257-8263	270	135.00	.85
1365H100	9257-8264	273	136.50	.85

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1400H100	9257-3223	280	140.00	.70
1510H100	9257-8265	302	151.00	.80
1550H100	9257-3244	310	155.00	.75
1645H100	9257-8266	329	164.50	1.00
1680H100	9257-8267	336	168.00	1.04
1700H100	9257-3224	340	170.00	.85
2090H100	9257-8268	418	209.00	1.31
2100H100	9257-8269	420	210.00	1.44
2120H100	9257-8270	424	212.00	1.45
2330H100	9257-8271	466	233.00	1.52

1/2" Pitch (.500"/H) — 1 1/2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
210H150	9257-3325	42	21.00	.15
220H150	9257-3326	44	22.00	.15
225H150	9257-3345	45	22.50	.21
230H150	9257-3327	46	23.00	.15
240H150	9257-3300	48	24.00	.15
270H150	9257-3301	54	27.00	.20
300H150	9257-3302	60	30.00	.25
310H150	9257-3346	62	31.00	.25
315H150	9257-3347	63	31.50	.30
320H150	9257-3328	64	32.00	.25
330H150	9257-3303	66	33.00	.25
340H150	9257-3329	68	34.00	.25
350H150	9257-3330	70	35.00	.25
360H150	9257-3304	72	36.00	.30
370H150	9257-3331	74	37.00	.30
390H150	9257-3305	78	39.00	.30
400H150	9257-3332	80	40.00	.30
410H150	9257-3333	82	41.00	.30
415H150	9257-3348	83	41.50	.39
420H150	9257-3306	84	42.00	.40
445H150	9257-3349	89	44.50	.35
450H150	9257-3307	90	45.00	.35
455H150	9257-8350	91	45.50	.40
465H150	9257-8351	93	46.50	.35
480H150	9257-3308	96	48.00	.35
490H150	9257-3334	98	49.00	.40
495H150	9257-8352	99	49.50	.45
510H150	9257-3309	102	51.00	.35
525H150	9257-8353	105	52.50	.50
540H150	9257-3310	108	54.00	.40
555H150	9257-8354	111	55.50	.51
560H150	9257-3335	112	56.00	.45
570H150	9257-3311	114	57.00	.45
585H150	9257-3336	117	58.50	.45
600H150	9257-3312	120	60.00	.45
605H150	9257-8355	121	60.50	.56

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
630H150	9257-3313	126	63.00	.55
645H150	9257-3337	129	64.50	.50
655H150	9257-8356	131	65.50	.60
660H150	9257-3314	132	66.00	.50
670H150	9257-8357	134	67.00	.65
700H150	9257-3315	140	70.00	.55
730H150	9257-3338	146	73.00	.60
750H150	9257-3316	150	75.00	.55
775H150	9257-8358	155	77.50	.72
780H150	9257-3339	156	78.00	.60
800H150	9257-3317	160	80.00	.60
810H150	9257-8359	162	81.00	.74
820H150	9257-3340	164	82.00	.75
840H150	9257-3341	168	84.00	.70
850H150	9257-3318	170	85.00	.65
900H150	9257-3319	180	90.00	.70
950H150	9257-8360	190	95.00	.80
960H150	9257-3342	192	96.00	.75
1000H150	9257-3320	200	100.00	.85
1100H150	9257-3321	220	110.00	.90
1140H150	9257-3343	228	114.00	.95
1180H150	9257-8361	236	118.00	.95
1250H150	9257-3322	250	125.00	1.00
1325H150	9257-8362	265	132.50	1.48
1350H150	9257-8363	270	135.00	1.55
1365H150	9257-8364	273	136.50	1.52
1400H150	9257-3323	280	140.00	1.15
1510H150	9257-8365	302	151.00	1.30
1550H150	9257-3344	310	155.00	1.25
1645H150	9257-8366	329	164.50	1.80
1680H150	9257-8367	336	168.00	1.83
1700H150	9257-3324	340	170.00	1.30
2090H150	9257-8368	418	209.00	1.90
2100H150	9257-8369	420	210.00	2.31
2120H150	9257-8370	424	212.00	2.32
2330H150	9257-8371	466	233.00	2.38

1/2" Pitch (.500"/H) — 2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
210H200	9257-3425	42	21.00	.25
220H200	9257-3426	44	22.00	.25
225H200	9257-3445	45	22.50	.27
230H200	9257-3427	46	23.00	.25
240H200	9257-3400	48	24.00	.25

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
270H200	9257-3401	54	27.00	.25
300H200	9257-3402	60	30.00	.30
310H200	9257-3446	62	31.00	.40
315H200	9257-3447	63	31.50	.39
320H200	9257-3428	64	32.00	.30



Product No. Series 9257 (continued)

1/2" Pitch (.500"/H) — 2" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
330H200	9257-3403	66	33.00	.35
340H200	9257-3429	68	34.00	.35
350H200	9257-3430	70	35.00	.35
360H200	9257-3404	72	36.00	.40
370H200	9257-3431	74	37.00	.40
390H200	9257-3405	78	39.00	.40
400H200	9257-3432	80	40.00	.45
410H200	9257-3433	82	41.00	.19
415H200	9257-3448	83	41.50	.50
420H200	9257-3406	84	42.00	.45
445H200	9257-3449	89	44.50	.50
450H200	9257-3407	90	45.00	.45
455H200	9257-8450	91	45.50	.56
465H200	9257-8451	93	46.50	.50
480H200	9257-3408	96	48.00	.50
490H200	9257-3434	98	49.00	.24
495H200	9257-8452	99	49.50	.61
510H200	9257-3409	102	51.00	.55
525H200	9257-8453	105	52.50	.60
540H200	9257-3410	108	54.00	.55
555H200	9257-8454	111	55.50	.60
560H200	9257-3435	112	56.00	.55
570H200	9257-3411	114	57.00	.55
585H200	9257-3436	117	58.50	.95
600H200	9257-3412	120	60.00	.65
605H200	9257-8455	121	60.50	.75
630H200	9257-3413	126	63.00	.70
645H200	9257-3437	129	64.50	.65
655H200	9257-8456	131	65.50	.81
660H200	9257-3414	132	66.00	.70
670H200	9257-8457	134	67.00	.86

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
700H200	9257-3415	140	70.00	.70
730H200	9257-3438	146	73.00	.85
750H200	9257-3416	150	75.00	.85
775H200	9257-8458	155	77.50	.80
780H200	9257-3439	156	78.00	.80
800H200	9257-3417	160	80.00	.85
810H200	9257-8459	162	81.00	1.02
820H200	9257-3440	164	82.00	1.00
840H200	9257-3441	168	84.00	1.04
850H200	9257-3418	170	85.00	.95
900H200	9257-3419	180	90.00	1.30
950H200	9257-8460	190	95.00	1.20
960H200	9257-3442	192	96.00	.15
1000H200	9257-3420	200	100.00	1.05
1100H200	9257-3421	220	110.00	1.15
1140H200	9257-3443	228	114.00	1.20
1180H200	9257-8461	236	118.00	1.55
1250H200	9257-3422	250	125.00	1.50
1325H200	9257-8462	265	132.50	1.64
1350H200	9257-8463	270	135.00	1.69
1365H200	9257-8464	273	136.50	1.71
1400H200	9257-3423	280	140.00	1.45
1510H200	9257-8465	302	151.00	1.84
1550H200	9257-3444	310	155.00	1.70
1645H200	9257-8466	329	164.50	2.09
1680H200	9257-8467	336	168.00	2.17
1700H200	9257-3424	340	170.00	1.85
2090H200	9257-8468	418	209.00	3.21
2100H200	9257-8469	420	210.00	3.23
2120H200	9257-8470	424	212.00	3.28
2330H200	9257-8471	466	233.00	3.80

1/2" Pitch (.500"/H) — 3" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
210H300	9257-3525	42	21.00	.40
220H300	9257-3526	44	22.00	.40
225H300	9257-3545	45	22.50	.41
230H300	9257-3527	46	23.00	.42
240H300	9257-3500	48	24.00	.35
270H300	9257-3501	54	27.00	.45
300H300	9257-3502	60	30.00	.46
310H300	9257-3546	62	31.00	.56
315H300	9257-3547	63	31.50	.58
320H300	9257-3528	64	32.00	.60
330H300	9257-3503	66	33.00	.50
340H300	9257-3529	68	34.00	.60
350H300	9257-3530	70	35.00	.60
360H300	9257-3504	72	36.00	.55
370H300	9257-3531	74	37.00	.70
390H300	9257-3505	78	39.00	.60
400H300	9257-3532	80	40.00	.75
410H300	9257-3533	82	41.00	.75
415H300	9257-3548	83	41.50	.76
420H300	9257-3506	84	42.00	.65
445H300	9257-3549	89	44.50	.80
450H300	9257-3507	90	45.00	.75
455H300	9257-8550	91	45.50	.84
465H300	9257-8551	93	46.50	.75
480H300	9257-3508	96	48.00	.75
490H300	9257-3534	98	49.00	.85

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
495H300	9257-8552	99	49.50	.92
510H300	9257-3509	102	51.00	.85
525H300	9257-8553	105	52.50	.97
540H300	9257-3510	108	54.00	.85
555H300	9257-8554	111	55.50	1.00
560H300	9257-3535	112	56.00	.90
570H300	9257-3511	114	57.00	.85
585H300	9257-3536	117	58.50	1.55
600H300	9257-3512	120	60.00	.95
605H300	9257-8555	121	60.50	1.14
630H300	9257-3513	126	63.00	1.50
645H300	9257-3537	129	64.50	.74
655H300	9257-8556	131	65.50	1.31
660H300	9257-3514	132	66.00	1.55
670H300	9257-8557	134	67.00	1.45
700H300	9257-3515	140	70.00	1.60
730H300	9257-3538	146	73.00	1.75
750H300	9257-3516	150	75.00	1.70
775H300	9257-8558	155	77.50	1.51
780H300	9257-3539	156	78.00	1.80
800H300	9257-3517	160	80.00	1.90
810H300	9257-8559	162	81.00	1.54
820H300	9257-3540	164	82.00	1.80
840H300	9257-3541	168	84.00	2.00
850H300	9257-3518	170	85.00	1.90
900H300	9257-3519	180	90.00	1.90



PowerGrip® Timing Belts

Product No. Series 9257 (continued)

1/2" Pitch (.500"/H) — 3" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
950H300	9257-8560	190	95.00	2.01
960H300	9257-3542	192	96.00	2.10
1000H300	9257-3520	200	100.00	2.05
1100H300	9257-3521	220	110.00	2.40
1140H300	9257-3543	228	114.00	2.55
1180H300	9257-8561	236	118.00	2.89
1250H300	9257-3522	250	125.00	3.00
1325H300	9257-8562	265	132.50	2.05
1350H300	9257-8563	270	135.00	3.15
1365H300	9257-8564	273	136.50	3.19

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1400H300	9257-3523	280	140.00	2.80
1510H300	9257-8565	302	151.00	2.40
1550H300	9257-3544	310	155.00	4.21
1645H300	9257-8566	329	164.50	4.47
1680H300	9257-8567	336	168.00	4.57
1700H300	9257-3524	340	170.00	3.30
2090H300	9257-8568	418	209.00	5.69
2100H300	9257-8569	420	210.00	5.72
2120H300	9257-8570	424	212.00	5.77
2330H300	9257-8571	466	233.00	6.34

7/8" Pitch (.875"/XH) — 2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
507XH200	9257-4100	58	50.75	2.05
560XH200	9257-4101	64	56.00	2.75
630XH200	9257-4102	72	63.00	2.45
700XH200	9257-4103	80	70.00	3.25
770XH200	9257-4104	88	77.00	3.50
840XH200	9257-4105	96	84.00	3.70

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
980XH200	9257-4106	112	98.00	4.10
1120XH200	9257-4107	128	112.00	5.00
1260XH200	9257-4108	144	126.00	5.25
1400XH200	9257-4109	160	140.00	5.25
1540XH200	9257-4110	176	154.00	3.95
1750XH200	9257-4111	200	175.00	6.75

7/8" Pitch (.875"/XH) — 3" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
507XH300	9257-4200	58	50.75	3.08
560XH300	9257-4201	64	56.00	4.45
630XH300	9257-4202	72	63.00	4.40
700XH300	9257-4203	80	70.00	4.30
770XH300	9257-4204	88	77.00	4.69
840XH300	9257-4205	96	84.00	5.45

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
980XH300	9257-4206	112	98.00	5.65
1120XH300	9257-4207	128	112.00	6.75
1260XH300	9257-4208	144	126.00	7.40
1400XH300	9257-4209	160	140.00	7.70
1540XH300	9257-4210	176	154.00	7.10
1750XH300	9257-4211	200	175.00	9.60

7/8" Pitch (.875"/XH) — 4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
507XH400	9257-4300	58	50.75	4.00
560XH400	9257-4301	64	56.00	4.90
630XH400	9257-4302	72	63.00	5.25
700XH400	9257-4303	80	70.00	5.70
770XH400	9257-4304	88	77.00	6.25
840XH400	9257-4305	96	84.00	6.75

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
980XH400	9257-4306	112	98.00	7.30
1120XH400	9257-4307	128	112.00	8.15
1260XH400	9257-4308	144	126.00	9.20
1400XH400	9257-4309	160	140.00	8.70
1540XH400	9257-4310	176	154.00	10.05
1750XH400	9257-4311	200	175.00	12.05

1 1/4" Pitch (1.250"/XXH) — 2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
700XXH200	9257-5100	56	70.00	4.00
800XXH200	9257-5101	64	80.00	4.45
900XXH200	9257-5102	72	90.00	4.90
1000XXH200	9257-5103	80	100.00	5.55

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1200XXH200	9257-5104	96	120.00	6.35
1400XXH200	9257-5105	112	140.00	7.25
1600XXH200	9257-5106	128	160.00	8.05
1800XXH200	9257-5107	144	180.00	8.95



Product No. Series 9257 (continued)

1 1/4" Pitch (1.250"/XXH) — 3" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
700XXH300	9257-5200	56	70.00	4.90
800XXH300	9257-5201	64	80.00	6.40
900XXH300	9257-5202	72	90.00	6.85
1000XXH300	9257-5203	80	100.00	7.55

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1200XXH300	9257-5204	96	120.00	5.70
1400XXH300	9257-5205	112	140.00	10.35
1600XXH300	9257-5206	128	160.00	11.30
1800XXH300	9257-5207	144	180.00	12.00

1 1/4" Pitch (1.250"/XXH) — 4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
700XXH400	9257-5300	56	70.00	7.02
800XXH400	9257-5301	64	80.00	7.95
900XXH400	9257-5302	72	90.00	9.00
1000XXH400	9257-5303	80	100.00	10.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1200XXH400	9257-5304	96	120.00	11.25
1400XXH400	9257-5305	112	140.00	13.10
1600XXH400	9257-5306	128	160.00	15.00
1800XXH400	9257-5307	144	180.00	18.12

1 1/4" Pitch (1.250"/XXH) — 5" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
700XXH500	9257-5400	56	70.00	8.75
800XXH500	9257-5401	64	80.00	9.60
900XXH500	9257-5402	72	90.00	10.80
1000XXH500	9257-5403	80	100.00	12.40

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
1200XXH500	9257-5404	96	120.00	14.00
1400XXH500	9257-5405	112	140.00	16.15
1600XXH500	9257-5406	128	160.00	18.05
1800XXH500	9257-5407	144	180.00	20.15

Cotton Cleaner Belts

Cotton cleaner belts have a trapezoidal tooth profile and now KEVLAR® tensile cords.

Markets/Applications

Cotton Cleaner belts are specifically designed for use on Cotton Gin and inclined cleaner machines.

Features/Advantages

- **KEVLAR tensile cords** for increased shock resistance.
- Long service life in harsh environments.

Recommended Pulleys—Contact the Gates Made-To-Order Metals Team.



Product No. Series 9259

1" Pitch

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
61CCB142K	9259-3831	60	61.07	2.26
63CCB165K	9259-3832	63	63.00	1.35
64CCB170K	9259-3833	64	63.95	.97
65CCB175K	9259-3834	65	64.95	2.40

NOTE: Steel tensile cord available as a made to order product. Lead time and minimum order quantities apply. Contact Customer Service for availability.

PowerGrip® GT®2 Twin Power® Belts - 3MR and 5MR


Twin Power belts have teeth on both sides to provide synchronization from both driving surfaces.

Markets/Applications

PowerGrip GT2 Twin Power belts are ideal for many applications including data storage, machine tool, hand power tools, postage handling, medicine diagnostic, sewing machines, ticket dispensers, robotics, vending machines and vacuum cleaners.

Features/Advantages

- Gates Twin Power belts have **nylon facing** on both tooth surfaces providing equal load carrying capabilities on either side of belt.
- Belt capacity is equal to standard single-sided PowerGrip belts.
- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- Eliminates lubrication and re-tensioning to reduce maintenance and labor required on the drive.



Recommended Sprockets

PowerGrip GT2 Sprockets - 3MR

5M Sprockets - PowerGrip GT2 and Poly Chain™ GT

Notes

PowerGrip GT2 Twin Power belts in standard width are Standard/Non-Stock. Minimum order quantities are not required on standard widths.

3MR GT2 Standard Belt Widths		
Belt Width Code	Belt Width (mm)	Belt Width (In.)
06	6	0.236
09	9	0.354
15	15	0.591

5MR GT2 Standard Belt Widths		
Belt Width Code	Belt Width (mm)	Belt Width (In.)
09	9	0.354
15	15	0.591
25	25	0.984

3MR Aluminum Barstock can be used with 3MR PowerGrip GT2 Twin Power Belts.

PowerGrip GT2 Twin Power part numbers are comprised of pitch, pitch length and width. For example; part number TP3MR-426-06 denotes "TP for Twin Power, 3mm pitch, 426mm pitch length and 6mm width.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of a PowerGrip GT2 Twin Power belt lies within the tensile member.

Product No. Series 9232

3MR - Twin Power Belts

Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth	Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth	Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth
TP3MR-381	381	15.00	127	TP3MR-513	513	20.20	171	TP3MR-639	639	25.16	213
TP3MR-396	396	15.59	132	TP3MR-519	519	20.43	173	TP3MR-645	645	25.39	215
TP3MR-399	399	15.71	133	TP3MR-525	525	20.67	175	TP3MR-648	648	25.51	216
TP3MR-405	405	15.94	135	TP3MR-528	528	20.79	176	TP3MR-654	654	25.75	218
TP3MR-411	411	16.18	137	TP3MR-531	531	20.91	177	TP3MR-657	657	25.87	219
TP3MR-420	420	16.54	140	TP3MR-537	537	21.14	179	TP3MR-663	663	26.10	221
TP3MR-426	426	16.77	142	TP3MR-552	552	21.73	184	TP3MR-669	669	26.34	223
TP3MR-432	432	17.01	144	TP3MR-558	558	21.97	186	TP3MR-684	684	26.93	228
TP3MR-435	435	17.13	145	TP3MR-564	564	22.20	188	TP3MR-687	687	27.05	229
TP3MR-447	447	17.60	149	TP3MR-570	570	22.44	190	TP3MR-696	696	27.40	232
TP3MR-465	465	18.31	155	TP3MR-576	576	22.68	192	TP3MR-711	711	27.99	237
TP3MR-468	468	18.43	156	TP3MR-585	585	23.03	195	TP3MR-735	735	28.94	245
TP3MR-471	471	18.54	157	TP3MR-591	591	23.27	197	TP3MR-738	738	29.06	246
TP3MR-474	474	18.66	158	TP3MR-597	597	23.50	199	TP3MR-750	750	29.53	250
TP3MR-480	480	18.90	160	TP3MR-600	600	23.62	200	TP3MR-753	753	29.65	251
TP3MR-486	486	19.13	162	TP3MR-606	606	23.86	202	TP3MR-786	786	30.94	262
TP3MR-489	489	19.25	163	TP3MR-609	609	23.98	203	TP3MR-795	795	31.30	265
TP3MR-492	492	19.37	164	TP3MR-612	612	24.09	204	TP3MR-822	822	32.36	274
TP3MR-501	501	19.72	167	TP3MR-627	627	24.69	209	TP3MR-837	837	32.95	279
TP3MR-510	510	20.08	170	TP3MR-633	633	24.92	211	TP3MR-840	840	33.07	280



PowerGrip® GT®2 Twin Power® Belts - 3MR and 5MR

Product No. Series 9232 (continued)

3MR - Twin Power Belts (continued)

Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth
TP3MR-843	843	33.19	281
TP3MR-873	873	34.37	291
TP3MR-882	882	34.72	294
TP3MR-891	891	35.08	297
TP3MR-900	900	35.43	300
TP3MR-915	915	36.02	305
TP3MR-945	945	37.20	315
TP3MR-951	951	37.44	317
TP3MR-981	981	38.62	327
TP3MR-1002	1002	39.45	334

Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth
TP3MR-1026	1026	40.39	342
TP3MR-1035	1035	40.74	345
TP3MR-1050	1050	41.34	350
TP3MR-1056	1056	41.57	352
TP3MR-1062	1062	41.81	354
TP3MR-1080	1080	42.52	360
TP3MR-1125	1125	44.29	375
TP3MR-1155	1155	45.47	385
TP3MR-1191	1191	46.89	397
TP3MR-1263	1263	49.72	421

Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth
TP3MR-1335	1335	52.56	445
TP3MR-1500	1500	59.06	500
TP3MR-1512	1512	59.53	504
TP3MR-1536	1536	60.47	512
TP3MR-1587	1587	62.48	529
TP3MR-1956	1956	77.01	652
TP3MR-2004	2004	78.90	668
TP3MR-2061	2061	81.14	687

5MR - Twin Power Belts

Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth
TP5MR-400	400	15.75	80
TP5MR-425	425	16.73	85
TP5MR-450	450	17.72	90
TP5MR-500	500	19.69	100
TP5MR-535	535	21.06	107
TP5MR-565	565	22.24	113
TP5MR-575	575	22.64	115
TP5MR-580	580	22.83	116
TP5MR-600	600	23.62	120
TP5MR-625	625	24.61	125
TP5MR-650	650	25.69	130
TP5MR-700	700	27.56	140
TP5MR-710	710	27.95	142
TP5MR-740	740	29.13	148
TP5MR-745	745	29.33	149
TP5MR-750	750	29.53	150
TP5MR-765	765	30.12	153
TP5MR-790	790	31.10	158
TP5MR-800	800	31.50	160
TP5MR-815	815	32.09	163
TP5MR-830	830	32.68	166

Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth
TP5MR-835	835	32.87	167
TP5MR-850	850	33.46	170
TP5MR-870	870	34.25	174
TP5MR-890	890	35.04	178
TP5MR-900	900	35.43	180
TP5MR-925	925	36.42	185
TP5MR-950	950	37.40	190
TP5MR-975	975	38.39	195
TP5MR-985	985	38.78	197
TP5MR-1000	1000	39.37	200
TP5MR-1050	1050	41.34	210
TP5MR-1115	1115	43.91	223
TP5MR-1125	1125	44.29	225
TP5MR-1150	1150	45.28	230
TP5MR-1195	1195	47.05	239
TP5MR-1250	1250	49.21	250
TP5MR-1270	1270	50.00	254
TP5MR-1295	1295	50.98	259
TP5MR-1300	1300	51.18	260
TP5MR-1375	1375	54.13	275
TP5MR-1420	1420	55.91	284

Part No.	Pitch Length (mm)	Pitch Length (In.)	No. of Teeth
TP5MR-1450	1450	57.09	290
TP5MR-1575	1575	62.01	315
TP5MR-1595	1595	62.80	319
TP5MR-1635	1635	64.37	327
TP5MR-1690	1690	66.54	338
TP5MR-1790	1790	70.47	358
TP5MR-1800	1800	70.87	360
TP5MR-1895	1895	74.61	379
TP5MR-1945	1945	76.57	389
TP5MR-2000	2000	78.74	400
TP5MR-2110	2110	83.07	422
TP5MR-2250	2250	88.58	450
TP5MR-2525	2525	99.41	505
TP5MR-2760	2760	108.66	552
TP5MR-3120	3120	122.83	624
TP5MR-3170	3170	124.80	634
TP5MR-3200	3200	125.98	640
TP5MR-3430	3430	135.04	686
TP5MR-3800	3800	149.61	760



PowerGrip® GT®2 Twin Power® Belts

Twin Power belts have teeth on both sides to provide synchronization from both driving surfaces.

Markets/Applications

PowerGrip GT2 Twin Power belts are ideal for serpentine applications requiring rotation reversal or synchronization of driven shafts. Ideal for use in industries such as textile, paper, packaging and printing.

Features/Advantages

- Gates Twin Power belts have **nylon facing** on both tooth surfaces providing equal load carrying capabilities on either side of belt.
- Belt capacity is equal to standard single-sided PowerGrip GT2 belts.
- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- Eliminates lubrication and re-tensioning to reduce maintenance and labor required on drives.

Recommended Sprockets


PowerGrip GT2 Sprockets

Notes

If you currently use PowerGrip HTD Twin Power belts, consider PowerGrip GT2 Twin Power belts at reduced widths to lower your costs.

PowerGrip GT2 Twin Power part numbers are comprised of pitch, pitch length and width. For example; part number TP4400-8MGT-30 denotes a "TP" for Twin Power, 4400mm pitch length, 8mm pitch and 30mm width.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of a PowerGrip GT2 Twin Power belt lies within the tensile member.



Product No. Series 9232

8mm Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP560-8MGT-20	9232-0005	70	22.05	.32
TP600-8MGT-20	9232-0009	75	23.62	.34
TP640-8MGT-20	9232-0013	80	25.20	.36
TP720-8MGT-20	9232-0017	90	28.35	.40
TP800-8MGT-20	9232-0021	100	31.50	.20
TP840-8MGT-20	9232-1025	105	33.08	.47
TP880-8MGT-20	9232-0025	110	34.65	.50
TP920-8MGT-20	9232-1001	115	36.23	.52
TP960-8MGT-20	9232-0029	120	37.80	.54
TP1040-8MGT-20	9232-0033	130	40.95	.30
TP1064-8MGT-20	9232-1005	133	41.89	.60
TP1120-8MGT-20	9232-0037	140	44.10	.63
TP1160-8MGT-20	9232-2049	146	45.83	.66
TP1200-8MGT-20	9232-0041	150	47.25	.35
TP1224-8MGT-20	9232-1029	153	48.20	.35

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1280-8MGT-20	9232-0045	160	50.40	.72
TP1440-8MGT-20	9232-0049	180	56.70	.45
TP1512-8MGT-20	9232-1013	189	59.53	.84
TP1600-8MGT-20	9232-0053	200	63.00	.45
TP1760-8MGT-20	9232-0057	220	69.30	.50
TP1800-8MGT-20	9232-0061	225	70.88	.50
TP2000-8MGT-20	9232-0065	250	78.75	.60
TP2200-8MGT-20	9232-1033	275	86.63	.65
TP2400-8MGT-20	9232-0069	300	94.50	.70
TP2600-8MGT-20	9232-0077	325	102.38	1.45
TP2800-8MGT-20	9232-0073	350	110.25	.80
TP3048-8MGT-20	9232-0081	381	120.02	1.70
TP3280-8MGT-20	9232-0085	410	129.15	.90
TP3600-8MGT-20	9232-0089	450	141.75	2.02
TP4400-8MGT-20	9232-0093	550	173.25	2.46

8mm Pitch — 30mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP560-8MGT-30	9232-0006	70	22.05	.46
TP600-8MGT-30	9232-0010	75	23.62	.50
TP640-8MGT-30	9232-0014	80	25.20	.54
TP720-8MGT-30	9232-0018	90	28.35	.60
TP800-8MGT-30	9232-0022	100	31.50	.66
TP840-8MGT-30	9232-1026	105	33.08	.70
TP880-8MGT-30	9232-0026	110	34.65	.40
TP920-8MGT-30	9232-1002	115	36.23	.77
TP960-8MGT-30	9232-0030	120	37.80	.45

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1040-8MGT-30	9232-0034	130	40.95	.45
TP1064-8MGT-30	9232-1006	133	41.89	.88
TP1120-8MGT-30	9232-0038	140	44.10	.50
TP1160-8MGT-30	9232-1010	146	45.83	.96
TP1200-8MGT-30	9232-0042	150	47.25	.55
TP1224-8MGT-30	9232-1030	153	48.20	1.02
TP1280-8MGT-30	9232-0046	160	50.40	.60
TP1440-8MGT-30	9232-0050	180	56.70	.65
TP1512-8MGT-30	9232-1014	189	59.53	1.26



PowerGrip® GT®2 Twin Power® Belts

Product No. Series 9232 (continued)

8mm Pitch — 30mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1600-8MGT-30	9232-0054	200	63.00	.70
TP1760-8MGT-30	9232-0058	220	69.30	.75
TP1800-8MGT-30	9232-0062	225	70.88	.80
TP2000-8MGT-30	9232-0066	250	78.75	.90
TP2200-8MGT-30	9232-1034	275	86.63	1.00
TP2400-8MGT-30	9232-0070	300	94.50	1.00

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP2600-8MGT-30	9232-0078	325	102.38	1.10
TP2800-8MGT-30	9232-0074	350	110.25	1.20
TP3048-8MGT-30	9232-0082	381	120.02	2.54
TP3280-8MGT-30	9232-0086	410	129.15	1.45
TP3600-8MGT-30	9232-0090	450	141.75	1.55
TP4400-8MGT-30	9232-0094	550	173.25	1.90

8mm Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP560-8MGT-50	9232-0007	70	22.05	.78
TP600-8MGT-50	9232-0011	75	23.62	.84
TP640-8MGT-50	9232-0015	80	25.20	.85
TP720-8MGT-50	9232-0019	90	28.35	1.00
TP800-8MGT-50	9232-0023	100	31.50	1.12
TP840-8MGT-50	9232-1027	105	33.08	1.18
TP880-8MGT-50	9232-0027	110	34.65	1.23
TP920-8MGT-50	9232-1003	115	36.23	1.29
TP960-8MGT-50	9232-0031	120	37.80	1.34
TP1040-8MGT-50	9232-0035	130	40.95	1.46
TP1064-8MGT-50	9232-1007	133	41.89	1.50
TP1120-8MGT-50	9232-0039	140	44.10	1.59
TP1160-8MGT-50	9232-1011	146	45.83	1.60
TP1200-8MGT-50	9232-0043	150	47.25	.90
TP1224-8MGT-50	9232-1031	153	48.20	1.71

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1280-8MGT-50	9232-0047	160	50.40	1.78
TP1440-8MGT-50	9232-0051	180	56.70	1.10
TP1512-8MGT-50	9232-1015	189	59.53	2.10
TP1600-8MGT-50	9232-0055	200	63.00	1.20
TP1760-8MGT-50	9232-0059	220	69.30	1.30
TP1800-8MGT-50	9232-0063	225	70.88	2.50
TP2000-8MGT-50	9232-0067	250	78.75	1.45
TP2200-8MGT-50	9232-1035	275	86.63	3.08
TP2400-8MGT-50	9232-0071	300	94.50	1.80
TP2600-8MGT-50	9232-0079	325	102.38	1.55
TP2800-8MGT-50	9232-0075	350	110.25	2.00
TP3048-8MGT-50	9232-0083	381	120.02	4.20
TP3280-8MGT-50	9232-0087	410	129.15	2.40
TP3600-8MGT-50	9232-0091	450	141.75	5.02
TP4400-8MGT-50	9232-0095	550	173.25	6.14

8mm Pitch — 85mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP560-8MGT-85	9232-0008	70	22.05	1.32
TP600-8MGT-85	9232-0012	75	23.62	1.42
TP640-8MGT-85	9232-0016	80	25.20	1.52
TP720-8MGT-85	9232-0020	90	28.35	1.70
TP800-8MGT-85	9232-0024	100	31.50	1.90
TP840-8MGT-85	9232-1028	105	33.08	1.98
TP880-8MGT-85	9232-0028	110	34.65	2.08
TP920-8MGT-85	9232-1004	115	36.23	2.17
TP960-8MGT-85	9232-1008	120	37.80	2.27
TP1040-8MGT-85	9232-0036	130	40.95	2.46
TP1064-8MGT-85	9232-2048	133	41.89	2.50
TP1120-8MGT-85	9232-0040	140	44.10	2.65
TP1160-8MGT-85	9232-1012	146	45.83	2.76
TP1200-8MGT-85	9232-0044	150	47.25	2.84
TP1224-8MGT-85	9232-1032	153	48.20	2.89

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1280-8MGT-85	9232-0048	160	50.40	3.04
TP1440-8MGT-85	9232-0052	180	56.70	3.42
TP1512-8MGT-85	9232-1016	189	59.53	3.56
TP1600-8MGT-85	9232-0056	200	63.00	3.80
TP1760-8MGT-85	9232-0060	220	69.30	4.16
TP1800-8MGT-85	9232-0064	225	70.88	4.30
TP2000-8MGT-85	9232-0068	250	78.75	4.74
TP2200-8MGT-85	9232-1036	275	86.63	5.20
TP2400-8MGT-85	9232-0072	300	94.50	5.68
TP2600-8MGT-85	9232-0080	325	102.38	6.18
TP2800-8MGT-85	9232-0076	350	110.25	6.64
TP3048-8MGT-85	9232-0084	381	120.02	7.24
TP3280-8MGT-85	9232-0088	410	129.15	7.78
TP3600-8MGT-85	9232-0092	450	141.75	4.40
TP4400-8MGT-85	9232-0096	550	173.25	10.44



PowerGrip® HTD® Twin Power® Belts


Twin Power belts have teeth on both sides to provide synchronization from both driving surfaces.

Markets/Applications

PowerGrip HTD Twin Power belts are suitable for many applications including data storage, hand power tools, postage handling, food processors, office machines, centrifuges money handling, medicine diagnostic, sewing machines, ticket dispensers, robotics, vending machines and vacuum cleaners.

Features/Advantages

- Gates Twin Power belts have **nylon facing** on both tooth surfaces providing equal load carrying capabilities on either side of the belt.
- Belt capacity is equal to standard single-sided PowerGrip HTD belts.
- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Quieter than roller chain drives and eliminates lubrication and re-tensioning to reduce maintenance and labor.



Recommended Sprockets

PowerGrip HTD Sprockets

Notes

PowerGrip HTD Twin Power belts in standard widths are Standard/Non-Stock. Minimum order quantities are not required on standard widths.

3M HTD Standard Belt Widths		
Belt Width Code	Belt Width (mm)	Belt Width (In.)
06	6	0.236
09	9	0.354
15	15	0.591

5M HTD Standard Belt Widths		
Belt Width Code	Belt Width (mm)	Belt Width (In.)
09	9	0.354
15	15	0.591
25	25	0.984

PowerGrip HTD Twin Power part numbers are comprised of pitch, pitch length and width. For example; part number TP444-3M-09 denotes TP for Twin Power, 444mm pitch, 3mm pitch length and 9mm width.

Belt **pitch** is the distance in millimeters between two adjacent tooth centers as measured on the pitch line of the belt. Belt **pitch length** is the total length (circumference) in millimeters as measured along the pitch line. The theoretical pitch line of a PowerGrip HTD Twin Power belt lies within the tensile member.

Product No. Series 9252

3mm Pitch

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP381-3M	127	15.00	381
TP396-3M	132	15.59	396
TP399-3M	133	15.71	399
TP405-3M	135	15.94	404
TP411-3M	137	16.18	410
TP417-3M	139	16.42	417
TP420-3M	140	16.54	420
TP426-3M	142	16.77	425
TP432-3M	144	17.01	432
TP435-3M	145	17.13	435
TP438-3M	146	17.24	437
TP447-3M	149	17.60	447
TP468-3M	156	18.43	468
TP471-3M	157	18.54	470
TP474-3M	158	18.66	473
TP480-3M	160	18.90	480
TP486-3M	162	19.13	485
TP489-3M	163	19.25	488
TP492-3M	164	19.37	492
TP501-3M	167	19.72	500

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP510-3M	170	20.08	510
TP513-3M	171	20.20	513
TP525-3M	175	20.67	525
TP528-3M	176	20.79	528
TP531-3M	177	20.91	531
TP537-3M	179	21.14	536
TP558-3M	186	21.97	558
TP564-3M	188	22.20	563
TP570-3M	190	22.44	569
TP576-3M	192	22.68	576
TP585-3M	195	23.03	584
TP591-3M	197	23.07	585
TP597-3M	199	23.50	596
TP600-3M	200	23.62	599
TP606-3M	202	23.86	606
TP609-3M	203	23.98	609
TP612-3M	204	24.09	611
TP627-3M	209	24.69	627
TP633-3M	211	24.92	632
TP639-3M	213	25.16	639

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP645-3M	215	25.39	644
TP648-3M	216	25.51	647
TP654-3M	218	25.75	657
TP657-3M	219	25.87	662
TP663-3M	221	26.10	669
TP669-3M	223	26.34	669
TP684-3M	228	26.93	684
TP687-3M	229	27.05	687
TP696-3M	232	27.40	695
TP711-3M	237	27.99	710
TP735-3M	245	28.94	735
TP738-3M	246	29.06	738
TP753-3M	251	29.65	753
TP795-3M	265	31.30	795
TP822-3M	274	32.36	821
TP837-3M	279	32.95	836
TP843-3M	281	33.19	843
TP873-3M	291	34.37	873
TP882-3M	294	34.72	881
TP891-3M	297	35.08	891



PowerGrip® HTD® Twin Power® Belts

Product No. Series 9252 (continued)

3mm Pitch (continued)

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP900-3M	300	35.43	899
TP915-3M	305	36.02	914
TP945-3M	315	37.20	944
TP951-3M	317	37.44	950
TP981-3M	327	38.62	980
TP1002-3M	334	39.45	1002

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP1026-3M	342	40.39	1025
TP1035-3M	345	40.75	1035
TP1062-3M	354	41.81	1061
TP1125-3M	375	44.29	1124
TP1155-3M	385	45.47	1154
TP1191-3M	397	46.89	1191

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP1263-3M	421	49.72	1262
TP1500-3M	500	59.06	1500
TP1512-3M	504	59.53	1512
TP1587-3M	529	62.48	1587
TP1956-3M	652	77.01	1956
TP2004-3M	668	78.90	2004

5mm Pitch

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP400-5M	80	15.75	400
TP415-5M	83	16.34	415
TP450-5M	90	17.72	450
TP460-5M	92	18.11	460
TP475-5M	95	18.70	475
TP480-5M	96	18.90	480
TP495-5M	99	19.49	495
TP500-5M	100	19.69	500
TP520-5M	104	20.47	520
TP535-5M	107	21.06	535
TP555-5M	111	21.85	555
TP565-5M	113	22.24	565
TP580-5M	116	22.83	580
TP585-5M	117	23.03	585
TP600-5M	120	23.62	600
TP615-5M	123	24.21	615
TP635-5M	127	25.00	635
TP655-5M	131	25.79	655
TP665-5M	133	26.18	665
TP670-5M	134	26.38	671
TP680-5M	136	26.77	680
TP685-5M	137	29.97	761
TP695-5M	139	29.36	746

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP710-5M	142	27.95	710
TP740-5M	148	29.13	740
TP745-5M	149	29.33	745
TP765-5M	153	30.12	765
TP790-5M	158	31.10	790
TP800-5M	160	31.50	800
TP830-5M	166	32.68	830
TP835-5M	167	32.87	835
TP850-5M	170	33.46	850
TP870-5M	174	34.25	870
TP890-5M	178	35.04	890
TP925-5M	185	36.42	925
TP950-5M	190	37.40	950
TP975-5M	195	38.39	975
TP985-5M	197	38.78	985
TP1000-5M	200	39.37	1000
TP1050-5M	210	41.34	1050
TP1115-5M	223	43.90	1115
TP1125-5M	225	44.29	1125
TP1195-5M	239	47.05	1195
TP1250-5M	250	49.21	1250
TP1270-5M	254	50.00	1270
TP1295-5M	259	50.98	1295

Part No.	No. of Teeth	Pitch Length (In.)	Pitch Length (mm)
TP1375-5M	275	64.13	1629
TP1420-5M	284	55.91	1420
TP1575-5M	315	62.01	1575
TP1595-5M	319	62.80	1595
TP1635-5M	327	64.37	1635
TP1690-5M	338	66.54	1690
TP1720-5M	344	67.72	1720
TP1790-5M	358	70.47	1790
TP1800-5M	360	70.87	1800
TP1895-5M	379	74.61	1895
TP1945-5M	389	76.57	1945
TP1980-5M	396	77.95	1980
TP2000-5M	400	78.74	2000
TP2110-5M	422	83.07	2110
TP2250-5M	450	88.58	2250
TP2525-5M	505	99.41	2525
TP2760-5M	552	108.66	2760
TP3120-5M	624	122.83	3120
TP3170-5M	634	124.80	3170
TP3430-5M	686	135.04	3430
TP3800-5M	760	149.61	3800



PowerGrip® Twin Power® Timing Belts


Twin Power belts have teeth on both sides to provide synchronization from both driving surfaces.

Markets/Applications

PowerGrip Twin Power Timing belts are suitable for all industrial serpentine applications requiring rotation reversal in some driven shafts.

Features/Advantages

- Gates Twin Power belts have **nylon facing** on both tooth surfaces providing equal load carrying capabilities on either side of belt.
- Belt capacity is equal to standard single-sided PowerGrip Timing belts.
- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- Quieter than roller chain drives and eliminates lubrication and re-tensioning to reduce maintenance and labor.



Recommended Pulleys—PowerGrip Timing Pulleys

Notes

Gates PowerGrip Twin Power Timing belt part numbers are comprised of pitch length, pitch and width. TP denotes Twin Power.

Length — The length is shown in the first part of the belt designation. The first number is the pitch length in tenths of an inch. A TP300L075 has a 30.0" pitch length.

Pitch — The pitch of a PowerGrip Twin Power Timing belt is the distance from center to center of the teeth (in inches). It is shown in the second part of the belt designation by a letter or letters. Part number TP300L075 has a .375" pitch. The letters correspond to pitches as follows:

XL = Extra Light = 0.200" pitch;

L = Light = 0.375" pitch;

H = Heavy = 0.500" pitch.

Width — The width is shown in the last part of the belt designation. Part number TP300L075 is .75" wide.

Product No. Series 9246

1/5" Pitch (.200"/XL) — 1/4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)	Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP126XL025	9246-1169	63	12.60	.01	TP184XL025	9246-1192	92	18.40	.03
TP128XL025	9246-1170	64	12.80	.01	TP186XL025	9246-1193	93	18.60	.03
TP130XL025	9246-1107	65	13.00	.01	TP188XL025	9246-1194	94	18.80	.03
TP132XL025	9246-1171	66	13.20	.01	TP190XL025	9246-1113	95	19.00	.03
TP134XL025	9246-1172	67	13.40	.01	TP192XL025	9246-1195	96	19.20	.03
TP136XL025	9246-1173	68	13.60	.01	TP200XL025	9246-1114	100	20.00	.01
TP138XL025	9246-1174	69	13.80	.01	TP202XL025	9246-1197	101	20.20	.03
TP140XL025	9246-1108	70	14.00	.01	TP204XL025	9246-1198	102	20.40	.03
TP142XL025	9246-1175	71	14.20	.01	TP206XL025	9246-1199	103	20.60	.03
TP144XL025	9246-1176	72	14.40	.01	TP210XL025	9246-1115	105	21.00	.03
TP146XL025	9246-1177	73	14.60	.01	TP212XL025	9246-8100	106	21.20	.03
TP148XL025	9246-1178	74	14.80	.01	TP214XL025	9246-8101	107	21.40	.03
TP150XL025	9246-1109	75	15.00	.01	TP218XL025	9246-8102	109	21.80	.03
TP152XL025	9246-1179	76	15.20	.01	TP220XL025	9246-1116	110	22.00	.03
TP156XL025	9246-1181	78	15.60	.01	TP222XL025	9246-8103	111	22.20	.03
TP158XL025	9246-1182	79	15.80	.01	TP226XL025	9246-8104	113	22.60	.03
TP160XL025	9246-1110	80	16.00	.01	TP228XL025	9246-8105	114	22.80	.03
TP162XL025	9246-1183	81	16.20	.01	TP230XL025	9246-1117	115	23.00	.03
TP166XL025	9246-1185	83	16.60	.01	TP232XL025	9246-8106	116	23.20	.03
TP168XL025	9246-1186	84	16.80	.01	TP234XL025	9246-8107	117	23.40	.03
TP170XL025	9246-1111	85	17.00	.02	TP236XL025	9246-8108	118	23.60	.03
TP172XL025	9246-1187	86	17.20	.02	TP240XL025	9246-1118	120	24.00	.03
TP174XL025	9246-1188	87	17.40	.02	TP244XL025	9246-8109	122	24.40	.03
TP176XL025	9246-1189	88	17.60	.02	TP246XL025	9246-8110	123	24.60	.03
TP178XL025	9246-1190	89	17.80	.02	TP250XL025	9246-1119	125	25.00	.03
TP180XL025	9246-1112	90	18.00	.03	TP254XL025	9246-8111	127	25.40	.03
TP182XL025	9246-1191	91	18.20	.03	TP258XL025	9246-8112	129	25.80	.03



PowerGrip® Twin Power® Timing Belts

Product No. Series 9246 (continued)

1/5" Pitch (.200"/XL) — 1/4" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP260XL025	9246-1120	130	26.00	.03
TP262XL025	9246-8113	131	26.20	.03
TP264XL025	9246-8114	132	26.40	.03
TP266XL025	9246-8115	133	26.60	.03
TP268XL025	9246-8116	134	26.80	.03
TP270XL025	9246-8148	135	27.00	.03
TP274XL025	9246-8117	137	27.40	.03
TP280XL025	9246-1122	140	28.00	.03
TP286XL025	9246-8118	143	28.60	.03
TP290XL025	9246-1123	145	29.00	.04
TP296XL025	9246-8119	148	29.60	.04
TP300XL025	9246-1124	150	30.00	.04
TP306XL025	9246-8120	153	30.60	.04
TP310XL025	9246-1125	155	31.00	.04
TP316XL025	9246-8121	158	31.60	.04
TP320XL025	9246-8122	160	32.00	.04
TP322XL025	9246-8123	161	32.20	.04
TP330XL025	9246-1126	165	33.00	.04
TP338XL025	9246-8124	169	33.80	.04
TP340XL025	9246-1128	170	34.00	.05
TP344XL025	9246-8125	172	34.40	.05
TP348XL025	9246-8126	174	34.80	.05
TP350XL025	9246-1127	175	35.00	.05
TP352XL025	9246-8146	176	35.20	.05
TP362XL025	9246-8127	181	36.20	.05
TP370XL025	9246-1129	185	37.00	.05
TP380XL025	9246-1130	190	38.00	.05
TP384XL025	9246-8128	192	38.40	.05

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP390XL025	9246-1131	195	39.00	.05
TP400XL025	9246-1132	200	40.00	.06
TP412XL025	9246-8129	206	41.20	.06
TP420XL025	9246-1133	210	42.00	.06
TP424XL025	9246-8130	212	42.40	.06
TP432XL025	9246-8131	216	43.20	.06
TP438XL025	9246-8132	219	43.80	.06
TP444XL025	9246-8133	222	44.40	.06
TP450XL025	9246-1134	225	45.00	.06
TP454XL025	9246-8134	227	45.40	.07
TP460XL025	9246-1135	230	46.00	.07
TP468XL025	9246-8135	234	46.80	.07
TP480XL025	9246-1136	240	48.00	.08
TP492XL025	9246-8136	246	49.20	.08
TP498XL025	9246-8137	249	49.80	.08
TP500XL025	9246-1137	250	50.00	.08
TP506XL025	9246-8138	253	50.60	.08
TP524XL025	9246-8139	262	52.40	.08
TP570XL025	9246-1138	285	57.00	.08
TP580XL025	9246-8140	290	58.00	.09
TP592XL025	9246-8141	296	59.20	.09
TP612XL025	9246-8142	306	61.20	.09
TP630XL025	9246-1139	315	63.00	.09
TP672XL025	9246-8143	336	67.20	.10
TP690XL025	9246-8147	345	69.00	.10
TP770XL025	9246-1140	385	77.00	.12
TP850XL025	9246-8145	425	85.00	.14

1/5" Pitch (.200"/XL) — 3/8" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP126XL037	9246-1369	63	12.60	.02
TP128XL037	9246-1370	64	12.80	.02
TP130XL037	9246-1307	65	13.00	.05
TP132XL037	9246-1371	66	13.20	.02
TP134XL037	9246-1372	67	13.40	.02
TP136XL037	9246-1373	68	13.60	.02
TP138XL037	9246-1374	69	13.80	.02
TP140XL037	9246-1308	70	14.00	.05
TP142XL037	9246-1375	71	14.20	.02
TP144XL037	9246-1376	72	14.40	.02
TP146XL037	9246-1377	73	14.60	.02
TP148XL037	9246-1378	74	14.80	.02
TP150XL037	9246-1309	75	15.00	.02
TP152XL037	9246-1379	76	15.20	.02
TP156XL037	9246-1381	78	15.60	.02
TP158XL037	9246-1382	79	15.80	.02
TP160XL037	9246-1310	80	16.00	.02
TP162XL037	9246-1383	81	16.20	.02
TP166XL037	9246-1385	83	16.60	.02
TP168XL037	9246-1386	84	16.80	.02
TP170XL037	9246-1311	85	17.00	.03
TP172XL037	9246-1387	86	17.20	.03
TP174XL037	9246-1388	87	17.40	.03
TP176XL037	9246-1389	88	17.60	.03
TP178XL037	9246-1390	89	17.80	.03
TP180XL037	9246-1312	90	18.00	.03
TP182XL037	9246-1391	91	18.20	.03
TP184XL037	9246-1392	92	18.40	.03
TP186XL037	9246-1393	93	18.60	.03

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP188XL037	9246-1394	94	18.80	.04
TP190XL037	9246-1313	95	19.00	.04
TP192XL037	9246-1395	96	19.20	.04
TP200XL037	9246-1314	100	20.00	.02
TP202XL037	9246-1397	101	20.20	.04
TP204XL037	9246-1398	102	20.40	.04
TP206XL037	9246-1399	103	20.60	.04
TP210XL037	9246-1315	105	21.00	.04
TP212XL037	9246-8300	106	21.20	.04
TP214XL037	9246-8301	107	21.40	.04
TP218XL037	9246-8302	109	21.80	.04
TP220XL037	9246-1316	110	22.00	.04
TP222XL037	9246-8303	111	22.20	.04
TP226XL037	9246-8304	113	22.60	.04
TP228XL037	9246-8305	114	22.80	.04
TP230XL037	9246-1317	115	23.00	.04
TP232XL037	9246-8306	116	23.20	.04
TP234XL037	9246-8307	117	23.40	.05
TP236XL037	9246-8308	118	23.60	.05
TP240XL037	9246-1318	120	24.00	.05
TP244XL037	9246-8309	122	24.40	.05
TP246XL037	9246-8310	123	24.60	.05
TP250XL037	9246-1319	125	25.00	.05
TP254XL037	9246-8311	127	25.40	.05
TP258XL037	9246-8312	129	25.80	.05
TP260XL037	9246-1320	130	26.00	.03
TP262XL037	9246-8313	131	26.20	.05
TP264XL037	9246-8314	132	26.40	.05
TP266XL037	9246-8315	133	26.60	.05



PowerGrip® Twin Power® Timing Belts

Product No. Series 9246 (continued)

1/5" Pitch (.200"/XL) — 3/8" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP268XL037	9246-8316	134	26.80	.05
TP270XL037	9246-8348	135	27.00	.05
TP274XL037	9246-8317	137	27.40	.05
TP280XL037	9246-1322	140	28.00	.10
TP286XL037	9246-8318	143	28.60	.05
TP290XL037	9246-1323	145	29.00	.06
TP296XL037	9246-8319	148	29.60	.06
TP300XL037	9246-1324	150	30.00	.15
TP306XL037	9246-8320	153	30.60	.06
TP310XL037	9246-1325	155	31.00	.06
TP316XL037	9246-8321	158	31.60	.06
TP320XL037	9246-8322	160	32.00	.06
TP322XL037	9246-8323	161	32.20	.06
TP330XL037	9246-1326	165	33.00	.04
TP338XL037	9246-8324	169	33.80	.06
TP340XL037	9246-1328	170	34.00	.06
TP344XL037	9246-8325	172	34.40	.06
TP348XL037	9246-8326	174	34.80	.06
TP350XL037	9246-1327	175	35.00	.06
TP352XL037	9246-8346	176	35.20	.06
TP362XL037	9246-8327	181	36.20	.06
TP370XL037	9246-1329	185	37.00	.07
TP380XL037	9246-1330	190	38.00	.07
TP384XL037	9246-8328	192	38.40	.07
TP390XL037	9246-1331	195	39.00	.07
TP400XL037	9246-1332	200	40.00	.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP412XL037	9246-8329	206	41.20	.08
TP420XL037	9246-1333	210	42.00	.08
TP424XL037	9246-8330	212	42.40	.08
TP432XL037	9246-8331	216	43.20	.08
TP438XL037	9246-8332	219	43.80	.08
TP444XL037	9246-8333	222	44.40	.09
TP450XL037	9246-1334	225	45.00	.09
TP454XL037	9246-8334	227	45.40	.09
TP460XL037	9246-1335	230	46.00	.09
TP468XL037	9246-8335	234	46.80	.09
TP480XL037	9246-1336	240	48.00	.09
TP492XL037	9246-8336	246	49.20	.10
TP498XL037	9246-8337	249	49.80	.10
TP500XL037	9246-1337	250	50.00	.10
TP506XL037	9246-8338	253	50.60	.10
TP524XL037	9246-8339	262	52.40	.11
TP570XL037	9246-1338	285	57.00	.11
TP580XL037	9246-8340	290	58.00	.12
TP592XL037	9246-8341	296	59.20	.12
TP612XL037	9246-8342	306	61.20	.12
TP630XL037	9246-1339	315	63.00	.13
TP672XL037	9246-8343	336	67.20	.13
TP690XL037	9246-8347	345	69.00	.14
TP770XL037	9246-1340	385	77.00	.15
TP850XL037	9246-8345	425	85.00	.17

3/8" Pitch (.375"/L) — 1/2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP150L050	9246-2101	40	15.00	.06
TP154L050	9246-2127	41	15.38	.06
TP158L050	9246-2128	42	15.75	.06
TP165L050	9246-2121	44	16.50	.06
TP173L050	9246-2129	46	17.25	.06
TP176L050	9246-7133	47	17.63	.06
TP187L050	9246-2102	50	18.75	.10
TP195L050	9246-2122	52	19.50	.07
TP199L050	9246-7134	53	19.88	.07
TP210L050	9246-2103	56	21.00	.07
TP218L050	9246-7136	58	21.75	.07
TP225L050	9246-2104	60	22.50	.10
TP240L050	9246-2105	64	24.00	.71
TP248L050	9246-7137	66	24.75	.08
TP255L050	9246-2106	68	25.50	.06
TP263L050	9246-7138	70	26.25	.09
TP270L050	9246-2107	72	27.00	.06
TP285L050	9246-2108	76	28.50	.07
TP300L050	9246-2109	80	30.00	.10

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP315L050	9246-2123	84	31.50	.10
TP322L050	9246-2110	86	32.25	.10
TP345L050	9246-2111	92	34.50	.07
TP367L050	9246-2112	98	36.75	.10
TP375L050	9246-7139	100	37.50	.12
TP390L050	9246-2113	104	39.00	.10
TP420L050	9246-2114	112	42.00	.09
TP446L050	9246-7140	119	44.63	.15
TP450L050	9246-2115	120	45.00	.11
TP480L050	9246-2116	128	48.00	.10
TP510L050	9246-2117	136	51.00	.12
TP540L050	9246-2118	144	54.00	.15
TP566L050	9246-7141	151	56.63	.19
TP600L050	9246-2119	160	60.00	.20
TP660L050	9246-2120	176	66.00	.22
TP720L050	9246-7145	192	72.00	.24
TP817L050	9246-2125	218	81.75	.27
TP900L050	9246-2126	240	90.00	.30
TP945L050	9246-7148	252	94.50	.33

3/8" Pitch (.375"/L) — 3/4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP150L075	9246-2201	40	15.00	.08
TP154L075	9246-2227	41	15.38	.08
TP158L075	9246-2228	42	15.75	.08
TP165L075	9246-2221	44	16.50	.08
TP173L075	9246-2229	46	17.25	.08
TP176L075	9246-7223	47	17.63	.08

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP187L075	9246-2202	50	18.75	.08
TP195L075	9246-2222	52	19.50	.10
TP199L075	9246-7234	53	19.88	.10
TP210L075	9246-2203	56	21.00	.08
TP218L075	9246-7236	58	21.75	.10
TP225L075	9246-2204	60	22.50	.10



PowerGrip® Twin Power® Timing Belts

Product No. Series 9246 (continued)

3/8" Pitch (.375"/L) — 3/4" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP240L075	9246-2205	64	24.00	.12
TP248L075	9246-7237	66	24.75	.12
TP255L075	9246-2206	68	25.50	.12
TP263L075	9246-7238	70	26.25	.13
TP270L075	9246-2207	72	27.00	.13
TP285L075	9246-2208	76	28.50	.10
TP300L075	9246-2209	80	30.00	.14
TP315L075	9246-2223	84	31.50	.15
TP322L075	9246-2210	86	32.25	.16
TP345L075	9246-2211	92	34.50	.12
TP367L075	9246-2212	98	36.75	.17
TP375L075	9246-7239	100	37.50	.17
TP390L075	9246-2213	104	39.00	.18

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP420L075	9246-2214	112	42.00	.05
TP446L075	9246-7240	119	44.63	.20
TP450L075	9246-2215	120	45.00	.17
TP480L075	9246-2216	128	48.00	.16
TP510L075	9246-2217	136	51.00	.20
TP540L075	9246-2218	144	54.00	.35
TP566L075	9246-7241	151	56.63	.27
TP600L075	9246-2219	160	60.00	.30
TP660L075	9246-2220	176	66.00	.33
TP720L075	9246-7245	192	72.00	.36
TP817L075	9246-2225	218	81.75	.41
TP900L075	9246-2226	240	90.00	.45
TP945L075	9246-7248	252	94.50	.47

3/8" Pitch (.375"/L) — 1" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP150L100	9246-2301	40	15.00	.11
TP154L100	9246-2327	41	15.38	.11
TP158L100	9246-2328	42	15.75	.11
TP165L100	9246-2321	44	16.50	.12
TP173L100	9246-2329	46	17.25	.12
TP176L100	9246-7333	47	17.63	.12
TP187L100	9246-2302	50	18.75	.12
TP195L100	9246-2322	52	19.50	.13
TP199L100	9246-7334	53	19.88	.13
TP210L100	9246-2303	56	21.00	.13
TP218L100	9246-7336	58	21.75	.13
TP225L100	9246-2304	60	22.50	.14
TP240L100	9246-2305	64	24.00	.16
TP248L100	9246-7337	66	24.75	.17
TP255L100	9246-2306	68	25.50	.17
TP263L100	9246-7338	70	26.25	.17
TP270L100	9246-2307	72	27.00	.17
TP285L100	9246-2308	76	28.50	.18
TP300L100	9246-2309	80	30.00	.30

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP315L100	9246-2323	84	31.50	.21
TP322L100	9246-2310	86	32.25	.21
TP345L100	9246-2311	92	34.50	.15
TP367L100	9246-2312	98	36.75	.23
TP375L100	9246-7339	100	37.50	.24
TP390L100	9246-2313	104	39.00	.25
TP420L100	9246-2314	112	42.00	.20
TP446L100	9246-7340	119	44.63	.28
TP450L100	9246-2315	120	45.00	.29
TP480L100	9246-2316	128	48.00	.20
TP510L100	9246-2317	136	51.00	.34
TP540L100	9246-2318	144	54.00	.25
TP566L100	9246-7341	151	56.63	.36
TP600L100	9246-2319	160	60.00	.30
TP660L100	9246-2320	176	66.00	.30
TP720L100	9246-7345	192	72.00	.48
TP817L100	9246-2325	218	81.75	.55
TP900L100	9246-2326	240	90.00	.61
TP945L100	9246-7348	252	94.50	.65

1/2" Pitch (.500"/H) — 3/4" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP210H075	9246-3125	42	21.00	.15
TP220H075	9246-3126	44	22.00	.16
TP225H075	9246-3145	45	22.50	.17
TP230H075	9246-3127	46	23.00	.17
TP240H075	9246-3100	48	24.00	.18
TP270H075	9246-3101	54	27.00	.20
TP300H075	9246-3102	60	30.00	.22
TP310H075	9246-3103	62	31.00	.23
TP315H075	9246-3147	63	31.50	.23
TP320H075	9246-3128	64	32.00	.24
TP330H075	9246-3124	66	33.00	.24
TP340H075	9246-3129	68	34.00	.25
TP350H075	9246-3130	70	35.00	.25
TP360H075	9246-3104	72	36.00	.26
TP370H075	9246-3131	74	37.00	.27
TP390H075	9246-3105	78	39.00	.29
TP400H075	9246-3132	80	40.00	.30
TP410H075	9246-3133	82	41.00	.30
TP415H075	9246-3148	83	41.50	1.23

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP420H075	9246-3106	84	42.00	.31
TP445H075	9246-3149	89	44.50	.31
TP450H075	9246-3107	90	45.00	.25
TP455H075	9246-8150	91	45.50	.32
TP465H075	9246-8151	93	46.50	.33
TP480H075	9246-3108	96	48.00	.35
TP490H075	9246-3134	98	49.00	.34
TP495H075	9246-8152	99	49.50	.34
TP510H075	9246-3109	102	51.00	.25
TP525H075	9246-8153	105	52.50	.36
TP540H075	9246-3110	108	54.00	.37
TP555H075	9246-8154	111	55.50	.38
TP560H075	9246-3135	112	56.00	.39
TP570H075	9246-3111	114	57.00	.42
TP585H075	9246-3136	117	58.50	.42
TP600H075	9246-3112	120	60.00	.43
TP605H075	9246-8155	121	60.50	.43
TP630H075	9246-3113	126	63.00	.30
TP645H075	9246-3137	129	64.50	.44



PowerGrip® Twin Power® Timing Belts

Product No. Series 9246 (continued)

1/2" Pitch (.500"/H) — 3/4" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP655H075	9246-8156	131	65.50	.45
TP660H075	9246-3114	132	66.00	.48
TP700H075	9246-3115	140	70.00	.35
TP730H075	9246-3138	146	73.00	.54
TP750H075	9246-3116	150	75.00	.55
TP775H075	9246-8158	155	77.50	.55
TP780H075	9246-3139	156	78.00	.57
TP800H075	9246-3117	160	80.00	.35
TP820H075	9246-3140	164	82.00	.60
TP840H075	9246-3141	168	84.00	.61
TP850H075	9246-3118	170	85.00	.40
TP900H075	9246-3119	180	90.00	.66
TP960H075	9246-3142	192	96.00	.70
TP1000H075	9246-3120	200	100.00	.73

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1100H075	9246-3121	220	110.00	.81
TP1140H075	9246-3143	228	114.00	.83
TP1180H075	9246-8161	236	118.00	.86
TP1250H075	9246-3122	250	125.00	.91
TP1400H075	9246-3123	280	140.00	1.02
TP1510H075	9246-8165	302	151.00	1.09
TP1550H075	9246-3144	310	155.00	1.13
TP1645H075	9246-8166	329	164.50	1.18
TP1680H075	9246-8167	336	168.00	1.21
TP1700H075	9246-3146	340	170.00	1.23
TP2090H075	9246-8168	418	209.00	1.52
TP2100H075	9246-8169	420	210.00	1.53
TP2120H075	9246-8170	424	212.00	1.54
TP2330H075	9246-8171	466	233.00	1.68

1/2" Pitch (.500"/H) — 1" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP210H100	9246-3225	42	21.00	.22
TP220H100	9246-3226	44	22.00	.23
TP225H100	9246-3245	45	22.50	.24
TP230H100	9246-3227	46	23.00	.25
TP240H100	9246-3200	48	24.00	.25
TP270H100	9246-3201	54	27.00	.27
TP300H100	9246-3202	60	30.00	.20
TP315H100	9246-3247	63	31.50	.31
TP320H100	9246-3228	64	32.00	.32
TP330H100	9246-3224	66	33.00	.30
TP340H100	9246-3229	68	34.00	.34
TP350H100	9246-3230	70	35.00	.34
TP360H100	9246-3204	72	36.00	.25
TP370H100	9246-3231	74	37.00	.37
TP390H100	9246-3205	78	39.00	.40
TP400H100	9246-3232	80	40.00	.40
TP410H100	9246-3233	82	41.00	.41
TP415H100	9246-3248	83	41.50	.42
TP420H100	9246-3206	84	42.00	.30
TP445H100	9246-3249	89	44.50	.45
TP450H100	9246-3207	90	45.00	.50
TP455H100	9246-8250	91	45.50	.46
TP465H100	9246-8251	93	46.50	.47
TP480H100	9246-3208	96	48.00	.50
TP490H100	9246-3234	98	49.00	.50
TP495H100	9246-8252	99	49.50	.50
TP510H100	9246-3209	102	51.00	.51
TP525H100	9246-8253	105	52.50	.52
TP540H100	9246-3210	108	54.00	.50
TP555H100	9246-8254	111	55.50	.55
TP560H100	9246-3235	112	56.00	.56
TP570H100	9246-3211	114	57.00	.60
TP585H100	9246-3236	117	58.50	.59

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP600H100	9246-3212	120	60.00	.60
TP605H100	9246-8255	121	60.50	.61
TP630H100	9246-3213	126	63.00	.65
TP645H100	9246-3237	129	64.50	.64
TP655H100	9246-8256	131	65.50	.65
TP660H100	9246-3214	132	66.00	.70
TP700H100	9246-3215	140	70.00	.75
TP730H100	9246-3238	146	73.00	.73
TP750H100	9246-3216	150	75.00	.75
TP775H100	9246-8258	155	77.50	.77
TP780H100	9246-3239	156	78.00	.78
TP800H100	9246-3217	160	80.00	.80
TP820H100	9246-3240	164	82.00	.82
TP840H100	9246-3241	168	84.00	.84
TP850H100	9246-3218	170	85.00	.80
TP900H100	9246-3219	180	90.00	.60
TP960H100	9246-3242	192	96.00	.96
TP1000H100	9246-3220	200	100.00	.65
TP1100H100	9246-3221	220	110.00	1.10
TP1140H100	9246-3243	228	114.00	1.10
TP1180H100	9246-8261	236	118.00	1.12
TP1250H100	9246-3222	250	125.00	.70
TP1400H100	9246-3223	280	140.00	1.39
TP1510H100	9246-8265	302	151.00	1.50
TP1550H100	9246-3244	310	155.00	1.54
TP1645H100	9246-8266	329	164.50	1.63
TP1680H100	9246-8267	336	168.00	1.67
TP1700H100	9246-3246	340	170.00	1.69
TP2090H100	9246-8268	418	209.00	2.08
TP2100H100	9246-8269	420	210.00	2.09
TP2120H100	9246-8270	424	212.00	2.11
TP2330H100	9246-8271	466	233.00	2.32

1/2" Pitch (.500"/H) — 1 1/2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP210H150	9246-3325	42	21.00	.33
TP220H150	9246-3326	44	22.00	.35
TP225H150	9246-3345	45	22.50	.36
TP230H150	9246-3327	46	23.00	.37

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP240H150	9246-3300	48	24.00	.38
TP270H150	9246-3301	54	27.00	.40
TP300H150	9246-3302	60	30.00	.50
TP310H150	9246-3303	62	31.00	.48



PowerGrip® Twin Power® Timing Belts

Product No. Series 9246 (continued)

1/2" Pitch (.500"/H) — 1 1/2" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP315H150	9246-3347	63	31.50	.49
TP320H150	9246-3328	64	32.00	.50
TP330H150	9246-3324	66	33.00	.52
TP340H150	9246-3329	68	34.00	.54
TP350H150	9246-3330	70	35.00	.56
TP360H150	9246-3304	72	36.00	.59
TP370H150	9246-3331	74	37.00	.59
TP390H150	9246-3305	78	39.00	.35
TP400H150	9246-3332	80	40.00	.61
TP410H150	9246-3333	82	41.00	.62
TP415H150	9246-3348	83	41.50	.63
TP420H150	9246-3306	84	42.00	.60
TP445H150	9246-3349	89	44.50	.67
TP450H150	9246-3307	90	45.00	.68
TP455H150	9246-8350	91	45.50	.69
TP465H150	9246-8351	93	46.50	.71
TP480H150	9246-3308	96	48.00	.73
TP490H150	9246-3334	98	49.00	.74
TP495H150	9246-8352	99	49.50	.75
TP510H150	9246-3309	102	51.00	.77
TP525H150	9246-8353	105	52.50	.80
TP540H150	9246-3310	108	54.00	.55
TP555H150	9246-8354	111	55.50	.84
TP560H150	9246-3335	112	56.00	.85
TP570H150	9246-3311	114	57.00	.55
TP585H150	9246-3336	117	58.50	.74
TP600H150	9246-3312	120	60.00	.62
TP605H150	9246-8355	121	60.50	.74
TP630H150	9246-3313	126	63.00	.65

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP645H150	9246-3337	129	64.50	.74
TP655H150	9246-8356	131	65.50	.74
TP660H150	9246-3314	132	66.00	.68
TP700H150	9246-3315	140	70.00	.72
TP730H150	9246-3338	146	73.00	.76
TP750H150	9246-3316	150	75.00	.78
TP775H150	9246-8358	155	77.50	.79
TP780H150	9246-3339	156	78.00	.80
TP800H150	9246-3317	160	80.00	.83
TP820H150	9246-3340	164	82.00	.84
TP840H150	9246-3341	168	84.00	.86
TP850H150	9246-3318	170	85.00	.88
TP900H150	9246-3319	180	90.00	.95
TP960H150	9246-3342	192	96.00	.99
TP1000H150	9246-3320	200	100.00	1.10
TP1100H150	9246-3321	220	110.00	1.14
TP1140H150	9246-3343	228	114.00	1.17
TP1180H150	9246-8361	236	118.00	1.20
TP1250H150	9246-3322	250	125.00	1.25
TP1400H150	9246-3323	280	140.00	1.45
TP1510H150	9246-8365	302	151.00	1.52
TP1550H150	9246-3344	310	155.00	1.65
TP1645H150	9246-8366	329	164.50	.74
TP1680H150	9246-8367	336	168.00	1.89
TP1700H150	9246-3346	340	170.00	2.11
TP2090H150	9246-8368	418	209.00	2.11
TP2100H150	9246-8369	420	210.00	2.28
TP2120H150	9246-8370	424	212.00	2.34
TP2330H150	9246-8371	466	233.00	2.48

1/2" Pitch (.500"/H) — 2" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP210H200	9246-3425	42	21.00	.43
TP220H200	9246-3426	44	22.00	.45
TP225H200	9246-3445	45	22.50	.46
TP230H200	9246-3427	46	23.00	.47
TP240H200	9246-3400	48	24.00	.49
TP270H200	9246-3401	54	27.00	.57
TP300H200	9246-3402	60	30.00	.61
TP310H200	9246-3403	62	31.00	.63
TP315H200	9246-3447	63	31.50	.64
TP320H200	9246-3428	64	32.00	.66
TP330H200	9246-3424	66	33.00	.68
TP340H200	9246-3429	68	34.00	.69
TP350H200	9246-3430	70	35.00	.70
TP360H200	9246-3404	72	36.00	.34
TP370H200	9246-3431	74	37.00	.75
TP390H200	9246-3405	78	39.00	.79
TP400H200	9246-3432	80	40.00	.80
TP410H200	9246-3433	82	41.00	.83
TP415H200	9246-3448	83	41.50	.84
TP420H200	9246-3406	84	42.00	.85
TP445H200	9246-3449	89	44.50	.90
TP450H200	9246-3407	90	45.00	.91
TP455H200	9246-8450	91	45.50	.92
TP465H200	9246-8451	93	46.50	.94
TP480H200	9246-3408	96	48.00	.98
TP490H200	9246-3434	98	49.00	.99
TP495H200	9246-8452	99	49.50	1.00
TP510H200	9246-3409	102	51.00	.70

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP525H200	9246-8453	105	52.50	1.06
TP540H200	9246-3410	108	54.00	1.09
TP555H200	9246-8454	111	55.50	1.12
TP560H200	9246-3435	112	56.00	1.13
TP570H200	9246-3411	114	57.00	1.16
TP585H200	9246-3436	117	58.50	1.18
TP600H200	9246-3412	120	60.00	1.21
TP605H200	9246-8455	121	60.50	1.22
TP630H200	9246-3413	126	63.00	1.27
TP645H200	9246-3437	129	64.50	1.29
TP655H200	9246-8456	131	65.50	1.32
TP660H200	9246-3414	132	66.00	1.33
TP700H200	9246-3415	140	70.00	.95
TP730H200	9246-3438	146	73.00	1.47
TP750H200	9246-3416	150	75.00	1.60
TP775H200	9246-8458	155	77.50	1.56
TP780H200	9246-3439	156	78.00	1.57
TP800H200	9246-3417	160	80.00	1.35
TP820H200	9246-3440	164	82.00	1.65
TP840H200	9246-3441	168	84.00	1.69
TP850H200	9246-3418	170	85.00	1.72
TP900H200	9246-3419	180	90.00	1.82
TP960H200	9246-3442	192	96.00	1.94
TP1000H200	9246-3420	200	100.00	2.25
TP1100H200	9246-3421	220	110.00	2.20
TP1140H200	9246-3443	228	114.00	2.30
TP1180H200	9246-8461	236	118.00	2.38
TP1250H200	9246-3422	250	125.00	2.52



PowerGrip® Twin Power® Timing Belts

Product No. Series 9246 (continued)

1/2" Pitch (.500"/H) — 2" Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1400H200	9246-3423	280	140.00	2.82
TP1510H200	9246-8465	302	151.00	3.04
TP1550H200	9246-3444	310	155.00	3.12
TP1645H200	9246-8466	329	164.50	3.31
TP1680H200	9246-8467	336	168.00	3.38

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP1700H200	9246-3446	340	170.00	3.42
TP2090H200	9246-8468	418	209.00	4.20
TP2100H200	9246-8469	420	210.00	4.22
TP2120H200	9246-8470	424	212.00	4.26
TP2330H200	9246-8471	466	233.00	4.68

1/2" Pitch (.500"/H) — 3" Wide

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP210H300	9246-3525	42	21.00	.66
TP220H300	9246-3526	44	22.00	.69
TP225H300	9246-3545	45	22.50	.71
TP230H300	9246-3527	46	23.00	.73
TP240H300	9246-3500	48	24.00	.75
TP270H300	9246-3501	54	27.00	.82
TP300H300	9246-3502	60	30.00	.91
TP310H300	9246-3503	62	31.00	.94
TP315H300	9246-3547	63	31.50	.95
TP320H300	9246-3528	64	32.00	.96
TP330H300	9246-3524	66	33.00	.98
TP340H300	9246-3529	68	34.00	1.01
TP350H300	9246-3530	70	35.00	1.04
TP360H300	9246-3504	72	36.00	1.09
TP370H300	9246-3531	74	37.00	1.14
TP390H300	9246-3505	78	39.00	1.18
TP400H300	9246-3532	80	40.00	1.23
TP410H300	9246-3533	82	41.00	1.25
TP415H300	9246-3548	83	41.50	1.26
TP420H300	9246-3506	84	42.00	1.27
TP445H300	9246-3549	89	44.50	1.36
TP450H300	9246-3507	90	45.00	1.37
TP455H300	9246-8550	91	45.50	1.39
TP465H300	9246-8551	93	46.50	1.42
TP480H300	9246-3508	96	48.00	1.46
TP490H300	9246-3534	98	49.00	1.48
TP495H300	9246-8552	99	49.50	1.49
TP510H300	9246-3509	102	51.00	1.55
TP525H300	9246-8553	105	52.50	1.60
TP540H300	9246-3510	108	54.00	1.64
TP555H300	9246-8554	111	55.50	1.68
TP560H300	9246-3535	112	56.00	1.70
TP570H300	9246-3511	114	57.00	1.73

Part No.	Product No.	No. of Teeth	Pitch Length (In.)	Wt. Ea. (Lbs.)
TP585H300	9246-3536	117	58.50	1.77
TP600H300	9246-3512	120	60.00	1.22
TP605H300	9246-8555	121	60.50	1.84
TP630H300	9246-3513	126	63.00	1.91
TP645H300	9246-3537	129	64.50	1.95
TP655H300	9246-8556	131	65.50	1.97
TP660H300	9246-3514	132	66.00	1.37
TP700H300	9246-3515	140	70.00	2.13
TP730H300	9246-3538	146	73.00	2.23
TP750H300	9246-3516	150	75.00	2.30
TP775H300	9246-8558	155	77.50	2.36
TP780H300	9246-3539	156	78.00	2.38
TP800H300	9246-3517	160	80.00	2.43
TP820H300	9246-3540	164	82.00	2.49
TP840H300	9246-3541	168	84.00	2.54
TP850H300	9246-3518	170	85.00	2.59
TP900H300	9246-3519	180	90.00	2.73
TP960H300	9246-3542	192	96.00	2.94
TP1000H300	9246-3520	200	100.00	3.06
TP1100H300	9246-3521	220	110.00	3.34
TP1140H300	9246-3543	228	114.00	3.45
TP1180H300	9246-8561	236	118.00	3.63
TP1250H300	9246-3522	250	125.00	3.80
TP1400H300	9246-3523	280	140.00	2.70
TP1510H300	9246-8565	302	151.00	4.59
TP1550H300	9246-3544	310	155.00	4.71
TP1645H300	9246-8566	329	164.50	5.00
TP1680H300	9246-8567	336	168.00	5.11
TP1700H300	9246-3546	340	170.00	5.16
TP2090H300	9246-8568	418	209.00	6.34
TP2100H300	9246-8569	420	210.00	6.37
TP2120H300	9246-8570	424	212.00	5.03
TP2330H300	9246-8571	466	233.00	7.07



Long-Length PowerGrip® GT®2 Belting

Long-length PowerGrip GT2 belting is a cost effective, low maintenance drive alternative.

Markets/Applications

Well suited for linear movement, positioning and conveying applications.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation. Steel tensile cord is available in some belt types for added length stability.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- The PowerGrip GT2 **belt tooth** is designed for use with a specific sprocket groove profile. The sprocket groove-belt tooth combination increases capacity, while improving registration.
- PowerGrip GT2 has more tooth ratchet resistance than HTD®.
- Eliminates lubrication and re-tensioning reduce maintenance and labor as compared to roller chain drives.
- PowerGrip GT2 belt/sprocket combinations match or exceed the positional accuracy of PowerGrip Timing belt/pulley systems.
- Fully operational in temperature extremes of -65°F to +185°F (-54°C to +85°C).

Recommended Sprockets

PowerGrip GT2 Sprockets

Notes

Minimum order lengths for fiberglass tensile cord belting is 50 feet, ordered in 50 foot increments thereafter.

Minimum order lengths for steel tensile belting is 98 feet, ordered in 98 foot increments thereafter.

Continuous lengths, if needed, must be specified when ordering, and must be ordered in increments of the minimum order quantity (unless ordering the maximum continuous lengths).

Minimum order quantities may vary for non-standard widths. Continuous lengths may require lead times. Check with Customer Service.



Product No. Series 9396

PowerGrip® GT®2 Belting — 2mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL2MR04	9396-0033	4	.01	50 ft.	300 ft.
LL2MR06	9396-0009	6	.01	50 ft.	300 ft.
LL2MR09	9396-0052	9	.02	50 ft.	300 ft.

PowerGrip® GT®2 Belting — 3mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL3MR06	9396-0002	6	.02	50 ft.	600 ft.
LL3MR09	9396-0012	9	.02	50 ft.	385 ft.
LL3MR15	9396-0021	15	.04	50 ft.	240 ft.

PowerGrip® GT®2 Belting — 5mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL5MR09	9396-0020	9	.03	50 ft.	360 ft.
LL5MR15	9396-0025	15	.05	50 ft.	230 ft.

PowerGrip® GT®2 Belting — 8mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL8MR20	9396-0029	20	.08	50 ft.	300 ft.
LL8MR30	9396-0030	30	.13	50 ft.	300 ft.
LL8MR50	9396-0031	50	.21	50 ft.	300 ft.
LL8MR85	9396-0032	85	.36	50 ft.	300 ft.

PowerGrip® GT®2 Belting - Steel Tensile — 5mm Pitch Steel

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL5MR15 ST	9396-10043	15	.18	98 ft.	392 ft.
LL5MR25 ST	9396-40417	25	.23	98 ft.	392 ft.

PowerGrip® GT®2 Belting - Steel Tensile — 8mm Pitch Steel

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL8MR20 ST	9396-10049	20	.29	98 ft.	392 ft.
LL8MR30 ST	9396-10050	30	.37	98 ft.	392 ft.
LL8MR50 ST	9396-40433	50	.53	98 ft.	392 ft.

Long-Length PowerGrip® HTD® Belting

PowerGrip HTD belts have a larger, more robust tooth profile for increased capacity, as compared to timing belts.

Markets/Applications

Long length PowerGrip HTD belting is a cost effective, low maintenance drive alternative that is well suited for linear movement, positing and conveying applications.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation. Steel tensile cord is available in some belt types for added length stability.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Eliminates lubrication and re-tensioning to reduce maintenance and labor required on drives.

Recommended Sprockets

PowerGrip HTD Sprockets

Notes

Minimum order lengths for fiberglass tensile cord belting is 50 feet, ordered in 50 foot increments thereafter.

Minimum order lengths for steel tensile belting is 98 feet, ordered in 98 foot increments thereafter.

Continuous lengths, if needed, must be specified when ordering, and must be ordered in increments of the minimum order quantity (unless ordering the maximum continuous lengths).

Continuous lengths may require lead times.

Minimum order quantities may vary for non-standard widths. Check with Customer Service.



Product No. Series 9308

PowerGrip® HTD® Belting — 3mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL3M06	9308-0044	6	.01	50 ft.	300 ft.
LL3M09	9308-0003	9	.01	50 ft.	300 ft.
LL3M15	9308-0084	15	.01	50 ft.	185 ft.

PowerGrip® HTD® Belting — 14mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL14M40	9308-10009	40	.26	98 ft.	392 ft.
LL14M55	9308-10020	55	.35	98 ft.	392 ft.
LL14M85	9308-10057	85	.55	98 ft.	392 ft.

PowerGrip® HTD® Belting — 5mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL5M09	9308-0045	9	.01	50 ft.	300 ft.
LL5M15	9308-0033	15	.01	50 ft.	185 ft.
LL5M25	9308-0025	25	.05	50 ft.	100 ft.

PowerGrip® HTD® Belting - Steel Tensile — 14mm Pitch Steel

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL14M40 ST	9308-10016	40	.76	98 ft.	392 ft.
LL14M55 ST	9308-10051	55	1.02	98 ft.	392 ft.
LL14M85 ST	9308-10084	85	1.51	98 ft.	392 ft.

PowerGrip® HTD® Belting — 8mm Pitch

Part No.	Product No.	Width (mm)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL8M20	9308-0001	20	.08	50 ft.	300 ft.
LL8M30	9308-0004	30	.13	50 ft.	300 ft.
LL8M50	9308-0005	50	.21	50 ft.	300 ft.
LL8M85	9308-0006	85	.36	50 ft.	300 ft.



Long-Length PowerGrip® Timing Belting

The trapezoidal tooth makes this belt well suited for use in positioning applications.

Markets/Applications

Long length PowerGrip Timing belting is a cost effective, low maintenance drive alternative that is well suited for linear movement, positioning and conveying applications.

Features/Advantages

- **Fiberglass tensile cord** provides high strength, excellent flex life, and high resistance to elongation. Steel tensile cord is available in some belt types for added length stability.
- **Neoprene body** provides protection against grime, grease, oil, and moisture.
- **Nylon tooth facing** provides a durable wear surface for long service life.
- Eliminates lubrication and re-tensioning to reduce maintenance and labor required on drives.

Notes

Minimum order lengths for fiberglass tensile cord belting is 50 feet, ordered in 50 foot increments thereafter.

Minimum order lengths for steel tensile belting is 98 feet, ordered in 98 foot increments thereafter.

Continuous lengths, if needed, must be specified when ordering, and must be ordered in increments of the minimum order quantity (unless ordering the maximum continuous lengths).

Continuous lengths may require lead times.

Minimum order quantities may vary for non-standard widths. Check with Customer Service.



Product No. Series 9314

PowerGrip® Timing Belting — MXL (.080" Pitch)

Part No.	Product No.	Width (In.)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL025MXL	9314-2020	1/4	.01	50 ft.	300 ft.
LL037MXL	9314-2014	3/8	.01	50 ft.	300 ft.
LL050MXL	9314-2038	1/2	.02	50 ft.	300 ft.

PowerGrip® Timing Belting — XL (.200" Pitch)

Part No.	Product No.	Width (In.)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL025XL	9314-0001	1/4	.01	50 ft.	300 ft.
LL037XL	9314-0002	3/8	.02	50 ft.	225 ft.
LL050XL	9314-2012	1/2	.03	50 ft.	150 ft.

PowerGrip® Timing Belting — L (.375" Pitch)

Part No.	Product No.	Width (In.)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL037L	9314-2089	3/8	.03	50 ft.	300 ft.
LL050L	9314-0004	1/2	.02	50 ft.	300 ft.
LL075L	9314-0007	3/4	.04	50 ft.	300 ft.
LL100L	9314-0015	1	.05	50 ft.	300 ft.

PowerGrip® Timing Belting — H (.500" Pitch)

Part No.	Product No.	Width (In.)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL050H	9314-0003	1/2	.04	50 ft.	500 ft.
LL075H	9314-0006	3/4	.06	50 ft.	500 ft.
LL100H	9314-0008	1	.12	50 ft.	500 ft.
LL150H	9314-0017	1 1/2	.12	50 ft.	500 ft.
LL200H	9314-0021	2	.13	50 ft.	500 ft.
LL300H	9314-0025	3	.27	50 ft.	500 ft.

PowerGrip® Timing Belting - Steel Tensile — H (.500" Pitch) Steel

Part No.	Product No.	Width (In.)	Net Wt. per Ft.	Min Order Qty	Max. Cont. Length
LL075H ST	9314-10011	3/4	.22	98 ft.	492 ft.
LL100H ST	9314-10037	1	.25	98 ft.	492 ft.

Synchro-Power® Polyurethane Belts

Endless urethane construction provides higher strength as compared to welded urethane belts, making them well suited for use in power transmission applications.

Markets/Applications

Synchro-Power metric pitch timing belts are ideal for use in office machines, machine tools, postage equipment, sewing machines, vending machines, agriculture, outdoor power equipment, wood and paper, sand/gravel operations, oil fields, food processing and HVAC.

Features/Advantages


- **Steel tensile cord** for length stability.
- Eliminates lubrication and re-tensioning reduce maintenance and labor as compared to roller chain drives.
- Abrasion, chemical, and wear resistant for extended life.
- Temperature ranges from -22°F to +176°F (-30°C to +80°C).

Notes

Synchro-Power belts are available in pitches T5, T10, AT5 and AT10.

Minimum order quantities may apply.

Synchro-Power belts T2.5, DT5, DT10 are available until stock is depleted.



Belt Width (mm)	Belts per Sleeve	Belt Section			
		T 5	T 10	AT 5	AT 10
3	66	N/A	N/A	N/A	N/A
4	50	MTO	N/A	MTO	N/A
6	33	X	MTO	X	MTO
8	25	X	MTO	X	MTO
10	20	X	X	X	MTO
12	16	X	X	X	MTO
14	14	MTO	X	MTO	MTO
16	12	X	X	X	X

Belt Width (mm)	Belts per Sleeve	Belt Section			
		T 5	T 10	AT 5	AT 10
20	10	X	X	X	X
25	8	X	X	X	X
32	6	MTO	X	MTO	X
50	4	MTO	X	MTO	X
75	2	MTO	MTO	MTO	MTO
100	2	MTO	MTO	MTO	MTO
200	1	MTO	MTO	MTO	MTO

		T 5	T 10	AT 5	AT 10
Available Belt Widths	Minimum	4mm	6mm	4mm	6mm
	Maximum	200mm	200mm	200mm	200mm
All belts are available in increments of 1mm from Minimum Width 1mm Width Increments are Made To Order					

Symbol	Gates Minimum Order Quantity Policy - Steel
X	Stock Line Product - No minimum Order Quantity
MTO	Made to Order - Minimum Order Quantity is full sleeve Yield +/- 10%



Synchro-Power® Polyurethane Belts

Product No. Series 7762

T2.5 Pitch — 4mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-4	7762-0001	48	120	.01
T2.5-145-4	7762-0002	59	145	.01
T2.5-160-4	7762-0003	64	160	.01
T2.5-177.5-4	7762-0004	71	177	.01
T2.5-180-4	7762-0005	72	180	.01
T2.5-182.5-4	7762-0006	73	182	.01
T2.5-185-4	7762-0007	74	185	.01
T2.5-200-4	7762-0008	80	200	.01
T2.5-230-4	7762-0009	92	230	.01
T2.5-245-4	7762-0010	98	245	.01
T2.5-265-4	7762-0011	106	265	.01
T2.5-285-4	7762-0012	114	285	.01
T2.5-290-4	7762-0013	116	290	.01
T2.5-305-4	7762-0014	122	305	.01
T2.5-317.5-4	7762-0015	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-4	7762-0016	132	330	.01
T2.5-380-4	7762-0017	152	380	.01
T2.5-395-4	7762-0018	158	395	.01
T2.5-420-4	7762-0019	168	420	.01
T2.5-480-4	7762-0020	192	480	.01
T2.5-500-4	7762-0021	200	500	.01
T2.5-540-4	7762-0022	216	540	.01
T2.5-600-4	7762-0023	240	600	.01
T2.5-620-4	7762-0024	248	620	.01
T2.5-650-4	7762-0025	260	650	.01
T2.5-700-4	7762-0026	280	700	.01
T2.5-780-4	7762-0027	312	780	.01
T2.5-915-4	7762-0028	366	915	.01
T2.5-950-4	7762-0029	380	950	.01

T2.5 Pitch — 6mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-6	7762-0030	48	120	.01
T2.5-145-6	7762-0031	59	145	.01
T2.5-160-6	7762-0032	64	160	.01
T2.5-177.5-6	7762-0033	71	177	.01
T2.5-180-6	7762-0034	72	180	.01
T2.5-182.5-6	7762-0035	73	182	.01
T2.5-185-6	7762-0036	74	185	.01
T2.5-200-6	7762-0037	80	200	.01
T2.5-230-6	7762-0038	92	230	.01
T2.5-245-6	7762-0039	98	245	.01
T2.5-265-6	7762-0040	106	265	.01
T2.5-285-6	7762-0041	114	285	.01
T2.5-290-6	7762-0042	116	290	.01
T2.5-305-6	7762-0043	122	305	.01
T2.5-317.5-6	7762-0044	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-6	7762-0045	132	330	.01
T2.5-380-6	7762-0046	152	380	.01
T2.5-395-6	7762-0047	158	395	.01
T2.5-420-6	7762-0048	168	420	.01
T2.5-480-6	7762-0049	192	480	.01
T2.5-500-6	7762-0050	200	500	.01
T2.5-540-6	7762-0051	216	540	.01
T2.5-600-6	7762-0052	240	600	.01
T2.5-620-6	7762-0053	248	620	.01
T2.5-650-6	7762-0054	260	650	.01
T2.5-700-6	7762-0055	280	700	.01
T2.5-780-6	7762-0056	312	780	.01
T2.5-915-6	7762-0057	366	915	.01
T2.5-950-6	7762-0058	380	950	.01

T2.5 Pitch — 8mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-8	7762-0059	48	120	.01
T2.5-145-8	7762-0060	59	145	.01
T2.5-160-8	7762-0061	64	160	.01
T2.5-177.5-8	7762-0062	71	177	.01
T2.5-180-8	7762-0063	72	180	.01
T2.5-182.5-8	7762-0064	73	182	.01
T2.5-185-8	7762-0065	74	185	.01
T2.5-200-8	7762-0066	80	200	.01
T2.5-230-8	7762-0067	92	230	.01
T2.5-245-8	7762-0068	98	245	.01
T2.5-265-8	7762-0069	106	265	.01
T2.5-285-8	7762-0070	114	285	.01
T2.5-290-8	7762-0071	116	290	.01
T2.5-305-8	7762-0072	122	305	.01
T2.5-317.5-8	7762-0073	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-8	7762-0074	132	330	.01
T2.5-380-8	7762-0075	152	380	.01
T2.5-395-8	7762-0076	158	395	.01
T2.5-420-8	7762-0077	168	420	.01
T2.5-480-8	7762-0078	192	480	.01
T2.5-500-8	7762-0079	200	500	.01
T2.5-540-8	7762-0080	216	540	.01
T2.5-600-8	7762-0081	240	600	.01
T2.5-620-8	7762-0082	248	620	.01
T2.5-650-8	7762-0083	260	650	.01
T2.5-700-8	7762-0084	280	700	.01
T2.5-780-8	7762-0085	312	780	.01
T2.5-915-8	7762-0086	366	915	.01
T2.5-950-8	7762-0087	380	950	.01



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T2.5 Pitch — 10mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-10	7762-0088	48	120	.01
T2.5-145-10	7762-0089	59	145	.01
T2.5-160-10	7762-0090	64	160	.01
T2.5-177.5-10	7762-0091	71	177	.01
T2.5-180-10	7762-0092	72	180	.01
T2.5-182.5-10	7762-0093	73	182	.01
T2.5-185-10	7762-0094	74	185	.01
T2.5-200-10	7762-0095	80	200	.01
T2.5-230-10	7762-0096	92	230	.01
T2.5-245-10	7762-0097	98	245	.01
T2.5-265-10	7762-0098	106	265	.01
T2.5-285-10	7762-0099	114	285	.01
T2.5-290-10	7762-0100	116	290	.01
T2.5-305-10	7762-0101	122	305	.01
T2.5-317.5-10	7762-0102	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-10	7762-0103	132	330	.01
T2.5-380-10	7762-0104	152	380	.01
T2.5-395-10	7762-0105	158	395	.01
T2.5-420-10	7762-0106	168	420	.01
T2.5-480-10	7762-0107	192	480	.01
T2.5-500-10	7762-0108	200	500	.01
T2.5-540-10	7762-0109	216	540	.01
T2.5-600-10	7762-0110	240	600	.01
T2.5-620-10	7762-0111	248	620	.01
T2.5-650-10	7762-0112	260	650	.01
T2.5-700-10	7762-0113	280	700	.01
T2.5-780-10	7762-0114	312	780	.01
T2.5-915-10	7762-0115	366	915	.01
T2.5-950-10	7762-0116	380	950	.01

T2.5 Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-12	7762-0117	48	120	.01
T2.5-145-12	7762-0118	59	145	.01
T2.5-160-12	7762-0119	64	160	.01
T2.5-177.5-12	7762-0120	71	177	.01
T2.5-180-12	7762-0121	72	180	.01
T2.5-182.5-12	7762-0122	73	182	.01
T2.5-185-12	7762-0123	74	185	.01
T2.5-200-12	7762-0124	80	200	.01
T2.5-230-12	7762-0125	92	230	.01
T2.5-245-12	7762-0126	98	245	.01
T2.5-265-12	7762-0127	106	265	.01
T2.5-285-12	7762-0128	114	285	.01
T2.5-290-12	7762-0129	116	290	.01
T2.5-305-12	7762-0130	122	305	.01
T2.5-317.5-12	7762-0131	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-12	7762-0132	132	330	.01
T2.5-380-12	7762-0133	152	380	.01
T2.5-395-12	7762-0134	158	395	.01
T2.5-420-12	7762-0135	168	420	.01
T2.5-480-12	7762-0136	192	480	.01
T2.5-500-12	7762-0137	200	500	.01
T2.5-540-12	7762-0138	216	540	.01
T2.5-600-12	7762-0139	240	600	.01
T2.5-620-12	7762-0140	248	620	.01
T2.5-650-12	7762-0141	260	650	.01
T2.5-700-12	7762-0142	280	700	.01
T2.5-780-12	7762-0143	312	780	.01
T2.5-915-12	7762-0144	366	915	.01
T2.5-950-12	7762-0145	380	950	.01

T2.5 Pitch — 16mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-16	7762-0146	48	120	.01
T2.5-145-16	7762-0147	59	145	.01
T2.5-160-16	7762-0148	64	160	.01
T2.5-177.5-16	7762-0149	71	177	.01
T2.5-180-16	7762-0150	72	180	.01
T2.5-182.5-16	7762-0151	73	182	.01
T2.5-185-16	7762-0152	74	185	.01
T2.5-200-16	7762-0153	80	200	.01
T2.5-230-16	7762-0154	92	230	.01
T2.5-245-16	7762-0155	98	245	.01
T2.5-265-16	7762-0156	106	265	.01
T2.5-285-16	7762-0157	114	285	.01
T2.5-290-16	7762-0158	116	290	.01
T2.5-305-16	7762-0159	122	305	.01
T2.5-317.5-16	7762-0160	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-16	7762-0161	132	330	.01
T2.5-380-16	7762-0162	152	380	.01
T2.5-395-16	7762-0163	158	395	.01
T2.5-420-16	7762-0164	168	420	.01
T2.5-480-16	7762-0165	192	480	.01
T2.5-500-16	7762-0166	200	500	.01
T2.5-540-16	7762-0167	216	540	.01
T2.5-600-16	7762-0168	240	600	.01
T2.5-620-16	7762-0169	248	620	.01
T2.5-650-16	7762-0170	260	650	.01
T2.5-700-16	7762-0171	280	700	.01
T2.5-780-16	7762-0172	312	780	.01
T2.5-915-16	7762-0173	366	915	.01
T2.5-950-16	7762-0174	380	950	.01



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T2.5 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-20	7762-0175	48	120	.01
T2.5-145-20	7762-0176	59	145	.01
T2.5-160-20	7762-0177	64	160	.01
T2.5-177.5-20	7762-0178	71	177	.01
T2.5-180-20	7762-0179	72	180	.01
T2.5-182.5-20	7762-0180	73	182	.01
T2.5-185-20	7762-0181	74	185	.01
T2.5-200-20	7762-0182	80	200	.01
T2.5-230-20	7762-0183	92	230	.01
T2.5-245-20	7762-0184	98	245	.01
T2.5-265-20	7762-0185	106	265	.01
T2.5-285-20	7762-0186	114	285	.01
T2.5-290-20	7762-0187	116	290	.01
T2.5-305-20	7762-0188	122	305	.01
T2.5-317.5-20	7762-0189	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-20	7762-0190	132	330	.01
T2.5-380-20	7762-0191	152	380	.01
T2.5-395-20	7762-0192	158	395	.01
T2.5-420-20	7762-0193	168	420	.01
T2.5-480-20	7762-0194	192	480	.01
T2.5-500-20	7762-0195	200	500	.01
T2.5-540-20	7762-0196	216	540	.01
T2.5-600-20	7762-0197	240	600	.01
T2.5-620-20	7762-0198	248	620	.01
T2.5-650-20	7762-0199	260	650	.01
T2.5-700-20	7762-0200	280	700	.01
T2.5-780-20	7762-0201	312	780	.01
T2.5-915-20	7762-0202	366	915	.01
T2.5-950-20	7762-0203	380	950	.01

T2.5 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-25	7762-0204	48	120	.01
T2.5-145-25	7762-0205	59	145	.01
T2.5-160-25	7762-0206	64	160	.01
T2.5-177.5-25	7762-0207	71	177	.01
T2.5-180-25	7762-0208	72	180	.01
T2.5-182.5-25	7762-0209	73	182	.01
T2.5-185-25	7762-0210	74	185	.01
T2.5-200-25	7762-0211	80	200	.01
T2.5-230-25	7762-0212	92	230	.01
T2.5-245-25	7762-0213	98	245	.01
T2.5-265-25	7762-0214	106	265	.01
T2.5-285-25	7762-0215	114	285	.01
T2.5-290-25	7762-0216	116	290	.01
T2.5-305-25	7762-0217	122	305	.01
T2.5-317.5-25	7762-0218	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-25	7762-0219	132	330	.01
T2.5-380-25	7762-0220	152	380	.01
T2.5-395-25	7762-0221	158	395	.01
T2.5-420-25	7762-0222	168	420	.01
T2.5-480-25	7762-0223	192	480	.01
T2.5-500-25	7762-0224	200	500	.01
T2.5-540-25	7762-0225	216	540	.01
T2.5-600-25	7762-0226	240	600	.01
T2.5-620-25	7762-0227	248	620	.01
T2.5-650-25	7762-0228	260	650	.01
T2.5-700-25	7762-0229	280	700	.01
T2.5-780-25	7762-0230	312	780	.01
T2.5-915-25	7762-0231	366	915	.01
T2.5-950-25	7762-0232	380	950	.01

T2.5 Pitch — 32mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-32	7762-0233	48	120	.01
T2.5-145-32	7762-0234	59	145	.01
T2.5-160-32	7762-0235	64	160	.01
T2.5-177.5-32	7762-0236	71	177	.01
T2.5-180-32	7762-0237	72	180	.01
T2.5-182.5-32	7762-0238	73	182	.01
T2.5-185-32	7762-0239	74	185	.01
T2.5-200-32	7762-0240	80	200	.01
T2.5-230-32	7762-0241	92	230	.01
T2.5-245-32	7762-0242	98	245	.01
T2.5-265-32	7762-0243	106	265	.01
T2.5-285-32	7762-0244	114	285	.01
T2.5-290-32	7762-0245	116	290	.01
T2.5-305-32	7762-0246	122	305	.01
T2.5-317.5-32	7762-0247	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-32	7762-0248	132	330	.01
T2.5-380-32	7762-0249	152	380	.01
T2.5-395-32	7762-0250	158	395	.01
T2.5-420-32	7762-0251	168	420	.01
T2.5-480-32	7762-0252	192	480	.01
T2.5-500-32	7762-0253	200	500	.01
T2.5-540-32	7762-0254	216	540	.01
T2.5-600-32	7762-0255	240	600	.01
T2.5-620-32	7762-0256	248	620	.01
T2.5-650-32	7762-0257	260	650	.01
T2.5-700-32	7762-0258	280	700	.01
T2.5-780-32	7762-0259	312	780	.01
T2.5-915-32	7762-0260	366	915	.01
T2.5-950-32	7762-0261	380	950	.01

Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T2.5 Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-50	7762-0262	48	120	.01
T2.5-145-50	7762-0263	59	145	.01
T2.5-160-50	7762-0264	64	160	.01
T2.5-177.5-50	7762-0265	71	177	.01
T2.5-180-50	7762-0266	72	180	.01
T2.5-182.5-50	7762-0267	73	182	.01
T2.5-185-50	7762-0268	74	185	.01
T2.5-200-50	7762-0269	80	200	.01
T2.5-230-50	7762-0270	92	230	.01
T2.5-245-50	7762-0271	98	245	.01
T2.5-265-50	7762-0272	106	265	.01
T2.5-285-50	7762-0273	114	285	.01
T2.5-290-50	7762-0274	116	290	.01
T2.5-305-50	7762-0275	122	305	.01
T2.5-317.5-50	7762-0276	127	317	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-50	7762-0277	132	330	.01
T2.5-380-50	7762-0278	152	380	.01
T2.5-395-50	7762-0279	158	395	.01
T2.5-420-50	7762-0280	168	420	.01
T2.5-480-50	7762-0281	192	480	.01
T2.5-500-50	7762-0282	200	500	.01
T2.5-540-50	7762-0283	216	540	.01
T2.5-600-50	7762-0284	240	600	.01
T2.5-620-50	7762-0285	248	620	.01
T2.5-650-50	7762-0286	260	650	.01
T2.5-700-50	7762-0287	280	700	.01
T2.5-780-50	7762-0288	312	780	.01
T2.5-915-50	7762-0289	366	915	.01
T2.5-950-50	7762-0290	380	950	.01

T2.5 Pitch — 200mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-120-200	7762-0291	48	120	.01
T2.5-145-200	7762-0292	59	145	.01
T2.5-160-200	7762-0293	64	160	.01
T2.5-177.5-200	7762-0294	71	177	.01
T2.5-180-200	7762-0295	72	180	.01
T2.5-182.5-200	7762-0296	73	182	.01
T2.5-185-200	7762-0297	74	185	.01
T2.5-200-200	7762-0298	80	200	.01
T2.5-230-200	7762-0299	92	230	.01
T2.5-245-200	7762-0300	98	245	.01
T2.5-265-200	7762-0301	106	265	.02
T2.5-285-200	7762-0302	114	285	.02
T2.5-290-200	7762-0303	116	290	.02
T2.5-305-200	7762-0304	122	305	.02
T2.5-317.5-200	7762-0305	127	317	.02

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T2.5-330-200	7762-0306	132	330	.02
T2.5-380-200	7762-0307	152	380	.02
T2.5-395-200	7762-0308	158	395	.02
T2.5-420-200	7762-0309	168	420	.03
T2.5-480-200	7762-0310	192	480	.03
T2.5-500-200	7762-0311	200	500	.03
T2.5-540-200	7762-0312	216	540	.03
T2.5-600-200	7762-0313	240	600	.04
T2.5-620-200	7762-0314	248	620	.04
T2.5-650-200	7762-0315	260	650	.04
T2.5-700-200	7762-0316	280	700	.04
T2.5-780-200	7762-0317	312	780	.05
T2.5-915-200	7762-0318	366	915	.06
T2.5-950-200	7762-0319	380	950	.06



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 4mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-150-4	7762-1000	30	150	.01
⁶ T5-165-4	7762-1001	33	165	.01
⁶ T5-180-4	7762-1002	36	180	.01
⁶ T5-185-4	7762-1003	37	185	.01
⁶ T5-200-4	7762-1004	40	200	.01
⁶ T5-215-4	7762-1005	43	215	.01
⁶ T5-220-4	7762-1006	44	220	.01
⁶ T5-225-4	7762-1007	45	225	.01
⁶ T5-245-4	7762-1008	49	245	.01
⁶ T5-250-4	7762-1009	50	250	.01
⁶ T5-255-4	7762-1010	51	255	.01
⁶ T5-260-4	7762-1011	52	260	.01
⁶ T5-270-4	7762-1012	54	270	.01
⁶ T5-275-4	7762-1013	55	275	.01
⁶ T5-280-4	7762-1014	56	280	.01
⁶ T5-295-4	7762-1015	59	295	.01
⁶ T5-305-4	7762-1016	61	305	.01
⁶ T5-315-4	7762-1017	63	315	.01
⁶ T5-330-4	7762-1018	66	330	.01
⁶ T5-340-4	7762-1019	68	340	.01
⁶ T5-350-4	7762-1020	70	350	.01
⁶ T5-355-4	7762-1021	71	355	.01
⁶ T5-365-4	7762-1022	73	365	.01
⁶ T5-390-4	7762-1023	78	390	.01
⁶ T5-400-4	7762-1024	80	400	.01
⁶ T5-410-4	7762-1025	82	410	.01
⁶ T5-420-4	7762-1026	84	420	.01
⁶ T5-445-4	7762-1027	89	445	.01
⁶ T5-450-4	7762-1028	90	450	.01
⁶ T5-455-4	7762-1029	91	455	.01
⁶ T5-475-4	7762-1030	95	475	.01
⁶ T5-480-4	7762-1031	96	480	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-500-4	7762-1032	100	500	.01
⁶ T5-510-4	7762-1033	102	510	.01
⁶ T5-525-4	7762-1034	105	525	.01
⁶ T5-545-4	7762-1035	109	545	.01
⁶ T5-550-4	7762-1036	110	550	.01
⁶ T5-560-4	7762-1037	112	560	.01
⁶ T5-575-4	7762-1038	115	575	.01
⁶ T5-610-4	7762-1039	122	610	.01
⁶ T5-620-4	7762-1040	124	620	.01
⁶ T5-630-4	7762-1041	126	630	.01
⁶ T5-640-4	7762-1042	128	640	.01
⁶ T5-650-4	7762-1043	130	650	.01
⁶ T5-660-4	7762-1044	132	660	.01
⁶ T5-675-4	7762-1045	135	675	.01
⁶ T5-690-4	7762-1046	138	690	.01
⁶ T5-700-4	7762-1047	140	700	.01
⁶ T5-720-4	7762-1048	144	720	.01
⁶ T5-725-4	7762-0454	145	725	.01
⁶ T5-750-4	7762-1049	150	750	.01
⁶ T5-780-4	7762-1050	156	780	.02
⁶ T5-800-4	7762-0363	160	800	.02
⁶ T5-815-4	7762-1051	163	815	.02
⁶ T5-840-4	7762-1052	168	840	.02
⁶ T5-850-4	7762-0377	170	850	.02
⁶ T5-900-4	7762-1053	180	900	.02
⁶ T5-940-4	7762-1054	188	940	.02
⁶ T5-990-4	7762-1055	198	990	.02
⁶ T5-1075-4	7762-1056	215	1075	.02
⁶ T5-1100-4	7762-1057	220	1100	.02
⁶ T5-1215-4	7762-1058	243	1215	.02
⁶ T5-1315-4	7762-1059	263	1315	.03
⁶ T5-1380-4	7762-1060	276	1380	.03

T5 Pitch — 6mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-150-6	7762-1070	30	150	.01
T5-165-6	7762-1071	33	165	.01
T5-180-6	7762-1072	36	180	.01
T5-185-6	7762-1073	37	185	.01
T5-200-6	7762-1074	40	200	.01
T5-215-6	7762-1075	43	215	.01
T5-220-6	7762-1076	44	220	.01
T5-225-6	7762-1077	45	225	.01
T5-245-6	7762-1078	49	245	.01
T5-250-6	7762-1079	50	250	.01
T5-255-6	7762-1080	51	255	.01
T5-260-6	7762-1081	52	260	.01
T5-270-6	7762-1082	54	270	.01
T5-275-6	7762-1083	55	275	.01
T5-280-6	7762-1084	56	280	.01
T5-295-6	7762-1085	59	295	.01
T5-305-6	7762-1086	61	305	.01
T5-315-6	7762-1087	63	315	.01
T5-330-6	7762-1088	66	330	.01
T5-340-6	7762-1089	68	340	.01
T5-350-6	7762-1090	70	350	.01
T5-355-6	7762-1091	71	355	.01
T5-365-6	7762-1092	73	365	.01
T5-390-6	7762-1093	78	390	.01
T5-400-6	7762-1094	80	400	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-410-6	7762-1095	82	410	.01
T5-420-6	7762-1096	84	420	.01
T5-445-6	7762-1097	89	445	.01
T5-450-6	7762-1098	90	450	.01
T5-455-6	7762-1099	91	455	.01
T5-475-6	7762-1100	95	475	.01
T5-480-6	7762-1101	96	480	.01
T5-500-6	7762-1102	100	500	.01
T5-510-6	7762-1103	102	510	.01
T5-525-6	7762-1104	105	525	.02
T5-545-6	7762-1105	109	545	.02
T5-550-6	7762-1106	110	550	.02
T5-560-6	7762-1107	112	560	.02
T5-575-6	7762-1108	115	575	.02
T5-610-6	7762-1109	122	610	.02
T5-620-6	7762-1110	124	620	.02
T5-630-6	7762-1111	126	630	.02
T5-640-6	7762-1112	128	640	.02
T5-650-6	7762-1113	130	650	.02
T5-660-6	7762-1114	132	660	.02
T5-675-6	7762-1115	135	675	.02
T5-690-6	7762-1116	138	690	.02
T5-700-6	7762-1117	140	700	.02
T5-720-6	7762-1118	144	720	.02
T5-725-6	7762-0455	145	725	.02

⁶ Standard/Non-Stock item. Check with Customer Service for availability.

Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 6mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-750-6	7762-1119	150	750	.02
T5-780-6	7762-1120	156	780	.02
T5-800-6	7762-0364	160	800	.02
T5-815-6	7762-1121	163	815	.02
T5-840-6	7762-1122	168	840	.02
T5-850-6	7762-0378	170	850	.02
T5-900-6	7762-1123	180	900	.03

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-940-6	7762-1124	188	940	.03
T5-990-6	7762-1125	198	990	.03
T5-1075-6	7762-1126	215	1075	.03
T5-1100-6	7762-1127	220	1100	.03
T5-1215-6	7762-1128	243	1215	.04
T5-1315-6	7762-1129	263	1315	.04
T5-1380-6	7762-1130	276	1380	.04

T5 Pitch — 8mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-150-8	7762-1140	30	150	.01
T5-165-8	7762-1141	33	165	.01
T5-180-8	7762-1142	36	180	.01
T5-185-8	7762-1143	37	185	.01
T5-200-8	7762-1144	40	200	.01
T5-215-8	7762-1145	43	215	.01
T5-220-8	7762-1146	44	220	.01
T5-225-8	7762-1147	45	225	.01
T5-245-8	7762-1148	49	245	.01
T5-250-8	7762-1149	50	250	.01
T5-255-8	7762-1150	51	255	.01
T5-260-8	7762-1151	52	260	.01
T5-270-8	7762-1152	54	270	.01
T5-275-8	7762-1153	55	275	.01
T5-280-8	7762-1154	56	280	.01
T5-295-8	7762-1155	59	295	.01
T5-305-8	7762-1156	61	305	.01
T5-315-8	7762-1157	63	315	.01
T5-330-8	7762-1158	66	330	.01
T5-340-8	7762-1159	68	340	.01
T5-350-8	7762-1160	70	350	.01
T5-355-8	7762-1161	71	355	.01
T5-365-8	7762-1162	73	365	.01
T5-390-8	7762-1163	78	390	.02
T5-400-8	7762-1164	80	400	.02
T5-410-8	7762-1165	82	410	.02
T5-420-8	7762-1166	84	420	.02
T5-445-8	7762-1167	89	445	.02
T5-450-8	7762-1168	90	450	.02
T5-455-8	7762-1169	91	455	.02
T5-475-8	7762-1170	95	475	.02
T5-480-8	7762-1171	96	480	.02

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-500-8	7762-1172	100	500	.02
T5-510-8	7762-1173	102	510	.02
T5-525-8	7762-1174	105	525	.02
T5-545-8	7762-1175	109	545	.02
T5-550-8	7762-1176	110	550	.02
T5-560-8	7762-1177	112	560	.02
T5-575-8	7762-1178	115	575	.02
T5-610-8	7762-1179	122	610	.02
T5-620-8	7762-1180	124	620	.02
T5-630-8	7762-1181	126	630	.02
T5-640-8	7762-1182	128	640	.02
T5-650-8	7762-1183	130	650	.03
T5-660-8	7762-1184	132	660	.03
T5-675-8	7762-1185	135	675	.03
T5-690-8	7762-1186	138	690	.03
T5-700-8	7762-1187	140	700	.03
T5-720-8	7762-1188	144	720	.03
T5-725-8	7762-0456	145	725	.03
T5-750-8	7762-1189	150	750	.03
T5-780-8	7762-1190	156	780	.03
T5-800-8	7762-0365	160	800	.03
T5-815-8	7762-1191	163	815	.03
T5-840-8	7762-1192	168	840	.03
T5-850-8	7762-0379	170	850	.03
T5-900-8	7762-1193	180	900	.03
T5-940-8	7762-1194	188	940	.04
T5-990-8	7762-1195	198	990	.04
T5-1075-8	7762-1196	215	1075	.04
T5-1100-8	7762-1197	220	1100	.04
T5-1215-8	7762-1198	243	1215	.05
T5-1315-8	7762-1199	263	1315	.05
T5-1380-8	7762-1200	276	1380	.05

T5 Pitch — 10mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-150-10	7762-1210	30	150	.01
T5-165-10	7762-1211	33	165	.01
T5-180-10	7762-1212	36	180	.01
T5-185-10	7762-1213	37	185	.01
T5-200-10	7762-1214	40	200	.01
T5-215-10	7762-1215	43	215	.01
T5-220-10	7762-1216	44	220	.01
T5-225-10	7762-1217	45	225	.01
T5-245-10	7762-1218	49	245	.01
T5-250-10	7762-1219	50	250	.01
T5-255-10	7762-1220	51	255	.01
T5-260-10	7762-1221	52	260	.01

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-270-10	7762-1222	54	270	.01
T5-275-10	7762-1223	55	275	.01
T5-280-10	7762-1224	56	280	.01
T5-295-10	7762-1225	59	295	.01
T5-305-10	7762-1226	61	305	.01
T5-315-10	7762-1227	63	315	.02
T5-330-10	7762-1228	66	330	.02
T5-340-10	7762-1229	68	340	.02
T5-350-10	7762-1230	70	350	.02
T5-355-10	7762-1231	71	355	.02
T5-365-10	7762-1232	73	365	.02
T5-390-10	7762-1233	78	390	.02



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 10mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-400-10	7762-1234	80	400	.02
T5-410-10	7762-1235	82	410	.02
T5-420-10	7762-1236	84	420	.02
T5-445-10	7762-1237	89	445	.02
T5-450-10	7762-1238	90	450	.02
T5-455-10	7762-1239	91	455	.02
T5-475-10	7762-1240	95	475	.02
T5-480-10	7762-1241	96	480	.02
T5-500-10	7762-1242	100	500	.02
T5-510-10	7762-1243	102	510	.02
T5-525-10	7762-1244	105	525	.03
T5-545-10	7762-1245	109	545	.03
T5-550-10	7762-1246	110	550	.03
T5-560-10	7762-1247	112	560	.03
T5-575-10	7762-1248	115	575	.03
T5-610-10	7762-1249	122	610	.03
T5-620-10	7762-1250	124	620	.03
T5-630-10	7762-1251	126	630	.03
T5-640-10	7762-1252	128	640	.03
T5-650-10	7762-1253	130	650	.03

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-660-10	7762-1254	132	660	.03
T5-675-10	7762-1255	135	675	.03
T5-690-10	7762-1256	138	690	.03
T5-700-10	7762-1257	140	700	.03
T5-720-10	7762-1258	144	720	.03
T5-725-10	7762-0457	145	725	.03
T5-750-10	7762-1259	150	750	.04
T5-780-10	7762-1260	156	780	.04
T5-800-10	7762-0366	160	800	.04
T5-815-10	7762-1261	163	815	.04
T5-840-10	7762-1262	168	840	.04
T5-850-10	7762-0380	170	850	.04
T5-900-10	7762-1263	180	900	.04
T5-940-10	7762-1264	188	940	.05
T5-990-10	7762-1265	198	990	.05
T5-1075-10	7762-1266	215	1075	.05
T5-1100-10	7762-1267	220	1100	.05
T5-1215-10	7762-1268	243	1215	.06
T5-1315-10	7762-1269	263	1315	.06
T5-1380-10	7762-1270	276	1380	.07

T5 Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-150-12	7762-1280	30	150	.01
T5-165-12	7762-1281	33	165	.01
T5-180-12	7762-1282	36	180	.01
T5-185-12	7762-1283	37	185	.01
T5-200-12	7762-1284	40	200	.01
T5-215-12	7762-1285	43	215	.01
T5-220-12	7762-1286	44	220	.01
T5-225-12	7762-1287	45	225	.01
T5-245-12	7762-1288	49	245	.01
T5-250-12	7762-1289	50	250	.01
T5-255-12	7762-1290	51	255	.01
T5-260-12	7762-1291	52	260	.02
T5-270-12	7762-1292	54	270	.02
T5-275-12	7762-1293	55	275	.02
T5-280-12	7762-1294	56	280	.02
T5-295-12	7762-1295	59	295	.02
T5-305-12	7762-1296	61	305	.02
T5-315-12	7762-1297	63	315	.02
T5-330-12	7762-1298	66	330	.02
T5-340-12	7762-1299	68	340	.02
T5-350-12	7762-1300	70	350	.02
T5-355-12	7762-1301	71	355	.02
T5-365-12	7762-1302	73	365	.02
T5-390-12	7762-1303	78	390	.02
T5-400-12	7762-1304	80	400	.02
T5-410-12	7762-1305	82	410	.02
T5-420-12	7762-1306	84	420	.02
T5-445-12	7762-1307	89	445	.03
T5-450-12	7762-1308	90	450	.03
T5-455-12	7762-1309	91	455	.03
T5-475-12	7762-1310	95	475	.03
T5-480-12	7762-1311	96	480	.03

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-500-12	7762-1312	100	500	.03
T5-510-12	7762-1313	102	510	.03
T5-525-12	7762-1314	105	525	.03
T5-545-12	7762-1315	109	545	.03
T5-550-12	7762-1316	110	550	.03
T5-560-12	7762-1317	112	560	.03
T5-575-12	7762-1318	115	575	.03
T5-610-12	7762-1319	122	610	.04
T5-620-12	7762-1320	124	620	.04
T5-630-12	7762-1321	126	630	.04
T5-640-12	7762-1322	128	640	.04
T5-650-12	7762-1323	130	650	.04
T5-660-12	7762-1324	132	660	.04
T5-675-12	7762-1325	135	675	.04
T5-690-12	7762-1326	138	690	.04
T5-700-12	7762-1327	140	700	.04
T5-720-12	7762-1328	144	720	.04
T5-725-12	7762-0458	145	725	.04
T5-750-12	7762-1329	150	750	.04
T5-780-12	7762-1330	156	780	.05
T5-800-12	7762-0367	160	800	.05
T5-815-12	7762-1331	163	815	.05
T5-840-12	7762-1332	168	840	.05
T5-850-12	7762-0381	170	850	.05
T5-900-12	7762-1333	180	900	.05
T5-940-12	7762-1334	188	940	.05
T5-990-12	7762-1335	198	990	.06
T5-1075-12	7762-1336	215	1075	.06
T5-1100-12	7762-1337	220	1100	.06
T5-1215-12	7762-1338	243	1215	.07
T5-1315-12	7762-1339	263	1315	.08
T5-1380-12	7762-1340	276	1380	.08



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 16mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-150-16	7762-1350	30	150	.01
T5-165-16	7762-1351	33	165	.01
T5-180-16	7762-1352	36	180	.01
T5-185-16	7762-1353	37	185	.01
T5-200-16	7762-1354	40	200	.02
T5-215-16	7762-1355	43	215	.02
T5-220-16	7762-1356	44	220	.02
T5-225-16	7762-1357	45	225	.02
T5-245-16	7762-1358	49	245	.02
T5-250-16	7762-1359	50	250	.02
T5-255-16	7762-1360	51	255	.02
T5-260-16	7762-1361	52	260	.02
T5-270-16	7762-1362	54	270	.02
T5-275-16	7762-1363	55	275	.02
T5-280-16	7762-1364	56	280	.02
T5-295-16	7762-1365	59	295	.02
T5-305-16	7762-1366	61	305	.02
T5-315-16	7762-1367	63	315	.02
T5-330-16	7762-1368	66	330	.03
T5-340-16	7762-1369	68	340	.03
T5-350-16	7762-1370	70	350	.03
T5-355-16	7762-1371	71	355	.03
T5-365-16	7762-1372	73	365	.03
T5-390-16	7762-1373	78	390	.03
T5-400-16	7762-1374	80	400	.03
T5-410-16	7762-1375	82	410	.03
T5-420-16	7762-1376	84	420	.03
T5-445-16	7762-1377	89	445	.03
T5-450-16	7762-1378	90	450	.03
T5-455-16	7762-1379	91	455	.04
T5-475-16	7762-1380	95	475	.04
T5-480-16	7762-1381	96	480	.04

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-500-16	7762-1382	100	500	.04
T5-510-16	7762-1383	102	510	.04
T5-525-16	7762-1384	105	525	.04
T5-545-16	7762-1385	109	545	.04
T5-550-16	7762-1386	110	550	.04
T5-560-16	7762-1387	112	560	.04
T5-575-16	7762-1388	115	575	.04
T5-610-16	7762-1389	122	610	.05
T5-620-16	7762-1390	124	620	.05
T5-630-16	7762-1391	126	630	.05
T5-640-16	7762-1392	128	640	.05
T5-650-16	7762-1393	130	650	.05
T5-660-16	7762-1394	132	660	.05
T5-675-16	7762-1395	135	675	.05
T5-690-16	7762-1396	138	690	.05
T5-700-16	7762-1397	140	700	.05
T5-720-16	7762-1398	144	720	.06
T5-725-16	7762-0459	145	725	.06
T5-750-16	7762-1399	150	750	.06
T5-780-16	7762-1400	156	780	.06
T5-800-16	7762-0369	160	800	.06
T5-815-16	7762-1401	163	815	.06
T5-840-16	7762-1402	168	840	.06
T5-850-16	7762-0383	170	850	.06
T5-900-16	7762-1403	180	900	.07
T5-940-16	7762-1404	188	940	.07
T5-990-16	7762-1405	198	990	.08
T5-1075-16	7762-1406	215	1075	.08
T5-1100-16	7762-1407	220	1100	.08
T5-1215-16	7762-1408	243	1215	.09
T5-1315-16	7762-1409	263	1315	.10
T5-1380-16	7762-1410	276	1380	.11

T5 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-150-20	7762-1420	30	150	.01
T5-165-20	7762-1421	33	165	.02
T5-180-20	7762-1422	36	180	.02
T5-185-20	7762-1423	37	185	.02
T5-200-20	7762-1424	40	200	.02
T5-215-20	7762-1425	43	215	.02
T5-220-20	7762-1426	44	220	.02
T5-225-20	7762-1427	45	225	.02
T5-245-20	7762-1428	49	245	.02
T5-250-20	7762-1429	50	250	.02
T5-255-20	7762-1430	51	255	.02
T5-260-20	7762-1431	52	260	.03
T5-270-20	7762-1432	54	270	.03
T5-275-20	7762-1433	55	275	.03
T5-280-20	7762-1434	56	280	.03
T5-295-20	7762-1435	59	295	.03
T5-305-20	7762-1436	61	305	.03
T5-315-20	7762-1437	63	315	.03
T5-330-20	7762-1438	66	330	.03
T5-340-20	7762-1439	68	340	.03
T5-350-20	7762-1440	70	350	.03
T5-355-20	7762-1441	71	355	.03
T5-365-20	7762-1442	73	365	.04
T5-390-20	7762-1443	78	390	.04
T5-400-20	7762-1444	80	400	.04

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-410-20	7762-1445	82	410	.04
T5-420-20	7762-1446	84	420	.04
T5-445-20	7762-1447	89	445	.04
T5-450-20	7762-1448	90	450	.04
T5-455-20	7762-1449	91	455	.04
T5-475-20	7762-1450	95	475	.05
T5-480-20	7762-1451	96	480	.05
T5-500-20	7762-1452	100	500	.05
T5-510-20	7762-1453	102	510	.05
T5-525-20	7762-1454	105	525	.05
T5-545-20	7762-1455	109	545	.05
T5-550-20	7762-1456	110	550	.05
T5-560-20	7762-1457	112	560	.05
T5-575-20	7762-1458	115	575	.06
T5-610-20	7762-1459	122	610	.06
T5-620-20	7762-1460	124	620	.06
T5-630-20	7762-1461	126	630	.06
T5-640-20	7762-1462	128	640	.06
T5-650-20	7762-1463	130	650	.06
T5-660-20	7762-1464	132	660	.06
T5-675-20	7762-1465	135	675	.06
T5-690-20	7762-1466	138	690	.07
T5-700-20	7762-1467	140	700	.07
T5-720-20	7762-1468	144	720	.07
T5-725-20	7762-0460	145	725	.08



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 20mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-750-20	7762-1469	150	750	.07
T5-780-20	7762-1470	156	780	.08
T5-800-20	7762-0370	160	800	.08
T5-815-20	7762-1471	163	815	.08
T5-840-20	7762-1472	168	840	.08
T5-850-20	7762-0384	170	850	.08
T5-900-20	7762-1473	180	900	.09

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-940-20	7762-1474	188	940	.09
T5-990-20	7762-1475	198	990	.10
T5-1075-20	7762-1476	215	1075	.10
T5-1100-20	7762-1477	220	1100	.11
T5-1215-20	7762-1478	243	1215	.12
T5-1315-20	7762-1479	263	1315	.13
T5-1380-20	7762-1480	276	1380	.13

T5 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-150-25	7762-1490	30	150	.02
T5-165-25	7762-1491	33	165	.02
T5-180-25	7762-1492	36	180	.02
T5-185-25	7762-1493	37	185	.02
T5-200-25	7762-1494	40	200	.02
T5-215-25	7762-1495	43	215	.03
T5-220-25	7762-1496	44	220	.03
T5-225-25	7762-1497	45	225	.03
T5-245-25	7762-1498	49	245	.03
T5-250-25	7762-1499	50	250	.03
T5-255-25	7762-1500	51	255	.03
T5-260-25	7762-1501	52	260	.03
T5-270-25	7762-1502	54	270	.03
T5-275-25	7762-1503	55	275	.03
T5-280-25	7762-1504	56	280	.03
T5-295-25	7762-1505	59	295	.04
T5-305-25	7762-1506	61	305	.04
T5-315-25	7762-1507	63	315	.04
T5-330-25	7762-1508	66	330	.04
T5-340-25	7762-1509	68	340	.04
T5-350-25	7762-1510	70	350	.04
T5-355-25	7762-1511	71	355	.04
T5-365-25	7762-1512	73	365	.04
T5-390-25	7762-1513	78	390	.05
T5-400-25	7762-1514	80	400	.05
T5-410-25	7762-1515	82	410	.05
T5-420-25	7762-1516	84	420	.05
T5-445-25	7762-1517	89	445	.05
T5-450-25	7762-1518	90	450	.05
T5-455-25	7762-1519	91	455	.05
T5-475-25	7762-1520	95	475	.06
T5-480-25	7762-1521	96	480	.06

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T5-500-25	7762-1522	100	500	.06
T5-510-25	7762-1523	102	510	.06
T5-525-25	7762-1524	105	525	.06
T5-545-25	7762-1525	109	545	.07
T5-550-25	7762-1526	110	550	.07
T5-560-25	7762-1527	112	560	.07
T5-575-25	7762-1528	115	575	.07
T5-610-25	7762-1529	122	610	.07
T5-620-25	7762-1530	124	620	.07
T5-630-25	7762-1531	126	630	.08
T5-640-25	7762-1532	128	640	.08
T5-650-25	7762-1533	130	650	.08
T5-660-25	7762-1534	132	660	.08
T5-675-25	7762-1535	135	675	.08
T5-690-25	7762-1536	138	690	.08
T5-700-25	7762-1537	140	700	.08
T5-720-25	7762-1538	144	720	.09
T5-725-25	7762-0461	145	725	.09
T5-750-25	7762-1539	150	750	.09
T5-780-25	7762-1540	156	780	.09
T5-800-25	7762-0371	160	800	.10
T5-815-25	7762-1541	163	815	.10
T5-840-25	7762-1542	168	840	.10
T5-850-25	7762-0385	170	850	.10
T5-900-25	7762-1543	180	900	.11
T5-940-25	7762-1544	188	940	.11
T5-990-25	7762-1545	198	990	.12
T5-1075-25	7762-1546	215	1075	.13
T5-1100-25	7762-1547	220	1100	.13
T5-1215-25	7762-1548	243	1215	.15
T5-1315-25	7762-1549	263	1315	.16
T5-1380-25	7762-1550	276	1380	.17

T5 Pitch — 32mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-150-32	7762-1560	30	150	.02
⁶ T5-165-32	7762-1561	33	165	.03
⁶ T5-180-32	7762-1562	36	180	.03
⁶ T5-185-32	7762-1563	37	185	.03
⁶ T5-200-32	7762-1564	40	200	.03
⁶ T5-215-32	7762-1565	43	215	.03
⁶ T5-220-32	7762-1566	44	220	.03
⁶ T5-225-32	7762-1567	45	225	.03
⁶ T5-245-32	7762-1568	49	245	.04
⁶ T5-250-32	7762-1569	50	250	.04
⁶ T5-255-32	7762-1570	51	255	.04
⁶ T5-260-32	7762-1571	52	260	.04

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-270-32	7762-1572	54	270	.04
⁶ T5-275-32	7762-1573	55	275	.04
⁶ T5-280-32	7762-1574	56	280	.04
⁶ T5-295-32	7762-1575	59	295	.05
⁶ T5-305-32	7762-1576	61	305	.05
⁶ T5-315-32	7762-1577	63	315	.05
⁶ T5-330-32	7762-1578	66	330	.05
⁶ T5-340-32	7762-1579	68	340	.05
⁶ T5-350-32	7762-1580	70	350	.05
⁶ T5-355-32	7762-1581	71	355	.05
⁶ T5-365-32	7762-1582	73	365	.06
⁶ T5-390-32	7762-1583	78	390	.06

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 32mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
6 T5-400-32	7762-1584	80	400	.06
6 T5-410-32	7762-1585	82	410	.06
6 T5-420-32	7762-1586	84	420	.06
6 T5-445-32	7762-1587	89	445	.07
6 T5-450-32	7762-1588	90	450	.07
6 T5-455-32	7762-1589	91	455	.07
6 T5-475-32	7762-1590	95	475	.07
6 T5-480-32	7762-1591	96	480	.07
6 T5-500-32	7762-1592	100	500	.08
6 T5-510-32	7762-1593	102	510	.08
6 T5-525-32	7762-1594	105	525	.08
6 T5-545-32	7762-1595	109	545	.08
6 T5-550-32	7762-1596	110	550	.08
6 T5-560-32	7762-1597	112	560	.09
6 T5-575-32	7762-1598	115	575	.09
6 T5-610-32	7762-1599	122	610	.09
6 T5-620-32	7762-1600	124	620	.10
6 T5-630-32	7762-1601	126	630	.10
6 T5-640-32	7762-1602	128	640	.10
6 T5-650-32	7762-1603	130	650	.10

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
6 T5-660-32	7762-1604	132	660	.10
6 T5-675-32	7762-1605	135	675	.10
6 T5-690-32	7762-1606	138	690	.11
6 T5-700-32	7762-1607	140	700	.11
6 T5-720-32	7762-1608	144	720	.11
6 T5-725-32	7762-0462	145	725	.11
6 T5-750-32	7762-1609	150	750	.12
6 T5-780-32	7762-1610	156	780	.12
6 T5-800-32	7762-0372	160	800	.13
6 T5-815-32	7762-1611	163	815	.13
6 T5-840-32	7762-1612	168	840	.13
6 T5-850-32	7762-0386	170	850	.13
6 T5-900-32	7762-1613	180	900	.14
6 T5-940-32	7762-1614	188	940	.14
6 T5-990-32	7762-1615	198	990	.15
6 T5-1075-32	7762-1616	215	1075	.17
6 T5-1100-32	7762-1617	220	1100	.17
6 T5-1215-32	7762-1618	243	1215	.19
6 T5-1315-32	7762-1619	263	1315	.20
6 T5-1380-32	7762-1620	276	1380	.21

T5 Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
6 T5-150-50	7762-1630	30	150	.04
6 T5-165-50	7762-1631	33	165	.04
6 T5-180-50	7762-1632	36	180	.04
6 T5-185-50	7762-1633	37	185	.04
6 T5-200-50	7762-1634	40	200	.05
6 T5-215-50	7762-1635	43	215	.05
6 T5-220-50	7762-1636	44	220	.05
6 T5-225-50	7762-1637	45	225	.05
6 T5-245-50	7762-1638	49	245	.06
6 T5-250-50	7762-1639	50	250	.06
6 T5-255-50	7762-1640	51	255	.06
6 T5-260-50	7762-1641	52	260	.06
6 T5-270-50	7762-1642	54	270	.06
6 T5-275-50	7762-1643	55	275	.07
6 T5-280-50	7762-1644	56	280	.07
6 T5-295-50	7762-1645	59	295	.07
6 T5-305-50	7762-1646	61	305	.07
6 T5-315-50	7762-1647	63	315	.08
6 T5-330-50	7762-1648	66	330	.08
6 T5-340-50	7762-1649	68	340	.08
6 T5-350-50	7762-1650	70	350	.08
6 T5-355-50	7762-1651	71	355	.09
6 T5-365-50	7762-1652	73	365	.09
6 T5-390-50	7762-1653	78	390	.09
6 T5-400-50	7762-1654	80	400	.10
6 T5-410-50	7762-1655	82	410	.10
6 T5-420-50	7762-1656	84	420	.10
6 T5-445-50	7762-1657	89	445	.11
6 T5-450-50	7762-1658	90	450	.11
6 T5-455-50	7762-1659	91	455	.11
6 T5-475-50	7762-1660	95	475	.11
6 T5-480-50	7762-1661	96	480	.12

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
6 T5-500-50	7762-1662	100	500	.12
6 T5-510-50	7762-1663	102	510	.12
6 T5-525-50	7762-1664	105	525	.13
6 T5-545-50	7762-1665	109	545	.13
6 T5-550-50	7762-1666	110	550	.13
6 T5-560-50	7762-1667	112	560	.13
6 T5-575-50	7762-1668	115	575	.14
6 T5-610-50	7762-1669	122	610	.15
6 T5-620-50	7762-1670	124	620	.15
6 T5-630-50	7762-1671	126	630	.15
6 T5-640-50	7762-1672	128	640	.15
6 T5-650-50	7762-1673	130	650	.16
6 T5-660-50	7762-1674	132	660	.16
6 T5-675-50	7762-1675	135	675	.16
6 T5-690-50	7762-1676	138	690	.17
6 T5-700-50	7762-1677	140	700	.17
6 T5-720-50	7762-1678	144	720	.17
6 T5-725-50	7762-0463	145	725	.17
6 T5-750-50	7762-1679	150	750	.18
6 T5-780-50	7762-1680	156	780	.19
6 T5-800-50	7762-0373	160	800	.20
6 T5-815-50	7762-1681	163	815	.20
6 T5-840-50	7762-1682	168	840	.20
6 T5-850-50	7762-0387	170	850	.20
6 T5-900-50	7762-1683	180	900	.22
6 T5-940-50	7762-1684	188	940	.23
6 T5-990-50	7762-1685	198	990	.24
6 T5-1075-50	7762-1686	215	1075	.26
6 T5-1100-50	7762-1687	220	1100	.26
6 T5-1215-50	7762-1688	243	1215	.29
6 T5-1315-50	7762-1689	263	1315	.32
6 T5-1380-50	7762-1690	276	1380	.33

6 Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 75mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-150-75	7762-1700	30	150	.05
⁶ T5-165-75	7762-1701	33	165	.06
⁶ T5-180-75	7762-1702	36	180	.06
⁶ T5-185-75	7762-1703	37	185	.07
⁶ T5-200-75	7762-1704	40	200	.07
⁶ T5-215-75	7762-1705	43	215	.08
⁶ T5-220-75	7762-1706	44	220	.08
⁶ T5-225-75	7762-1707	45	225	.08
⁶ T5-245-75	7762-1708	49	245	.09
⁶ T5-250-75	7762-1709	50	250	.09
⁶ T5-255-75	7762-1710	51	255	.09
⁶ T5-260-75	7762-1711	52	260	.09
⁶ T5-270-75	7762-1712	54	270	.10
⁶ T5-275-75	7762-1713	55	275	.10
⁶ T5-280-75	7762-1714	56	280	.10
⁶ T5-295-75	7762-1715	59	295	.11
⁶ T5-305-75	7762-1716	61	305	.11
⁶ T5-315-75	7762-1717	63	315	.11
⁶ T5-330-75	7762-1718	66	330	.12
⁶ T5-340-75	7762-1719	68	340	.12
⁶ T5-350-75	7762-1720	70	350	.13
⁶ T5-355-75	7762-1721	71	355	.13
⁶ T5-365-75	7762-1722	73	365	.13
⁶ T5-390-75	7762-1723	78	390	.14
⁶ T5-400-75	7762-1724	80	400	.14
⁶ T5-410-75	7762-1725	82	410	.15
⁶ T5-420-75	7762-1726	84	420	.15
⁶ T5-445-75	7762-1727	89	445	.16
⁶ T5-450-75	7762-1728	90	450	.16
⁶ T5-455-75	7762-1729	91	455	.16
⁶ T5-475-75	7762-1730	95	475	.17
⁶ T5-480-75	7762-1731	96	480	.17

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-500-75	7762-1732	100	500	.18
⁶ T5-510-75	7762-1733	102	510	.18
⁶ T5-525-75	7762-1734	105	525	.19
⁶ T5-545-75	7762-1735	109	545	.20
⁶ T5-550-75	7762-1736	110	550	.20
⁶ T5-560-75	7762-1737	112	560	.20
⁶ T5-575-75	7762-1738	115	575	.21
⁶ T5-610-75	7762-1739	122	610	.22
⁶ T5-620-75	7762-1740	124	620	.22
⁶ T5-630-75	7762-1741	126	630	.23
⁶ T5-640-75	7762-1742	128	640	.23
⁶ T5-650-75	7762-1743	130	650	.23
⁶ T5-660-75	7762-1744	132	660	.24
⁶ T5-675-75	7762-1745	135	675	.24
⁶ T5-690-75	7762-1746	138	690	.25
⁶ T5-700-75	7762-1747	140	700	.25
⁶ T5-720-75	7762-1748	144	720	.26
⁶ T5-725-75	7762-0464	145	725	.26
⁶ T5-750-75	7762-1749	150	750	.27
⁶ T5-780-75	7762-1750	156	780	.28
⁶ T5-800-75	7762-0374	160	800	.29
⁶ T5-815-75	7762-1751	163	815	.29
⁶ T5-840-75	7762-1752	168	840	.30
⁶ T5-850-75	7762-0388	170	850	.30
⁶ T5-900-75	7762-1753	180	900	.32
⁶ T5-940-75	7762-1754	188	940	.34
⁶ T5-990-75	7762-1755	198	990	.36
⁶ T5-1075-75	7762-1756	215	1075	.39
⁶ T5-1100-75	7762-1757	220	1100	.40
⁶ T5-1215-75	7762-1758	243	1215	.44
⁶ T5-1315-75	7762-1759	263	1315	.47
⁶ T5-1380-75	7762-1760	276	1380	.50

T5 Pitch — 200mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-150-200	7762-1770	30	150	.14
⁶ T5-165-200	7762-1771	33	165	.16
⁶ T5-180-200	7762-1772	36	180	.17
⁶ T5-185-200	7762-1773	37	185	.18
⁶ T5-200-200	7762-1774	40	200	.19
⁶ T5-215-200	7762-1775	43	215	.21
⁶ T5-220-200	7762-1776	44	220	.21
⁶ T5-225-200	7762-1777	45	225	.22
⁶ T5-245-200	7762-1778	49	245	.24
⁶ T5-250-200	7762-1779	50	250	.24
⁶ T5-255-200	7762-1780	51	255	.25
⁶ T5-260-200	7762-1781	52	260	.25
⁶ T5-270-200	7762-1782	54	270	.26
⁶ T5-275-200	7762-1783	55	275	.26
⁶ T5-280-200	7762-1784	56	280	.27
⁶ T5-295-200	7762-1785	59	295	.28
⁶ T5-305-200	7762-1786	61	305	.29
⁶ T5-315-200	7762-1787	63	315	.30
⁶ T5-330-200	7762-1788	66	330	.32
⁶ T5-340-200	7762-1789	68	340	.33
⁶ T5-350-200	7762-1790	70	350	.34
⁶ T5-355-200	7762-1791	71	355	.34
⁶ T5-365-200	7762-1792	73	365	.35
⁶ T5-390-200	7762-1793	78	390	.38
⁶ T5-400-200	7762-1794	80	400	.38

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-410-200	7762-1795	82	410	.39
⁶ T5-420-200	7762-1796	84	420	.40
⁶ T5-445-200	7762-1797	89	445	.43
⁶ T5-450-200	7762-1798	90	450	.43
⁶ T5-455-200	7762-1799	91	455	.44
⁶ T5-475-200	7762-1800	95	475	.46
⁶ T5-480-200	7762-1801	96	480	.46
⁶ T5-500-200	7762-1802	100	500	.48
⁶ T5-510-200	7762-1803	102	510	.49
⁶ T5-525-200	7762-1804	105	525	.51
⁶ T5-545-200	7762-1805	109	545	.52
⁶ T5-550-200	7762-1806	110	550	.53
⁶ T5-560-200	7762-1807	112	560	.54
⁶ T5-575-200	7762-1808	115	575	.55
⁶ T5-610-200	7762-1809	122	610	.59
⁶ T5-620-200	7762-1810	124	620	.60
⁶ T5-630-200	7762-1811	126	630	.61
⁶ T5-640-200	7762-1812	128	640	.62
⁶ T5-650-200	7762-1813	130	650	.63
⁶ T5-660-200	7762-1814	132	660	.63
⁶ T5-675-200	7762-1815	135	675	.65
⁶ T5-690-200	7762-1816	138	690	.66
⁶ T5-700-200	7762-1817	140	700	.67
⁶ T5-720-200	7762-1818	144	720	.69
⁶ T5-725-200	7762-0465	145	725	.69

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T5 Pitch — 200mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-750-200	7762-1819	150	750	.72
⁶ T5-780-200	7762-1820	156	780	.75
⁶ T5-800-200	7762-0376	160	800	.77
⁶ T5-815-200	7762-1821	163	815	.78
⁶ T5-840-200	7762-1822	168	840	.81
⁶ T5-850-200	7762-0390	170	850	.82
⁶ T5-900-200	7762-1823	180	900	.87

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T5-940-200	7762-1824	188	940	.90
⁶ T5-990-200	7762-1825	198	990	.95
⁶ T5-1075-200	7762-1826	215	1075	1.03
⁶ T5-1100-200	7762-1827	220	1100	1.06
⁶ T5-1215-200	7762-1828	243	1215	1.17
⁶ T5-1315-200	7762-1829	263	1315	1.26
⁶ T5-1380-200	7762-1830	276	1380	1.33

T10 Pitch — 10mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-10	7762-2000	26	260	.03
T10-370-10	7762-2001	37	370	.04
T10-400-10	7762-2002	40	400	.04
T10-410-10	7762-2003	41	410	.04
T10-440-10	7762-2004	44	440	.04
T10-450-10	7762-2005	45	450	.05
T10-500-10	7762-2006	50	500	.05
T10-530-10	7762-2007	53	530	.05
T10-560-10	7762-2008	56	560	.06
T10-600-10	7762-2009	60	600	.06
T10-610-10	7762-2010	61	610	.06
T10-630-10	7762-2011	63	630	.06
T10-660-10	7762-2012	66	660	.07
T10-690-10	7762-2013	69	690	.07
T10-700-10	7762-2014	70	700	.07
T10-720-10	7762-2015	72	720	.07
T10-730-10	7762-2016	73	730	.07
T10-750-10	7762-2017	75	750	.08
T10-780-10	7762-2018	78	780	.08
T10-800-10	7762-0326	80	800	.08
T10-810-10	7762-2019	81	810	.08
T10-840-10	7762-2020	84	840	.08
T10-880-10	7762-2021	88	880	.09
T10-890-10	7762-2022	89	890	.09
T10-900-10	7762-2023	90	900	.09
T10-910-10	7762-2024	91	910	.09
T10-920-10	7762-2025	92	920	.09
T10-950-10	7762-0339	95	950	.10
T10-960-10	7762-2026	96	960	.10

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-970-10	7762-2027	97	970	.10
T10-980-10	7762-2028	98	980	.10
T10-1000-10	7762-0352	100	1000	.10
T10-1010-10	7762-2029	101	1010	.10
T10-1080-10	7762-2030	108	1080	.11
T10-1100-10	7762-2031	110	1100	.11
T10-1110-10	7762-2032	111	1110	.11
T10-1140-10	7762-2033	114	1140	.11
T10-1150-10	7762-2034	115	1150	.12
T10-1210-10	7762-2035	121	1210	.12
T10-1240-10	7762-2036	124	1240	.12
T10-1250-10	7762-2037	125	1250	.13
T10-1300-10	7762-2038	130	1300	.13
T10-1320-10	7762-2039	132	1320	.13
T10-1350-10	7762-2040	135	1350	.14
T10-1390-10	7762-2041	139	1390	.14
T10-1400-10	7762-2042	140	1400	.14
T10-1420-10	7762-2043	142	1420	.14
T10-1450-10	7762-2044	145	1450	.15
T10-1460-10	7762-2045	146	1460	.15
T10-1500-10	7762-2046	150	1500	.15
T10-1560-10	7762-2047	156	1600	.16
T10-1610-10	7762-2048	161	1610	.16
T10-1750-10	7762-2049	175	1750	.18
T10-1780-10	7762-2050	178	1780	.18
T10-1880-10	7762-2051	188	1880	.19
T10-1960-10	7762-2052	196	1960	.20
T10-2250-10	7762-2053	225	2250	.23

T10 Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-260-12	7762-2054	26	260	.03
⁶ T10-370-12	7762-2055	37	370	.04
⁶ T10-400-12	7762-2056	40	400	.05
⁶ T10-410-12	7762-2057	41	410	.05
⁶ T10-440-12	7762-2058	44	440	.05
⁶ T10-450-12	7762-2059	45	450	.05
⁶ T10-500-12	7762-2060	50	500	.06
⁶ T10-530-12	7762-2061	53	530	.06
⁶ T10-560-12	7762-2062	56	560	.07
⁶ T10-600-12	7762-2063	60	600	.07
⁶ T10-610-12	7762-2064	61	610	.07
⁶ T10-630-12	7762-2065	63	630	.08
⁶ T10-660-12	7762-2066	66	660	.08
⁶ T10-690-12	7762-2067	69	690	.08
⁶ T10-700-12	7762-2068	70	700	.08

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-720-12	7762-2069	72	720	.09
⁶ T10-730-12	7762-2070	73	730	.09
⁶ T10-750-12	7762-2071	75	750	.09
⁶ T10-780-12	7762-2072	78	780	.09
⁶ T10-800-12	7762-0327	80	800	.10
⁶ T10-810-12	7762-2073	81	810	.10
⁶ T10-840-12	7762-2074	84	840	.10
⁶ T10-880-12	7762-2075	88	880	.11
⁶ T10-890-12	7762-2076	89	890	.11
⁶ T10-900-12	7762-2077	90	900	.11
⁶ T10-910-12	7762-2078	91	910	.11
⁶ T10-920-12	7762-2079	92	920	.11
⁶ T10-950-12	7762-0340	95	950	.12
⁶ T10-960-12	7762-2080	96	960	.12
⁶ T10-970-12	7762-2081	97	970	.12

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T10 Pitch — 12mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-980-12	7762-2082	98	980	.12
⁶ T10-1000-12	7762-0353	100	1000	.12
⁶ T10-1010-12	7762-2083	101	1010	.12
⁶ T10-1080-12	7762-2084	108	1080	.13
⁶ T10-1100-12	7762-2085	110	1100	.13
⁶ T10-1110-12	7762-2086	111	1110	.13
⁶ T10-1140-12	7762-2087	114	1140	.14
⁶ T10-1150-12	7762-2088	115	1150	.14
⁶ T10-1210-12	7762-2089	121	1210	.15
⁶ T10-1240-12	7762-2090	124	1240	.15
⁶ T10-1250-12	7762-2091	125	1250	.15
⁶ T10-1300-12	7762-2092	130	1300	.16
⁶ T10-1320-12	7762-2093	132	1320	.16
⁶ T10-1350-12	7762-2094	135	1350	.16

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-1390-12	7762-2095	139	1390	.17
⁶ T10-1400-12	7762-2096	140	1400	.17
⁶ T10-1420-12	7762-2097	142	1420	.17
⁶ T10-1450-12	7762-2098	145	1450	.17
⁶ T10-1460-12	7762-2099	146	1460	.18
⁶ T10-1500-12	7762-2100	150	1500	.18
⁶ T10-1560-12	7762-2101	156	1560	.19
⁶ T10-1610-12	7762-2102	161	1610	.19
⁶ T10-1750-12	7762-2103	175	1750	.21
⁶ T10-1780-12	7762-2104	178	1780	.21
⁶ T10-1880-12	7762-2105	188	1880	.23
⁶ T10-1960-12	7762-2106	196	1960	.24
⁶ T10-2250-12	7762-2107	225	2250	.27

T10 Pitch — 14mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-14	7762-2108	26	260	.04
T10-370-14	7762-2109	37	370	.05
T10-400-14	7762-2110	40	400	.06
T10-410-14	7762-2111	41	410	.06
T10-440-14	7762-2112	44	440	.06
T10-450-14	7762-2113	45	450	.06
T10-500-14	7762-2114	50	500	.07
T10-530-14	7762-2115	53	530	.07
T10-560-14	7762-2116	56	560	.08
T10-600-14	7762-2117	60	600	.08
T10-610-14	7762-2118	61	610	.09
T10-630-14	7762-2119	63	630	.09
T10-660-14	7762-2120	66	660	.09
T10-690-14	7762-2121	69	690	.10
T10-700-14	7762-2122	70	700	.10
T10-720-14	7762-2123	72	720	.10
T10-730-14	7762-2124	73	730	.10
T10-750-14	7762-2125	75	750	.11
T10-780-14	7762-2126	78	780	.11
T10-800-14	7762-0328	80	800	.11
T10-810-14	7762-2127	81	810	.11
T10-840-14	7762-2128	84	840	.12
T10-880-14	7762-2129	88	880	.12
T10-890-14	7762-2130	89	890	.13
T10-900-14	7762-2131	90	900	.13
T10-910-14	7762-2132	91	910	.13
T10-920-14	7762-2133	92	920	.13
T10-950-14	7762-0341	95	950	.13
T10-960-14	7762-2134	96	960	.13

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-970-14	7762-2135	97	970	.14
T10-980-14	7762-2136	98	980	.14
T10-1000-14	7762-0354	100	1000	.14
T10-1010-14	7762-2137	101	1010	.14
T10-1080-14	7762-2138	108	1080	.15
T10-1100-14	7762-2139	110	1100	.15
T10-1110-14	7762-2140	111	1110	.16
T10-1140-14	7762-2141	114	1140	.16
T10-1150-14	7762-2142	115	1150	.16
T10-1210-14	7762-2143	121	1210	.17
T10-1240-14	7762-2144	124	1240	.17
T10-1250-14	7762-2145	125	1250	.18
T10-1300-14	7762-2146	130	1300	.18
T10-1320-14	7762-2147	132	1320	.19
T10-1350-14	7762-2148	135	1350	.19
T10-1390-14	7762-2149	139	1390	.20
T10-1400-14	7762-2150	140	1400	.20
T10-1420-14	7762-2151	142	1420	.20
T10-1450-14	7762-2152	145	1450	.20
T10-1460-14	7762-2153	146	1460	.21
T10-1500-14	7762-2154	150	1500	.21
T10-1560-14	7762-2155	156	1560	.22
T10-1610-14	7762-2156	161	1610	.23
T10-1750-14	7762-2157	175	1750	.25
T10-1780-14	7762-2158	178	1780	.25
T10-1880-14	7762-2159	188	1880	.26
T10-1960-14	7762-2160	196	1960	.28
T10-2250-14	7762-2161	225	2250	.32

T10 Pitch — 16mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-16	7762-2165	26	260	.04
T10-370-16	7762-2166	37	370	.06
T10-400-16	7762-2167	40	400	.06
T10-410-16	7762-2168	41	410	.07
T10-440-16	7762-2169	44	440	.07
T10-450-16	7762-2170	45	450	.07
T10-500-16	7762-2171	50	500	.08
T10-530-16	7762-2172	53	530	.09

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-560-16	7762-2173	56	560	.09
T10-600-16	7762-2174	60	600	.10
T10-610-16	7762-2175	61	610	.10
T10-630-16	7762-2176	63	630	.10
T10-660-16	7762-2177	66	660	.11
T10-690-16	7762-2178	69	690	.11
T10-700-16	7762-2179	70	700	.11
T10-720-16	7762-2180	72	720	.12

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T10 Pitch — 16mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-730-16	7762-2181	73	730	.12
T10-750-16	7762-2182	75	750	.12
T10-780-16	7762-2183	78	780	.13
T10-800-16	7762-0329	80	800	.13
T10-810-16	7762-2184	81	810	.13
T10-840-16	7762-2185	84	840	.13
T10-880-16	7762-2186	88	880	.14
T10-890-16	7762-2187	89	890	.14
T10-900-16	7762-2188	90	900	.14
T10-910-16	7762-2189	91	910	.15
T10-920-16	7762-2190	92	920	.15
T10-950-16	7762-0342	95	950	.15
T10-960-16	7762-2191	96	960	.15
T10-970-16	7762-2192	97	970	.16
T10-980-16	7762-2193	98	980	.16
T10-1000-16	7762-0355	100	1000	.16
T10-1010-16	7762-2194	101	1010	.16
T10-1080-16	7762-2195	108	1080	.17
T10-1100-16	7762-2196	110	1100	.18
T10-1110-16	7762-2197	111	1110	.18
T10-1140-16	7762-2198	114	1140	.18

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-1150-16	7762-2199	115	1150	.18
T10-1210-16	7762-2200	121	1210	.19
T10-1240-16	7762-2201	124	1240	.20
T10-1250-16	7762-2202	125	1250	.20
T10-1300-16	7762-2203	130	1300	.21
T10-1320-16	7762-2204	132	1320	.21
T10-1350-16	7762-2205	135	1350	.22
T10-1390-16	7762-2206	139	1390	.22
T10-1400-16	7762-2207	140	1400	.22
T10-1420-16	7762-2208	142	1420	.23
T10-1450-16	7762-2209	145	1450	.23
T10-1460-16	7762-2210	146	1460	.23
T10-1500-16	7762-2211	150	1500	.24
T10-1560-16	7762-2212	156	1560	.25
T10-1610-16	7762-2213	161	1610	.26
T10-1750-16	7762-2214	175	1750	.28
T10-1780-16	7762-2215	178	1780	.29
T10-1880-16	7762-2216	188	1880	.30
T10-1960-16	7762-2217	196	1960	.31
T10-2250-16	7762-2218	225	2250	.36

T10 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-20	7762-2220	26	260	.05
T10-370-20	7762-2221	37	370	.07
T10-400-20	7762-2222	40	400	.08
T10-410-20	7762-2223	41	410	.08
T10-440-20	7762-2224	44	440	.09
T10-450-20	7762-2225	45	450	.09
T10-500-20	7762-2226	50	500	.10
T10-530-20	7762-2227	53	530	.11
T10-560-20	7762-2228	56	560	.11
T10-600-20	7762-2229	60	600	.12
T10-610-20	7762-2230	61	610	.12
T10-630-20	7762-2231	63	630	.13
T10-660-20	7762-2232	66	660	.13
T10-690-20	7762-2233	69	690	.14
T10-700-20	7762-2234	70	700	.14
T10-720-20	7762-2235	72	720	.14
T10-730-20	7762-2236	73	730	.15
T10-750-20	7762-2237	75	750	.15
T10-780-20	7762-2238	78	780	.16
T10-800-20	7762-0330	80	800	.16
T10-810-20	7762-2239	81	810	.16
T10-840-20	7762-2240	84	840	.17
T10-880-20	7762-2241	88	880	.18
T10-890-20	7762-2242	89	890	.18
T10-900-20	7762-2243	90	900	.18
T10-910-20	7762-2244	91	910	.18
T10-920-20	7762-2245	92	920	.18
T10-950-20	7762-0343	95	950	.19
T10-960-20	7762-2246	96	960	.19

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-970-20	7762-2247	97	970	.19
T10-980-20	7762-2248	98	980	.20
T10-1000-20	7762-0356	100	1000	.20
T10-1010-20	7762-2249	101	1010	.20
T10-1080-20	7762-2250	108	1080	.22
T10-1100-20	7762-2251	110	1100	.22
T10-1110-20	7762-2252	111	1110	.22
T10-1140-20	7762-2253	114	1140	.23
T10-1150-20	7762-2254	115	1150	.23
T10-1210-20	7762-2255	121	1210	.24
T10-1240-20	7762-2256	124	1240	.25
T10-1250-20	7762-2257	125	1250	.25
T10-1300-20	7762-2258	130	1300	.26
T10-1320-20	7762-2259	132	1320	.27
T10-1350-20	7762-2260	135	1350	.27
T10-1390-20	7762-2261	139	1390	.28
T10-1400-20	7762-2262	140	1400	.28
T10-1420-20	7762-2263	142	1420	.29
T10-1450-20	7762-2264	145	1450	.29
T10-1460-20	7762-2265	146	1460	.29
T10-1500-20	7762-2266	150	1500	.30
T10-1560-20	7762-2267	156	1560	.31
T10-1610-20	7762-2268	161	1610	.32
T10-1750-20	7762-2269	175	1750	.35
T10-1780-20	7762-2270	178	1780	.36
T10-1880-20	7762-2271	188	1880	.38
T10-1960-20	7762-2272	196	1960	.39
T10-2250-20	7762-2273	225	2250	.45



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T10 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-25	7762-2275	26	260	.07
T10-370-25	7762-2276	37	370	.09
T10-400-25	7762-2277	40	400	.10
T10-410-25	7762-2278	41	410	.10
T10-440-25	7762-2279	44	440	.11
T10-450-25	7762-2280	45	450	.11
T10-500-25	7762-2281	50	500	.13
T10-530-25	7762-2282	53	530	.13
T10-560-25	7762-2283	56	560	.14
T10-600-25	7762-2284	60	600	.15
T10-610-25	7762-2285	61	610	.15
T10-630-25	7762-2286	63	630	.16
T10-660-25	7762-2287	66	660	.17
T10-690-25	7762-2288	69	690	.17
T10-700-25	7762-2289	70	700	.18
T10-720-25	7762-2290	72	720	.18
T10-730-25	7762-2291	73	730	.18
T10-750-25	7762-2292	75	750	.19
T10-780-25	7762-2293	78	780	.20
T10-800-25	7762-0331	80	800	.20
T10-810-25	7762-2294	81	810	.20
T10-840-25	7762-2295	84	840	.21
T10-880-25	7762-2296	88	880	.22
T10-890-25	7762-2297	89	890	.22
T10-900-25	7762-2298	90	900	.23
T10-910-25	7762-2299	91	910	.23
T10-920-25	7762-2300	92	920	.23
T10-950-25	7762-0344	95	950	.24
T10-960-25	7762-2301	96	960	.24

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-970-25	7762-2302	97	970	.24
T10-980-25	7762-2303	98	980	.25
T10-1000-25	7762-0357	100	1000	.25
T10-1010-25	7762-2304	101	1010	.25
T10-1080-25	7762-2305	108	1080	.27
T10-1100-25	7762-2306	110	1100	.28
T10-1110-25	7762-2307	111	1110	.28
T10-1140-25	7762-2308	114	1140	.29
T10-1150-25	7762-2309	115	1150	.29
T10-1210-25	7762-2310	121	1210	.30
T10-1240-25	7762-2311	124	1240	.31
T10-1250-25	7762-2312	125	1250	.31
T10-1300-25	7762-2313	130	1300	.33
T10-1320-25	7762-2314	132	1320	.33
T10-1350-25	7762-2315	135	1350	.34
T10-1390-25	7762-2316	139	1390	.35
T10-1400-25	7762-2317	140	1400	.35
T10-1420-25	7762-2318	142	1420	.36
T10-1450-25	7762-2319	145	1450	.36
T10-1460-25	7762-2320	146	1460	.37
T10-1500-25	7762-2321	150	1500	.38
T10-1560-25	7762-2322	156	1560	.39
T10-1610-25	7762-2323	161	1610	.40
T10-1750-25	7762-2324	175	1750	.44
T10-1780-25	7762-2325	178	1780	.45
T10-1880-25	7762-2326	188	1880	.47
T10-1960-25	7762-2327	196	1960	.49
T10-2250-25	7762-2328	225	2250	.56

T10 Pitch — 32mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-32	7762-2330	26	260	.08
T10-370-32	7762-2331	37	370	.12
T10-400-32	7762-2332	40	400	.13
T10-410-32	7762-2333	41	410	.13
T10-440-32	7762-2334	44	440	.14
T10-450-32	7762-2335	45	450	.14
T10-500-32	7762-2336	50	500	.16
T10-530-32	7762-2337	53	530	.17
T10-560-32	7762-2338	56	560	.18
T10-600-32	7762-2339	60	600	.19
T10-610-32	7762-2340	61	610	.20
T10-630-32	7762-2341	63	630	.20
T10-660-32	7762-2342	66	660	.21
T10-690-32	7762-2343	69	690	.22
T10-700-32	7762-2344	70	700	.22
T10-720-32	7762-2345	72	720	.23
T10-730-32	7762-2346	73	730	.23
T10-750-32	7762-2347	75	750	.24
T10-780-32	7762-2348	78	780	.25
T10-800-32	7762-0332	80	800	.26
T10-810-32	7762-2349	81	810	.26
T10-840-32	7762-2350	84	840	.27
T10-880-32	7762-2351	88	880	.28
T10-890-32	7762-2352	89	890	.29

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-900-32	7762-2353	90	900	.29
T10-910-32	7762-2354	91	910	.29
T10-920-32	7762-2355	92	920	.30
T10-950-32	7762-0345	95	950	.31
T10-960-32	7762-2356	96	960	.31
T10-970-32	7762-2357	97	970	.31
T10-980-32	7762-2358	98	980	.31
T10-1000-32	7762-0358	100	1000	.32
T10-1010-32	7762-2359	101	1010	.32
T10-1080-32	7762-2360	108	1080	.35
T10-1100-32	7762-2361	110	1100	.35
T10-1110-32	7762-2362	111	1110	.36
T10-1140-32	7762-2363	114	1140	.37
T10-1150-32	7762-2364	115	1150	.37
T10-1210-32	7762-2365	121	1210	.39
T10-1240-32	7762-2366	124	1240	.40
T10-1250-32	7762-2367	125	1250	.40
T10-1300-32	7762-2368	130	1300	.42
T10-1320-32	7762-2369	132	1320	.42
T10-1350-32	7762-2370	135	1350	.43
T10-1390-32	7762-2371	139	1390	.45
T10-1400-32	7762-2372	140	1400	.45
T10-1420-32	7762-2373	142	1420	.46



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T10 Pitch — 32mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-1450-32	7762-2374	145	1450	.47
T10-1460-32	7762-2375	146	1460	.47
T10-1500-32	7762-2376	150	1500	.48
T10-1560-32	7762-2377	156	1560	.50
T10-1610-32	7762-2378	161	1610	.52

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-1750-32	7762-2379	175	1750	.56
T10-1780-32	7762-2380	178	1780	.57
T10-1880-32	7762-2381	188	1880	.60
T10-1960-32	7762-2382	196	1960	.63
T10-2250-32	7762-2383	225	2250	.72

T10 Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-260-50	7762-2385	26	260	.13
T10-370-50	7762-2386	37	370	.19
T10-400-50	7762-2387	40	400	.20
T10-410-50	7762-2388	41	410	.21
T10-440-50	7762-2389	44	440	.22
T10-450-50	7762-2390	45	450	.23
T10-500-50	7762-2391	50	500	.25
T10-530-50	7762-2392	53	530	.27
T10-560-50	7762-2393	56	560	.28
T10-600-50	7762-2394	60	600	.30
T10-610-50	7762-2395	61	610	.31
T10-630-50	7762-2396	63	630	.32
T10-660-50	7762-2397	66	660	.33
T10-690-50	7762-2398	69	690	.35
T10-700-50	7762-2399	70	700	.35
T10-720-50	7762-2400	72	720	.36
T10-730-50	7762-2401	73	730	.37
T10-750-50	7762-2402	75	750	.38
T10-780-50	7762-2403	78	780	.39
T10-800-50	7762-0333	80	800	.40
T10-810-50	7762-2404	81	810	.41
T10-840-50	7762-2405	84	840	.42
T10-880-50	7762-2406	88	880	.44
T10-890-50	7762-2407	89	890	.45
T10-900-50	7762-2408	90	900	.45
T10-910-50	7762-2409	91	910	.46
T10-920-50	7762-2410	92	920	.46
T10-950-50	7762-0346	95	950	.48
T10-960-50	7762-2411	96	960	.48

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
T10-970-50	7762-2412	97	970	.49
T10-980-50	7762-2413	98	980	.49
T10-1000-50	7762-0359	100	1000	.50
T10-1010-50	7762-2414	101	1010	.51
T10-1080-50	7762-2415	108	1080	.54
T10-1100-50	7762-2416	110	1100	.55
T10-1110-50	7762-2417	111	1110	.56
T10-1140-50	7762-2418	114	1140	.57
T10-1150-50	7762-2419	115	1150	.58
T10-1210-50	7762-2420	121	1210	.61
T10-1240-50	7762-2421	124	1240	.62
T10-1250-50	7762-2422	125	1250	.63
T10-1300-50	7762-2423	130	1300	.65
T10-1320-50	7762-2424	132	1320	.66
T10-1350-50	7762-2425	135	1350	.68
T10-1390-50	7762-2426	139	1390	.70
T10-1400-50	7762-2427	140	1400	.70
T10-1420-50	7762-2428	142	1420	.71
T10-1450-50	7762-2429	145	1450	.73
T10-1460-50	7762-2430	146	1460	.73
T10-1500-50	7762-2431	150	1500	.75
T10-1560-50	7762-2432	156	1560	.78
T10-1610-50	7762-2433	161	1610	.81
T10-1750-50	7762-2434	175	1750	.88
T10-1780-50	7762-2435	178	1780	.89
T10-1880-50	7762-2436	188	1880	.94
T10-1960-50	7762-2437	196	1960	.98
T10-2250-50	7762-2438	225	2250	1.13

T10 Pitch — 75mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-260-75	7762-2450	26	260	.20
⁶ T10-370-75	7762-2451	37	370	.28
⁶ T10-400-75	7762-2452	40	400	.30
⁶ T10-410-75	7762-2453	41	410	.31
⁶ T10-440-75	7762-2454	44	440	.33
⁶ T10-450-75	7762-2455	45	450	.34
⁶ T10-500-75	7762-2456	50	500	.38
⁶ T10-530-75	7762-2457	53	530	.40
⁶ T10-560-75	7762-2458	56	560	.42
⁶ T10-600-75	7762-2459	60	600	.45
⁶ T10-610-75	7762-2460	61	610	.46
⁶ T10-630-75	7762-2461	63	630	.47
⁶ T10-660-75	7762-2462	66	660	.50
⁶ T10-690-75	7762-2463	69	690	.52
⁶ T10-700-75	7762-2464	70	700	.53
⁶ T10-720-75	7762-2465	72	720	.54
⁶ T10-730-75	7762-2466	73	730	.55

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-750-75	7762-2467	75	750	.56
⁶ T10-780-75	7762-2468	78	780	.59
⁶ T10-800-75	7762-0334	80	800	.60
⁶ T10-810-75	7762-2469	81	810	.61
⁶ T10-840-75	7762-2470	84	840	.63
⁶ T10-880-75	7762-2471	88	880	.66
⁶ T10-890-75	7762-2472	89	890	.67
⁶ T10-900-75	7762-2473	90	900	.68
⁶ T10-910-75	7762-2474	91	910	.69
⁶ T10-920-75	7762-2475	92	920	.69
⁶ T10-950-75	7762-0347	95	950	.71
⁶ T10-960-75	7762-2476	96	960	.72
⁶ T10-970-75	7762-2477	97	970	.73
⁶ T10-980-75	7762-2478	98	980	.74
⁶ T10-1000-75	7762-0360	100	1000	.75
⁶ T10-1010-75	7762-2479	101	1010	.76
⁶ T10-1080-75	7762-2480	108	1080	.81

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T10 Pitch — 75mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-1100-75	7762-2481	110	1100	.83
⁶ T10-1110-75	7762-2482	111	1110	.84
⁶ T10-1140-75	7762-2483	114	1140	.86
⁶ T10-1150-75	7762-2484	115	1150	.87
⁶ T10-1210-75	7762-2485	121	1210	.91
⁶ T10-1240-75	7762-2486	124	1240	.93
⁶ T10-1250-75	7762-2487	125	1250	.94
⁶ T10-1300-75	7762-2488	130	1300	.98
⁶ T10-1320-75	7762-2489	132	1320	.99
⁶ T10-1350-75	7762-2490	135	1350	1.02
⁶ T10-1390-75	7762-2491	139	1390	1.05
⁶ T10-1400-75	7762-2492	140	1400	1.05

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-1420-75	7762-2493	142	1420	1.07
⁶ T10-1450-75	7762-2494	145	1450	1.09
⁶ T10-1460-75	7762-2495	146	1460	1.10
⁶ T10-1500-75	7762-2496	150	1500	1.13
⁶ T10-1560-75	7762-2497	156	1560	1.17
⁶ T10-1610-75	7762-2498	161	1610	1.21
⁶ T10-1750-75	7762-2499	175	1750	1.32
⁶ T10-1780-75	7762-2500	178	1780	1.34
⁶ T10-1880-75	7762-2501	188	1880	1.42
⁶ T10-1960-75	7762-2502	196	1960	1.48
⁶ T10-2250-75	7762-2503	225	2250	1.69

T10 Pitch — 100mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-260-100	7762-2505	26	260	.52
⁶ T10-370-100	7762-2506	37	370	.74
⁶ T10-400-100	7762-2507	40	400	.80
⁶ T10-410-100	7762-2508	41	410	.82
⁶ T10-440-100	7762-2509	44	440	.88
⁶ T10-450-100	7762-2510	45	450	.90
⁶ T10-500-100	7762-2511	50	500	1.00
⁶ T10-530-100	7762-2512	53	530	1.06
⁶ T10-560-100	7762-2513	56	560	1.12
⁶ T10-600-100	7762-2514	60	600	1.20
⁶ T10-610-100	7762-2515	61	610	1.22
⁶ T10-630-100	7762-2516	63	630	1.26
⁶ T10-660-100	7762-2517	66	660	1.33
⁶ T10-690-100	7762-2518	69	690	1.39
⁶ T10-700-100	7762-2519	70	700	1.41
⁶ T10-720-100	7762-2520	72	720	1.45
⁶ T10-730-100	7762-2521	73	730	1.47
⁶ T10-750-100	7762-2522	75	750	1.51
⁶ T10-780-100	7762-2523	78	780	1.57
⁶ T10-800-100	7762-0335	80	800	1.61
⁶ T10-810-100	7762-2524	81	810	1.63
⁶ T10-840-100	7762-2525	84	840	1.69
⁶ T10-880-100	7762-2526	88	880	1.77
⁶ T10-890-100	7762-2527	89	890	1.79
⁶ T10-900-100	7762-2528	90	900	1.81
⁶ T10-910-100	7762-2529	91	910	1.83
⁶ T10-920-100	7762-2530	92	920	1.85
⁶ T10-950-100	7762-0348	95	950	1.91
⁶ T10-960-100	7762-2531	96	960	1.93

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-970-100	7762-2532	97	970	1.95
⁶ T10-980-100	7762-2533	98	980	1.97
⁶ T10-1000-100	7762-0361	100	1000	2.01
⁶ T10-1010-100	7762-2534	101	1010	2.03
⁶ T10-1080-100	7762-2535	108	1080	2.17
⁶ T10-1100-100	7762-2536	110	1100	2.21
⁶ T10-1110-100	7762-2537	111	1110	2.23
⁶ T10-1140-100	7762-2538	114	1140	2.29
⁶ T10-1150-100	7762-2539	115	1150	2.31
⁶ T10-1210-100	7762-2540	121	1210	2.43
⁶ T10-1240-100	7762-2541	124	1240	2.24
⁶ T10-1250-100	7762-2542	125	1250	1.25
⁶ T10-1300-100	7762-2543	130	1300	1.31
⁶ T10-1320-100	7762-2544	132	1320	1.33
⁶ T10-1350-100	7762-2545	135	1350	1.36
⁶ T10-1390-100	7762-2546	139	1390	1.40
⁶ T10-1400-100	7762-2547	140	1400	1.41
⁶ T10-1420-100	7762-2548	142	1420	1.43
⁶ T10-1450-100	7762-2549	145	1450	1.46
⁶ T10-1460-100	7762-2550	146	1460	1.47
⁶ T10-1500-100	7762-2551	150	1500	1.51
⁶ T10-1560-100	7762-2552	156	1560	1.57
⁶ T10-1610-100	7762-2553	161	1610	1.62
⁶ T10-1750-100	7762-2554	175	1750	1.76
⁶ T10-1780-100	7762-2555	178	1780	1.79
⁶ T10-1880-100	7762-2556	188	1880	1.89
⁶ T10-1960-100	7762-2557	196	1960	1.97
⁶ T10-2250-100	7762-2558	225	2250	2.26

T10 Pitch — 200mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-260-200	7762-2560	26	260	.52
⁶ T10-370-200	7762-2561	37	370	.74
⁶ T10-400-200	7762-2562	40	400	.80
⁶ T10-410-200	7762-2563	41	410	.82
⁶ T10-440-200	7762-2564	44	440	.88
⁶ T10-450-200	7762-2565	45	450	.90
⁶ T10-500-200	7762-2566	50	500	1.00
⁶ T10-530-200	7762-2567	53	530	1.06
⁶ T10-560-200	7762-2568	56	560	1.12
⁶ T10-600-200	7762-2569	60	600	1.20

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-610-200	7762-2570	61	610	1.22
⁶ T10-630-200	7762-2571	63	630	1.26
⁶ T10-660-200	7762-2572	66	660	1.33
⁶ T10-690-200	7762-2573	69	690	1.39
⁶ T10-700-200	7762-2574	70	700	1.41
⁶ T10-720-200	7762-2575	72	720	1.45
⁶ T10-730-200	7762-2576	73	730	1.47
⁶ T10-750-200	7762-2577	75	750	1.51
⁶ T10-780-200	7762-2578	78	780	1.57
⁶ T10-800-200	7762-0336	80	800	1.61

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

T10 Pitch — 200mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-810-200	7762-2579	81	810	1.63
⁶ T10-840-200	7762-2580	84	840	1.69
⁶ T10-880-200	7762-2581	88	880	1.77
⁶ T10-890-200	7762-2582	89	890	1.79
⁶ T10-900-200	7762-2583	90	900	1.81
⁶ T10-910-200	7762-2584	91	910	1.83
⁶ T10-920-200	7762-2585	92	920	1.85
⁶ T10-950-200	7762-0349	95	950	1.91
⁶ T10-960-200	7762-2586	96	960	1.93
⁶ T10-970-200	7762-2587	97	970	1.95
⁶ T10-980-200	7762-2588	98	980	1.97
⁶ T10-1000-200	7762-0362	100	1000	2.01
⁶ T10-1010-200	7762-2589	101	1010	2.03
⁶ T10-1080-200	7762-2590	108	1080	2.17
⁶ T10-1100-200	7762-2591	110	1100	2.21
⁶ T10-1110-200	7762-2592	111	1110	2.23
⁶ T10-1140-200	7762-2593	114	1140	2.29
⁶ T10-1150-200	7762-2594	115	1150	2.31
⁶ T10-1210-200	7762-2595	121	1210	2.43

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ T10-1240-200	7762-2596	124	1240	2.49
⁶ T10-1250-200	7762-2597	125	1250	2.51
⁶ T10-1300-200	7762-2598	130	1300	2.61
⁶ T10-1320-200	7762-2599	132	1320	2.65
⁶ T10-1350-200	7762-2600	135	1350	2.71
⁶ T10-1390-200	7762-2601	139	1390	2.79
⁶ T10-1400-200	7762-2602	140	1400	2.81
⁶ T10-1420-200	7762-2603	142	1420	2.85
⁶ T10-1450-200	7762-2604	145	1450	2.91
⁶ T10-1460-200	7762-2605	146	1460	2.93
⁶ T10-1500-200	7762-2606	150	1500	3.01
⁶ T10-1560-200	7762-2607	156	1560	3.13
⁶ T10-1610-200	7762-2608	161	1610	3.23
⁶ T10-1750-200	7762-2609	175	1750	3.51
⁶ T10-1780-200	7762-2610	178	1780	3.57
⁶ T10-1880-200	7762-2611	188	1880	3.77
⁶ T10-1960-200	7762-2612	196	1960	3.94
⁶ T10-2250-200	7762-2613	225	2250	4.52

AT5 Pitch — 4mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-4	7762-3000	45	225	.01
⁶ AT5-255-4	7762-3001	51	255	.01
⁶ AT5-275-4	7762-3002	55	275	.01
⁶ AT5-280-4	7762-3003	56	280	.01
⁶ AT5-300-4	7762-3004	60	300	.01
⁶ AT5-340-4	7762-3005	68	340	.01
⁶ AT5-375-4	7762-3006	75	375	.01
⁶ AT5-390-4	7762-3007	78	390	.01
⁶ AT5-420-4	7762-3008	84	420	.01
⁶ AT5-455-4	7762-3009	91	455	.01
⁶ AT5-500-4	7762-3010	100	500	.02
⁶ AT5-545-4	7762-3011	109	545	.02

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-600-4	7762-3012	120	600	.02
⁶ AT5-610-4	7762-3013	122	610	.02
⁶ AT5-630-4	7762-3014	126	630	.02
⁶ AT5-660-4	7762-3015	132	660	.02
⁶ AT5-720-4	7762-3016	144	720	.02
⁶ AT5-750-4	7762-3017	150	750	.02
⁶ AT5-780-4	7762-3018	156	780	.02
⁶ AT5-825-4	7762-3019	165	825	.02
⁶ AT5-975-4	7762-3020	195	975	.03
⁶ AT5-1050-4	7762-3021	210	1050	.03
⁶ AT5-1125-4	7762-3022	225	1125	.03

AT5 Pitch — 6mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-225-6	7762-3024	45	225	.01
AT5-255-6	7762-3025	51	255	.01
AT5-275-6	7762-3026	55	275	.01
AT5-280-6	7762-3027	56	280	.01
AT5-300-6	7762-3028	60	300	.01
AT5-340-6	7762-3029	68	340	.02
AT5-375-6	7762-3030	75	375	.02
AT5-390-6	7762-3031	78	390	.02
AT5-420-6	7762-3032	84	420	.02
AT5-455-6	7762-3033	91	455	.02
AT5-500-6	7762-3034	100	500	.02
AT5-545-6	7762-3035	109	545	.02

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-600-6	7762-3036	120	600	.03
AT5-610-6	7762-3037	122	610	.03
AT5-630-6	7762-3038	126	630	.03
AT5-660-6	7762-3039	132	660	.03
AT5-720-6	7762-3040	144	720	.03
AT5-750-6	7762-3041	150	750	.03
AT5-780-6	7762-3042	156	780	.04
AT5-825-6	7762-3043	165	825	.04
AT5-975-6	7762-3044	195	975	.04
AT5-1050-6	7762-3045	210	1050	.05
AT5-1125-6	7762-3046	225	1125	.05
AT5-1500-6	7762-3312	300	1500	.06

AT5 Pitch — 8mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-8	7762-3048	45	225	.01
⁶ AT5-255-8	7762-3049	51	255	.02
⁶ AT5-275-8	7762-3050	55	275	.02

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-280-8	7762-3051	56	280	.02
⁶ AT5-300-8	7762-3052	60	300	.02
⁶ AT5-340-8	7762-3053	68	340	.02

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



The Driving Force in Power Transmission.

Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

AT5 Pitch — 8mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-375-8	7762-3054	75	375	.02
⁶ AT5-390-8	7762-3055	78	390	.02
⁶ AT5-420-8	7762-3056	84	420	.03
⁶ AT5-455-8	7762-3057	91	455	.03
⁶ AT5-500-8	7762-3058	100	500	.03
⁶ AT5-545-8	7762-3059	109	545	.03
⁶ AT5-600-8	7762-3060	120	600	.04
⁶ AT5-610-8	7762-3061	122	610	.04
⁶ AT5-630-8	7762-3062	126	630	.04

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-660-8	7762-3063	132	660	.04
⁶ AT5-720-8	7762-3064	144	720	.04
⁶ AT5-750-8	7762-3065	150	750	.05
⁶ AT5-780-8	7762-3066	156	780	.05
⁶ AT5-825-8	7762-3067	165	825	.05
⁶ AT5-975-8	7762-3068	195	975	.06
⁶ AT5-1050-8	7762-3069	210	1050	.06
⁶ AT5-1125-8	7762-3070	225	1125	.07
⁶ AT5-1500-8	7762-3313	300	1500	.09

AT5 Pitch — 10mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-225-10	7762-3072	45	225	.02
AT5-255-10	7762-3073	51	255	.02
AT5-275-10	7762-3074	55	275	.02
AT5-280-10	7762-3075	56	280	.02
AT5-300-10	7762-3076	60	300	.02
AT5-340-10	7762-3077	68	340	.03
AT5-375-10	7762-3078	75	375	.03
AT5-390-10	7762-3079	78	390	.03
AT5-420-10	7762-3080	84	420	.03
AT5-455-10	7762-3081	91	455	.03
AT5-500-10	7762-3082	100	500	.04
AT5-545-10	7762-3083	109	545	.04

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-600-10	7762-3084	120	600	.05
AT5-610-10	7762-3085	122	610	.05
AT5-630-10	7762-3086	126	630	.05
AT5-660-10	7762-3087	132	660	.05
AT5-720-10	7762-3088	144	720	.05
AT5-750-10	7762-3089	150	750	.06
AT5-780-10	7762-3090	156	780	.06
AT5-825-10	7762-3091	165	825	.06
AT5-975-10	7762-3092	195	975	.07
AT5-1050-10	7762-3093	210	1050	.08
AT5-1125-10	7762-3094	225	1125	.09
AT5-1500-10	7762-3314	300	1500	.11

AT5 Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-12	7762-3096	45	225	.02
⁶ AT5-255-12	7762-3097	51	255	.02
⁶ AT5-275-12	7762-3098	55	275	.02
⁶ AT5-280-12	7762-3099	56	280	.03
⁶ AT5-300-12	7762-3100	60	300	.03
⁶ AT5-340-12	7762-3101	68	340	.03
⁶ AT5-375-12	7762-3102	75	375	.03
⁶ AT5-390-12	7762-3103	78	390	.04
⁶ AT5-420-12	7762-3104	84	420	.04
⁶ AT5-455-12	7762-3105	91	455	.04
⁶ AT5-500-12	7762-3106	100	500	.05
⁶ AT5-545-12	7762-3107	109	545	.05

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-600-12	7762-3108	120	600	.05
⁶ AT5-610-12	7762-3109	122	610	.06
⁶ AT5-630-12	7762-3110	126	630	.06
⁶ AT5-660-12	7762-3111	132	660	.06
⁶ AT5-720-12	7762-3112	144	720	.07
⁶ AT5-750-12	7762-3113	150	750	.07
⁶ AT5-780-12	7762-3114	156	780	.07
⁶ AT5-825-12	7762-3115	165	825	.07
⁶ AT5-975-12	7762-3116	195	975	.09
⁶ AT5-1050-12	7762-3117	210	1050	.10
⁶ AT5-1125-12	7762-3118	225	1125	.10
⁶ AT5-1500-12	7762-3315	300	1500	.13

AT5 Pitch — 16mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-225-16	7762-3120	45	225	.03
AT5-255-16	7762-3121	51	255	.03
AT5-275-16	7762-3122	55	275	.03
AT5-280-16	7762-3123	56	280	.03
AT5-300-16	7762-3124	60	300	.04
AT5-340-16	7762-3125	68	340	.04
AT5-375-16	7762-3126	75	375	.05
AT5-390-16	7762-3127	78	390	.05
AT5-420-16	7762-3128	84	420	.05
AT5-455-16	7762-3129	91	455	.06
AT5-500-16	7762-3130	100	500	.06
AT5-545-16	7762-3131	109	545	.07
AT5-600-16	7762-3132	120	600	.07

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-610-16	7762-3133	122	610	.07
AT5-630-16	7762-3134	126	630	.08
AT5-660-16	7762-3135	132	660	.08
AT5-720-16	7762-3136	144	720	.09
AT5-750-16	7762-3137	150	750	.09
AT5-780-16	7762-3138	156	780	.09
AT5-825-16	7762-3139	165	825	.10
AT5-975-16	7762-3140	195	975	.12
AT5-1050-16	7762-3141	210	1050	.13
AT5-1125-16	7762-3142	225	1125	.14
AT5-1500-16	7762-3316	300	1500	.18

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

AT5 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-225-20	7762-3144	45	225	.03
AT5-255-20	7762-3145	51	255	.04
AT5-275-20	7762-3146	55	275	.04
AT5-280-20	7762-3147	56	280	.04
AT5-300-20	7762-3148	60	300	.05
AT5-340-20	7762-3149	68	340	.05
AT5-375-20	7762-3150	75	375	.06
AT5-390-20	7762-3151	78	390	.06
AT5-420-20	7762-3152	84	420	.06
AT5-455-20	7762-3153	91	455	.07
AT5-500-20	7762-3154	100	500	.08
AT5-545-20	7762-3155	109	545	.08

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-600-20	7762-3156	120	600	.09
AT5-610-20	7762-3157	122	610	.09
AT5-630-20	7762-3158	126	630	.10
AT5-660-20	7762-3159	132	660	.10
AT5-720-20	7762-3160	144	720	.11
AT5-750-20	7762-3161	150	750	.11
AT5-780-20	7762-3162	156	780	.12
AT5-825-20	7762-3163	165	825	.12
AT5-975-20	7762-3164	195	975	.15
AT5-1050-20	7762-3165	210	1050	.16
AT5-1125-20	7762-3166	225	1125	.17
AT5-1500-20	7762-3317	300	1500	.22

AT5 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-225-25	7762-3168	45	225	.04
AT5-255-25	7762-3169	51	255	.05
AT5-275-25	7762-3170	55	275	.05
AT5-280-25	7762-3171	56	280	.05
AT5-300-25	7762-3172	60	300	.06
AT5-340-25	7762-3173	68	340	.06
AT5-375-25	7762-3174	75	375	.07
AT5-390-25	7762-3175	78	390	.07
AT5-420-25	7762-3176	84	420	.08
AT5-455-25	7762-3177	91	455	.09
AT5-500-25	7762-3178	100	500	.09
AT5-545-25	7762-3179	109	545	.10

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT5-600-25	7762-3180	120	600	.11
AT5-610-25	7762-3181	122	610	.12
AT5-630-25	7762-3182	126	630	.12
AT5-660-25	7762-3183	132	660	.12
AT5-720-25	7762-3184	144	720	.14
AT5-750-25	7762-3185	150	750	.14
AT5-780-25	7762-3186	156	780	.15
AT5-825-25	7762-3187	165	825	.16
AT5-975-25	7762-3188	195	975	.18
AT5-1050-25	7762-3189	210	1050	.20
AT5-1125-25	7762-3190	225	1125	.21
AT5-1500-25	7762-3318	300	1500	.28

AT5 Pitch — 32mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-32	7762-3192	45	225	.04
⁶ AT5-255-32	7762-3193	51	255	.05
⁶ AT5-275-32	7762-3194	55	275	.05
⁶ AT5-280-32	7762-3195	56	280	.05
⁶ AT5-300-32	7762-3196	60	300	.06
⁶ AT5-340-32	7762-3197	68	340	.06
⁶ AT5-375-32	7762-3198	75	375	.07
⁶ AT5-390-32	7762-3199	78	390	.07
⁶ AT5-420-32	7762-3200	84	420	.08
⁶ AT5-455-32	7762-3201	91	455	.09
⁶ AT5-500-32	7762-3202	100	500	.09
⁶ AT5-545-32	7762-3203	109	545	.10

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-600-32	7762-3204	120	600	.11
⁶ AT5-610-32	7762-3205	122	610	.12
⁶ AT5-630-32	7762-3206	126	630	.12
⁶ AT5-660-32	7762-3207	132	660	.12
⁶ AT5-720-32	7762-3208	144	720	.14
⁶ AT5-750-32	7762-3209	150	750	.14
⁶ AT5-780-32	7762-3210	156	780	.15
⁶ AT5-825-32	7762-3211	165	825	.16
⁶ AT5-975-32	7762-3212	195	975	.18
⁶ AT5-1050-32	7762-3213	210	1050	.20
⁶ AT5-1125-32	7762-3214	225	1125	.21
⁶ AT5-1500-32	7762-3319	300	1500	.28

AT5 Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-50	7762-3216	45	225	.09
⁶ AT5-255-50	7762-3217	51	255	.10
⁶ AT5-275-50	7762-3218	55	275	.10
⁶ AT5-280-50	7762-3219	56	280	.11
⁶ AT5-300-50	7762-3220	60	300	.11
⁶ AT5-340-50	7762-3221	68	340	.13
⁶ AT5-375-50	7762-3222	75	375	.14
⁶ AT5-390-50	7762-3223	78	390	.15
⁶ AT5-420-50	7762-3224	84	420	.16
⁶ AT5-455-50	7762-3225	91	455	.17

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-500-50	7762-3226	100	500	.19
⁶ AT5-545-50	7762-3227	109	545	.21
⁶ AT5-600-50	7762-3228	120	600	.23
⁶ AT5-610-50	7762-3229	122	610	.23
⁶ AT5-630-50	7762-3230	126	630	.24
⁶ AT5-660-50	7762-3231	132	660	.25
⁶ AT5-720-50	7762-3232	144	720	.27
⁶ AT5-750-50	7762-3233	150	750	.28
⁶ AT5-780-50	7762-3234	156	780	.30
⁶ AT5-825-50	7762-3235	165	825	.31

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

AT5 Pitch — 50mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-975-50	7762-3236	195	975	.37
⁶ AT5-1050-50	7762-3237	210	1050	.40

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-1125-50	7762-3238	225	1125	.43
⁶ AT5-1500-50	7762-3320	300	1500	.56

AT5 Pitch — 75mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-75	7762-3240	45	225	.13
⁶ AT5-255-75	7762-3241	51	255	.14
⁶ AT5-275-75	7762-3242	55	275	.16
⁶ AT5-280-75	7762-3243	56	280	.16
⁶ AT5-300-75	7762-3244	60	300	.17
⁶ AT5-340-75	7762-3245	68	340	.19
⁶ AT5-375-75	7762-3246	75	375	.21
⁶ AT5-390-75	7762-3247	78	390	.22
⁶ AT5-420-75	7762-3248	84	420	.24
⁶ AT5-455-75	7762-3249	91	455	.26
⁶ AT5-500-75	7762-3250	100	500	.28
⁶ AT5-545-75	7762-3251	109	545	.31

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-600-75	7762-3252	120	600	.34
⁶ AT5-610-75	7762-3253	122	610	.35
⁶ AT5-630-75	7762-3254	126	630	.36
⁶ AT5-660-75	7762-3255	132	660	.37
⁶ AT5-720-75	7762-3256	144	720	.41
⁶ AT5-750-75	7762-3257	150	750	.43
⁶ AT5-780-75	7762-3258	156	780	.44
⁶ AT5-825-75	7762-3259	165	825	.47
⁶ AT5-975-75	7762-3260	195	975	.55
⁶ AT5-1050-75	7762-3261	210	1050	.60
⁶ AT5-1125-75	7762-3262	225	1125	.64
⁶ AT5-1500-75	7762-3321	300	1500	.85

AT5 Pitch — 100mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-100	7762-3264	45	225	.17
⁶ AT5-255-100	7762-3265	51	255	.19
⁶ AT5-275-100	7762-3266	55	275	.21
⁶ AT5-280-100	7762-3267	56	280	.21
⁶ AT5-300-100	7762-3268	60	300	.23
⁶ AT5-340-100	7762-3269	68	340	.26
⁶ AT5-375-100	7762-3270	75	375	.28
⁶ AT5-390-100	7762-3271	78	390	.30
⁶ AT5-420-100	7762-3272	84	420	.32
⁶ AT5-455-100	7762-3273	91	455	.34
⁶ AT5-500-100	7762-3274	100	500	.38
⁶ AT5-545-100	7762-3275	109	545	.41

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-600-100	7762-3276	120	600	.45
⁶ AT5-610-100	7762-3277	122	610	.46
⁶ AT5-630-100	7762-3278	126	630	.48
⁶ AT5-660-100	7762-3279	132	660	.50
⁶ AT5-720-100	7762-3280	144	720	.55
⁶ AT5-750-100	7762-3281	150	750	.57
⁶ AT5-780-100	7762-3282	156	780	.59
⁶ AT5-825-100	7762-3283	165	825	.62
⁶ AT5-975-100	7762-3284	195	975	.74
⁶ AT5-1050-100	7762-3285	210	1050	.80
⁶ AT5-1125-100	7762-3286	225	1125	.85
⁶ AT5-1500-100	7762-3322	300	1500	1.13

AT5 Pitch — 200mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-225-200	7762-3288	45	225	.34
⁶ AT5-255-200	7762-3289	51	255	.39
⁶ AT5-275-200	7762-3290	55	275	.42
⁶ AT5-280-200	7762-3291	56	280	.42
⁶ AT5-300-200	7762-3292	60	300	.45
⁶ AT5-340-200	7762-3293	68	340	.52
⁶ AT5-375-200	7762-3294	75	375	.57
⁶ AT5-390-200	7762-3295	78	390	.59
⁶ AT5-420-200	7762-3296	84	420	.64
⁶ AT5-455-200	7762-3297	91	455	.69
⁶ AT5-500-200	7762-3298	100	500	.76
⁶ AT5-545-200	7762-3299	109	545	.83

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT5-600-200	7762-3300	120	600	.91
⁶ AT5-610-200	7762-3301	122	610	.92
⁶ AT5-630-200	7762-3302	126	630	.95
⁶ AT5-660-200	7762-3303	132	660	1.00
⁶ AT5-720-200	7762-3304	144	720	1.09
⁶ AT5-750-200	7762-3305	150	750	1.14
⁶ AT5-780-200	7762-3306	156	780	1.18
⁶ AT5-825-200	7762-3307	165	825	1.25
⁶ AT5-975-200	7762-3308	195	975	1.48
⁶ AT5-1050-200	7762-3309	210	1050	1.59
⁶ AT5-1125-200	7762-3310	225	1125	1.70
⁶ AT5-1500-200	7762-3323	300	1500	2.27

AT10 Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-500-12	7762-4000	50	500	.08
⁶ AT10-560-12	7762-4001	56	560	.08

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-610-12	7762-4002	61	610	.09
⁶ AT10-660-12	7762-4003	66	660	.10

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

AT10 Pitch — 12mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-700-12	7762-4004	70	700	.11
⁶ AT10-730-12	7762-4005	73	730	.11
⁶ AT10-780-12	7762-4006	78	780	.12
⁶ AT10-800-12	7762-4007	80	800	.12
⁶ AT10-810-12	7762-4008	81	810	.12
⁶ AT10-840-12	7762-4009	84	840	.13
⁶ AT10-890-12	7762-4010	89	890	.13
⁶ AT10-920-12	7762-4011	92	920	.14
⁶ AT10-960-12	7762-4012	96	960	.14
⁶ AT10-980-12	7762-4013	98	980	.15
⁶ AT10-1010-12	7762-4014	101	1010	.15

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-1050-12	7762-4015	105	1050	.16
⁶ AT10-1080-12	7762-4016	108	1080	.16
⁶ AT10-1150-12	7762-4017	115	1150	.17
⁶ AT10-1210-12	7762-4018	121	1210	.18
⁶ AT10-1250-12	7762-4019	125	1250	.19
⁶ AT10-1320-12	7762-4020	132	1320	.20
⁶ AT10-1400-12	7762-4021	140	1400	.21
⁶ AT10-1500-12	7762-4022	150	1500	.23
⁶ AT10-1600-12	7762-4023	160	1600	.24
⁶ AT10-1700-12	7762-4024	170	1700	.26
⁶ AT10-1800-12	7762-4226	180	1800	.27

AT10 Pitch — 16mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-500-16	7762-4025	50	500	.10
AT10-560-16	7762-4026	56	560	.11
AT10-610-16	7762-4027	61	610	.12
AT10-660-16	7762-4028	66	660	.13
AT10-700-16	7762-4029	70	700	.14
AT10-730-16	7762-4030	73	730	.15
AT10-780-16	7762-4031	78	780	.16
AT10-800-16	7762-4032	80	800	.16
AT10-810-16	7762-4033	81	810	.16
AT10-840-16	7762-4034	84	840	.17
AT10-890-16	7762-4035	89	890	.18
AT10-920-16	7762-4036	92	920	.18
AT10-960-16	7762-4037	96	960	.19

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-980-16	7762-4038	98	980	.20
AT10-1010-16	7762-4039	101	1010	.20
AT10-1050-16	7762-4040	105	1050	.21
AT10-1080-16	7762-4041	108	1080	.22
AT10-1150-16	7762-4042	115	1150	.23
AT10-1210-16	7762-4043	121	1210	.24
AT10-1250-16	7762-4044	125	1250	.25
AT10-1320-16	7762-4045	132	1320	.26
AT10-1400-16	7762-4046	140	1400	.28
AT10-1500-16	7762-4047	150	1500	.30
AT10-1600-16	7762-4048	160	1600	.32
AT10-1700-16	7762-4049	170	1700	.34
AT10-1800-16	7762-4228	180	1800	.36

AT10 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-500-20	7762-4050	50	500	.13
⁶ AT10-560-20	7762-4051	56	560	.14
⁶ AT10-610-20	7762-4052	61	610	.15
⁶ AT10-660-20	7762-4053	66	660	.17
⁶ AT10-700-20	7762-4054	70	700	.18
⁶ AT10-730-20	7762-4055	73	730	.18
⁶ AT10-780-20	7762-4056	78	780	.20
⁶ AT10-800-20	7762-4057	80	800	.20
⁶ AT10-810-20	7762-4058	81	810	.20
⁶ AT10-840-20	7762-4059	84	840	.21
⁶ AT10-890-20	7762-4060	89	890	.22
⁶ AT10-920-20	7762-4061	92	920	.23
⁶ AT10-960-20	7762-4062	96	960	.24

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-980-20	7762-4063	98	980	.25
⁶ AT10-1010-20	7762-4064	101	1010	.25
⁶ AT10-1050-20	7762-4065	105	1050	.26
⁶ AT10-1080-20	7762-4066	108	1080	.27
⁶ AT10-1150-20	7762-4067	115	1150	.29
⁶ AT10-1210-20	7762-4068	121	1210	.30
⁶ AT10-1250-20	7762-4069	125	1250	.31
⁶ AT10-1320-20	7762-4070	132	1320	.33
⁶ AT10-1400-20	7762-4071	140	1400	.35
⁶ AT10-1500-20	7762-4072	150	1500	.38
⁶ AT10-1600-20	7762-4073	160	1600	.40
⁶ AT10-1700-20	7762-4074	170	1700	.43
⁶ AT10-1800-20	7762-4230	180	1800	.45

AT10 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-500-25	7762-4075	50	500	.16
AT10-560-25	7762-4076	56	560	.18
AT10-610-25	7762-4077	61	610	.19
AT10-660-25	7762-4078	66	660	.21
AT10-700-25	7762-4079	70	700	.22
AT10-730-25	7762-4080	73	730	.23
AT10-780-25	7762-4081	78	780	.24
AT10-800-25	7762-4082	80	800	.25
AT10-810-25	7762-4083	81	810	.25

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-840-25	7762-4084	84	840	.26
AT10-890-25	7762-4085	89	890	.28
AT10-920-25	7762-4086	92	920	.29
AT10-960-25	7762-4087	96	960	.30
AT10-980-25	7762-4088	98	980	.31
AT10-1010-25	7762-4089	101	1010	.32
AT10-1050-25	7762-4090	105	1050	.33
AT10-1080-25	7762-4091	108	1080	.34
AT10-1150-25	7762-4092	115	1150	.36

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

AT10 Pitch — 25mm Wide (continued)

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-1210-25	7762-4093	121	1210	.38
AT10-1250-25	7762-4094	125	1250	.39
AT10-1320-25	7762-4095	132	1320	.41
AT10-1400-25	7762-4096	140	1400	.44

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-1500-25	7762-4097	150	1500	.47
AT10-1600-25	7762-4098	160	1600	.50
AT10-1700-25	7762-4099	170	1700	.53
AT10-1800-25	7762-4242	180	1800	.56

AT10 Pitch — 32mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-500-32	7762-4100	50	500	.20
AT10-560-32	7762-4101	56	560	.22
AT10-610-32	7762-4102	61	610	.24
AT10-660-32	7762-4103	66	660	.26
AT10-700-32	7762-4104	70	700	.28
AT10-730-32	7762-4105	73	730	.29
AT10-780-32	7762-4106	78	780	.31
AT10-800-32	7762-4107	80	800	.32
AT10-810-32	7762-4108	81	810	.33
AT10-840-32	7762-4109	84	840	.34
AT10-890-32	7762-4110	89	890	.36
AT10-920-32	7762-4111	92	920	.37
AT10-960-32	7762-4112	96	960	.39

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-980-32	7762-4113	98	980	.39
AT10-1010-32	7762-4114	101	1010	.41
AT10-1050-32	7762-4115	105	1050	.42
AT10-1080-32	7762-4116	108	1080	.43
AT10-1150-32	7762-4117	115	1150	.46
AT10-1210-32	7762-4118	121	1210	.49
AT10-1250-32	7762-4119	125	1250	.50
AT10-1320-32	7762-4120	132	1320	.53
AT10-1400-32	7762-4121	140	1400	.56
AT10-1500-32	7762-4122	150	1500	.60
AT10-1600-32	7762-4123	160	1600	.64
AT10-1700-32	7762-4124	170	1700	.68
AT10-1800-32	7762-4233	180	1800	.72

AT10 Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-500-50	7762-4125	50	500	.31
AT10-560-50	7762-4126	56	560	.35
AT10-610-50	7762-4127	61	610	.38
AT10-660-50	7762-4128	66	660	.41
AT10-700-50	7762-4129	70	700	.44
AT10-730-50	7762-4130	73	730	.46
AT10-780-50	7762-4131	78	780	.49
AT10-800-50	7762-4132	80	800	.50
AT10-810-50	7762-4133	81	810	.51
AT10-840-50	7762-4134	84	840	.53
AT10-890-50	7762-4135	89	890	.56
AT10-920-50	7762-4136	92	920	.58
AT10-960-50	7762-4137	96	960	.60

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
AT10-980-50	7762-4138	98	980	.61
AT10-1010-50	7762-4139	101	1010	.63
AT10-1050-50	7762-4140	105	1050	.66
AT10-1080-50	7762-4141	108	1080	.68
AT10-1150-50	7762-4142	115	1150	.72
AT10-1210-50	7762-4143	121	1210	.76
AT10-1250-50	7762-4144	125	1250	.78
AT10-1320-50	7762-4145	132	1320	.83
AT10-1400-50	7762-4146	140	1400	.88
AT10-1500-50	7762-4147	150	1500	.94
AT10-1600-50	7762-4148	160	1600	1.00
AT10-1700-50	7762-4149	170	1700	1.07
AT10-1800-50	7762-4235	180	1800	1.12

AT10 Pitch — 75mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-500-75	7762-4150	50	500	.47
⁶ AT10-560-75	7762-4151	56	560	.53
⁶ AT10-610-75	7762-4152	61	610	.57
⁶ AT10-660-75	7762-4153	66	660	.62
⁶ AT10-700-75	7762-4154	70	700	.66
⁶ AT10-730-75	7762-4155	73	730	.69
⁶ AT10-780-75	7762-4156	78	780	.73
⁶ AT10-800-75	7762-4157	80	800	.75
⁶ AT10-810-75	7762-4158	81	810	.76
⁶ AT10-840-75	7762-4159	84	840	.79
⁶ AT10-890-75	7762-4160	89	890	.84
⁶ AT10-920-75	7762-4161	92	920	.87
⁶ AT10-960-75	7762-4162	96	960	.90

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-980-75	7762-4163	98	980	.92
⁶ AT10-1010-75	7762-4164	101	1010	.95
⁶ AT10-1050-75	7762-4165	105	1050	.99
⁶ AT10-1080-75	7762-4166	108	1080	1.02
⁶ AT10-1150-75	7762-4167	115	1150	1.08
⁶ AT10-1210-75	7762-4168	121	1210	1.14
⁶ AT10-1250-75	7762-4169	125	1250	1.18
⁶ AT10-1320-75	7762-4170	132	1320	1.24
⁶ AT10-1400-75	7762-4171	140	1400	1.32
⁶ AT10-1500-75	7762-4172	150	1500	1.41
⁶ AT10-1600-75	7762-4173	160	1600	1.51
⁶ AT10-1700-75	7762-4174	170	1700	1.60
⁶ AT10-1800-75	7762-4237	180	1800	1.69

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

AT10 Pitch — 100mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-500-100	7762-4175	50	500	.63
⁶ AT10-560-100	7762-4176	56	560	.70
⁶ AT10-610-100	7762-4177	61	610	.77
⁶ AT10-660-100	7762-4178	66	660	.83
⁶ AT10-700-100	7762-4179	70	700	.88
⁶ AT10-730-100	7762-4180	73	730	.92
⁶ AT10-780-100	7762-4181	78	780	.98
⁶ AT10-800-100	7762-4182	80	800	1.00
⁶ AT10-810-100	7762-4183	81	810	1.02
⁶ AT10-840-100	7762-4184	84	840	1.05
⁶ AT10-890-100	7762-4185	89	890	1.12
⁶ AT10-920-100	7762-4186	92	920	1.15
⁶ AT10-960-100	7762-4187	96	960	1.20

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-980-100	7762-4188	98	980	1.23
⁶ AT10-1010-100	7762-4189	101	1010	1.27
⁶ AT10-1050-100	7762-4190	105	1050	1.32
⁶ AT10-1080-100	7762-4191	108	1080	1.35
⁶ AT10-1150-100	7762-4192	115	1150	1.44
⁶ AT10-1210-100	7762-4193	121	1210	1.52
⁶ AT10-1250-100	7762-4194	125	1250	1.57
⁶ AT10-1320-100	7762-4195	132	1320	1.66
⁶ AT10-1400-100	7762-4196	140	1400	1.76
⁶ AT10-1500-100	7762-4197	150	1500	1.88
⁶ AT10-1600-100	7762-4198	160	1600	2.01
⁶ AT10-1700-100	7762-4199	170	1700	2.13
⁶ AT10-1800-100	7762-4239	180	1800	2.25

AT10 Pitch — 200mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-500-200	7762-4200	50	500	1.25
⁶ AT10-560-200	7762-4201	56	560	1.41
⁶ AT10-610-200	7762-4202	61	610	1.53
⁶ AT10-660-200	7762-4203	66	660	1.66
⁶ AT10-700-200	7762-4204	70	700	1.76
⁶ AT10-730-200	7762-4205	73	730	1.83
⁶ AT10-780-200	7762-4206	78	780	1.96
⁶ AT10-800-200	7762-4207	80	800	2.01
⁶ AT10-810-200	7762-4208	81	810	2.03
⁶ AT10-840-200	7762-4209	84	840	2.11
⁶ AT10-890-200	7762-4210	89	890	2.23
⁶ AT10-920-200	7762-4211	92	920	2.31
⁶ AT10-960-200	7762-4212	96	960	2.41
⁶ AT10-980-200	7762-4213	98	980	2.46

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
⁶ AT10-1010-200	7762-4214	101	1010	2.53
⁶ AT10-1050-200	7762-4215	105	1050	2.63
⁶ AT10-1080-200	7762-4216	108	1080	2.71
⁶ AT10-1150-200	7762-4217	115	1150	2.89
⁶ AT10-1210-200	7762-4218	121	1210	3.04
⁶ AT10-1250-200	7762-4219	125	1250	3.14
⁶ AT10-1320-200	7762-4220	132	1320	3.31
⁶ AT10-1400-200	7762-4221	140	1400	3.51
⁶ AT10-1500-200	7762-4222	150	1500	3.76
⁶ AT10-1600-200	7762-4223	160	1600	4.01
⁶ AT10-1700-200	7762-4224	170	1700	4.27
⁶ AT10-1800-200	7762-4241	180	1800	4.51

⁶ Standard/Non-Stock item. Check with Customer Service for availability.



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

Twin Power® - DT5 Pitch — 6mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-6	7762-5000	52	260	.01
DT5-410-6	7762-5001	82	410	.01
DT5-460-6	7762-0391	92	460	.02
DT5-480-6	7762-5002	96	480	.02
DT5-515-6	7762-5003	103	515	.02
DT5-590-6	7762-5004	118	590	.02

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-6	7762-5005	124	620	.02
DT5-750-6	7762-5006	150	750	.03
DT5-815-6	7762-5007	163	815	.03
DT5-860-6	7762-5008	172	860	.03
DT5-940-6	7762-5009	188	940	.03

Twin Power - DT5 Pitch — 8mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-8	7762-5010	52	260	.01
DT5-410-8	7762-5011	82	410	.02
DT5-460-8	7762-0392	92	460	.02
DT5-480-8	7762-5012	92	460	.02
DT5-515-8	7762-5013	103	515	.02
DT5-590-8	7762-5014	118	590	.03

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-8	7762-5015	124	620	.03
DT5-750-8	7762-5016	150	750	.03
DT5-815-8	7762-5017	163	815	.04
DT5-860-8	7762-5018	172	860	.04
DT5-940-8	7762-5019	188	940	.04

Twin Power - DT5 Pitch — 10mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-10	7762-5020	52	260	.01
DT5-410-10	7762-5021	82	410	.02
DT5-460-10	7762-0393	92	460	.03
DT5-480-10	7762-5022	96	480	.03
DT5-515-10	7762-5023	103	515	.03
DT5-590-10	7762-5024	118	590	.03

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-10	7762-5025	124	620	.04
DT5-750-10	7762-5026	150	750	.04
DT5-815-10	7762-5027	163	815	.05
DT5-860-10	7762-5028	172	860	.05
DT5-940-10	7762-5029	188	940	.05

Twin Power® - DT5 Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-12	7762-5030	52	260	.02
DT5-410-12	7762-5031	82	410	.03
DT5-460-12	7762-0394	92	460	.03
DT5-480-12	7762-5032	96	480	.03
DT5-515-12	7762-5033	103	515	.04
DT5-590-12	7762-5034	118	590	.04

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-12	7762-5035	124	620	.04
DT5-750-12	7762-5036	150	750	.05
DT5-815-12	7762-5037	163	815	.06
DT5-860-12	7762-5038	172	860	.06
DT5-940-12	7762-5039	188	940	.06

Twin Power® - DT5 Pitch — 16mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-16	7762-5040	52	260	.02
DT5-410-16	7762-5041	82	410	.04
DT5-460-16	7762-0396	92	460	.04
DT5-480-16	7762-5042	96	480	.04
DT5-515-16	7762-5043	103	515	.05
DT5-590-16	7762-5044	118	590	.05

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-16	7762-5045	124	620	.06
DT5-750-16	7762-5046	150	750	.07
DT5-815-16	7762-5047	163	815	.07
DT5-860-16	7762-5048	172	860	.08
DT5-940-16	7762-5049	188	940	.09

Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

Twin Power® - DT5 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-20	7762-5050	52	260	.03
DT5-410-20	7762-5051	82	410	.05
DT5-460-20	7762-0397	92	460	.05
DT5-480-20	7762-5052	96	480	.05
DT5-515-20	7762-5053	103	515	.06
DT5-590-20	7762-5054	118	590	.07

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-20	7762-5055	124	620	.07
DT5-750-20	7762-5056	150	750	.09
DT5-815-20	7762-5057	163	815	.09
DT5-860-20	7762-5058	172	860	.10
DT5-940-20	7762-5059	188	940	.11

Twin Power® - DT5 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-25	7762-5060	52	260	.04
DT5-410-25	7762-5061	82	410	.06
DT5-460-25	7762-0398	92	460	.07
DT5-480-25	7762-5062	96	480	.07
DT5-515-25	7762-5063	103	515	.07
DT5-590-25	7762-5064	118	590	.08

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-25	7762-5065	124	620	.09
DT5-750-25	7762-5066	150	750	.11
DT5-815-25	7762-5067	163	815	.12
DT5-860-25	7762-5068	172	860	.12
DT5-940-25	7762-5069	188	940	.13

Twin Power® - DT5 Pitch — 32mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-32	7762-5070	52	260	.05
DT5-410-32	7762-5071	82	410	.07
DT5-460-32	7762-0399	92	460	.09
DT5-480-32	7762-5072	96	480	.09
DT5-515-32	7762-5073	103	515	.09
DT5-590-32	7762-5074	118	590	.11

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-32	7762-5075	124	620	.11
DT5-750-32	7762-5076	150	750	.14
DT5-815-32	7762-5077	163	815	.15
DT5-860-32	7762-5078	172	860	.16
DT5-940-32	7762-5079	188	940	.17

Twin Power® - DT5 Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-50	7762-5080	52	260	.07
DT5-410-50	7762-5081	82	410	.12
DT5-460-50	7762-0400	92	460	.13
DT5-480-50	7762-5082	96	480	.14
DT5-515-50	7762-5083	103	515	.15
DT5-590-50	7762-5084	118	590	.17

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-50	7762-5085	124	620	.18
DT5-750-50	7762-5086	150	750	.21
DT5-815-50	7762-5087	163	815	.23
DT5-860-50	7762-5088	172	860	.24
DT5-940-50	7762-5089	188	940	.27

Twin Power® - DT5 Pitch — 75mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-75	7762-5090	52	260	.11
DT5-410-75	7762-5091	82	410	.17
DT5-460-75	7762-0401	92	460	.19
DT5-480-75	7762-5092	96	480	.20
DT5-515-75	7762-5093	103	515	.22
DT5-590-75	7762-5094	118	590	.25

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-75	7762-5095	124	620	.26
DT5-750-75	7762-5096	150	750	.32
DT5-815-75	7762-5097	163	815	.35
DT5-860-75	7762-5098	172	860	.37
DT5-940-75	7762-5099	188	940	.40



Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

Twin Power® - DT5 Pitch — 100mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-100	7762-5100	52	260	.15
DT5-410-100	7762-5101	82	410	.23
DT5-460-100	7762-0402	92	460	.26
DT5-480-100	7762-5102	96	480	.27
DT5-515-100	7762-5103	103	515	.29
DT5-590-100	7762-5104	118	590	.33

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-100	7762-5105	124	620	.35
DT5-750-100	7762-5106	150	750	.43
DT5-815-100	7762-5107	163	815	.46
DT5-860-100	7762-5108	172	860	.49
DT5-940-100	7762-5109	188	940	.53

Twin Power® - DT5 Pitch — 200mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-260-200	7762-5110	52	260	.30
DT5-410-200	7762-5111	82	410	.47
DT5-460-200	7762-0403	92	460	.52
DT5-480-200	7762-5112	96	480	.54
DT5-515-200	7762-5113	103	515	.58
DT5-590-200	7762-5114	118	590	.67

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT5-620-200	7762-5115	124	620	.70
DT5-750-200	7762-5116	150	750	.85
DT5-815-200	7762-5117	163	815	.93
DT5-860-200	7762-5118	172	860	.98
DT5-940-200	7762-5119	188	940	1.07

Twin Power® - DT10 Pitch — 10mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-10	7762-5500	60	600	.04
DT10-630-10	7762-5501	63	630	.04
DT10-720-10	7762-5502	72	720	.04
DT10-840-10	7762-5503	84	840	.05

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-10	7762-5504	92	920	.06
DT10-980-10	7762-5505	98	980	.06
DT10-1210-10	7762-5506	121	1210	.07

Twin Power® - DT10 Pitch — 12mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-12	7762-5507	60	600	.04
DT10-630-12	7762-5508	63	630	.05
DT10-720-12	7762-5509	72	720	.05
DT10-840-12	7762-5510	84	840	.06

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-12	7762-5511	92	920	.07
DT10-980-12	7762-5512	98	980	.07
DT10-1210-12	7762-5513	121	1210	.09

Twin Power® - DT10 Pitch — 14mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-14	7762-5514	60	600	.05
DT10-630-14	7762-5515	63	630	.05
DT10-720-14	7762-5516	72	720	.06
DT10-840-14	7762-5517	84	840	.07

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-14	7762-5518	92	920	.08
DT10-980-14	7762-5519	98	980	.08
DT10-1210-14	7762-5520	121	1210	.10

Twin Power® - DT10 Pitch — 16mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-16	7762-5521	60	600	.06
DT10-630-16	7762-5522	63	630	.06
DT10-720-16	7762-5523	72	720	.07
DT10-840-16	7762-5524	84	840	.08

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-16	7762-5525	92	920	.09
DT10-980-16	7762-5526	98	980	.10
DT10-1210-16	7762-5527	121	1210	.12

Synchro-Power® Polyurethane Belts

Product No. Series 7762 (continued)

Twin Power® - DT10 Pitch — 20mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-20	7762-5528	60	600	.07
DT10-630-20	7762-5529	63	630	.08
DT10-720-20	7762-5530	72	720	.09
DT10-840-20	7762-5531	84	840	.10

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-20	7762-5532	92	920	.11
DT10-980-20	7762-5533	98	980	.12
DT10-1210-20	7762-5534	121	1210	.15

Twin Power® - DT10 Pitch — 25mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-25	7762-5535	60	600	.09
DT10-630-25	7762-5536	63	630	.10
DT10-720-25	7762-5537	72	720	.11
DT10-840-25	7762-5538	84	840	.13

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-25	7762-5539	92	920	.14
DT10-980-25	7762-5540	98	980	.15
DT10-1210-25	7762-5541	121	1210	.19

Twin Power® - DT10 Pitch — 32mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-32	7762-5542	60	600	.12
DT10-630-32	7762-5543	63	630	.12
DT10-720-32	7762-5544	72	720	.14
DT10-840-32	7762-5545	84	840	.17

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-32	7762-5546	92	920	.18
DT10-980-32	7762-5547	98	980	.19
DT10-1210-32	7762-5548	121	1210	.24

Twin Power® - DT10 Pitch — 50mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-50	7762-5549	60	600	.18
DT10-630-50	7762-5550	63	630	.19
DT10-720-50	7762-5551	72	720	.22
DT10-840-50	7762-5552	84	840	.26

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-50	7762-5553	92	920	.28
DT10-980-50	7762-5554	98	980	.30
DT10-1210-50	7762-5555	121	1210	.37

Twin Power® - DT10 Pitch — 75mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-75	7762-5556	60	600	.28
DT10-630-75	7762-5557	63	630	.29
DT10-720-75	7762-5558	72	720	.33
DT10-840-75	7762-5559	84	840	.39

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-75	7762-5560	92	920	.42
DT10-980-75	7762-5561	98	980	.45
DT10-1210-75	7762-5562	121	1210	.56

Twin Power® - DT10 Pitch — 100mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-100	7762-5563	60	600	.37
DT10-630-100	7762-5564	63	630	.39
DT10-720-100	7762-5565	72	720	.44
DT10-840-100	7762-5566	84	840	.52

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-100	7762-5567	92	920	.57
DT10-980-100	7762-5568	98	980	.60
DT10-1210-100	7762-5569	121	1210	.74

Twin Power® - DT10 Pitch — 200mm Wide

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-600-200	7762-5570	60	600	.74
DT10-630-200	7762-5571	63	630	.78
DT10-720-200	7762-5572	72	720	.89
DT10-840-200	7762-5573	84	840	1.03

Part No.	Product No.	No. of Teeth	Pitch Length (mm)	Wt. Ea. (Lbs.)
DT10-920-200	7762-5574	92	920	1.13
DT10-980-200	7762-5575	98	980	1.21
DT10-1210-200	7762-5576	121	1210	1.49



Super HC® Belts

Pioneered by Gates, these "narrow" cross-sections can transmit up to three times the horsepower of the classical cross-sections (A, B, C, and D) in the same amount of drive space.

Markets/Applications

Suitable for all industrial applications, particularly where space, weight and horsepower capacity are critical.

Features/Advantages


- **Gates Curves** provide proper cord support and full contact with the sheave-groove for uniform loading, uniform wear, and increased belt life.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- **The Flex-Weave® Cover** is a patented construction for longer cover life, providing extended protection to the core of the belt from oil, dirt, and heat.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.

Recommended Sheaves

Super HC Sheaves

Notes

Gates Super HC belts are available in 3V, 5V, and 8V cross-sections.



Product No. Series 9332



3V Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
3V650	9332-0650	65.0	.37	1
3V730	9332-0730	73.0	.40	1
3V830	9332-0830	83.0	.44	1


Product No. Series 9334



5V Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
5V1630	9334-1630	163.0	2.31	1
5V1710	9334-1710	171.0	2.43	1

Product No. Series 9336



8V Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
8V2300	9336-2300	230.0	8.69	1
8V6000	9336-6000	600.0	22.79	1

See NBH line for additional sizes and parts.

Super HC® Molded Notch Belts

Constructed with Gates proprietary construction, this belt has a superior combination of flex and load carrying capacity, as well as transmitting more horsepower than the classical cross sections in the same amount of drive space.

Markets/Applications

Suitable for all industrial applications, particularly where space, weight and horsepower capacity are critical.

Features/Advantages


- **Notches molded** into the belt during manufacturing make this belt well suited for drives with smaller diameter sheaves.
- **Belt Edge** is machined for even sheave groove contact resulting in less slip and wear.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.

Recommended Sheaves

Super HC Sheaves

Notes

Gates Super HC Molded Notch belts are available in 3VX and 5VX cross-sections.



Product No. Series 9412

3VX Section



Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
3VX290	9412-0290	29.0	.10	1
3VX326	9412-0326	32.6	.14	5
3VX350	9412-0350	35.0	.10	5
3VX366	9412-0366	36.6	.10	5
3VX385	9412-0385	38.5	.15	5
3VX390	9412-0390	39.0	.16	1
3VX415	9412-0415	41.5	.15	5
3VX464	9412-0464	46.4	.15	5
3VX487	9412-0487	48.7	.15	5
3VX520	9412-0520	52.0	.29	5
3VX540	9412-0540	54.0	.20	5
3VX550	9412-0550	55.0	.20	5
3VX570	9412-0570	57.0	.20	5
3VX580	9412-0580	58.0	.20	5

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
3VX590	9412-0590	59.0	.25	5
3VX616	9412-0616	61.6	.15	5
3VX650	9412-0650	65.0	.25	5
3VX690	9412-0690	69.0	.10	5
3VX771	9412-0771	77.1	.30	5
3VX826	9412-0826	82.6	.30	5
3VX926	9412-0926	92.6	.35	5
3VX974	9412-0974	97.4	.40	5
3VX1027	9412-1027	102.7	.40	5
3VX1088	9412-1088	108.8	.40	5
3VX1146	9412-1146	114.6	.30	5
3VX1224	9412-1224	122.4	.50	5
3VX1296	9412-1296	129.6	.50	5

See NBH line for additional sizes and parts.



Super HC® Molded Notch Belts

Product No. Series 9414

5VX Section



Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
5VX350	9414-0350	35.0	.30	1
5VX362	9414-0362	36.2	.35	1
5VX372	9414-0372	37.2	.35	1
5VX382	9414-0382	38.2	.40	1
5VX392	9414-0392	39.2	.40	1
5VX402	9414-0402	40.2	.40	1
5VX412	9414-0412	41.2	.40	1
5VX422	9414-0422	42.2	.40	1
5VX433	9414-0433	43.3	.45	1
5VX459	9414-0459	45.9	.50	1
5VX479	9414-0479	47.9	.50	1
5VX519	9414-0519	51.9	.55	1
5VX619	9414-0619	61.9	.60	5
5VX700	9414-0700	70.0	.70	1
5VX720	9414-0720	72.0	.70	1
5VX760	9414-0760	76.0	.75	5
5VX769	9414-0769	76.9	.80	5

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
5VX790	9414-0790	79.0	.80	5
5VX867	9414-0867	86.7	.85	5
5VX890	9414-0890	89.0	.90	1
5VX918	9414-0918	91.8	.95	1
5VX940	9414-0940	94.0	.95	1
5VX978	9414-0978	97.8	.95	1
5VX990	9414-0990	99.0	1.75	1
5VX1017	9414-1017	101.7	1.10	1
5VX1050	9414-1050	105.0	1.05	1
5VX1108	9414-1108	110.8	1.15	1
5VX1139	9414-1139	113.9	1.10	1
5VX1162	9414-1162	116.2	.95	1
5VX1220	9414-1220	122.0	1.20	1
5VX1277	9414-1277	127.7	1.15	1
5VX1374	9414-1374	137.4	1.30	1
5VX1469	9414-1469	146.9	1.40	5
5VX1701	9414-1701	170.1	1.20	5

See NBH line for additional sizes and parts.

Super HC® PowerBand® Belts


The PowerBand construction allows multiple belts to function as a single unit, with even load distribution and each strand fitting securely in the sheave groove.

Markets/Applications

Recommended for multiple V-belt drives exposed to pulsating or heavy shock loads which can make belts whip, turn over or jump off the drive.

Features/Advantages

- The **Tie Band** assures high lateral rigidity, guiding the belt in a straight line and preventing it from coming off the drive.
- **Concave sidewalls** provide proper cord support and full contact with the sheave-groove for equal loading and uniform wear.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.



Size Range/Availability

- **Large Inventory** of standard lengths and widths are readily available. See sizing tables for details.
- **Belt Slitters** at Gates Service Centers provide ready availability of additional belt widths cut from inventory.
- **7 Days or Less** manufacturing time and **No Minimum Order Quantity** for all catalog belt length sizes.
- **Made-To-Order Belt Lengths** are available in any size from: 3V (45 to 220 inch), 5V (50 to 660 inch) and 8V (100 to 660 inch). Check with Customer Service for minimum order quantity and manufacturing lead time.

Recommended Sheaves

Super HC Sheaves

Notes

The part number is constructed by placing the number of strands required followed by a slash (/) in front of the belt size. For example; 3/3V1400 represents a 3V1400 with 3 strands.

3V PowerBand® Belts are non-notched, raw edge construction for sizes 3V300 through 3V750. Sizes 3V800 and longer are banded (covered) construction.



Product No. Series 9385

3V Section



Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
¹⁵ 3V300	30.0	.18	+	+	+	+
¹⁵ 3V315	31.5	.20	+	+	+	+
¹⁵ 3V335	33.5	.20	+	+	+	+
¹⁵ 3V355	35.5	.20	+	+	+	+
¹⁵ 3V375	37.5	.22	+	+	+	+
¹⁵ 3V400	40.0	.24	+	+	+	+
¹⁵ 3V425	42.5	.26	+	+	+	+
¹⁵ 3V450	45.0	.28	+	+	+	+
¹⁵ 3V475	47.5	.29	+	+	+	+
¹⁵ 3V500	50.0	.30	+	+	+	+
¹⁵ 3V530	53.0	.33	+	+	+	+
¹⁵ 3V560	56.0	.34	+	+	+	+
¹⁵ 3V600	60.0	.37	O	+	+	+
¹⁵ 3V630	63.0	.40	+	+	+	+
¹⁵ 3V670	67.0	.41	+	+	+	+
¹⁵ 3V710	71.0	.44	+	+	+	+
¹⁵ 3V750	75.0	.46	+	+	+	+
3V800	80.0	.50	+	+	+	+
3V850	85.0	.53	+	+	+	+
3V900	90.0	.56	+	+	+	+

See NBH line for additional sizes and parts.

¹⁵ Not included in V-80 matching program.



The Driving Force in Power Transmission.

Super HC® PowerBand® Belts

Product No. Series 9385 (continued)

3V Section (continued)

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
3V950	95.0	.60	+	+	+	+
3V1000	100.0	.63	+	+	+	+
3V1060	106.0	.66	+	+	+	+
3V1120	112.0	.70	+	+	+	+
3V1180	118.0	.74	+	+	+	+
3V1250	125.0	.79	+	+	+	+
3V1320	132.0	.83	+	+	+	+
3V1400	140.0	.88	+	+	+	+



Product No. Series 9386

5V Section

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
¹⁵ 5V500	50.0	.70	+	+	+	+
¹⁵ 5V530	53.0	.80	+	+	+	+
¹⁵ 5V560	56.0	.86	+	+	+	+
¹⁵ 5V600	60.0	.96	+	+	+	+
¹⁵ 5V630	63.0	1.00	+	+	+	+
5V670	67.0	1.04	+	+	+	+
5V710	71.0	1.18	+	+	+	+
5V750	75.0	1.18	+	O	+	+
5V800	80.0	1.25	+	+	+	+
5V850	85.0	1.36	+	+	+	+
5V900	90.0	1.39	+	+	+	+
5V950	95.0	1.50	O	+	+	+
5V1000	100.0	1.57	+	+	+	+
5V1060	106.0	1.71	+	+	+	+
5V1120	112.0	1.79	+	+	+	+
5V1180	118.0	1.86	+	+	+	+
5V1200	120.0	1.90	+	+	+	+
5V1210	121.0	1.92	+	+	+	+
5V1250	125.0	2.00	+	+	+	+
5V1320	132.0	2.11	+	+	+	+
5V1400	140.0	2.25	+	+	+	+
5V1500	150.0	2.39	+	+	+	+
5V1600	160.0	2.57	+	+	+	+
5V1700	170.0	2.75	+	+	+	+
5V1800	180.0	2.89	+	+	+	+
5V1900	190.0	3.07	+	+	+	+
5V2000	200.0	3.25	+	+	O	O
5V2120	212.0	3.46	+	+	+	+
5V2240	224.0	3.68	+	+	+	+
5V2360	236.0	3.89	+	+	+	+
5V2500	250.0	4.07	+	+	+	+
5V2650	265.0	4.32	+	+	+	+
5V2800	280.0	4.57	+	+	+	+
5V3000	300.0	4.89	+	+	+	+
5V3150	315.0	5.18	+	+	+	+
5V3350	335.0	5.50	+	+	+	+
5V3550	355.0	5.79	+	+	+	+

See NBH line for additional sizes and parts.

¹⁵ Not included in V-80 matching program.



Product No. Series 9387

8V Section

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
8V1000	100.0	3.90	O	+	+	+
8V1060	106.0	4.15	O	+	+	+
8V1120	112.0	4.42	O	+	+	+
8V1180	118.0	4.67	+	+	+	+
8V1250	125.0	5.00	O	+	+	+
8V1320	132.0	5.25	O	+	+	+
8V1400	140.0	5.58	O	+	+	+
8V1500	150.0	6.00	O	+	+	+
8V1600	160.0	6.33	O	+	+	+
8V1700	170.0	6.75	O	+	+	+
8V1800	180.0	7.25	O	+	+	+
8V1900	190.0	7.67	O	+	+	+
8V2000	200.0	8.00	O	O	+	O
8V2120	212.0	8.50	O	+	+	+
8V2240	224.0	9.00	+	+	+	+
8V2360	236.0	9.42	O	+	+	+
8V2500	250.0	10.00	O	+	O	+
8V2650	265.0	10.58	O	+	+	+
8V2800	280.0	11.33	+	+	+	+
8V3000	300.0	12.08	O	+	+	+
8V3150	315.0	12.75	O	+	+	+
8V3350	335.0	13.58	O	+	+	+
8V3550	355.0	14.33	O	+	+	+
8V3750	375.0	15.08	O	+	+	+
8V4000	400.0	16.08	O	+	+	+
8V4250	425.0	17.08	O	+	+	+
8V4500	450.0	18.08	O	+	+	+
8V4750	475.0	19.17	O	+	+	+
8V5000	500.0	20.17	O	+	+	+
8V5600	560.0	22.75	O	+	+	+
8V6000	600.0	24.42	O	+	+	+

See NBH line for additional sizes and parts.

Super HC® Molded Notch PowerBand® Belts

The PowerBand construction allows multiple belts to function as a single unit, with even load distribution and each strand fitting securely in the sheave groove.

Markets/Applications

Recommended for multiple V-belt drives exposed to pulsating or heavy shock loads which can make belts whip, turn over or jump off the drive.

Features/Advantages

- The **Tie Band** assures high lateral rigidity, guiding the belt in a straight line and preventing it from coming off the drive.
- **Notches molded** into the belt during manufacturing make this belt well suited for drives with smaller diameter sheaves.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.


Size Range/Availability

- **Large Inventory** of standard lengths and widths are readily available. See sizing tables for details.
- **Belt Slitters** at Gates Service Centers provide ready availability of additional belt widths cut from inventory.
- **7 Days or Less** manufacturing time and **No Minimum Order Quantity** for all catalog belt sizes.

Recommended Sheaves
Super HC Sheaves

Notes

The part number is constructed by placing the number of strands required followed by a slash (/) in front of the belt size. For example; 5/5VX1400 represents a 5VX1400 with 5 strands.



Product No. Series 9388

3VX Section



Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands (+=Standard Stock Size, O=Available Size, NO MOQ, 7 days or less)																				
			2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22
3VX250	25.0	.10	+	+	+	+					O												
3VX265	26.5	.14	+	+	+	+					O												
3VX280	26.5	.14	+	+	+	+					O												
3VX300	30.0	.18	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX315	31.5	.20	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX335	33.5	.20	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX355	35.5	.20	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX375	37.5	.22	O	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX400	40.0	.24	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX425	42.5	.26	+	+	O	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX450	45.0	.28	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX475	47.5	.29	O	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX500	50.0	.30	O	O	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX530	53.0	.33	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	+
3VX560	56.0	.34	+	O	+	+	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	+
3VX600	60.0	.37	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	+
3VX630	63.0	.40	O	+	+	+	+	O	O	O	O	O	O	O	O	+	O	O	O	O	O	O	+
3VX670	67.0	.41	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	+
3VX710	71.0	.44	+	+	+	+	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX750	75.0	.46	+	+	O	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX800	80.0	.50	+	+	+	+	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX850	85.0	.53	+	+	+	+	+	O	O	O	+	O	O	O	O	O	O	O	O	O	O	O	O
3VX900	90.0	.56	+	+	+	+	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	+
3VX950	95.0	.60	+	+	+	+	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX1000	100.0	.63	+	+	+	+	+	O	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O
3VX1060	106.0	.66	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX1120	112.0	.70	+	+	+	+	+	O	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O
3VX1180	118.0	.74	+	+	+	+	O	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX1250	125.0	.79	+	+	+	+	+	O	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O
3VX1320	132.0	.83	+	+	+	+	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O
3VX1400	140.0	.88	+	+	+	+	+	O	+	O	O	O	O	O	O	O	O	O	O	O	O	O	O

See NBH line for additional sizes and parts.

Super HC® Molded Notch PowerBand® Belts



Product No. Series 9389

5VX Section

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands (+=Standard Stock Size, O=Available Size, NO MOQ, 7 days or less)											
			2	3	4	5	6	7	8	9	10	11	12	13
5VX500	50.0	.70	+	+	+	+	O	O	O	O	O	O	O	O
5VX530	53.0	.80	+	+	+	+	O	O	O	O	O	O	O	O
5VX560	56.0	.86	O	+	+	+	O	O	O	O	O	O	O	O
5VX600	60.0	.96	O	+	+	+	O	O	O	O	O	O	O	O
5VX630	63.0	1.00	+	+	+	+	O	O	O	O	O	O	O	O
5VX670	67.0	1.04	O	+	+	+	+	O	O	O	O	O	O	O
5VX710	71.0	1.18	O	+	+	+	+	O	O	O	O	O	O	O
5VX750	75.0	1.21	+	+	+	+	+	O	O	O	O	O	O	O
5VX800	80.0	1.25	O	+	+	O	+	O	O	O	O	O	O	O
5VX850	85.0	1.36	O	+	+	+	+	O	O	O	O	O	O	O
5VX900	90.0	1.39	+	+	+	+	+	O	O	O	O	O	O	O
5VX950	95.0	1.50	O	+	+	+	+	O	O	O	O	O	O	O
5VX1000	100.0	1.57	O	+	+	+	+	O	O	O	O	O	O	O
5VX1060	106.0	1.71	+	+	+	+	+	O	+	O	O	O	O	O
5VX1120	112.0	1.79	+	+	+	+	+	O	+	O	+	O	O	O
5VX1180	118.0	1.86	+	+	+	+	+	+	+	O	+	O	O	O
5VX1250	125.0	2.00	+	+	+	+	+	O	+	O	O	O	O	O
5VX1320	132.0	2.11	+	+	+	+	+	O	+	O	+	O	O	O
5VX1400	140.0	2.25	O	O	O	O	+	O	+	O	O	O	O	O
5VX1500	150.0	2.39	+	+	+	+	+	O	O	O	+	O	O	O
5VX1600	160.0	2.57	+	+	+	+	+	O	+	O	+	O	O	O
5VX1700	170.0	2.75	+	+	+	+	+	O	+	O	O	O	O	O
5VX1800	180.0	2.89	+	+	+	+	+	O	+	O	O	O	O	O
5VX1900	190.0	3.07	+	+	+	+	+	O	O	O	O	O	O	O
5VX2000	200.0	3.25	+	+	+	+	+	O	+	O	+	O	O	O

See NBH line for additional sizes and parts.



Predator® Single Belts

Specifically designed for aggressive applications, this extra heavy-duty belt construction provides extraordinary high impact strength, capacity, and wear resistance.

Markets/Applications

Predator belts are well suited as replacement belts for applications exposed to pulsating loads or heavy shock loads, such as mining, agriculture, wood processing, oil field equipment, heavy construction and sand/gravel operations.


Features/Advantages

- **Aramid Tensile Cords** combine limited stretch with extraordinary strength and durability that is pound-for-pound stronger than steel.
- **Bareback Cover** resists debris and allows the belt to slip under extreme shock load conditions, reducing heat buildup and prolonging belt life.
- **Gates Curves** provide proper cord support and full contact with the sheave-groove for equal loading, uniform wear, and increased belt life.
- Meets RMA oil and heat resistant standards.

Notes

Predator belts do not meet RMA requirements for belt static conductivity.

When application requires Predator belt sets, request belts with same group/match number.



Product No. Series 9185

AP Section



Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
AP31	9185-0031	33.0	.20
AP33	9185-0033	35.0	.25
AP35	9185-0035	37.0	.30
AP38	9185-0038	40.0	.30
AP40	9185-0040	42.0	.56
AP42	9185-0042	44.0	.30
AP43	9185-0043	45.0	.33
AP44	9185-0044	46.0	.35
AP45	9185-0045	47.0	.43
AP46	9185-0046	48.0	.35
AP47	9185-0047	49.0	.40
AP48	9185-0048	50.0	.35
AP50	9185-0050	52.0	.60
AP51	9185-0051	53.0	.40
AP52	9185-0052	54.0	.66
AP53	9185-0053	55.0	.40
AP54	9185-0054	56.0	.40

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
AP55	9185-0055	57.0	.40
AP56	9185-0056	58.0	.45
AP58	9185-0058	60.0	.45
AP59	9185-0059	61.0	.45
AP60	9185-0060	62.0	.45
AP61	9185-0061	63.0	.45
AP62	9185-0062	64.0	.50
AP63	9185-0063	65.0	.75
AP66	9185-0066	68.0	.75
AP68	9185-0068	70.0	.45
AP70	9185-0070	72.0	.75
AP71	9185-0071	73.0	.80
AP85	9185-0085	87.0	.65
AP87	9185-0087	89.0	.67
AP90	9185-0090	92.0	.69
AP91	9185-0091	93.0	.72

Product No. Series 9186

BP Section



Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
BP32	9186-0032	35.0	.53
BP38	9186-0038	41.0	.70
BP40	9186-0040	43.0	.50
BP42	9186-0042	45.0	.50
BP44	9186-0044	47.0	.68
BP46	9186-0046	49.0	.79

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
BP48	9186-0048	51.0	.55
BP50	9186-0050	53.0	.60
BP51	9186-0051	54.0	.80
BP52	9186-0052	55.0	.85
BP53	9186-0053	56.0	.65
BP54	9186-0054	57.0	.80

Predator® Single Belts

Product No. Series 9186 (continued)

BP Section (continued)

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
BP55	9186-0055	58.0	.65
BP56	9186-0056	59.0	.65
BP57	9186-0057	60.0	.65
BP58	9186-0058	61.0	.65
BP59	9186-0059	62.0	.70
BP60	9186-0060	63.0	.70
BP61	9186-0061	64.0	.95
BP62	9186-0062	65.0	.75
BP63	9186-0063	66.0	.70
BP64	9186-0064	67.0	.75
BP65	9186-0065	68.0	.75
BP66	9186-0066	69.0	.70
BP68	9186-0068	71.0	.92
BP70	9186-0070	73.0	.80
BP71	9186-0071	74.0	.90
BP75	9186-0075	78.0	1.15
BP78	9186-0078	81.0	.90
BP80	9186-0080	83.0	1.22

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
BP81	9186-0081	84.0	.90
BP83	9186-0083	86.0	.95
BP85	9186-0085	88.0	1.25
BP90	9186-0090	93.0	1.05
BP93	9186-0093	96.0	1.20
BP97	9186-0097	100.0	1.10
BP103	9186-0103	106.0	1.20
BP105	9186-0105	108.0	1.20
BP112	9186-0112	115.0	1.30
BP120	9186-0120	123.0	1.35
BP124	9186-0124	127.0	2.45
BP128	9186-0128	131.0	1.50
BP136	9186-0136	139.0	2.60
BP144	9186-0144	147.0	2.70
BP158	9186-0158	161.0	2.75
BP173	9186-0173	176.0	2.00
BP195	9186-0195	198.0	3.25

Product No. Series 9187

CP Section



Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
CP85	9187-0085	89.0	1.90
CP90	9187-0090	94.0	1.90
CP96	9187-0096	100.0	2.40
CP99	9187-0099	103.0	2.25
CP100	9187-0100	104.0	2.50
CP112	9187-0112	116.0	2.45
CP120	9187-0120	124.0	2.90
CP128	9187-0128	132.0	3.10

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
CP136	9187-0136	140.0	4.20
CP144	9187-0144	148.0	4.40
CP158	9187-0158	162.0	4.70
CP162	9187-0162	166.0	4.75
CP173	9187-0173	177.0	5.00
CP180	9187-0180	184.0	5.15
CP195	9187-0195	199.0	5.48
CP240	9187-0240	242.0	5.18

Product No. Series 9188

5VP Section



Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
5VP800	9188-0080	80.0	1.05
5VP850	9188-0085	85.0	1.45
5VP900	9188-0090	90.0	1.05
5VP950	9188-0095	95.0	1.15
5VP1000	9188-0100	100.0	1.50
5VP1060	9188-0106	106.0	2.75
5VP1120	9188-0112	112.0	9.60
5VP1180	9188-0118	118.0	1.40
5VP1250	9188-0125	125.0	1.55
5VP1320	9188-0132	132.0	1.60
5VP1400	9188-0140	140.0	1.70
5VP1500	9188-0150	150.0	1.75
5VP1600	9188-0160	160.0	3.10
5VP1700	9188-0170	170.0	3.25

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
5VP1800	9188-0180	180.0	3.60
5VP1900	9188-0190	190.0	2.35
5VP2000	9188-0200	200.0	2.65
5VP2120	9188-0212	212.0	2.60
5VP2240	9188-0224	224.0	2.70
5VP2360	9188-0236	236.0	4.40
5VP2500	9188-0250	250.0	4.15
5VP2650	9188-0265	265.0	3.15
5VP2800	9188-0280	280.0	3.60
5VP3000	9188-0300	300.0	6.19
5VP3150	9188-0315	315.0	6.38
5VP3350	9188-0335	335.0	6.65
5VP3550	9188-0355	355.0	4.20



Predator® Single Belts

Product No. Series 9189

8VP Section

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
8VP1600	9189-0160	160.0	5.30
8VP1700	9189-0170	170.0	7.00
8VP1800	9189-0180	180.0	5.85
8VP1900	9189-0190	190.0	6.25
8VP2000	9189-0200	200.0	8.00
8VP2120	9189-0212	212.0	7.00
8VP2240	9189-0224	224.0	7.10
8VP2360	9189-0236	236.0	9.26



Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
8VP2500	9189-0250	250.0	10.25
8VP2650	9189-0265	265.0	8.80
8VP2800	9189-0280	280.0	9.25
8VP3000	9189-0300	300.0	9.85
8VP3150	9189-0315	315.0	11.10
8VP3350	9189-0335	335.0	11.05
8VP3550	9189-0355	355.0	11.60

Product No. Series 9190

SPBP Section

Part No.	Product No.	Pitch Length (mm)	Wt. Ea. (Lbs.)
SPB1260P	9190-01260	1260	.65
SPB1500P	9190-01500	1500	1.10
SPB1600P	9190-01600	1600	.80
SPB1700P	9190-01700	1700	1.10
SPB1800P	9190-01800	1800	.95
SPB1900P	9190-01900	1900	1.00
SPB2000P	9190-02000	2000	1.40
SPB2120P	9190-02120	2120	1.15
SPB2240P	9190-02240	2240	1.20
SPB2360P	9190-02360	2360	1.25
SPB2500P	9190-02500	2500	1.65
SPB2650P	9190-02650	2650	1.50
SPB2800P	9190-02800	2800	1.55
SPB3000P	9190-03000	3000	1.65
SPB3150P	9190-03150	3150	1.70
SPB3350P	9190-03350	3350	2.86



Part No.	Product No.	Pitch Length (mm)	Wt. Ea. (Lbs.)
SPB3550P	9190-03550	3550	1.95
SPB3750P	9190-03750	3750	3.08
SPB4000P	9190-04000	4000	2.10
SPB4250P	9190-04250	4250	3.35
SPB4500P	9190-04500	4500	3.70
SPB4750P	9190-04750	4750	2.45
SPB5000P	9190-05000	5000	3.90
SPB5300P	9190-05300	5300	4.14
SPB5600P	9190-05600	5600	4.30
SPB6000P	9190-06000	6000	4.52
SPB6300P	9190-06300	6300	4.68
SPB6700P	9190-06700	6700	5.86
SPB7100P	9190-07100	7100	6.05
SPB7500P	9190-07500	7500	6.29
SPB8000P	9190-08000	8000	6.56

Product No. Series 9191

SPCP Section

Part No.	Product No.	Pitch Length (mm)	Wt. Ea. (Lbs.)
SPC2000P	9191-02000	2000	1.95
SPC2120P	9191-02120	2120	2.39
SPC2240P	9191-02240	2240	2.51
SPC2360P	9191-02360	2360	2.35
SPC2500P	9191-02500	2500	2.40
SPC2650P	9191-02650	2650	2.60
SPC2800P	9191-02800	2800	3.06
SPC3000P	9191-03000	3000	3.26
SPC3150P	9191-03150	3150	3.40
SPC3350P	9191-03350	3350	3.30
SPC3550P	9191-03550	3550	3.45
SPC3750P	9191-03750	3750	3.99
SPC4000P	9191-04000	4000	5.19
SPC4250P	9191-04250	4250	5.43



Part No.	Product No.	Pitch Length (mm)	Wt. Ea. (Lbs.)
SPC4500P	9191-04500	4500	5.68
SPC4750P	9191-04750	4750	5.92
SPC5000P	9191-05000	5000	4.90
SPC5300P	9191-05300	5300	6.46
SPC5600P	9191-05600	5600	5.45
SPC6000P	9191-06000	6000	7.15
SPC6300P	9191-06300	6300	7.44
SPC6700P	9191-06700	6700	8.80
SPC7100P	9191-07100	7100	9.19
SPC7500P	9191-07500	7500	7.25
SPC8000P	9191-08000	8000	7.60
SPC8500P	9191-08500	8500	8.35
SPC9000P	9191-09000	9000	11.05

Predator® PowerBand® Belts


Specifically designed for aggressive applications, this extra heavy-duty belt construction provides extraordinary high impact strength, capacity, and wear resistance.

Markets/Applications

Predator belts are well suited as replacement belts for applications exposed to pulsating loads or heavy shock loads, such as mining, agriculture, wood processing, oil field equipment, heavy construction and sand/gravel operations.

Features/Advantages

- **Aramid Tensile Cords** combine limited stretch with extraordinary strength and durability that is pound-for-pound stronger than steel.
- **Bareback Cover** resists debris and allows the belt to slip under extreme shock load conditions, reducing heat buildup and prolonging belt life.
- Multiple layer **Tie Band** provides excellent lateral rigidity to prevent belts from turning over or from coming off of the drive.
- **Gates Curves** provide proper cord support and full contact with the sheave-groove for equal loading, uniform wear, and increased belt life.
- Meets RMA **oil and heat** resistant standards.



Size Range/Availability

- **Large Inventory** of standard lengths and widths are readily available. See sizing tables for details.
- **Belt Slitters** at Gates Service Centers provide ready availability of additional belt widths cut from inventory.
- **7 Days or Less** manufacturing time and **No Minimum Order Quantity** for all catalog belt sizes.
- **Made-To-Order Belt Lengths** are available in any size from: CP (80 to 400 inch), 3VP (45 to 220 inch), 5VP (50 to 660 inch) and 8VP (100 to 660 inch). Check with Customer Service for minimum order quantity and manufacturing lead time.

Recommended Sheaves

Super HC Sheaves as recommended by DesignFlex® Pro drive analysis.

Notes

When application requires Predator PowerBand belt sets, request same group/match number.

Predator belts do not meet RMA requirements for belt static conductivity.

The part number is constructed by placing the number of strands required followed by a slash (/) in front of the belt size. For example; 5/8VP3000 represents a 8VP3000 with 5 strands.

Product No. Series 9184

CP Section



Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
3/CP85	9184-3085	89.0	7.35
3/CP90	9184-3090	94.0	7.47
3/CP99	9184-3099	103.0	8.10
4/CP240	9184-4240	242.0	21.77
4/CP330	9184-4330	332.0	29.81
4/CP345	9184-4345	347.0	31.16
4/CP360	9184-4360	362.0	32.49
5/CP195	9184-5195	199.0	22.18
5/CP225	9184-5225	227.0	25.31
5/CP255	9184-5255	257.0	28.66

CP Predator® belts are available up to 12 strands.



Predator® PowerBand® Belts

Product No. Series 9180

3VP Section



Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands (+=Standard Stock Size, O=Available Size, NO MOQ, 7 days or less)									
			2	3	4	5	6	7	8	9	10	
3VP450	45.0	.28	+	+	+	+	O	O	O	O	O	O
3VP475	47.5	.29	+	+	+	+	O	O	+	O	O	O
3VP500	50.0	.30	+	+	+	+	O	O	O	O	O	O
3VP530	53.0	.33	+	+	+	+	O	O	O	O	O	O
3VP560	56.0	.34	+	+	+	+	O	O	O	O	O	O
3VP600	60.0	.37	+	+	+	+	O	O	O	O	O	O
3VP630	63.0	.40	+	+	+	+	O	O	O	O	O	O
3VP670	67.0	.41	+	+	+	+	O	O	O	O	O	O
3VP710	71.0	.44	+	+	+	+	O	O	O	O	O	O
3VP750	75.0	.46	+	+	+	+	O	O	O	O	O	O
3VP800	80.0	.50	+	+	+	+	O	O	O	O	O	O
3VP850	85.0	.53	+	+	+	+	O	O	O	O	O	O
3VP900	90.0	.56	+	+	+	+	O	O	O	O	O	O
3VP950	95.0	.60	+	+	+	+	O	O	O	O	O	O
3VP1000	100.0	.63	+	+	+	+	O	O	O	O	O	O
3VP1060	106.0	.66	+	+	+	+	O	O	O	O	O	O
3VP1120	112.0	.70	+	+	+	+	O	O	O	O	O	O
3VP1180	118.0	.74	+	+	+	+	O	O	O	O	O	O
3VP1250	125.0	.79	+	+	+	+	O	O	O	O	O	O
3VP1320	132.0	.83	+	+	+	+	O	O	O	O	O	O
3VP1400	140.0	.88	+	+	+	+	O	O	O	O	O	O



Product No. Series 9181

5VP Section

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands (+=Standard Stock Size, O=Available Size, NO MOQ, 7 days or less)															
			2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	
5VP600	60.0	.96	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP630	63.0	1.00	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP670	67.0	1.04	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP710	71.0	1.18	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP750	75.0	1.21	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP800	80.0	1.25	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP850	85.0	1.36	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP870	87.0	1.40	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP900	90.0	1.39	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP950	95.0	1.50	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1000	100.0	1.57	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	
5VP1060	106.0	1.25	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	
5VP1120	112.0	1.79	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1180	118.0	1.86	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1250	125.0	2.00	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1320	132.0	2.11	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	
5VP1400	140.0	2.25	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1500	150.0	2.39	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1600	160.0	2.57	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1700	170.0	2.75	+	+	+	+	O	O	O	O	+	O	+	O	O	O	O	
5VP1800	180.0	2.89	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP1900	190.0	3.07	+	+	+	+	+	O	O	O	+	O	O	O	O	O	O	
5VP2000	200.0	3.25	+	O	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP2030	203.0	3.30	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP2120	212.0	3.46	+	+	+	+	O	O	+	O	O	O	O	O	O	O	O	
5VP2240	224.0	3.68	+	+	+	+	+	O	O	O	O	O	O	O	O	O	O	
5VP2360	236.0	3.89	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP2500	250.0	4.07	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP2650	265.0	4.32	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP2800	280.0	4.57	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP3000	300.0	4.89	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP3150	315.0	5.18	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP3350	335.0	5.50	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	
5VP3550	355.0	5.79	+	+	+	+	O	O	O	O	O	O	O	O	O	O	O	



Product No. Series 9182

8VP Section

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands (+=Standard Stock Size, O=Available Size, NO MOQ, 7 days or less)										
			2	3	4	5	6	7	8	9	10	11	12
8VP1000	100.0	3.90	O	+	+	+	O	O	O	O	O	O	O
8VP1060	106.0	4.15	O	+	+	+	O	O	O	O	O	O	O
8VP1120	112.0	4.42	O	+	+	+	O	O	O	O	O	O	O
8VP1180	118.0	4.67	O	+	+	+	O	O	O	O	O	O	O
8VP1250	125.0	5.00	+	+	+	+	O	O	O	O	O	O	O
8VP1320	132.0	5.25	O	+	+	+	O	O	O	O	O	O	O
8VP1400	140.0	5.58	O	+	+	+	O	O	O	O	O	O	O
8VP1500	150.0	6.00	O	+	+	+	O	O	O	O	O	O	O
8VP1600	160.0	6.33	O	+	+	+	O	O	O	O	O	O	O
8VP1700	170.0	6.75	O	+	+	+	O	O	O	O	O	O	O
8VP1800	180.0	7.25	O	+	+	+	O	O	O	O	O	O	O
8VP1900	190.0	7.65	O	+	+	+	+	O	O	O	O	O	+
8VP2000	200.0	8.00	O	+	+	+	O	O	+	O	O	O	+
8VP2120	212.0	8.50	O	+	+	+	O	O	+	O	O	O	O
8VP2240	224.0	9.00	O	+	+	+	O	O	+	O	O	O	O
8VP2360	236.0	9.42	O	+	+	+	+	O	O	+	O	O	O
8VP2500	250.0	10.00	O	+	+	+	O	O	+	O	O	O	O
8VP2650	265.0	10.58	O	+	+	+	O	O	O	O	O	O	O
8VP2800	280.0	11.33	O	+	+	+	O	O	O	+	O	O	O
8VP3000	300.0	12.08	O	+	+	+	+	+	+	O	O	O	O
8VP3150	315.0	12.75	+	+	+	+	O	O	+	O	+	O	O
8VP3350	335.0	13.58	O	+	+	+	O	+	+	O	+	O	O
8VP3550	355.0	14.33	O	+	+	+	O	O	O	O	O	O	O
8VP3750	375.0	15.08	O	+	+	+	O	O	O	O	O	O	O
8VP4000	400.0	16.08	O	+	+	+	O	O	O	O	O	O	O
8VP4250	425.0	17.08	O	+	+	+	O	O	O	O	O	O	O
8VP4500	450.0	18.08	O	+	+	+	O	O	O	O	O	O	O
8VP4750	475.0	19.17	O	+	+	+	O	O	O	O	O	O	O
8VP5000	500.0	20.17	O	+	+	+	O	O	O	O	O	O	O
8VP5600	560.0	22.75	O	+	+	+	O	O	O	O	O	O	O
8VP6000	600.0	24.42	O	+	+	+	O	O	O	O	O	O	O

Hi-Power® II Belts

Featuring a composite, multi-purpose construction, these belts resist oil and heat, ozone, sunlight, weather, and aging.

Markets/Applications

Suitable for all industrial applications, including v-flat drives.

Features/Advantages


- **Gates Curves** provide proper cord support and full contact with the sheave-groove for uniform loading, uniform wear, and increased belt life.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- **The Flex-Weave® Cover** is a patented fabric construction for longer cover life, providing extended protection to the belt core from oil, dirt and heat.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.

Recommended Sheaves

Multi-Duty® Sheaves

Notes

Gates Hi-Power belts are available in A, B, C, D and E cross sections.



Product No. Series 9002

A Section



Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
A101	9002-2101	103.0	.65	1
A102	9002-2102	104.0	.65	1
A104	9002-2104	106.0	.74	1
A106	9002-2106	108.0	.75	1
A107	9002-2107	109.0	.75	1
A108	9002-2108	110.0	.75	1
A113	9002-2113	115.0	.75	1
A114	9002-2114	116.0	.86	1
A116	9002-2116	118.0	.75	1
A117	9002-2117	119.0	.75	1
A118	9002-2118	120.0	.80	1
A125	9002-2125	127.0	.87	1
A127	9002-2127	129.0	.89	1
A130	9002-2130	132.0	.85	1

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
A132	9002-2132	134.0	.85	1
A134	9002-2134	136.0	.88	1
A137	9002-2137	139.0	.90	1
A140	9002-2140	142.0	.95	1
A148	9002-2148	150.0	1.05	1
A152	9002-2152	154.0	1.00	1
A156	9002-2156	158.0	1.03	1
A157	9002-2157	159.0	1.03	1
A162	9002-2162	164.0	1.06	1
A167	9002-2167	169.0	1.05	1
A187	9002-2187	189.0	1.23	1
A197	9002-2197	199.0	1.43	1
A200	9002-2200	202.0	1.40	1

See NBH line for additional sizes and parts.

Product No. Series 9003

B Section



Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
B107	9003-2107	110.0	1.27	1
B109	9003-2109	112.0	1.20	1
B111	9003-2111	114.0	1.20	1
B113	9003-2113	116.0	1.25	1
B117	9003-2117	120.0	1.30	1
B119	9003-2119	122.0	1.45	1
B123	9003-2123	126.0	1.50	1
B125	9003-2125	128.0	1.53	1
B127	9003-2127	130.0	1.55	1
B131	9003-2131	134.0	1.45	1
B132	9003-2132	135.0	1.45	1
B134	9003-2134	137.0	1.65	1
B135	9003-2135	138.0	1.50	1
B137	9003-2137	140.0	1.65	5
B139	9003-2139	142.0	1.70	1
B141	9003-2141	144.0	1.55	1
B143	9003-2143	146.0	1.60	1
B145	9003-2145	148.0	1.75	1
B147	9003-2147	150.0	1.60	1
B149	9003-2149	152.0	1.65	1
B151	9003-2151	154.0	1.97	1
B153	9003-2153	156.0	1.70	1
B156	9003-2156	159.0	1.75	1
B157	9003-2157	160.0	2.03	1
B160	9003-2160	163.0	1.75	1
B161	9003-2161	164.0	1.79	1
B164	9003-2164	167.0	1.80	1
B165	9003-2165	168.0	1.80	1
B167	9003-2167	170.0	1.86	1
B169	9003-2169	172.0	1.85	1
B170	9003-2170	173.0	1.85	1
B172	9003-2172	175.0	1.91	1
B174	9003-2174	177.0	1.90	1
B175	9003-2175	178.0	1.90	1
B177	9003-2177	180.0	1.95	1
B178	9003-2178	181.0	1.95	1
B182	9003-2182	185.0	2.00	1
B184	9003-2184	187.0	2.05	1
B185	9003-2185	188.0	2.05	1

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
B186	9003-2186	189.0	2.42	1
B187	9003-2187	190.0	2.24	1
B191	9003-2191	194.0	2.12	1
B197	9003-2197	200.0	2.19	1
B200	9003-2200	203.0	2.15	1
B201	9003-2201	204.0	2.20	1
B204	9003-2204	207.0	2.25	1
B206	9003-2206	209.0	2.29	1
B212	9003-2212	213.0	2.37	1
B215	9003-2215	216.0	2.35	1
B217	9003-2217	218.0	2.43	1
B218	9003-2218	219.0	2.45	1
B220	9003-2220	221.0	2.45	1
B221	9003-2221	222.0	1.75	1
B223	9003-2223	224.0	2.49	1
B228	9003-2228	229.0	2.55	1
B234	9003-2234	235.0	2.62	1
B235	9003-2235	236.0	2.63	1
B236	9003-2236	237.0	2.64	1
B237	9003-2237	238.0	2.65	1
B248	9003-2248	249.0	2.77	1
B253	9003-2253	254.0	2.83	1
B265	9003-2265	266.0	2.96	1
B276	9003-2276	277.0	3.10	1
B279	9003-2279	280.0	3.16	1
B280	9003-2280	281.0	3.56	1
B290	9003-2290	291.0	3.20	1
B292	9003-2292	295.0	3.26	1
B293	9003-2293	294.0	3.71	1
B310	9003-2310	311.0	3.70	1
B330	9003-2330	331.0	3.55	1
B340	9003-2340	341.0	4.55	1
B345	9003-2345	346.0	4.65	1
B355	9003-2355	356.0	4.75	1
B360	9003-2360	361.0	4.25	1
B394	9003-2394	395.0	5.36	1
B433	9003-2433	444.0	5.82	1
B472	9003-2472	473.0	5.63	1

See NBH line for additional sizes and parts.

Hi-Power® II Belts



Product No. Series 9004

C Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
C44	9004-2044	48.0	.98	1
C45	9004-2045	49.0	1.00	1
C46	9004-2046	50.0	.95	1
C47	9004-2047	51.0	1.00	1
C49	9004-2049	53.0	1.08	1
C52	9004-2052	56.0	1.10	1
C56	9004-2056	60.0	1.15	1
C58	9004-2058	62.0	1.30	1
C59	9004-2059	63.0	1.35	1
C61	9004-2061	65.0	1.35	1
C64	9004-2064	68.0	1.30	1
C66	9004-2066	70.0	1.50	1
C69	9004-2069	73.0	1.40	1
C74	9004-2074	76.0	1.40	1
C77	9004-2077	81.0	1.55	1
C82	9004-2082	86.0	1.65	1
C88	9004-2088	92.0	1.75	1
C89	9004-2089	93.0	1.78	1
C91	9004-2091	95.0	1.80	1
C94	9004-2094	98.0	5.80	1
C102	9004-2102	106.0	2.05	1
C104	9004-2104	108.0	2.07	1
C113	9004-2113	117.0	2.24	1
C114	9004-2114	118.0	2.20	1
C117	9004-2117	121.0	2.30	1
C118	9004-2118	122.0	2.40	1
C119	9004-2119	123.0	2.36	1
C121	9004-2121	125.0	2.40	1
C123	9004-2123	127.0	2.44	1
C125	9004-2125	129.0	2.48	1
C127	9004-2127	131.0	2.50	1
C131	9004-2131	135.0	2.60	1
C132	9004-2132	136.0	2.65	1
C133	9004-2133	137.0	2.90	1
C134	9004-2134	138.0	2.70	1
C135	9004-2135	139.0	2.65	1
C137	9004-2137	141.0	3.00	1
C138	9004-2138	142.0	2.80	1
C139	9004-2139	143.0	2.75	1
C141	9004-2141	145.0	2.80	1
C142	9004-2142	146.0	2.85	1
C143	9004-2143	147.0	2.80	1
C145	9004-2145	149.0	2.85	1
C146	9004-2146	150.0	2.75	1
C147	9004-2147	151.0	2.85	1
C149	9004-2149	153.0	2.94	1
C153	9004-2153	157.0	3.05	1
C154	9004-2154	158.0	3.05	1
C155	9004-2155	159.0	3.06	1
C157	9004-2157	161.0	3.10	1
C160	9004-2160	164.0	3.15	1
C164	9004-2164	168.0	3.30	1

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
C165	9004-2165	169.0	3.30	1
C166	9004-2166	170.0	3.25	1
C167	9004-2167	171.0	3.67	1
C168	9004-2168	172.0	3.30	1
C169	9004-2169	173.0	3.30	1
C175	9004-2175	179.0	3.45	1
C176	9004-2176	180.0	3.80	1
C177	9004-2177	181.0	3.80	1
C178	9004-2178	182.0	3.84	1
C181	9004-2181	185.0	3.57	1
C182	9004-2182	186.0	3.92	1
C183	9004-2183	187.0	3.60	1
C184	9004-2184	188.0	3.96	1
C187	9004-2187	191.0	4.02	1
C188	9004-2188	192.0	3.70	1
C189	9004-2189	193.0	4.05	1
C193	9004-2193	197.0	4.14	1
C197	9004-2197	201.0	3.88	1
C198	9004-2198	202.0	4.24	1
C200	9004-2200	204.0	4.25	1
C202	9004-2202	206.0	3.95	1
C204	9004-2204	208.0	4.05	1
C205	9004-2205	209.0	4.44	1
C206	9004-2206	210.0	4.45	1
C207	9004-2207	211.0	4.30	1
C208	9004-2208	212.0	4.57	1
C214	9004-2214	216.0	4.45	1
C215	9004-2215	217.0	4.87	1
C218	9004-2218	220.0	4.56	1
C220	9004-2220	222.0	4.60	1
C221	9004-2221	223.0	4.62	1
C228	9004-2228	230.0	5.13	1
C229	9004-2229	231.0	4.79	1
C230	9004-2230	232.0	5.18	1
C235	9004-2235	237.0	4.85	1
C238	9004-2238	240.0	5.35	1
C245	9004-2245	247.0	5.10	1
C246	9004-2246	248.0	5.14	1
C248	9004-2248	250.0	5.18	1
C250	9004-2250	252.0	5.60	1
C264	9004-2264	266.0	5.80	1
C265	9004-2265	267.0	5.54	1
C275	9004-2275	279.0	6.12	1
C276	9004-2276	278.0	6.10	1
C280	9004-2280	282.0	6.20	1
C290	9004-2290	292.0	6.06	1
C295	9004-2295	297.0	6.52	1
C297	9004-2297	299.0	6.20	1
C303	9004-2303	305.0	6.32	1
C314	9004-2314	316.0	7.00	1
C320	9004-2320	322.0	6.67	1
C450	9004-2450	452.0	10.93	1

See NBH line for additional sizes and parts.



Product No. Series 9005

D Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
D98	9005-2098	103.0	4.75	1
D104	9005-2104	109.0	3.99	1
D107	9005-2107	112.0	4.10	1
D108	9005-2108	113.0	5.41	1
D110	9005-2110	115.0	5.49	1
D124	9005-2124	129.0	6.00	1
D132	9005-2132	137.0	6.29	1
D135	9005-2135	140.0	6.75	1
D140	9005-2140	145.0	6.59	1
D148	9005-2148	153.0	6.81	1
D152	9005-2152	157.0	7.02	1
D154	9005-2154	159.0	6.83	1
D160	9005-2160	165.0	7.33	1
D164	9005-2164	169.0	7.21	1
D165	9005-2165	170.0	7.49	1

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
D166	9005-2166	171.0	7.26	1
D167	9005-2167	172.0	6.40	1
D170	9005-2170	175.0	7.42	1
D171	9005-2171	176.0	7.46	1
D205	9005-2205	210.0	7.69	1
D220	9005-2220	223.0	10.15	1
D230	9005-2230	233.0	10.50	1
D248	9005-2248	251.0	9.64	1
D260	9005-2260	263.0	11.70	1
D280	9005-2280	283.0	12.48	1
D335	9005-2335	338.0	14.86	1
D354	9005-2354	357.0	15.60	1
D394	9005-2394	397.0	17.14	1
D441	9005-2441	444.0	18.92	1



Product No. Series 9006

E Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
E144	9006-2144	149.0	9.07	1
E158	9006-2158	165.0	10.48	1
E250	9006-2250	254.0	15.84	1

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
E310	9006-2310	314.0	16.87	1
E441	9006-2441	445.0	25.79	1
E460	9006-2460	464.0	26.82	1

See NBH line for additional sizes and parts.



Hi-Power® II PowerBand® V-Belts


The PowerBand® construction allows multiple belts to function as a single unit, with even load distribution and each strand fitting securely in the sheave groove.

Markets/Applications

Recommended for drives where single belts vibrate, turn over or jump off the drive.

Features/Advantages

- Concave sidewalls provide proper cord support and full contact with the sheave-groove for equal loading and uniform wear.
- Flex-Bonded Cords are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- Meets RMA oil and heat resistant standards.
- Meets RMA static conductivity requirements.
- The Tie Band assures high lateral rigidity, guiding the belt in a straight line and preventing it from coming off the drive.



Size Range/Availability

- **Large Inventory** of standard lengths and widths are readily available. See sizing tables for details.
- **Belt Slitters** at Gates Service Centers provide ready availability of additional belt widths cut from inventory.
- **7 Days or Less** manufacturing time and **No Minimum Order Quantity** for all catalog belt sizes.
- **Made-To-Order Belt Lengths** are available in any size from: A (38 to 212 inch), B (35 to 663 inch), C (56 to 662 inch) and D (126 to 665 inch). Check with Customer Service for minimum order quantity and manufacturing lead time.

Recommended Sheaves

Multi-Duty® Sheaves (B, C, D)

Notes

The part number is constructed by placing the number of strands required followed by a slash (/) in front of the belt size. For example; 5/B66 represents a B66 with 5 strands.

Most "A" Section sheaves are a combination "A-B" groove. "A" Section PowerBand® Belts are not recommended for use in sheaves with "A-B" combination grooves. "A" Section PowerBand® belts may be Made-To-Order and require minimum order quantities. Check with Customer Service for availability.

Product No. Series 9092

A Section



Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
¹⁵ A42	44.0	.36	+	+	+	+
¹⁵ A43	45.0	.37	+	+	+	+
¹⁵ A44	46.0	.38	+	+	+	+
¹⁵ A46	48.0	.40	+	+	+	+
¹⁵ A47	49.0	.40	+	+	+	+
¹⁵ A48	50.0	.40	O	+	+	+
¹⁵ A49	51.0	.42	+	+	+	+
¹⁵ A51	53.0	.44	+	+	+	+
¹⁵ A53	55.0	.46	+	+	+	+
¹⁵ A54	56.0	.46	+	+	+	+
¹⁵ A55	57.0	.47	+	O	+	+
¹⁵ A56	58.0	.48	+	+	+	+
¹⁵ A57	59.0	.50	+	+	+	+
¹⁵ A58	60.0	.50	+	+	+	+
¹⁵ A60	62.0	.52	+	+	+	+
A62	64.0	.54	+	+	+	+
A64	66.0	.56	+	+	+	+
A65	67.0	.56	+	+	+	+
A66	68.0	.57	+	+	+	+
A68	70.0	.58	+	+	+	+

See NBH line for additional sizes and parts.

¹⁵ Not included in V-80 matching program.



Hi-Power® II PowerBand® V-Belts

Product No. Series 9092 (continued)

A Section (continued)

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
A70	72.0	.61	+	+	+	+
A71	73.0	.61	+	+	+	+
A74	76.0	.64	O	+	+	+
A75	77.0	.66	+	+	+	+
A77	79.0	.66	+	+	+	+
A78	80.0	.67	+	+	+	+
A80	82.0	.70	+	+	+	+
A81	83.0	.70	+	+	+	+
A83	85.0	.71	+	+	+	+
A85	87.0	.74	+	O	+	+
A90	92.0	.77	+	+	+	+
A92	94.0	.80	+	+	+	+
A96	98.0	.84	+	+	+	+
A100	102.0	.86	+	+	+	+
A105	107.0	.90	+	+	+	+
A110	112.0	.96	+	+	+	+
A112	114.0	.96	+	+	+	+
A120	122.0	1.04	+	+	+	+
A128	130.0	1.10	+	+	+	+
A136	138.0	1.17	+	+	+	+
A144	146.0	1.24	+	+	+	+
A158	160.0	1.36	+	+	+	+
A173	175.0	1.50	+	+	+	+
A180	182.0	1.56	+	+	+	+

Product No. Series 9093

B Section



Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
¹⁵ B35	38.0	.52	+	+	+	+
¹⁵ B38	41.0	.56	+	+	+	+
¹⁵ B42	45.0	.62	+	+	+	+
¹⁵ B43	46.0	.64	+	+	+	+
¹⁵ B46	49.0	.68	+	+	+	+
¹⁵ B47	50.0	.70	+	+	+	+
¹⁵ B48	51.0	.71	O	+	+	+
¹⁵ B50	53.0	.74	+	+	+	+
¹⁵ B51	54.0	.76	+	+	+	+
¹⁵ B52	55.0	.77	+	+	+	+
¹⁵ B53	56.0	.78	+	+	+	+
¹⁵ B54	57.0	.80	+	+	+	+
¹⁵ B55	58.0	.81	+	O	O	+
¹⁵ B56	59.0	.84	+	+	+	+
¹⁵ B57	60.0	.84	+	+	+	+
¹⁵ B58	61.0	.86	+	+	+	+
¹⁵ B59	62.0	.87	+	+	+	+
¹⁵ B60	63.0	.90	+	+	+	+
¹⁵ B61	64.0	.90	O	+	+	+
B62	65.0	.92	+	+	+	+
B63	66.0	.94	+	+	+	+
B64	67.0	.96	O	+	+	+
B65	68.0	.96	+	+	+	+
B66	69.0	.98	+	+	+	+
B67	70.0	1.00	+	+	+	+
B68	71.0	1.00	O	+	+	+
B70	73.0	1.04	+	+	+	+
B71	74.0	1.06	+	+	+	+
B72	75.0	1.06	+	O	+	+
B73	76.0	1.08	+	+	+	+
B74	77.0	1.10	+	+	+	+
B75	78.0	1.11	O	+	+	+
B77	80.0	1.14	+	+	+	+
B78	81.0	1.16	+	+	+	+
B79	82.0	1.17	+	+	+	+
B80	83.0	1.18	O	+	+	+
B81	84.0	1.20	+	O	+	+
B82	85.0	1.21	+	+	+	+

See NBH line for additional sizes and parts.

¹⁵ Not included in V-80 matching program.



The Driving Force in Power Transmission.

Product No. Series 9093 (continued)

B Section (continued)

Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
B83	86.0	1.24	+	+	+	+
B84	87.0	1.25	+	+	+	+
B85	88.0	1.26	O	+	+	+
B86	89.0	1.28	O	+	+	+
B87	90.0	1.30	+	+	+	+
B88	91.0	1.30	+	+	+	+
B90	93.0	1.34	O	+	+	+
B92	95.0	1.36	O	+	+	+
B93	96.0	1.37	O	+	+	+
B95	98.0	1.41	O	+	+	+
B96	99.0	1.42	+	+	+	+
B97	100.0	1.44	+	+	+	+
B99	102.0	1.47	O	+	+	+
B100	103.0	1.48	+	+	+	+
B103	106.0	1.52	+	+	O	+
B104	107.0	1.59	+	+	+	+
B105	108.0	1.66	+	+	+	+
B108	111.0	1.60	+	+	+	+
B109	112.0	1.62	+	+	+	+
B110	113.0	1.63	+	+	+	+
B112	115.0	1.66	+	+	+	+
B113	116.0	1.72	+	+	+	+
B114	117.0	1.70	+	+	+	+
B115	118.0	1.71	+	+	+	+
B116	119.0	1.72	+	+	+	+
B118	121.0	1.75	+	+	+	+
B120	123.0	1.78	+	+	+	+
B124	127.0	1.84	+	+	+	+
B128	131.0	1.90	+	+	+	+
B130	133.0	1.93	+	+	+	+
B133	136.0	1.97	+	+	+	+
B136	139.0	2.00	+	+	+	+
B138	141.0	2.04	+	+	+	+
B139	142.0	2.05	+	+	+	+
B141	144.0	2.09	+	+	+	+
B144	147.0	2.14	+	+	+	+
B148	151.0	2.20	O	+	+	+
B150	153.0	2.22	+	+	+	+
B154	157.0	2.28	+	+	+	+
B158	161.0	2.34	+	+	+	+
B160	163.0	2.37	+	+	+	+
B162	165.0	2.40	O	+	+	+
B168	171.0	2.49	+	+	+	+
B173	176.0	2.56	+	+	+	+
B180	183.0	2.66	+	+	+	+
B185	188.0	2.74	+	+	+	+
B190	193.0	2.82	+	+	+	+
B195	198.0	2.90	+	+	+	+
B210	213.0	3.11	+	+	+	+
B218	219.9	3.23	+	+	+	+
B225	226.0	3.34	+	+	+	+
B240	241.0	3.55	+	+	+	+
B255	256.0	3.77	+	+	+	+
B270	271.0	4.00	+	+	+	+
B300	301.0	4.44	+	+	+	+
B315	316.0	4.66	+	+	+	+

See NBH line for additional sizes and parts.

Product No. Series 9094

C Section



Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
¹⁵ C60	64.0	1.56	+	+	+	+
C68	72.0	1.77	+	+	+	+
C72	76.0	1.88	+	+	+	+
C75	79.0	1.96	+	+	+	+
C78	82.0	2.04	+	+	+	+
C80	84.0	2.09	+	+	+	+
C81	85.0	2.11	+	+	+	+
C85	89.0	2.21	+	+	+	+
C87	91.0	2.26	+	+	+	+
C90	94.0	2.34	O	+	+	+
C96	100.0	2.50	+	+	+	+
C99	103.0	2.57	+	+	+	+
C100	104.0	2.60	+	+	+	+
C105	109.0	2.74	+	+	+	+
C108	112.0	2.81	+	+	+	+
C109	113.0	2.84	+	+	+	+
C112	116.0	2.91	+	+	+	+
C120	124.0	3.12	+	+	+	O
C124	128.0	3.22	+	+	+	+
C126	130.0	3.28	+	+	+	+
C128	132.0	3.34	+	+	+	+
C136	140.0	3.54	+	+	+	+
C144	148.0	3.74	+	+	+	+
C146	150.0	3.79	+	+	+	+
C151	154.9	3.92	+	+	+	+
C158	162.0	4.11	+	+	+	+
C162	166.0	4.21	+	+	+	+
C173	177.0	4.50	+	+	+	+
C180	184.0	4.68	+	+	+	+
C185	189.0	4.88	+	+	+	+
C190	194.0	4.88	+	+	+	+
C195	199.0	5.07	+	+	+	+
C204	208.0	5.30	+	+	+	+
C210	214.0	5.46	+	+	+	+
C225	227.0	5.86	+	+	+	+
C240	242.0	6.24	+	+	O	+
C255	257.0	6.64	+	+	+	+
C270	272.0	7.02	+	+	+	+
C285	287.0	7.41	+	+	+	+
C300	302.0	7.80	+	+	+	+
C315	317.0	8.20	+	+	+	+
C330	332.0	8.58	+	+	+	+
C345	347.0	8.97	+	+	+	+
C360	362.0	9.36	+	+	+	+
C390	392.0	10.14	+	+	+	+
C420	422.0	10.92	+	+	+	+

See NBH line for additional sizes and parts.

¹⁵ Not included in V-80 matching program.

Product No. Series 9095

D Section



Size	Belt O.C. (In.)	Wt. Per Strand (Lbs.)	Belt Width In Number of Strands +=Standard Stock Size, O=Available Size			
			2	3	4	5
D144	149.0	6.75	+	+	+	+
D158	163.0	7.40	+	+	+	+
D173	178.0	8.10	+	+	+	+
D180	185.0	8.44	+	+	+	+
D195	200.0	9.09	+	+	+	+
D210	215.0	9.84	+	+	+	+
D225	228.0	10.56	+	+	+	+
D240	243.0	11.26	+	+	+	+
D255	258.0	11.96	+	+	+	+
D270	273.0	12.66	+	+	+	+
D285	288.0	13.37	+	+	+	+
D300	303.0	14.07	+	+	+	+
D315	318.0	14.77	+	+	+	+
D330	333.0	15.48	+	+	+	+
D345	348.0	16.18	+	+	+	+
D360	363.0	16.88	+	+	+	+
D390	393.0	18.29	+	+	+	+
D420	423.0	19.70	+	+	+	+
D450	453.0	21.10	+	+	+	+
D480	483.0	22.50	+	+	+	+
D540	543.0	25.33	+	+	+	+
D600	603.0	28.14	+	+	+	+
⁴ D660	663.0	31.13	+	+	+	+

See NBH line for additional sizes and parts.

⁴ Minimum production quantity may apply. Contact Customer Service for availability.

Tri-Power® Belts

Constructed with Gates proprietary construction, this belt has a superior combination of flex and load carrying capacity, as well as less stretch resulting in less maintenance.

Markets/Applications

Suitable for all industrial applications, particularly where small or sub-minimal sheave diameters are required.


Features/Advantages

- **Notches molded** into the belt during manufacturing make this belt well suited for drives with smaller diameter sheaves.
- **Belt Edge** is machined for even sheave groove contact resulting in less slip and wear.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.

Recommended Sheaves
Multi-Duty Sheaves

Notes


Tri-Power belts are available in AX, BX, and CX sizes.



Product No. Series 9012

AX Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
AX21	9012-2021	23.0	.15	1
AX25	9012-2025	27.0	.15	1
AX30	9012-2030	32.0	.20	1



Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
AX83	9012-2083	85.0	.50	1
AX84	9012-2084	86.0	.45	1
AX89	9012-2089	91.0	.56	1

Product No. Series 9013

BX Section

Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
BX24	9013-2024	27.0	.30	1
BX25	9013-2025	28.0	.30	1
BX26	9013-2026	29.0	.30	1
BX27	9013-2027	30.0	.30	1
BX29	9013-2029	32.0	.35	1



Size	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)	Customer Pack
BX33	9013-2033	36.0	.35	1
BX39	9013-2039	42.0	.40	1
BX98	9013-2098	101.0	.90	1
BX106	9013-2106	109.0	1.15	1
BX110	9013-2110	113.0	1.20	1

See NBH line for additional sizes and parts.



The Driving Force in Power Transmission.

Metric-Power™ V-Belts

Manufactured in the Americas, these belts are made to Gates high quality global production standards.

Metric Power belts are readily available for replacement on drives that require metric cross sections.

Markets/Applications

Excellent for textile mills, machine tool and food processing applications.

Features/Advantages

- **Proprietary Construction** features an unbeatable combination of flex and load carrying capacity, reduced stretch and incredible cord adhesion properties.
- **Molded Notches** (in lengths 3,000mm and under) reduce thermal and bending stresses.
- **Flex-Bonded Cords** are chemically bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.

Recommended Sheaves


Contact the Gates Made-To-Order Metals Team.

Notes

Narrow cross sections include: XPZ/SPZ, XPA/SPA, XPB/SPB, and XPC/SPC.

Classical cross sections include 10X, 13X, and 17X.

Metric Power belts are Vextra molded notch construction in lengths 3,000mm and under. Metric Power belts are banded construction in lengths over 3,000mm.



Narrow Sizes

Product No. Series 9426

XPZ/SPZ Section



Part No.	Product No.	Part No.	Product No.	Part No.	Product No.
XPZ604	9426-10604	XPZ912	9426-10912	XPZ1212	9426-11212
XPZ612	9426-10612	XPZ925	9426-10925	XPZ1227	9426-11227
XPZ630	9426-10630	XPZ937	9426-10937	XPZ1237	9426-11237
XPZ637	9426-10637	XPZ950	9426-10950	XPZ1250	9426-11250
XPZ640	9426-10640	XPZ962	9426-10962	XPZ1262	9426-11262
XPZ660	9426-10660	XPZ987	9426-10987	XPZ1270	9426-11270
XPZ670	9426-10670	XPZ1000	9426-11000	XPZ1287	9426-11287
XPZ672	9426-10672	XPZ1010	9426-11010	XPZ1312	9426-11312
XPZ682	9426-10682	XPZ1012	9426-11012	XPZ1320	9426-11320
XPZ710	9426-10710	XPZ1024	9426-11024	XPZ1337	9426-11337
XPZ722	9426-10722	XPZ1037	9426-11037	XPZ1340	9426-11340
XPZ730	9426-10730	XPZ1047	9426-11047	XPZ1362	9426-11362
XPZ737	9426-10737	XPZ1060	9426-11060	XPZ1387	9426-11387
XPZ750	9426-10750	XPZ1077	9426-11077	XPZ1400	9426-11400
XPZ758	9426-10758	XPZ1080	9426-11080	XPZ1412	9426-11412
XPZ762	9426-10762	XPZ1087	9426-11087	XPZ1420	9426-11420
XPZ787	9426-10787	XPZ1112	9426-11112	XPZ1430	9426-11430
XPZ800	9426-10800	XPZ1120	9426-11120	XPZ1437	9426-11437
XPZ812	9426-10812	XPZ1137	9426-11137	XPZ1450	9426-11450
XPZ825	9426-10825	XPZ1140	9426-11140	XPZ1462	9426-11462
XPZ837	9426-10837	XPZ1150	9426-11150	XPZ1470	9426-11470
XPZ850	9426-10850	XPZ1162	9426-11162	XPZ1487	9426-11487
XPZ862	9426-10862	XPZ1180	9426-11180	XPZ1500	9426-11500
XPZ875	9426-10875	XPZ1187	9426-11187	XPZ1512	9426-11512
XPZ887	9426-10887	XPZ1202	9426-11202	XPZ1520	9426-11520
XPZ900	9426-10900	XPZ1210	9426-11210	XPZ1527	9426-11527

Product No. Series 9426 (continued)

XPZ/SPZ Section (continued)

Part No.	Product No.	Part No.	Product No.	Part No.	Product No.
XPZ1537	9426-11537	XPZ1837	9426-11837	XPZ2280	9426-12280
XPZ1560	9426-11560	XPZ1850	9426-11850	XPZ2287	9426-12287
XPZ1562	9426-11562	XPZ1862	9426-11862	XPZ2300	9426-12300
XPZ1587	9426-11587	XPZ1887	9426-11887	XPZ2360	9426-12360
XPZ1600	9426-11600	XPZ1900	9426-11900	XPZ2410	9426-12410
XPZ1612	9426-11612	XPZ1937	9426-11937	XPZ2437	9426-12437
XPZ1637	9426-11637	XPZ1950	9426-11950	XPZ2487	9426-12487
XPZ1650	9426-11650	XPZ1962	9426-11962	XPZ2500	9426-12500
XPZ1662	9426-11662	XPZ1987	9426-11987	XPZ2540	9426-12540
XPZ1687	9426-11687	XPZ2000	9426-12000	XPZ2650	9426-12650
XPZ1700	9426-11700	XPZ2030	9426-12030	XPZ2800	9426-12800
XPZ1712	9426-11712	XPZ2037	9426-12037	XPZ2840	9426-12840
XPZ1737	9426-11737	XPZ2062	9426-12062	XPZ3000	9426-13000
XPZ1750	9426-11750	XPZ2087	9426-12087	SPZ3150	9426-03150
XPZ1762	9426-11762	XPZ2120	9426-12120	SPZ3350	9426-03350
XPZ1787	9426-11787	XPZ2137	9426-12137	SPZ3550	9426-03550
XPZ1800	9426-11800	XPZ2187	9426-12187		
XPZ1812	9426-11812	XPZ2240	9426-12240		

Product No. Series 9420

XPA/SPA Section



Part No.	Product No.	Part No.	Product No.	Part No.	Product No.
XPA630	9420-10630	XPA1300	9420-11300	XPA1707	9420-11707
XPA670	9420-10670	XPA1307	9420-11307	XPA1732	9420-11732
XPA730	9420-10730	XPA1320	9420-11320	XPA1750	9420-11750
XPA732	9420-10732	XPA1332	9420-11332	XPA1757	9420-11757
XPA750	9420-10750	XPA1340	9420-11340	XPA1782	9420-11782
XPA760	9420-10760	XPA1357	9420-11357	XPA1800	9420-11800
XPA762	9420-10762	XPA1360	9420-11360	XPA1807	9420-11807
XPA772	9420-10772	XPA1375	9420-11375	XPA1832	9420-11832
XPA782	9420-10782	XPA1382	9420-11382	XPA1850	9420-11850
XPA800	9420-10800	XPA1400	9420-11400	XPA1857	9420-11857
XPA832	9420-10832	XPA1407	9420-11407	XPA1882	9420-11882
XPA850	9420-10850	XPA1425	9420-11425	XPA1900	9420-11900
XPA900	9420-10900	XPA1430	9420-11430	XPA1907	9420-11907
XPA910	9420-10910	XPA1432	9420-11432	XPA1932	9420-11932
XPA922	9420-10922	XPA1450	9420-11450	XPA1950	9420-11950
XPA932	9420-10932	XPA1457	9420-11457	XPA1982	9420-11982
XPA950	9420-10950	XPA1482	9420-11482	XPA2000	9420-12000
XPA967	9420-10967	XPA1500	9420-11500	XPA2032	9420-12032
XPA982	9420-10982	XPA1507	9420-11507	XPA2057	9420-12057
XPA1000	9420-11000	XPA1525	9420-11525	XPA2082	9420-12082
XPA1032	9420-11032	XPA1532	9420-11532	XPA2120	9420-12120
XPA1060	9420-11060	XPA1550	9420-11550	XPA2132	9420-12132
XPA1082	9420-11082	XPA1557	9420-11557	XPA2182	9420-12182
XPA1107	9420-11107	XPA1582	9420-11582	XPA2207	9420-12207
XPA1120	9420-11120	XPA1600	9420-11600	XPA2227	9420-12227
XPA1132	9420-11132	XPA1607	9420-11607	XPA2232	9420-12232
XPA1150	9420-11150	XPA1630	9420-11630	XPA2240	9420-12240
XPA1157	9420-11157	XPA1632	9420-11632	XPA2282	9420-12282
XPA1180	9420-11180	XPA1650	9420-11650	XPA2300	9420-12300
XPA1207	9420-11207	XPA1657	9420-11657	XPA2307	9420-12307
XPA1232	9420-11232	XPA1662	9420-11662	XPA2332	9420-12332
XPA1250	9420-11250	XPA1675	9420-11675	XPA2360	9420-12360
XPA1257	9420-11257	XPA1680	9420-11680	XPA2382	9420-12382
XPA1272	9420-11272	XPA1682	9420-11682	XPA2432	9420-12432
XPA1282	9420-11282	XPA1700	9420-11700	XPA2482	9420-12482

Metric-Power™ V-Belts

Product No. Series 9420 (continued)

XPA/SPA Section (continued)

Part No.	Product No.
XPA2500	9420-12500
XPA2532	9420-12532
XPA2582	9420-12582
XPA2607	9420-12607
XPA2650	9420-12650
XPA2682	9420-12682
XPA2732	9420-12732
XPA2782	9420-12782
XPA2800	9420-12800

Part No.	Product No.
XPA2832	9420-12832
XPA2882	9420-12882
XPA2982	9420-12982
XPA3000	9420-13000
SPA3070	9420-03070
SPA3082	9420-03082
SPA3150	9420-03150
SPA3182	9420-03182
SPA3282	9420-03282

Part No.	Product No.
SPA3350	9420-03350
SPA3482	9420-03482
SPA3550	9420-03550
SPA3750	9420-03750
SPA4000	9420-04000
SPA4250	9420-04250
SPA4500	9420-04500



Product No. Series 9421

XPB/SPB Section

Part No.	Product No.
XPB1250	9421-11250
XPB1260	9421-11260
XPB1320	9421-11320
XPB1340	9421-11340
XPB1400	9421-11400
XPB1410	9421-11410
XPB1450	9421-11450
XPB1500	9421-11500
XPB1510	9421-11510
XPB1590	9421-11590
XPB1600	9421-11600
XPB1627	9421-11627
XPB1690	9421-11690
XPB1700	9421-11700
XPB1800	9421-11800
XPB1900	9421-11900
XPB2000	9421-12000
XPB2020	9421-12020

Part No.	Product No.
XPB2098	9421-12098
XPB2120	9421-12120
XPB2150	9421-12150
XPB2180	9421-12180
XPB2240	9421-12240
XPB2280	9421-12280
XPB2300	9421-12300
XPB2360	9421-12360
XPB2391	9421-12391
XPB2410	9421-12410
XPB2500	9421-12500
XPB2530	9421-12530
XPB2650	9421-12650
XPB2680	9421-12680
XPB2800	9421-12800
XPB2990	9421-12990
XPB3000	9421-13000
SPB3150	9421-03150

Part No.	Product No.
SPB3350	9421-03350
SPB3550	9421-03550
SPB3750	9421-03750
SPB3800	9421-03800
SPB4000	9421-04000
SPB4250	9421-04250
SPB4500	9421-04500
SPB4750	9421-04750
SPB5000	9421-05000
SPB5300	9421-05300
SPB5600	9421-05600
SPB6000	9421-06000
SPB6300	9421-06300
SPB6700	9421-06700
SPB7100	9421-07100
SPB7500	9421-07500
SPB8000	9421-08000



Product No. Series 9422

XPC/SPC Section

Part No.	Product No.
XPC1800	9422-11800
XPC2000	9422-12000
XPC2120	9422-12120
XPC2240	9422-12240
XPC2360	9422-12360
XPC2500	9422-12500
XPC2650	9422-12650
XPC2800	9422-12800
XPC3000	9422-13000
SPC3150	9422-03150

Part No.	Product No.
SPC3350	9422-03350
SPC3550	9422-03550
SPC3750	9422-03750
SPC4000	9422-04000
SPC4250	9422-04250
SPC4500	9422-04500
SPC4750	9422-04750
SPC5000	9422-05000
SPC5300	9422-05300
SPC5600	9422-05600

Part No.	Product No.
SPC6000	9422-06000
SPC6300	9422-06300
SPC6700	9422-06700
SPC7100	9422-07100
SPC7500	9422-07500
SPC8000	9422-08000
SPC8500	9422-08500
SPC9000	9422-09000
SPC10000	9422-01000
SPC10600	9422-01060

Classical Sizes

Product No. Series 9424

10X Section



Part No.	Product No.
10X530LI	9424-10530
10X540LI	9424-10540
10X670LI	9424-10670
10X710LI	9424-10710
10X725LI	9424-10725
10X730LI	9424-10730
10X750LI	9424-10750
10X775LI	9424-10775

Part No.	Product No.
10X800LI	9424-10800
10X875LI	9424-10875
10X900LI	9424-10900
10X925LI	9424-10925
10X950LI	9424-10950
10X975LI	9424-10975
10X1000LI	9424-10100
10X1016LI	9424-10101

Part No.	Product No.
10X1060LI	9424-10106
10X1100LI	9424-10110
10X1120LI	9424-10112
10X1180LI	9424-10118
10X1400LI	9424-10140
10X1422LI	9424-10142
10X1750LI	9424-10175

Product No. Series 9423 & 9424

13X Section



Part No.	Product No.
13X715LI	9424-13715
13X750LI	9424-13750
13X813LI	9424-13813

Part No.	Product No.
13X925LI	9424-13925
13X975LI	9424-13975
13X2650LI	9424-13265

Part No.	Product No.
13X4000LI	9423-13400

17X Section



Part No.	Product No.
17X875LI	9424-17875
17X1500LI	9424-17150
17X1525LI	9424-17152
17X1800LI	9424-17180

Part No.	Product No.
17X2160LI	9424-17216
17X2240LI	9424-17224
17X2540LI	9424-17254
17X3658LI	9423-17365

Part No.	Product No.
17X8180LI	9423-17818
17X8375LI	9423-17837
17X8636LI	9423-17863

Hi-Power® II Dubl-V Belts

This belt is designed with a unique recessed top and bottom to maintain sidewall contact, while remaining flexible for drives that require power transmission from both sides of the belt.

Markets/Applications

Suitable for all industrial serpentine applications requiring rotation reversal on some driven shafts.

Features/Advantages


- **Gates Curves** provide proper cord support and full contact with the sheave-groove for uniform loading, uniform wear, and increased belt life.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- **The Flex-Weave® Cover** is a patented construction for longer cover life, providing extended protection to the core of the belt from oil, dirt, and heat.
- Meets RMA oil and heat resistant standards.
- Meets RMA static conductivity requirements.

Recommended Sheaves

Multi-Duty® Sheaves


Notes

Dubl-V belts are available in AA, BB, CC and DD cross sections.



Product No. Series 9052

AA Section




Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
AA51	9052-0051	53.0	.60
AA55	9052-0055	57.0	.50
AA60	9052-0060	62.0	.50
AA68	9052-0068	70.0	.55
AA73	9052-0073	75.0	.67
AA75	9052-0075	77.0	.60
AA80	9052-0080	82.0	.65
AA85	9052-0085	87.0	.70

Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
AA88	9052-0088	90.0	.70
AA90	9052-0090	92.0	.70
AA92	9052-0092	94.0	.75
AA96	9052-0096	98.0	.75
AA105	9052-0105	107.0	.85
AA112	9052-0112	114.0	.90
AA120	9052-0120	122.0	.95
AA128	9052-0128	130.0	1.00

Product No. Series 9053

BB Section



Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
BB35	9053-0035	38.0	.60
BB38	9053-0038	41.0	.50
BB42	9053-0042	45.0	.60
BB43	9053-0043	46.0	.70
BB45	9053-0045	48.0	.71
BB46	9053-0046	49.0	.70
BB51	9053-0051	54.0	.75
BB53	9053-0053	56.0	.75
BB55	9053-0055	58.0	.75
BB60	9053-0060	63.0	.80
BB66	9053-0066	69.0	.93
BB68	9053-0068	71.0	.90
BB71	9053-0071	74.0	.95


Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
BB73	9053-0073	76.0	1.00
BB74	9053-0074	77.0	1.00
BB75	9053-0075	78.0	1.00
BB81	9053-0081	84.0	1.10
BB85	9053-0085	88.0	1.15
BB90	9053-0090	93.0	1.20
BB92	9053-0092	95.0	.54
BB93	9053-0093	96.0	1.65
BB94	9053-0094	97.0	1.25
BB96	9053-0096	99.0	1.30
BB97	9053-0097	100.0	1.30
BB100	9053-0100	103.0	1.31
BB103	9053-0103	106.0	1.40

Product No. Series 9053 (continued)

BB Section (continued)

Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
BB105	9053-0105	108.0	1.35
BB107	9053-0107	110.0	1.40
BB108	9053-0108	111.0	1.50
BB111	9053-0111	114.0	1.50
BB112	9053-0112	115.0	2.10
BB114	9053-0114	117.0	1.57
BB116	9053-0116	119.0	1.60
BB118	9053-0118	121.0	1.53
BB120	9053-0120	123.0	1.57
BB122	9053-0122	125.0	1.55
BB123	9053-0123	126.0	1.70
BB124	9053-0124	127.0	1.71
BB127	9053-0127	130.0	1.60
BB128	9053-0128	131.0	1.75
BB129	9053-0129	132.0	1.75
BB130	9053-0130	133.0	.78
BB133	9053-0133	136.0	1.80
BB135	9053-0135	138.0	1.86
BB136	9053-0136	139.0	1.75
BB140	9053-0140	143.0	1.95

Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
BB144	9053-0144	147.0	.86
BB155	9053-0155	158.0	2.00
BB158	9053-0158	161.0	.92
BB168	9053-0168	171.0	2.20
BB169	9053-0169	172.0	2.30
BB170	9053-0170	173.0	2.30
BB173	9053-0173	176.0	2.30
BB180	9053-0180	183.0	2.35
BB182	9053-0182	185.0	2.49
BB187	9053-0187	190.0	2.50
BB190	9053-0190	193.0	2.45
BB195	9053-0195	198.0	1.10
BB210	9053-0210	213.0	1.24
BB226	9053-0226	227.0	3.10
BB228	9053-0228	229.0	3.10
BB230	9053-0230	231.0	3.15
BB240	9053-0240	241.0	2.75
BB270	9053-0270	271.0	4.14
BB277	9053-0277	278.0	4.25
BB300	9053-0300	301.0	3.95




Product No. Series 9054

CC Section

Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
CC75	9054-0075	79.0	1.85
CC81	9054-0081	85.0	2.05
CC85	9054-0085	89.0	2.05
CC90	9054-0090	94.0	2.15
CC96	9054-0096	100.0	2.40
CC105	9054-0105	109.0	2.50
CC112	9054-0112	116.0	2.65
CC120	9054-0120	124.0	3.00
CC128	9054-0128	132.0	3.05
CC136	9054-0136	140.0	3.25
CC140	9054-0140	144.0	3.46
CC144	9054-0144	148.0	3.30
CC158	9054-0158	162.0	4.20

Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
CC162	9054-0162	166.0	3.80
CC173	9054-0173	177.0	4.10
CC180	9054-0180	184.0	4.15
CC195	9054-0195	199.0	2.05
CC210	9054-0210	214.0	5.10
CC240	9054-0240	242.0	5.95
CC270	9054-0270	272.0	6.65
CC300	9054-0300	302.0	8.10
CC330	9054-0330	332.0	8.15
CC360	9054-0360	362.0	8.90
CC390	9054-0390	392.0	9.50
CC420	9054-0420	422.0	9.95



Product No. Series 9055

DD Section

Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
DD270	9055-0270	273.0	15.20
DD300	9055-0300	303.0	16.35

Part No.	Product No.	Belt Nominal E.L. (In.)	Wt. Ea. (Lbs.)
DD360	9055-0360	363.0	19.15



PowerBack® Belts

Specifically designed for live roller conveyor applications, this modified "B" section belt has a special flat back to increase top surface contact with Roll and from Roll to Roll.

Markets/Applications

Ideal for roll-to-roll drives in conveyor applications.

Features/Advantages


- **Flat Back** provides greater top surface contact with roll and from roll to roll.
- **Flex-Bonded Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- Meets RMA **oil and heat resistant** standards.

Recommended Sheaves

Multi-Duty Sheaves

Notes

PowerBack belts are available in B cross section.



Product No. Series 9003

B Section

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
B101PB	9003-8101	104.0	1.10
B113PB	9003-8113	116.0	1.20
B125PB	9003-8125	128.0	1.40
B137PB	9003-8137	140.0	1.55
B149PB	9003-8149	152.0	1.70
B161PB	9003-8161	164.0	1.64
B185PB	9003-8185	188.0	1.90
B197PB	9003-8197	200.0	2.10
B211PB	9003-8211	212.0	2.10
B247PB	9003-8247	248.0	2.50
B259PB	9003-8259	260.0	2.90
B315PB	9003-8315	316.0	3.20

Power Curve® Belts

The conveyor turn is a demanding application in which V-belts face varying degrees of transverse bending. The Gates Power Curve belt was specifically engineered to handle the bending and twisting of this demanding application.

Markets/Applications

Recommended for power turn conveyor beds and automotive manufacturing conveyors.

Features/Advantages


- Unique **under cord** construction allows greater than four times the flexibility of Gates standard B section belt.
- Gates patented **Flex-Weave® Cover** increases flexibility and reduces cover stress for longer life.
- Meets RMA **oil and heat resistant** standards.

Recommended Sheaves

Multi-Duty® Sheaves

Notes

Power Curve belts are available in B cross section.



Product No. Series 9003

B Section

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
B112PC	9003-7112	115.0	1.30
B116PC	9003-7116	119.0	1.30
B120PC	9003-7120	123.0	1.35
B124PC	9003-7124	127.0	1.40
B128PC	9003-7128	131.0	1.45
B133PC	9003-7133	136.0	1.50
B136PC	9003-7136	139.0	1.70
B140PC	9003-7140	143.0	1.75
B144PC	9003-7144	147.0	1.65
B150PC	9003-7150	153.0	1.70
B154PC	9003-7154	157.0	1.75
B158PC	9003-7158	161.0	1.77
B162PC	9003-7162	165.0	1.80
B173PC	9003-7173	176.0	3.00
B180PC	9003-7180	183.0	2.00
B190PC	9003-7190	193.0	2.15
B195PC	9003-7195	198.0	2.20
B205PC	9003-7205	208.0	2.30
B210PC	9003-7210	213.0	2.30

Part No.	Product No.	Belt O.C. (In.)	Wt. Ea. (Lbs.)
B225PC	9003-7225	226.0	2.50
B240PC	9003-7240	241.0	2.65
B255PC	9003-7255	256.0	2.80
B270PC	9003-7270	271.0	2.95
B285PC	9003-7285	286.0	3.15
B300PC	9003-7300	301.0	3.35
B315PC	9003-7315	316.0	3.50
B330PC	9003-7330	331.0	3.70
B345PC	9003-7345	346.0	3.80
B360PC	9003-7360	361.0	3.95
B375PC	9003-7375	376.0	4.15
B390PC	9003-7390	391.0	5.00
B405PC	9003-7405	406.0	5.20
B420PC	9003-7420	421.0	4.65
B430PC	9003-7430	431.0	4.80
B445PC	9003-7445	446.0	4.95
B460PC	9003-7460	461.0	5.75
B500PC	9003-7500	501.0	6.50



Micro-V® Belts

Exclusive truncated (shortened) profile gives Gates Micro-V belts increased flexibility, reduced heat buildup and allows performance at higher speeds on smaller diameter sheaves.

Markets/Applications

Well suited for applications such as appliances, outdoor power equipment, roller conveyors, machine tools, medical equipment and exercise equipment.

Features/Advantages

- **Fiber Reinforced Ribs** for excellent wear resistance.
- **High Modulus, low stretch tensile member** for added strength and dependability.
- Smooth Running for minimal vibration at high speeds.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.


Recommended Sheaves

Taper-Lock® Micro-V Sheaves


Notes

The part number is constructed by using the effective length in tenths of an inch, followed by cross section and the number of ribs. For example; 780L16 represents a 78" effective length, L cross section and 16 ribs.

Rib configurations listed will be stocked. Other rib configurations and Standard/Non-Stock and may require manufacturing lead times. Minimum order quantities are not required on lengths listed.



Product No. Series 9171



J Section


Size	Effective Length (In.)	Wt. Per Rib (Lbs.)	Max. No. of Ribs
180J	18.0	.008	30
190J	19.0	.009	30
200J	20.0	.009	30
220J	22.0	.010	211
230J	23.0	.011	211
240J	24.0	.011	211
260J	26.0	.012	211
280J	28.0	.013	211
290J	29.0	.014	211
300J	30.0	.014	211
320J	32.0	.015	211
330J	33.0	.016	211
340J	34.0	.016	211
360J	36.0	.017	211
380J	38.0	.018	211
400J	40.0	.019	211
410J	41.0	.019	211
420J	42.0	.020	211
430J	43.0	.020	211
440J	44.0	.021	211
460J	46.0	.022	211
480J	48.0	.023	211
490J	49.0	.023	211
500J	50.0	.024	211
520J	52.0	.024	211
550J	55.0	.026	211
580J	58.0	.027	211
610J	61.0	.029	211
650J	65.0	.031	211
730J	73.0	.034	211
870J	87.0	.041	211
³ 920J	92.0	.043	10
³ 980J	98.0	.046	10

3 Available only up to 10-rib configuration due to ground rib construction.



Product No. Series 9173


L Section



Size	Effective Length (In.)	Wt. Per Rib (Lbs.)	Max. No. of Ribs
500L	50.0	.087	105
540L	54.0	.093	105
560L	56.0	.097	105
615L	61.5	.106	105
635L	63.5	.110	105
655L	65.5	.113	105
675L	67.5	.117	105
695L	69.5	.120	105
725L	72.5	.125	105
765L	76.5	.132	105
780L	78.0	.135	105
795L	79.5	.138	105
815L	81.5	.141	105
840L	84.0	.145	105
865L	86.5	.150	105
915L	91.5	.158	60
975L	97.5	.169	60
990L	99.0	.171	60
1065L	106.5	.184	60
1120L	112.0	.194	60
1150L	115.0	.199	60
1215L	121.5	.201	60
1230L	123.0	.213	60
1295L	129.5	.224	60
1310L	131.0	.227	60
1455L	145.5	.252	60

Product No. Series 9174

M Section



Size	Effective Length (In.)	Wt. Per Rib (Lbs.)	Max. No. of Ribs
900M	90.0	.626	30
940M	94.0	.653	30
990M	99.0	.688	30
1060M	106.0	.736	30
1115M	111.5	.775	30
1150M	115.0	.799	30
1185M	118.5	.824	30
1230M	123.0	.855	30
1310M	131.0	.910	30
1390M	139.0	.966	30
1470M	147.0	1.022	30
1610M	161.0	1.119	30
1650M	165.0	1.147	30
1760M	176.0	1.223	30
1830M	183.0	1.272	30
1980M	198.0	1.376	30
2130M	213.0	1.480	30
2410M	241.0	1.675	30
2560M	256.0	1.779	30
2710M	271.0	1.883	30
3010M	301.0	2.092	30
3310M	331.0	2.300	30
3610M	361.0	2.509	30

Multi-Speed Belts

Multi-Speed belts are made banded or bandless construction featuring high-modulus, fiber-loaded stock that offers transverse rigidity and flexibility at the same time. This results in higher load carrying capacity and long belt life.

Markets/Applications

Suitable for all industrial, wide-speed range open pulley or enclosed device variable speed drives.

Features/Advantages

- **Notch Design** reduced thermal and bending stresses for longer life.
- **Smooth Running** construction for minimal vibration at high speeds.
- Meets RMA oil and heat resistant standards.

Recommended Sheaves

Contact the Gates Made-To-Order Metals Team.

Notes

HV in the part number denotes Heavy Construction, which has a thickness of .700+.


Product No. Prefix	Construction
9800	Banded
9804	Bandless
9833	Bandless/Aramid Tensile

Additional sizes may be available on a Made-To-Order basis. Contact Customer Service for information

Minimum Order Quantities for MTO Multi-Speed Belts

Size Range	Min. Quantity
1228V-1632V	42
1822V-2332V	28
2422V-2930V	20
3028V-3636V	16
3726V-4436V	12

Manufacturing variations may cause actual ship quantity to vary +/- 10% from these figures. Orders must be for a minimum of the quantities shown, or multiples thereof.



Product No. Series 9800, 9804 & 9833

Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)	Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)
1228V255	9804-0729	26.1	3/4	28	.45	1430V375	9804-0820	38.0	7/8	30	.47
⁴ 1230V341	9804-0814	34.6	3/4	30	.56	⁴ 1430V450	9804-0849	45.6	7/8	30	.77
1230V348	9804-0815	35.3	3/4	30	.60	⁴ 1430V500	9804-0850	50.5	7/8	30	.80
1330V242	9804-0447	24.7	13/16	30	.55	⁴ 1524V301	9804-0821	30.6	15/16	24	.63
1422V235	9804-0816	24.0	7/8	22	.50	1526V264	9804-0505	27.0	15/16	26	.61
1422V240	9804-0495	24.7	7/8	22	.50	1526V294	9804-0506	30.0	15/16	26	.65
1422V290	9804-0584	29.6	7/8	22	.55	1528V298	9804-0769	30.3	15/16	28	.62
1422V300	9804-0493	30.7	7/8	22	.55	1528V326	9804-0770	33.1	15/16	28	.61
1422V330	9804-0492	33.7	7/8	22	.60	1528V360	9804-0771	36.5	15/16	28	.70
1422V340	9804-0708	34.6	7/8	22	.75	1528V414	9804-0772	41.9	15/16	28	.79
1422V360	9804-0328	36.7	7/8	22	.70	1622V270	9804-0822	27.5	1	22	.60
1422V400	9804-0348	40.8	7/8	22	.65	1622V297	9804-0823	30.2	1	22	.65
1422V420	9804-0329	42.8	7/8	22	.70	1622V307	9804-0571	31.1	1	22	.65
1422V440	9804-0817	44.5	7/8	22	.70	1622V336	9804-0824	34.1	1	22	.65
1422V460	9804-0768	46.5	7/8	22	.75	1622V520	9804-0572	52.5	1	22	.85
1422V466	9804-0325	47.0	7/8	22	.75	1626V262	9804-0773	26.7	1	26	.56
1422V470	9804-0818	47.5	7/8	22	.70	1626V290	9804-0536	29.8	1	26	.75
1422V480	9804-0337	48.7	7/8	22	.75	1626V293	9804-0588	30.0	1	26	.75
1422V540	9804-0331	54.8	7/8	22	.90	1626V304	9804-0305	31.1	1	26	.70
1422V600	9804-0332	60.7	7/8	22	.85	1626V330	9804-0293	33.8	1	26	.75
1422V660	9804-0333	66.7	7/8	22	.92	1626V339	9804-0248	34.7	1	26	.74
1422V780	9804-0339	78.7	7/8	22	1.09	1626V380	9804-0774	38.5	1	26	.74
1426V298	9804-0259	30.4	7/8	26	.70	1626V384	9804-0308	39.2	1	26	.80
1426V299	9804-0656	30.5	7/8	26	.60	1626V395	9804-0618	40.3	1	26	.85
1426V328	9804-0636	33.3	7/8	26	.75	1626V411	9804-0537	41.9	1	26	.85
1426V362	9804-0635	36.7	7/8	26	.72	1626V428	9804-0775	43.3	1	26	.80
1430V215	9804-0702	21.8	7/8	30	.45	1626V440	9804-0291	44.7	1	26	1.05
⁴ 1430V315	9804-0819	32.0	7/8	30	.60	1626V455	9804-0617	46.2	1	26	.80

⁴ Minimum production quantity may apply. Contact Customer Service for availability.



Multi-Speed Belts

Product No. Series 9800, 9804 & 9833 (continued)

Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)	Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)
1626V513	9804-0776	51.8	1	26	.40	1930V400	9804-0144	40.7	1 3/16	30	1.00
1626V517	9804-0249	52.1	1	26	1.10	1930V425	9804-0790	43.1	1 3/16	30	1.10
1626V597	9804-0393	60.6	1	26	.95	1930V431	9804-0709	44.0	1 3/16	30	1.20
1626V604	9804-0306	61.2	1	26	1.30	1930V450	9804-0829	45.6	1 3/16	30	1.00
1626V658	9804-0397	66.7	1	26	1.18	⁴ 1930V475	9804-0830	48.1	1 3/16	30	1.24
1626V700	9804-0403	70.8	1	26	1.30	1930V485	9804-0177	49.1	1 3/16	30	1.26
1628V210	9804-0686	21.2	1	28	4.50	1930V491	9804-0710	50.0	1 3/16	30	1.25
1628V315	9804-0313	32.7	1	28	.75	1930V500	9804-0831	50.6	1 3/16	30	1.20
1632V210	9804-0323	21.9	1	32	5.50	1930V530	9804-0783	53.6	1 3/16	30	1.20
1822V290	9804-0648	29.5	1 1/8	22	.65	1930V541	9804-0220	55.0	1 3/16	30	1.45
1822V328	9804-0651	33.5	1 1/8	22	.85	1930V560	9804-0764	56.9	1 3/16	30	1.25
1826V250	9804-0592	25.4	1 1/8	26	.55	1930V585	9804-0178	59.1	1 3/16	30	1.33
1828V368	9804-0284	37.6	1 1/8	28	.90	1930V591	9804-0760	60.0	1 3/16	30	1.18
1832V338	9804-0777	34.4	1 1/8	32	.80	1930V600	9804-0784	60.6	1 3/16	30	1.21
1922V256	9804-0253	26.4	1 3/16	22	.70	1930V630	9804-0832	63.6	1 3/16	30	1.36
1922V277	9804-0611	28.2	1 3/16	22	.75	1930V641	9804-0221	64.6	1 3/16	30	1.43
1922V282	9804-0060	29.0	1 3/16	22	.08	1930V691	9804-0210	69.6	1 3/16	30	1.55
1922V298	9804-0500	30.6	1 3/16	22	.65	1930V750	9804-0209	75.6	1 3/16	30	1.68
1922V302	9804-0778	30.8	1 3/16	22	.80	1930V791	9804-0222	79.6	1 3/16	30	1.76
1922V321	9804-0070	33.0	1 3/16	22	.85	⁴ 1930V800	9804-0835	80.6	1 3/16	30	1.50
1922V332	9804-0713	34.0	1 3/16	22	.95	⁴ 1930V850	9804-0836	85.6	1 3/16	30	1.57
1922V338	9804-0501	34.7	1 3/16	22	.80	1930V891	9804-0206	89.6	1 3/16	30	1.96
1922V363	9804-0027	37.1	1 3/16	22	.95	1930V900	9804-0837	90.6	1 3/16	30	2.11
1922V381	9804-0307	38.8	1 3/16	22	1.00	⁴ 1930V950	9804-0838	95.6	1 3/16	30	1.78
1922V386	9804-0071	39.3	1 3/16	22	1.05	1930V991	9804-0181	99.6	1 3/16	30	2.14
1922V403	9804-0530	41.4	1 3/16	22	.95	⁴ 1930V1000	9804-0892	101.2	1 3/16	30	2.23
1922V417	9804-0376	42.5	1 3/16	22	.85	⁴ 1930V1060	9804-0839	106.6	1 3/16	30	2.08
1922V426	9804-0063	43.4	1 3/16	22	1.10	1930V1091	9804-0223	109.6	1 3/16	30	2.81
1922V443	9804-0072	45.1	1 3/16	22	1.25	⁴ 1930V1120	9804-0840	112.6	1 3/16	30	2.60
1922V454	9804-0028	46.2	1 3/16	22	1.10	1930V1191	9804-0373	119.6	1 3/16	30	2.54
1922V460	9804-0622	46.8	1 3/16	22	1.25	2026V422	9804-0394	43.0	1 1/4	26	.95
1922V484	9804-0057	49.2	1 3/16	22	1.17	2026V445	9804-0520	45.2	1 1/4	26	1.05
1922V526	9804-0602	53.3	1 3/16	22	1.25	2026V474	9804-0574	48.2	1 1/4	26	1.52
1922V544	9804-0029	55.1	1 3/16	22	1.30	2026V607	9804-0395	61.5	1 1/4	26	1.20
1922V604	9804-0026	61.2	1 3/16	22	1.50	2030V381	9804-0640	38.5	1 1/4	30	.78
1922V630	9804-0779	63.6	1 3/16	22	1.20	⁴ 2126V297	9804-0842	30.4	1 5/16	26	.83
1922V646	9804-0074	65.4	1 3/16	22	1.34	2126V307	9804-0785	31.4	1 5/16	26	.81
1922V666	9804-0075	67.4	1 3/16	22	1.60	2126V309	9804-0314	31.7	1 5/16	26	.90
1922V686	9804-0603	69.3	1 3/16	22	1.68	2126V365	9804-0526	37.4	1 5/16	26	1.05
1922V706	9804-0569	71.3	1 3/16	22	1.76	2126V377	9804-0843	38.4	1 5/16	26	.94
1922V726	9804-0673	73.0	1 3/16	22	1.80	2126V468	9804-0721	47.7	1 5/16	26	1.32
1922V751	9804-0007	75.8	1 3/16	22	1.74	2130V374	9804-0749	38.0	1 5/16	30	1.09
1922V756	9804-0179	76.4	1 3/16	22	1.70	2226V307	9804-0677	31.2	1 3/8	26	.85
1922V806	9804-0674	81.3	1 3/16	22	1.80	2230V266	9804-0615	27.5	1 3/8	30	.80
1922V846	9804-0716	85.4	1 3/16	22	1.87	2230V273	9804-0786	27.9	1 3/8	30	.80
⁴ 1922V1006	9804-0676	101.3	1 3/16	22	2.36	2230V275	9804-0358	28.1	1 3/8	30	.75
1922V1026	9804-0825	103.2	1 3/16	22	2.73	2230V326	9804-0725	33.5	1 3/8	30	.80
1922V1146	9804-0719	115.4	1 3/16	22	3.25	2230V375	9804-0678	38.2	1 3/8	30	1.15
1926V249	9804-0621	25.3	1 3/16	26	.60	2322V329	9804-0679	33.4	1 7/16	22	1.12
1926V250	9804-0633	25.7	1 3/16	26	.65	2322V347	9804-0680	35.2	1 7/16	22	1.05
1926V275	9804-0688	28.1	1 3/16	26	.65	2322V364	9804-0058	37.2	1 7/16	22	1.05
1926V333	9804-0255	33.9	1 3/16	26	.95	2322V384	9804-0905	39.3	1 7/16	22	1.10
1926V367	9804-0050	37.2	1 3/16	26	.95	2322V396	9804-0547	40.6	1 7/16	22	1.30
1926V376	9804-0624	38.8	1 3/16	26	.85	2322V421	9804-0076	42.9	1 7/16	22	1.35
1926V380	9804-0509	38.9	1 3/16	26	1.00	2322V434	9804-0681	44.2	1 7/16	22	1.30
1926V390	9804-0780	39.6	1 3/16	26	1.00	2322V441	9804-0127	45.1	1 7/16	22	1.40
1926V407	9804-0256	41.4	1 3/16	26	1.05	2322V461	9804-0726	47.0	1 7/16	22	1.50
⁴ 1926V415	9804-0826	42.1	1 3/16	26	1.10	2322V481	9804-0053	49.2	1 7/16	22	1.55
1926V427	9804-0827	40.3	1 3/16	26	1.10	2322V521	9804-0044	52.8	1 7/16	22	1.45
1926V507	9804-0508	51.4	1 3/16	26	1.20	2322V541	9804-0059	55.1	1 7/16	22	1.60
1926V542	9804-0638	55.4	1 3/16	26	1.34	2322V601	9804-0025	61.2	1 7/16	22	1.75
1930V355	9804-0828	36.1	1 3/16	30	.90	2322V621	9804-0734	63.0	1 7/16	22	1.85
1930V366	9804-0781	37.2	1 3/16	30	1.00	2322V661	9804-0078	67.4	1 7/16	22	2.15
1930V375	9804-0782	38.1	1 3/16	30	.94	2322V681	9804-0073	68.8	1 7/16	22	1.78

⁴ Minimum production quantity may apply. Contact Customer Service for availability.



Multi-Speed Belts

Product No. Series 9800, 9804 & 9833 (continued)

Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)	Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)
2322V701	9804-0162	71.4	1 7/16	22	2.02	2822V778	9800-0017	79.5	1 3/4	22	5.48
2322V721	9804-0062	73.4	1 7/16	22	2.07	2826V412	9800-0646	41.9	1 3/4	26	1.99
2322V801	9804-0079	81.4	1 7/16	22	2.46	2826V452	9800-0650	46.0	1 3/4	26	2.92
2322V846	9804-0787	85.3	1 7/16	22	2.67	2830V337	9800-0691	34.8	1 3/4	30	1.68
2322V886	9804-0714	89.5	1 7/16	22	2.63	2830V363	9833-0662	36.8	1 3/4	30	1.47
2322V1001	9804-0080	101.4	1 7/16	22	2.90	2830V366	9833-0434	37.2	1 3/4	30	1.07
2322V1061	9804-0788	106.8	1 7/16	22	3.70	2830V367	9800-0916	37.9	1 3/4	30	1.80
2326V310	9804-0706	31.8	1 7/16	26	.93	2830V393	9800-0664	39.9	1 3/4	30	1.38
2326V359	9804-0789	36.6	1 7/16	26	1.10	2830V396	9833-0435	40.3	1 3/4	30	1.28
2330V273	9804-0619	27.9	1 7/16	30	.80	2830V422	9800-0665	42.7	1 3/4	30	1.46
2330V338	9800-0728	34.6	1 7/16	30	1.04	⁴ 2830V428	9804-0859	43.6	1 3/4	30	1.88
2330V359	9804-0690	36.5	1 7/16	30	1.15	⁴ 2830V492	9804-0860	50.1	1 3/4	30	1.85
2330V537	9804-0682	54.6	1 7/16	30	1.53	2836V343	9800-0120	35.1	1 3/4	36	1.69
2332V373	9804-0479	38.0	1 7/16	32	1.10	2836V350	9800-0324	35.8	1 3/4	36	1.72
2422V570	9804-0844	57.7	1 1/2	22	1.85	2836V380	9800-0367	38.8	1 3/4	36	1.84
2426V343	9800-0483	35.4	1 1/2	26	1.33	2926V366	9804-0081	37.5	1 13/16	26	1.57
2428V757	9804-0054	76.6	1 1/2	28	2.81	2926V400	9804-0759	40.8	1 13/16	26	1.85
2430V297	9804-0717	30.7	1 1/2	30	1.00	2926V426	9800-0258	43.5	1 13/16	26	2.11
⁴ 2430V302	9804-0845	30.9	1 1/2	30	.96	2926V471	9800-0082	48.0	1 13/16	26	3.08
2430V319	9804-0846	32.6	1 1/2	30	1.01	2926V477	9804-0762	48.5	1 13/16	26	2.45
2430V345	9804-0847	35.2	1 1/2	30	1.10	2926V486	9800-0083	49.2	1 13/16	26	2.39
2430V379	9804-0848	38.6	1 1/2	30	1.49	2926V491	9800-0084	50.0	1 13/16	26	3.17
2436V331	9804-0366	34.0	1 1/2	36	1.00	2926V521	9800-0064	53.0	1 13/16	26	3.30
2526V302	9800-0069	30.7	1 9/16	26	1.02	⁴ 2926V534	9804-0861	54.2	1 13/16	26	2.29
2526V314	9800-0002	32.4	1 9/16	26	1.32	2926V546	9800-0067	55.5	1 13/16	26	3.38
2528V370	9804-0851	37.7	1 9/16	28	1.40	2926V574	9800-0085	58.3	1 13/16	26	3.52
2530V300	9800-0521	31.0	1 9/16	30	1.12	2926V586	9800-0068	59.5	1 13/16	26	3.55
2530V335	9804-0852	34.2	1 9/16	30	1.08	2926V606	9800-0015	61.5	1 13/16	26	3.66
2530V470	9804-0791	47.7	1 9/16	30	1.66	2926V616	9800-0149	63.3	1 13/16	26	3.75
2530V490	9800-0326	50.0	1 9/16	30	2.47	2926V636	9800-0086	64.4	1 13/16	26	3.79
2530V500	9800-0712	50.9	1 9/16	30	3.32	2926V646	9800-0087	65.5	1 13/16	26	3.81
2530V530	9800-0654	54.0	1 9/16	30	3.39	2926V666	9800-0088	67.5	1 13/16	26	4.16
2530V550	9800-0436	56.0	1 9/16	30	2.74	2926V686	9800-0089	69.5	1 13/16	26	4.00
2530V560	9804-0853	56.7	1 9/16	30	1.73	2926V706	9800-0118	71.5	1 13/16	26	4.10
2530V575	9833-0730	58.5	1 9/16	30	2.74	2926V726	9800-0035	73.5	1 13/16	26	4.17
2530V595	9800-0166	60.7	1 9/16	30	3.68	2926V776	9800-0090	78.5	1 13/16	26	4.38
2530V600	9804-0793	60.7	1 9/16	30	2.02	2926V786	9800-0735	79.4	1 13/16	26	4.44
2530V610	9800-0437	62.0	1 9/16	30	3.03	2926V834	9800-0704	84.2	1 13/16	26	4.64
2530V618	9800-0260	62.5	1 9/16	30	3.12	2926V856	9800-0040	86.4	1 13/16	26	4.77
2530V630	9800-0164	64.2	1 9/16	30	3.84	2926V891	9804-0092	90.0	1 13/16	26	3.92
2530V660	9800-0438	67.0	1 9/16	30	3.94	2926V906	9800-0093	91.5	1 13/16	26	4.96
2530V670	9800-0165	68.2	1 9/16	30	4.02	2926V966	9800-0094	97.5	1 13/16	26	5.20
⁴ 2530V680	9804-0854	68.7	1 9/16	30	2.16	2926V1006	9800-0095	101.5	1 13/16	26	5.39
2530V690	9800-0439	70.0	1 9/16	30	4.07	2926V1026	9800-0684	103.6	1 13/16	26	5.46
2530V700	9800-0275	71.0	1 9/16	30	4.14	2926V1086	9800-0685	109.6	1 13/16	26	5.76
2530V730	9800-0211	74.2	1 9/16	30	4.28	2930V348	9833-0727	35.5	1 13/16	26	1.45
2530V740	9800-0683	75.0	1 9/16	30	4.35	2930V492	9800-0590	50.0	1 13/16	26	3.14
2530V750	9800-0180	76.2	1 9/16	30	4.37	3028V386	9800-0529	39.4	1 7/8	28	1.97
2530V790	9800-0214	80.0	1 9/16	30	4.54	3030V357	9800-0692	36.5	1 7/8	30	1.88
2530V840	9800-0215	85.0	1 9/16	30	4.72	3030V377	9804-0863	38.7	1 7/8	30	1.50
⁴ 2530V850	9804-0857	85.7	1 9/16	30	3.71	3030V387	9800-0694	39.6	1 7/8	30	2.02
2530V890	9800-0216	90.0	1 9/16	30	4.98	⁴ 3036V351	9800-0310	36.0	1 7/8	36	1.79
2530V934	9800-0163	94.4	1 9/16	30	5.18	3226V392	9800-0670	39.8	2	26	2.21
2530V990	9800-0217	100.0	1 9/16	30	5.43	3226V400	9800-0012	41.1	2	26	2.28
2530V1090	9800-0218	110.0	1 9/16	30	5.87	3226V433	9804-0581	44.1	2	26	1.95
⁴ 2530V1190	9800-0219	119.7	1 9/16	30	6.30	3226V439	9804-0864	44.7	2	26	2.14
2530V1290	9800-0207	130.0	1 9/16	30	6.73	3226V450	9800-0695	45.8	2	26	2.72
2530V1490	9800-0904	150.0	1 9/16	30	5.85	3226V465	9800-0400	47.4	2	26	2.98
⁴ 2530V1690	9800-0794	169.8	1 9/16	30	6.40	3226V505	9800-0543	51.4	2	26	3.15
2626V369	9800-0645	37.4	1 5/8	26	1.64	3226V514	9800-0647	52.3	2	26	2.87
2626V388	9800-0649	39.7	1 5/8	26	1.65	3226V545	9800-0477	55.3	2	26	2.57
2630V345	9800-0616	35.3	1 5/8	30	1.33	3226V585	9800-0542	59.4	2	26	3.48
2630V395	9804-0858	40.2	1 5/8	30	1.50	3226V603	9800-0701	61.4	2	26	4.18
2636V332	9800-0360	34.0	1 5/8	36	1.41	3226V650	9804-0763	65.9	2	26	3.50

⁴ Minimum production quantity may apply. Contact Customer Service for availability.



Multi-Speed Belts

Product No. Series 9800, 9804 & 9833 (continued)

Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)	Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)
3226V663	9800-0423	67.4	2	26	3.80	4036V541	9800-0562	55.4	2 1/2	36	5.28
⁴ 3226V690	9804-0865	69.8	2	26	3.50	4036V574	9800-0369	58.3	2 1/2	36	5.02
3226V723	9800-0424	73.4	2	26	4.05	⁴ 4230V503	9800-0637	51.4	2 5/8	30	5.57
3226V783	9800-0700	79.5	2	26	5.11	4230V556	9800-0601	56.8	2 5/8	30	5.30
3226V843	9800-0426	85.4	2	26	4.55	4230V605	9800-0489	61.0	2 5/8	30	5.24
3226V903	9800-0427	91.4	2	26	4.80	4234V998	9800-0143	100.9	2 5/8	34	10.73
3226V963	9800-0428	97.4	2	26	5.05	4330V521	9800-0594	53.2	2 11/16	30	5.72
3226V1023	9800-0429	103.4	2	26	5.43	4430V510	9800-0513	52.0	2 3/4	30	5.48
3226V1083	9800-0430	109.4	2	26	5.54	4430V530	9800-0736	54.0	2 3/4	30	5.60
3230V419	9800-0653	42.7	2	30	3.06	4430V548	9800-0463	55.0	2 3/4	30	5.75
3230V481	9804-0866	48.9	2	30	2.55	4430V555	9800-0132	56.5	2 3/4	30	5.81
3230V560	9804-0795	56.8	2	30	2.81	4430V560	9804-0886	57.0	2 3/4	30	4.63
⁴ 3230V630	9804-0868	63.8	2	30	3.44	⁴ 4430V570	9804-0887	58.0	2 3/4	30	5.10
3230V670	9804-0796	67.8	2	30	2.45	4430V578	9800-0441	59.0	2 3/4	30	6.04
3230V701	9804-0869	70.9	2	30	3.46	4430V600	9804-0803	61.0	2 3/4	30	4.97
⁴ 3230V850	9804-0873	85.8	2	30	4.28	4430V610	9800-0111	62.0	2 3/4	30	6.31
^o 3230V871	9804-0874	87.9	2	30	4.89	4430V630	9800-0442	64.0	2 3/4	30	6.45
⁴ 3230V1180	9804-0875	118.8	2	30	6.72	4430V652	9804-0888	66.2	2 3/4	30	5.78
3230HV856	9800-0756	86.7	2	30	6.44	4430V660	9800-0443	67.0	2 3/4	30	6.70
3230HV931	9800-0755	94.2	2	30	7.01	4430V670	9800-0112	68.0	2 3/4	30	6.81
3236V369	9800-0122	37.7	2	36	2.07	4430V690	9800-0444	70.0	2 3/4	30	6.95
3236V389	9800-0121	39.7	2	36	2.17	4430V700	9800-0150	71.0	2 3/4	30	7.06
3236V432	9800-0368	44.2	2	36	2.39	⁴ 4430V710	9804-0889	72.1	2 3/4	30	6.54
3236HV528	9800-0612	53.8	2	36	3.58	4430V718	9804-0804	72.8	2 3/4	30	7.88
3236HV553	9800-0604	56.3	2	36	4.48	4430V730	9800-0065	74.0	2 3/4	30	7.31
3236HV570	9800-0605	58.0	2	36	4.59	4430V740	9800-0445	75.0	2 3/4	30	7.36
3236HV585	9800-0606	59.5	2	36	3.70	4430V750	9804-0805	76.0	2 3/4	30	8.17
3236HV603	9800-0607	61.3	2	36	4.79	4430V760	9804-0806	77.0	2 3/4	30	6.77
3236HV613	9800-0347	62.2	2	36	4.83	4430V772	9833-0723	78.6	2 3/4	30	10.59
3236HV620	9800-0608	63.0	2	36	4.91	⁴ 4430V780	9804-0890	79.0	2 3/4	30	6.50
3236HV626	9800-0370	63.6	2	36	4.93	4430V790	9800-0113	80.0	2 3/4	30	7.81
3236HV644	9800-0371	65.4	2	36	5.06	4430V850	9800-0114	86.0	2 3/4	30	8.31
3236HV670	9800-0372	68.0	2	36	5.22	4430V910	9800-0115	92.0	2 3/4	30	8.81
3236HV702	9800-0048	71.1	2	36	5.44	4430V970	9800-0116	98.0	2 3/4	30	9.31
3236HV723	9800-0431	73.2	2	36	5.57	4430V1000	9800-0753	101.1	2 3/4	30	10.24
3236HV821	9800-0639	83.1	2	36	6.14	4430V1030	9800-0117	104.0	2 3/4	30	9.81
3326V478	9800-0628	48.5	2 1/16	26	2.77	4430V1090	9800-0153	110.0	2 3/4	30	10.31
⁴ 3428V451	9804-0876	46.0	2 1/8	28	2.43	4430V1150	9800-0658	116.0	2 3/8	30	13.22
3430V424	9804-0877	43.3	2 1/8	30	2.35	4430V1250	9800-0752	126.1	2 3/4	30	12.51
3430V476	9800-0878	48.8	2 1/8	30	3.23	4430V1320	9800-0171	133.0	2 3/4	30	12.28
3430V493	9804-0879	50.1	2 1/8	30	2.80	4430V1410	9800-0765	142.0	2 3/4	30	13.53
3432V450	9804-0880	45.8	2 1/8	32	2.45	4430V1460	9800-0766	147.0	2 3/4	30	13.97
3432V456	9804-0797	46.5	2 1/8	32	2.50	4430V1610	9800-0767	162.0	2 3/4	30	15.28
3432V480	9804-0881	48.8	2 1/8	32	2.65	⁴ 4430V1810	9800-0808	182.0	2 3/4	30	17.04
3432V484	9804-0798	49.3	2 1/8	32	2.45	⁴ 4430V1917	9800-0809	192.7	2 3/4	30	17.98
3432V528	9804-0882	53.4	2 1/8	32	2.85	4436V525	9800-0125	53.5	2 3/4	36	5.56
3432V534	9804-0799	54.3	2 1/8	32	2.85	4436V551	9800-0154	56.1	2 3/4	36	5.70
3436V404	9804-0364	41.3	2 1/8	36	3.00	⁴ 4436V555	9800-0066	56.5	2 3/4	36	5.81
⁴ 3626V556	9800-0671	56.5	2 1/4	26	4.82	4436V561	9804-0810	57.1	2 3/4	36	4.65
3630V455	9804-0883	46.4	2 1/4	30	2.75	4436V576	9800-0131	58.6	2 3/4	36	5.99
3636V479	9800-0361	48.8	2 1/4	36	3.87	⁴ 4436V581	9804-0811	59.1	2 3/4	36	4.81
3726V558	9800-0757	56.9	2 5/16	26	5.39	4436V646	9800-0522	65.5	2 3/4	36	6.55
3826V459	9804-0004	46.8	2 3/8	26	2.80	4436V714	9800-0363	72.7	2 3/4	36	8.48
3826V465	9800-0055	47.5	2 3/8	26	4.06	4626V596	9800-0011	60.6	2 7/8	26	6.91
3830V501	9800-0379	51.0	2 3/8	30	4.50	4630V650	9800-0613	66.1	2 7/8	30	8.40
3830V510	9800-0689	52.0	2 3/8	30	4.68	4630V663	9800-0378	67.3	2 7/8	30	8.49
3830V517	9800-0614	52.7	2 3/8	30	4.36	4630V668	9800-0698	68.1	2 7/8	30	9.47
3830V580	9800-0696	59.0	2 3/8	30	5.18	4630V683	9800-0464	69.3	2 7/8	30	8.76
3830V587	9804-0800	59.6	2 3/8	30	4.13	4630V733	9800-0699	74.3	2 7/8	30	9.83
3836V418	9800-0124	42.7	2 3/8	36	3.67	4630V1070	9800-0034	108.1	2 7/8	30	11.49
3836V426	9800-0123	43.6	2 3/8	36	3.01	⁴ 4632V722	9800-0510	73.5	2 7/8	32	9.18
3836V654	9804-0801	66.3	2 3/8	36	4.29	4636V613	9800-0362	62.2	2 7/8	36	7.01
4030V538	9804-0687	54.5	2 1/2	30	3.30	4830V602	9800-0652	61.1	3	30	7.61
⁴ 4030V590	9804-0884	60.0	2 1/2	30	4.15	⁴ 4830V614	9800-0548	62.5	3	30	7.23

⁴ Minimum production quantity may apply. Contact Customer Service for availability.

^o Available Until Stock Depleted.



The Driving Force in Power Transmission.

Multi-Speed Belts

Product No. Series 9800, 9804 & 9833 (continued)

Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)	Part No.	Product No.	Belt O.C. (In.)	Top Width (In.)	Angle (°)	Wt. Ea. (Lbs.)
4830V653	9800-0546	66.4	3	30	7.61	5228V930	9800-0894	94.4	3 1/4	28	13.80
4830V692	9800-0545	70.3	3	30	7.99	⁵ 5228V930S	9800-0737	94.4	3 1/4	28	26.49
4830V699	9800-0610	71.0	3	30	8.06	5230V662	9800-0660	67.3	3 1/4	30	9.35
4830V730	9800-0544	74.1	3	30	8.44	5230V734	9800-0893	75.3	3 1/4	30	10.59
4830V750	9800-0813	76.0	3	30	8.55	⁵ 5230V734S	9800-0657	75.3	3 1/4	30	20.47
4830V850	9800-0566	86.1	3	30	9.55	5230V867	9800-0895	88.3	3 1/4	30	11.78
4830V970	9800-0567	98.1	3	30	10.73	^{4,5} 5230V867S	9800-0659	88.3	3 1/4	30	22.56
⁴ 4830V1070	9800-0598	108.1	3	30	11.63	⁴ 5636V750	9800-0235	76.4	3 1/2	36	12.39
⁴ 4836V588	9800-0010	59.8	3	36	6.88	5636V774	9800-0237	78.7	3 1/2	36	12.75
4836V608	9800-0096	61.9	3	36	7.05	5830V756	9800-0661	76.9	3 5/8	30	13.14
4836V618	9800-0155	63.4	3	36	7.22	5836V737	9800-0309	75.0	3 5/8	36	8.10
⁴ 4836V642	9800-0609	65.3	3	36	7.41	6036V761	9833-0738	77.7	3 3/4	36	14.70
4836V655	9800-0133	66.6	3	36	7.54	6036V850	9800-0105	86.3	3 3/4	36	13.28
⁴ 4836V729	9800-0101	74.0	3	36	8.25	6236V694	9800-0147	70.8	3 7/8	36	11.21
4836V789	9800-0102	80.0	3	36	8.83	⁴ 6236V725	9804-0006	73.9	3 7/8	36	12.58
4836V850	9800-0031	86.1	3	36	9.49	6236V762	9800-0104	77.6	3 7/8	36	13.19
4836V1180	9800-0758	119.3	3	36	13.54	6236V785	9804-0009	79.9	3 7/8	36	12.15
5126V938	9800-0246	95.0	3 3/16	26	11.65	⁴ 6236V905	9800-0013	91.9	3 7/8	36	14.38
5130V732	9800-0663	74.6	3 3/16	30	10.87						

⁴ Minimum production quantity may apply. Contact Customer Service for availability.

⁵ Set of 2.



Nu-T-Link® Belting

Nu-T-Link V-belting is designed for rapid installation in an assortment of lengths and operating conditions.

Markets/Applications

Suitable alternative to standard belts on all industrial applications and particularly suited to drives requiring link belting for ease of installation.

Features/Advantages

- **Color Coded Studs** make for easy identification and installation.
- **Orange Polyurethane/Polyester** composite resists oil, water, chemicals and heat (working temperature range: -40°F to +212°F (-40°C to +100°C)).
- May be assembled in an assortment of lengths to fit multiple drive configurations.

Recommended Sheaves

Multi-Duty Sheaves


Notes

Nu-T-Link is available in 50 foot reels.

The studs are color coded: 0 - Red; A - Silver; B - Green; C - Blue; D - Black; E - Black.

Nu-T-Link does not meet RMA requirements for V-belt static conductivity.

WARNING: Do **NOT** use with backside idlers.



Product No. Series 7760

Nu-T-Link®

Part No.	Product No.	Cross Section	Top Width (In.)	Std. Roll (Ft.)	Wt. (Ft.) (Lbs.)
NTL/0	7760-6101	0	3/8	50	.10
NTL/A	7760-6102	A	1/2	50	.12
NTL/B	7760-6103	B	21/32	50	.14
NTL/C	7760-6104	C	7/8	50	.11
NTL/D	7760-6105	D	1 1/4	50	.26
NTL/E	7760-6106	E	1 1/2	50	1.18

A Nu-T-Link assembly tool will be supplied free of charge with belting. Additional assembly tools are available. Contact Customer Service for availability.

Nu-T-Link® Belting Assembly Tool

Part No.	Product No.
900004	7469-0701



Easy-Splice V-Belting

Easy-Splice V-Belting has dependable, non-slip design with minimal stretch characteristics made to outlast other types of open-end belting.

Markets/Applications

Suitable alternative to standard belts on all industrial applications and particularly suited to drives requiring connected belting for ease of installation.

Features/Advantages

- Special resilient **tensile cords** impart high strength and keep stretch to a minimum, prolonging belt life and reducing maintenance.
- Special, **square cut fabric reinforcement** provides a tough, durable anchor for the fastener, while allowing the belt to remain flexible.
- Meets RMA **oil and heat resistant** standards.

Recommended Sheaves

Multi-Duty® Sheaves

Notes

Easy-Splice is available in cross sections A-VO, B-VO, C-VO, D-VO and BB-VO, which correspond to the A, B, C, D, and BB standard industrial V-belt cross sections.

Sold in full rolls only.

Easy-Splice fasteners are not available from Gates. Contact Flexible Steel Lacing Company in Downers Grove, IL at (630) 971-0150 or www.flexco.com.



Product No. Series 9300 & 9310

Part No.	Product No.	Std. Roll (Ft.)	Top Width (In.)	Wt. (Ft.) (Lbs.)	Max. Pieces Std. Roll	Min. Length Ea. Piece (Ft.)
AVO/525	9300-0002	525 +/- 10 ft.	1/2	.09	3	20
BBVO/350	9310-0003	350 +/- 30 ft.	21/32	.17	4	20
BVO/500	9300-0003	500 +/- 10 ft.	21/32	.13	3	20
CVO/450	9300-0004	450 +/- 10 ft.	7/8	.21	3	20
DVO/160	9300-0005	160 +/- 10 ft.	1 1/4	.48	3	20

Power Round™ Belts

Heavy-duty round belt designed for demanding applications. These belts are designed for 1/4 turn or twisted drives where more than an O-ring is required.

Markets/Applications

Designed to meet the needs of higher speed Conveyor Applications.

Ideal for 1/4 turn or twisted, serpentine drives, power turn and line shaft conveyors.

Features/Advantages


- **Flex-Bonded Higher Strength Polyester Tensile Cords** are strongly bonded to the body of the belt resulting in equal load distribution and the absorption of bending stress without cord deterioration.
- The **Flex-Weave® Double Layer Heavy-Duty Cover** is a patented fabric construction for longer cover life, providing extended protection to the belt core from oil, dirt and heat.
- **Installation Alignment Stripe** runs the entire length of the belt to aid in eliminating belt twists during installation.
- Minimal stretch for minimum take-up requirements.
- No splice for added durability.
- Meets RMA **oil and heat resistant** standards.
- Meets RMA **static conductivity** requirements.

Recommended Sheaves

Hi-Power Multi-Duty Sheaves

Notes

Additional sizes from 42 inches to 660 inches are available upon request and require minimum order quantities of 87 belts per size +/- 10%. Contact Customer Service for availability and setup.



Product No. Series 8819

9/16" Diameter

Part No.	Product No.	Inside Length (In.)
9 X 41 3/8 PR	8819-0010	41 3/8
9 X 54 PR	8819-0011	54
9 X 90 PR	8819-0012	90
9 X 101 PR	8819-0029	101
9 X 112 PR	8819-0013	112
9 X 120 PR	8819-0014	120
9 X 128 PR	8819-0015	128
9 X 129 3/4 PR	8819-0016	129 3/4
9 X 135 PR	8819-0017	135
9 X 144 PR	8819-0018	144
9 X 148 PR	8819-0019	148
9 X 155 PR	8819-0020	155
9 X 166 PR	8819-0021	166
9 X 172 PR	8819-0022	172
9 X 176 PR	8819-0023	176
9 X 190 PR	8819-0024	190

Part No.	Product No.	Inside Length (In.)
9 X 200 PR	8819-0008	200
9 X 210 PR	8819-0007	210
9 X 233 PR	8819-0002	233
9 X 250 PR	8819-0000	250
9 X 270 PR	8819-0001	270
9 X 308 PR	8819-0003	308
9 X 331 PR	8819-0004	331
9 X 345 PR	8819-0009	345
9 X 386 PR	8819-0006	386
9 X 416 PR	8819-0025	416
9 X 447 PR	8819-0026	447
9 X 465 PR	8819-0027	465
9 X 500 PR	8819-0030	500
9 X 564 PR	8819-0005	564
9 X 600 PR	8819-0031	600
9 X 660 PR	8819-0028	660



Round Endless Belts

These belts are designed for 1/4 turn or twisted drives where more than an O-ring is required.

Markets/Applications

Round Endless belts are ideal for 1/4 turn or twisted drives, serpentine drives, power turn and line shaft conveyors and commercial sewing machines.

Features/Advantages

- Minimal stretch for minimum take-up requirements.
- No splice for added durability.

Recommended Sheaves

Contact the Gates Made-To-Order Metals Team.

Notes

Standard-stocked Round Endless belts are footnoted. All others are Made-To-Order and may require minimum order quantities. Contact Customer Service for availability.



Product No. Series 8820

1/4" Diameter

Minimum order quantity for 1/4" Round Endless Belts is 180 belts per size +/- 10%.

Part No.	Product No.	Inside Length (In.)
4 X 33 RE BELT	8820-0499	33
4 X 34 RE BELT	8820-0503	34
4 X 35 RE BELT	8820-0507	35
4 X 36 RE BELT	8820-0511	36
4 X 37 RE BELT	8820-0515	37
4 X 38 RE BELT	8820-0519	38
4 X 39 RE BELT	8820-0523	39
4 X 40 RE BELT	8820-0527	40
4 X 41 RE BELT	8820-0531	41
4 X 42 RE BELT	8820-0535	42
4 X 43 RE BELT	8820-0539	43
4 X 44 RE BELT	8820-0543	44
4 X 45 RE BELT	8820-0547	45
4 X 46 RE BELT	8820-0551	46
4 X 47 RE BELT	8820-0555	47
4 X 48 RE BELT	8820-0559	48
4 X 49 RE BELT	8820-0563	49
4 X 50 RE BELT	8820-0567	50
4 X 51 RE BELT	8820-0571	51
4 X 52 RE BELT	8820-0575	52
4 X 53 RE BELT	8820-0579	53
4 X 54 RE BELT	8820-0583	54
4 X 55 RE BELT	8820-0587	55
4 X 56 RE BELT	8820-0591	56
4 X 57 RE BELT	8820-0595	57
4 X 58 RE BELT	8820-0599	58
4 X 59 RE BELT	8820-0603	59

Part No.	Product No.	Inside Length (In.)
4 X 60 RE BELT	8820-0607	60
4 X 61 RE BELT	8820-0611	61
4 X 62 RE BELT	8820-0615	62
4 X 63 RE BELT	8820-0619	63
4 X 64 RE BELT	8820-0623	64
4 X 65 RE BELT	8820-0627	65
4 X 66 RE BELT	8820-0631	66
4 X 67 RE BELT	8820-0635	67
4 X 68 RE BELT	8820-0639	68
4 X 69 RE BELT	8820-0643	69
4 X 70 RE BELT	8820-0647	70
4 X 71 RE BELT	8820-0651	71
4 X 72 RE BELT	8820-0655	72
4 X 73 RE BELT	8820-0659	73
4 X 74 RE BELT	8820-0663	74
4 X 75 RE BELT	8820-0667	75
4 X 76 RE BELT	8820-0671	76
4 X 77 RE BELT	8820-0675	77
4 X 78 RE BELT	8820-0679	78
4 X 79 RE BELT	8820-0683	79
4 X 80 RE BELT	8820-0687	80
4 X 81 RE BELT	8820-0691	81
4 X 82 RE BELT	8820-0695	82
4 X 83 RE BELT	8820-0699	83
4 X 84 RE BELT	8820-0703	84
4 X 85 RE BELT	8820-0707	85

5/16" Diameter

Minimum order quantity for 5/16" Round Endless Belts is 165 belts per size +/- 10%.

Part No.	Product No.	Inside Length (In.)
5 X 33 RE BELT	8820-0838	33
¹⁶ 5 X 33 1/2 RE BELT	8820-0840	33 1/2
¹⁶ 5 X 34 RE BELT	8820-0842	34
5 X 35 RE BELT	8820-0846	35
5 X 36 RE BELT	8820-0850	36
5 X 37 RE BELT	8820-0854	37
5 X 38 RE BELT	8820-0858	38
5 X 39 RE BELT	8820-0862	39
5 X 40 RE BELT	8820-0866	40

Part No.	Product No.	Inside Length (In.)
5 X 41 RE BELT	8820-0870	41
5 X 42 RE BELT	8820-0874	42
5 X 43 RE BELT	8820-0878	43
5 X 44 RE BELT	8820-0882	44
5 X 45 RE BELT	8820-0886	45
5 X 46 RE BELT	8820-0890	46
5 X 47 RE BELT	8820-0894	47
5 X 48 RE BELT	8820-0898	48
5 X 49 RE BELT	8820-0902	49

¹⁶ Stocked and minimum order quantities are not required. All others are Made-To-Order and lead times and minimum production quantities may apply. Contact Customer Service for availability.

Round Endless Belts

Product No. Series 8820 (continued)

5/16" Diameter (continued)

Part No.	Product No.	Inside Length (In.)
5 X 50 RE BELT	8820-0906	50
5 X 51 RE BELT	8820-0910	51
5 X 52 RE BELT	8820-0914	52
5 X 53 RE BELT	8820-0918	53
5 X 54 RE BELT	8820-0922	54
5 X 55 RE BELT	8820-0926	55
5 X 56 RE BELT	8820-0930	56
5 X 57 RE BELT	8820-0934	57
5 X 58 RE BELT	8820-0938	58
5 X 59 RE BELT	8820-0942	59
5 X 60 RE BELT	8820-0946	60
5 X 61 RE BELT	8820-0950	61
5 X 62 RE BELT	8820-0954	62
5 X 63 RE BELT	8820-0958	63
5 X 64 RE BELT	8820-0962	64
5 X 65 RE BELT	8820-0966	65
5 X 66 RE BELT	8820-0970	66
5 X 67 RE BELT	8820-0974	67
5 X 68 RE BELT	8820-0978	68
5 X 69 RE BELT	8820-0982	69
5 X 70 RE BELT	8820-0986	70

Part No.	Product No.	Inside Length (In.)
5 X 71 RE BELT	8820-0990	71
5 X 72 RE BELT	8820-0994	72
5 X 73 RE BELT	8820-0998	73
5 X 74 RE BELT	8820-1002	74
5 X 75 RE BELT	8820-1006	75
5 X 76 RE BELT	8820-1010	76
5 X 77 RE BELT	8820-1014	77
5 X 78 RE BELT	8820-1018	78
5 X 79 RE BELT	8820-1022	79
5 X 80 RE BELT	8820-1026	80
5 X 81 RE BELT	8820-1030	81
5 X 82 RE BELT	8820-1034	82
5 X 83 RE BELT	8820-1038	83
5 X 84 RE BELT	8820-1042	84
5 X 85 RE BELT	8820-1046	85
5 X 86 RE BELT	8820-1050	86
5 X 87 RE BELT	8820-1054	87
5 X 88 RE BELT	8820-1058	88
5 X 89 RE BELT	8820-1062	89
5 X 90 RE BELT	8820-1066	90

3/8" Diameter

Minimum order quantity for 3/8" Round Endless Belts is 139 belts per size +/- 10%.

Part No.	Product No.	Inside Length (In.)
6 X 33 RE BELT	8820-1222	33
¹⁶ 6 X 33 1/2 RE BELT	8820-1225	33 1/2
¹⁶ 6 X 34 RE BELT	8820-1226	34
6 X 35 RE BELT	8820-1230	35
¹⁶ 6 X 36 RE BELT	8820-1234	36
6 X 37 RE BELT	8820-1238	37
6 X 38 RE BELT	8820-1242	38
6 X 39 RE BELT	8820-1246	39
6 X 40 RE BELT	8820-1250	40
6 X 41 RE BELT	8820-1254	41
6 X 42 RE BELT	8820-1258	42
6 X 43 RE BELT	8820-1262	43
6 X 44 RE BELT	8820-1266	44
6 X 45 RE BELT	8820-1270	45
6 X 46 RE BELT	8820-1274	46
6 X 47 RE BELT	8820-1278	47
6 X 48 RE BELT	8820-1282	48
6 X 49 RE BELT	8820-1286	49
6 X 50 RE BELT	8820-1290	50
6 X 51 RE BELT	8820-1294	51
6 X 52 RE BELT	8820-1298	52
6 X 53 RE BELT	8820-1302	53
6 X 54 RE BELT	8820-1306	54
6 X 55 RE BELT	8820-1310	55
6 X 56 RE BELT	8820-1314	56
6 X 57 RE BELT	8820-1318	57
6 X 58 RE BELT	8820-1322	58
6 X 59 RE BELT	8820-1326	59
6 X 60 RE BELT	8820-1330	60
6 X 61 RE BELT	8820-1334	61
6 X 62 RE BELT	8820-1338	62
6 X 63 RE BELT	8820-1342	63
6 X 64 RE BELT	8820-1346	64
6 X 65 RE BELT	8820-1350	65
6 X 66 RE BELT	8820-1354	66

Part No.	Product No.	Inside Length (In.)
6 X 67 RE BELT	8820-1358	67
6 X 68 RE BELT	8820-1362	68
6 X 69 RE BELT	8820-1366	69
6 X 70 RE BELT	8820-1370	70
6 X 71 RE BELT	8820-1374	71
6 X 72 RE BELT	8820-1378	72
6 X 73 RE BELT	8820-1382	73
6 X 74 RE BELT	8820-1386	74
6 X 75 RE BELT	8820-1390	75
6 X 76 RE BELT	8820-1394	76
6 X 77 RE BELT	8820-1398	77
6 X 78 RE BELT	8820-1402	78
6 X 79 RE BELT	8820-1406	79
6 X 80 RE BELT	8820-1410	80
6 X 81 RE BELT	8820-1414	81
6 X 82 RE BELT	8820-1418	82
6 X 83 RE BELT	8820-1422	83
6 X 84 RE BELT	8820-1426	84
6 X 85 RE BELT	8820-1430	85
6 X 86 RE BELT	8820-1434	86
6 X 87 RE BELT	8820-1438	87
6 X 88 RE BELT	8820-1442	88
¹⁶ 6 X 89 RE BELT	8820-1446	89
6 X 90 RE BELT	8820-1460	90
6 X 91 RE BELT	8820-1454	91
6 X 92 RE BELT	8820-1458	92
6 X 93 RE BELT	8820-1462	93
6 X 94 RE BELT	8820-1466	94
6 X 95 RE BELT	8820-1470	95
¹⁶ 6 X 96 RE BELT	8820-1474	96
¹⁶ 6 X 97 RE BELT	8820-1478	97
¹⁶ 6 X 98 RE BELT	8820-1486	98
6 X 99 RE BELT	8820-148	99
6 X 100 RE BELT	8820-1490	100
6 X 101 RE BELT	8820-1494	101

¹⁶ Stocked and minimum order quantities are not required. All others are Made-To-Order and lead times and minimum production quantities may apply. Contact Customer Service for availability.



Round Endless Belts

Product No. Series 8820 (continued)

3/8" Diameter (continued)

Part No.	Product No.	Inside Length (In.)
6 X 102 RE BELT	8820-1498	102
6 X 103 RE BELT	8820-1502	103
6 X 104 RE BELT	8820-1506	104
6 X 105 RE BELT	8820-1510	105
6 X 106 RE BELT	8820-1514	106
6 X 107 RE BELT	8820-1518	107
6 X 108 RE BELT	8820-1522	108
6 X 109 RE BELT	8820-1526	109
6 X 110 RE BELT	8820-1530	110
6 X 111 RE BELT	8820-1534	111

Part No.	Product No.	Inside Length (In.)
6 X 112 RE BELT	8820-1538	112
6 X 113 RE BELT	8820-1542	113
6 X 114 RE BELT	8820-1546	114
6 X 115 RE BELT	8820-1550	115
6 X 116 RE BELT	8820-1554	116
6 X 117 RE BELT	8820-1558	117
6 X 118 RE BELT	8820-1562	118
6 X 119 RE BELT	8820-1566	119
6 X 120 RE BELT	8820-1570	120

7/16" Diameter

Minimum order quantity for 7/16" Round Endless Belts is 115 belts per size +/- 10%.

Part No.	Product No.	Inside Length (In.)
7 X 33 RE BELT	8820-1831	33
¹⁶ 7 X 34 RE BELT	8820-1835	34
7 X 35 RE BELT	8820-1839	35
¹⁶ 7 X 36 RE BELT	8820-1843	36
7 X 37 RE BELT	8820-1847	37
7 X 38 RE BELT	8820-1851	38
7 X 39 RE BELT	8820-1859	39
7 X 40 RE BELT	8820-1841	40
7 X 41 RE BELT	8820-1863	41
7 X 42 RE BELT	8820-1867	42
7 X 43 RE BELT	8820-1871	43
7 X 44 RE BELT	8820-1875	44
7 X 45 RE BELT	8820-1879	45
7 X 46 RE BELT	8820-1883	46
7 X 47 RE BELT	8820-1887	47
7 X 48 RE BELT	8820-1891	48
7 X 49 RE BELT	8820-1895	49
7 X 50 RE BELT	8820-1899	50
7 X 51 RE BELT	8820-1903	51
7 X 52 RE BELT	8820-1907	52
7 X 53 RE BELT	8820-1911	53
7 X 54 RE BELT	8820-1915	54
7 X 55 RE BELT	8820-1919	55
7 X 56 RE BELT	8820-1923	56
7 X 57 RE BELT	8820-1927	57
7 X 58 RE BELT	8820-1931	58
7 X 59 RE BELT	8820-1935	59
7 X 60 RE BELT	8820-1939	60
7 X 61 RE BELT	8820-1943	61
7 X 62 RE BELT	8820-1947	62
7 X 63 RE BELT	8820-1951	63
7 X 64 RE BELT	8820-1955	64
7 X 65 RE BELT	8820-1959	65
7 X 66 RE BELT	8820-1963	66
7 X 67 RE BELT	8820-1967	67
7 X 68 RE BELT	8820-1971	68
7 X 69 RE BELT	8820-1975	69
7 X 70 RE BELT	8820-1979	70

Part No.	Product No.	Inside Length (In.)
7 X 71 RE BELT	8820-1983	71
7 X 72 RE BELT	8820-1987	72
7 X 73 RE BELT	8820-1991	73
7 X 74 RE BELT	8820-1995	74
7 X 75 RE BELT	8820-1999	75
7 X 76 RE BELT	8820-2003	76
7 X 77 RE BELT	8820-2007	77
¹⁶ 7 X 77 1/4 RE BELT	8820-2008	77 1/4
7 X 78 RE BELT	8820-2011	78
7 X 79 RE BELT	8820-2015	79
7 X 80 RE BELT	8820-2019	80
7 X 81 RE BELT	8820-2023	81
7 X 82 RE BELT	8820-2027	82
7 X 83 RE BELT	8820-2031	83
7 X 84 RE BELT	8820-2035	84
7 X 85 RE BELT	8820-2039	85
7 X 86 RE BELT	8820-2043	86
7 X 87 RE BELT	8820-2047	87
7 X 88 RE BELT	8820-2051	88
7 X 89 RE BELT	8820-2055	89
7 X 90 RE BELT	8820-2059	90
7 X 91 RE BELT	8820-2063	91
7 X 92 RE BELT	8820-2067	92
7 X 93 RE BELT	8820-2071	93
7 X 94 RE BELT	8820-2075	94
7 X 95 RE BELT	8820-2079	95
7 X 96 RE BELT	8820-2083	96
7 X 97 RE BELT	8820-2087	97
7 X 98 RE BELT	8820-2091	98
7 X 99 RE BELT	8820-2095	99
7 X 100 RE BELT	8820-2099	100
7 X 101 RE BELT	8820-2103	101
7 X 102 RE BELT	8820-2107	102
7 X 103 RE BELT	8820-2111	103
7 X 104 RE BELT	8820-2115	104
7 X 105 RE BELT	8820-2119	105
7 X 106 RE BELT	8820-2123	106

¹⁶ Stocked and minimum order quantities are not required. All others are Made-To-Order and lead times and minimum production quantities may apply. Contact Customer Service for availability.

Round Endless Belts

Product No. Series 8820 (continued)

1/2" Diameter

Minimum order quantity for 1/2" Round Endless Belts is 95 belts per size +/- 10%.

Part No.	Product No.	Inside Length (In.)
8 X 53 RE BELT	8820-2685	53
8 X 54 RE BELT	8820-2689	54
8 X 55 RE BELT	8820-2693	55
8 X 56 RE BELT	8820-2697	56
8 X 57 RE BELT	8820-2701	57
8 X 58 RE BELT	8820-2705	58
8 X 59 RE BELT	8820-2709	59
8 X 61 RE BELT	8820-2717	61
8 X 62 RE BELT	8820-2721	62
8 X 63 RE BELT	8820-2725	63
8 X 64 RE BELT	8820-2729	64
8 X 65 RE BELT	8820-2733	65
8 X 66 RE BELT	8820-2737	66
8 X 67 RE BELT	8820-2741	67
8 X 68 RE BELT	8820-2745	68
8 X 69 RE BELT	8820-2749	69
8 X 70 RE BELT	8820-2753	70
8 X 71 RE BELT	8820-2757	71
8 X 72 RE BELT	8820-2761	72
8 X 73 RE BELT	8820-2765	73
8 X 74 RE BELT	8820-2769	74
8 X 75 RE BELT	8820-2773	75
8 X 76 RE BELT	8820-2777	76
8 X 77 RE BELT	8820-2781	77
8 X 78 RE BELT	8820-2785	78
8 X 79 RE BELT	8820-2789	79
8 X 80 RE BELT	8820-2793	80

Part No.	Product No.	Inside Length (In.)
8 X 81 RE BELT	8820-2797	81
8 X 82 RE BELT	8820-2801	82
8 X 83 RE BELT	8820-2805	83
8 X 84 RE BELT	8820-2809	84
8 X 85 RE BELT	8820-2813	85
8 X 86 RE BELT	8820-2817	86
8 X 87 RE BELT	8820-2821	87
8 X 88 RE BELT	8820-2825	88
8 X 89 RE BELT	8820-2829	89
8 X 90 RE BELT	8820-2833	90
8 X 91 RE BELT	8820-2837	91
8 X 92 RE BELT	8820-2841	92
8 X 93 RE BELT	8820-2845	93
8 X 94 RE BELT	8820-2849	94
8 X 95 RE BELT	8820-2853	95
8 X 96 RE BELT	8820-2857	96
8 X 97 RE BELT	8820-2861	97
8 X 98 RE BELT	8820-2865	98
8 X 99 RE BELT	8820-2869	99
8 X 100 RE BELT	8820-2873	100
8 X 101 RE BELT	8820-2877	101
8 X 102 RE BELT	8820-2881	102
8 X 103 RE BELT	8820-2885	103
8 X 104 RE BELT	8820-2889	104
8 X 105 RE BELT	8820-2893	105
8 X 106 RE BELT	8820-2897	106

9/16" Diameter

Minimum order quantity for 9/16" Round Endless Belts is 87 belts per size +/- 10%.

Part No.	Product No.	Inside Length (In.)
¹⁶ 9 X 41 3/8 RE BELT	8820-3217	41 3/8
9 X 49 RE BELT	8820-3239	49
9 X 50 RE BELT	8820-3242	50
9 X 51 RE BELT	8820-3245	51
9 X 52 RE BELT	8820-3248	52
9 X 53 RE BELT	8820-3251	53
¹⁶ 9 X 54 RE BELT	8820-3254	54
9 X 55 RE BELT	8820-3257	55
9 X 56 RE BELT	8820-3260	56
9 X 57 RE BELT	8820-3263	57
9 X 58 RE BELT	8820-3266	58
9 X 59 RE BELT	8820-3269	59
9 X 60 RE BELT	8820-3272	60
9 X 61 RE BELT	8820-3275	61
9 X 62 RE BELT	8820-3278	62
9 X 63 RE BELT	8820-3281	63
9 X 64 RE BELT	8820-3284	64
9 X 65 RE BELT	8820-3287	65
9 X 66 RE BELT	8820-3290	66
9 X 67 RE BELT	8820-3293	67
9 X 68 RE BELT	8820-3296	68
9 X 69 RE BELT	8820-3299	69
9 X 70 RE BELT	8820-3302	70
9 X 71 RE BELT	8820-3305	71
9 X 72 RE BELT	8820-3308	72
9 X 73 RE BELT	8820-3311	73
9 X 74 RE BELT	8820-3314	74
9 X 75 RE BELT	8820-3317	75
9 X 76 RE BELT	8820-3320	76

Part No.	Product No.	Inside Length (In.)
9 X 77 RE BELT	8820-3323	77
9 X 78 RE BELT	8820-3326	78
9 X 79 RE BELT	8820-3329	79
9 X 80 RE BELT	8820-3332	80
9 X 81 RE BELT	8820-3335	81
9 X 82 RE BELT	8820-3338	82
9 X 83 RE BELT	8820-3341	83
9 X 84 RE BELT	8820-3344	84
9 X 85 RE BELT	8820-3347	85
9 X 86 RE BELT	8820-3350	86
9 X 87 RE BELT	8820-3353	87
9 X 88 RE BELT	8820-3356	88
9 X 89 RE BELT	8820-3359	89
¹⁶ 9 X 90 RE BELT	8820-3362	90
9 X 91 RE BELT	8820-3365	91
9 X 92 RE BELT	8820-3368	92
9 X 93 RE BELT	8820-3371	93
9 X 94 RE BELT	8820-3374	94
9 X 95 RE BELT	8820-3377	95
9 X 96 RE BELT	8820-3380	96
9 X 97 RE BELT	8820-3383	97
9 X 98 RE BELT	8820-3386	98
9 X 99 RE BELT	8820-3389	99
9 X 100 RE BELT	8820-3392	100
9 X 101 RE BELT	8820-3395	101
9 X 102 RE BELT	8820-3398	102
9 X 103 RE BELT	8820-3401	103
9 X 104 RE BELT	8820-3404	104
9 X 105 RE BELT	8820-3407	105

¹⁶ Stocked and minimum order quantities are not required. All others are Made-To-Order and lead times and minimum production quantities may apply. Contact Customer Service for availability.



Round Endless Belts

Product No. Series 8820 (continued)

9/16" Diameter (continued)

Part No.	Product No.	Inside Length (In.)
9 X 106 RE BELT	8820-3485	106
9 X 107 RE BELT	8820-3413	107
9 X 108 RE BELT	8820-3416	108
9 X 109 RE BELT	8820-3419	109
9 X 110 RE BELT	8820-3422	110
9 X 111 RE BELT	8820-3425	111
¹⁶ 9 X 112 RE BELT	8820-3428	112
9 X 113 RE BELT	8820-3429	113
9 X 114 RE BELT	8820-3434	114
9 X 115 RE BELT	8820-3437	115
9 X 116 RE BELT	8820-3440	116
9 X 118 RE BELT	8820-3446	118
9 X 119 RE BELT	8820-3449	119
¹⁶ 9 X 120 RE BELT	8820-3452	120
¹⁶ 9 X 128 RE BELT	8820-3488	128
¹⁶ 9 X 1293/4RE	8820-3439	129 3/4
¹⁶ 9 X 135 RE BELT	8820-3489	135
¹⁶ 9 X 144 RE BELT	8820-3458	144
¹⁶ 9 X 148 RE BELT	8820-3490	148
¹⁶ 9 X 155 RE BELT	8820-3460	155
¹⁶ 9 X 166 RE BELT	8820-3491	166
¹⁶ 9 X 172 RE BELT	8820-4281	172
¹⁶ 9 X 176 RE BELT	8820-3492	176
¹⁶ 9 X 190 RE BELT	8820-3493	190
¹⁶ 9 X 200 RE BELT	8820-3469	200
¹⁶ 9 X 210 RE BELT	8820-3486	210
¹⁶ 9 X 233 RE BELT	8820-3470	233
¹⁶ 9 X 250 RE BELT	8820-3494	250
¹⁶ 9 X 270 RE BELT	8820-3471	270
¹⁶ 9 X 308 RE BELT	8820-3472	308
¹⁶ 9 X 331 RE BELT	8820-3473	331
¹⁶ 9 X 345 RE BELT	8820-3495	345
¹⁶ 9 X 386 RE BELT	8820-3474	386
¹⁶ 9 X 416 RE BELT	8820-3475	416
¹⁶ 9 X 447 RE BELT	8820-3484	447
¹⁶ 9 X 465 RE BELT	8820-3476	465
¹⁶ 9 X 564 RE BELT	8820-3477	564
¹⁶ 9 X 660 RE BELT	8820-3478	660

¹⁶ Stocked and minimum order quantities are not required. All others are Made-To-Order and lead times and minimum production quantities may apply. Contact Customer Service for availability.



Unique 60° angle polyurethane construction transmits greater loads at higher speeds in less space than conventional V-belts.

Markets/Applications

A partial listing of applications include machine tools, computer peripherals, medical equipment, library equipment, small appliances, blower drives and woodworking machines.

Features/Advantages

- **High Modulus Polyurethane** compound resists fatigue, wear, ozone, and most environmental conditions.
- Precise casting method eliminates layers and overlaps for **smooth running** and **low vibration**.
- **Ribbed backing** provides greater lateral stability and relieves bending stress.
- Working temperature range: -65°F to +180°F (-54°C to +85°C).


Recommended Sheaves

Polyflex Sheaves

Notes

Polyflex Belts are available in 3M, 5M, 7M, and 11M cross sections.

Matched sets may have a manufacturing lead time. Contact Customer Service for details.



Product No. Series 8901

3M

Nominal Top Width 1/8"

Part No.	Product No.	Effective Length (In.)
3M180	8901-0180	7.09
3M185	8901-0185	7.28
3M190	8901-0190	7.48
3M195	8901-0195	7.68
3M200	8901-0200	7.87
3M206	8901-0206	8.11
3M212	8901-0212	8.35
3M218	8901-0218	8.58
3M224	8901-0224	8.82
3M230	8901-0230	9.06
3M236	8901-0236	9.29
3M243	8901-0243	9.57
3M250	8901-0250	9.84
3M258	8901-0258	10.16
3M265	8901-0265	10.43
3M272	8901-0272	10.71
3M280	8901-0280	11.02
3M290	8901-0290	11.42
3M300	8901-0300	11.81
3M307	8901-0307	12.09
3M315	8901-0315	12.40
3M325	8901-0325	12.80
3M335	8901-0335	13.19
3M345	8901-0345	13.58
3M355	8901-0355	13.98
3M365	8901-0365	14.37

Part No.	Product No.	Effective Length (In.)
3M375	8901-0375	14.76
3M387	8901-0387	15.24
3M400	8901-0400	15.75
3M412	8901-0412	16.22
3M425	8901-0425	16.73
3M437	8901-0437	17.20
3M450	8901-0450	17.72
3M462	8901-0462	18.19
3M475	8901-0475	18.70
3M487	8901-0487	19.17
3M500	8901-0500	19.69
3M515	8901-0515	20.28
3M530	8901-0530	20.87
3M545	8901-0545	21.46
3M560	8901-0560	22.05
3M580	8901-0580	22.83
3M600	8901-0600	23.62
3M615	8901-0615	24.21
3M630	8901-0630	24.80
3M650	8901-0650	25.59
3M670	8901-0670	26.38
3M690	8901-0690	27.17
3M710	8901-0710	27.95
3M730	8901-0730	28.74
3M750	8901-0750	29.53

Product No. Series 8902

5M

Part No.	Product No.	Effective Length (in.)
5M280	8902-0280	11.02
5M290	8902-0290	11.42
5M300	8902-0300	11.81
5M307	8902-0307	12.09
5M315	8902-0315	12.40
5M325	8902-0325	12.80
5M335	8902-0335	13.19
5M345	8902-0345	13.58
5M355	8902-0355	13.98
5M365	8902-0365	14.37
5M375	8902-0375	14.76
5M387	8902-0387	15.24
5M400	8902-0400	15.75
5M412	8902-0412	16.22
5M425	8902-0425	16.73
5M437	8902-0437	17.20
5M450	8902-0450	17.72
5M462	8902-0462	18.19
5M475	8902-0475	18.70
5M487	8902-0487	19.17
5M500	8902-0500	19.69
5M515	8902-0515	20.28
5M530	8902-0530	20.87
5M545	8902-0545	21.46
5M560	8902-0560	22.05
5M580	8902-0580	22.83
5M600	8902-0600	23.62
5M615	8902-0615	24.21
5M630	8902-0630	24.80
5M650	8902-0650	25.59
5M670	8902-0670	26.38

Nominal Top Width 3/16"



Part No.	Product No.	Effective Length (in.)
5M690	8902-0690	27.17
5M710	8902-0710	27.95
5M730	8902-0730	28.74
5M750	8902-0750	29.53
5M775	8902-0775	30.51
5M800	8902-0800	31.50
5M825	8902-0825	32.48
5M850	8902-0850	33.46
5M875	8902-0875	34.45
5M900	8902-0900	35.43
5M925	8902-0925	36.42
5M950	8902-0950	37.40
5M975	8902-0975	38.39
5M1000	8902-1000	39.37
5M1030	8902-1030	40.55
5M1060	8902-1060	41.73
5M1090	8902-1090	42.91
5M1120	8902-1120	44.09
5M1150	8902-1150	45.28
5M1180	8902-1180	46.46
5M1220	8902-1220	48.03
5M1250	8902-1250	49.21
5M1280	8902-1280	50.39
5M1320	8902-1320	51.97
5M1360	8902-1360	53.54
5M1400	8902-1400	55.12
5M1450	8902-1450	57.09
5M1500	8902-1500	59.06
5M1600	8902-1600	62.99
5M1650	8902-1650	64.96
5M1850	8902-1850	72.83

Product No. Series 8903

7M

Part No.	Product No.	Effective Length (in.)
7M410	8903-0410	16.14
7M500	8903-0500	19.69
7M515	8903-0515	20.28
7M530	8903-0530	20.87
7M545	8903-0545	21.46
7M560	8903-0560	22.05
7M580	8903-0580	22.83
7M600	8903-0600	23.62
7M615	8903-0615	24.21
7M630	8903-0630	24.80
7M650	8903-0650	25.59
7M670	8903-0670	26.38
7M690	8903-0690	27.17
7M710	8903-0710	27.95
7M730	8903-0730	28.74
7M750	8903-0750	29.53
7M775	8903-0775	30.51
7M800	8903-0800	31.50
7M825	8903-0825	32.48
7M850	8903-0850	33.46
7M875	8903-0875	34.45
7M900	8903-0900	35.43
7M925	8903-0925	36.42

Nominal Top Width 9/32"



Part No.	Product No.	Effective Length (in.)
7M950	8903-0950	37.40
7M975	8903-0975	38.39
7M1000	8903-1000	39.37
7M1030	8903-1030	40.55
7M1060	8903-1060	41.73
7M1090	8903-1090	42.91
7M1120	8903-1120	44.09
7M1150	8903-1150	45.28
7M1180	8903-1180	46.46
7M1220	8903-1220	48.03
7M1250	8903-1250	49.21
7M1280	8903-1280	50.39
7M1320	8903-1320	51.97
7M1360	8903-1360	53.54
7M1400	8903-1400	55.12
7M1450	8903-1450	57.09
7M1500	8903-1500	59.06
7M1550	8903-1550	61.02
7M1600	8903-1600	62.99
7M1650	8903-1650	64.96
7M1700	8903-1700	66.93
7M1750	8903-1750	68.90
7M1800	8903-1800	70.87

Product No. Series 8903 (continued)

7M (continued)

Part No.	Product No.	Effective Length (In.)
7M1850	8903-1850	72.83
7M1900	8903-1900	74.80
7M1950	8903-1950	76.77
7M2000	8903-2000	78.74
7M2060	8903-2060	81.10

Part No.	Product No.	Effective Length (In.)
7M2120	8903-2120	83.46
7M2180	8903-2180	85.83
7M2240	8903-2240	88.19
7M2300	8903-2300	90.55

Nominal Top Width 7/16"



Product No. Series 8904

11M

Part No.	Product No.	Effective Length (In.)
11M710	8904-0710	27.95
11M730	8904-0730	28.74
11M750	8904-0750	29.53
11M775	8904-0775	30.51
11M800	8904-0800	31.50
11M825	8904-0825	32.48
11M850	8904-0850	33.46
11M875	8904-0875	34.45
11M900	8904-0900	35.43
11M925	8904-0925	36.42
11M950	8904-0950	37.40
11M975	8904-0975	38.39
11M1000	8904-1000	39.37
11M1030	8904-1030	40.55
11M1060	8904-1060	41.73
11M1090	8904-1090	42.91
11M1120	8904-1120	44.09
11M1150	8904-1150	45.28
11M1180	8904-1180	46.46
11M1220	8904-1220	48.03
11M1250	8904-1250	49.21

Part No.	Product No.	Effective Length (In.)
11M1280	8904-1280	50.39
11M1320	8904-1320	51.97
11M1360	8904-1360	53.54
11M1400	8904-1400	55.12
11M1450	8904-1450	57.09
11M1500	8904-1500	59.06
11M1550	8904-1550	61.02
11M1600	8904-1600	62.99
11M1650	8904-1650	64.96
11M1700	8904-1700	66.93
11M1750	8904-1750	68.90
11M1800	8904-1800	70.87
11M1850	8904-1850	72.83
11M1900	8904-1900	74.80
11M1950	8904-1950	76.77
11M2000	8904-2000	78.74
11M2060	8904-2060	81.10
11M2120	8904-2120	83.46
11M2180	8904-2180	85.83
11M2240	8904-2240	88.19
11M2300	8904-2300	90.55

Polyflex® JB® Belts

Joined Band belt construction provides increased belt stability, preventing belts from turning over or from coming off of the drive.

Unique 60° angle polyurethane construction transmits greater loads at higher speeds in less space than conventional V-belts.

Markets/Applications

Use in place of Polyflex singles on drives requiring joined sets. A partial listing of applications includes machine tools, computer peripherals, medical equipment, library equipment, small appliances, blower drives and dough mixers.

Features/Advantages

- **High Modulus Polyurethane** compound resists fatigue, wear, ozone, and most environmental conditions.
- Precise casting method eliminates layers and overlaps for **smooth running** and **low vibration**.
- **Ribbed backing** provides greater lateral stability and relieves bending stress.
- Working temperature range: -65°F to +180°F (-54°C to +85°C).
- **Joined belt construction** provides high stability, preventing belts from turning over or coming off of the drive.

Recommended Sheaves


Polyflex Sheaves

Notes

Polyflex JB Belts are available in 3M, 5M, 7M, and 11M cross sections.

The Polyflex JB belt part number is comprised of the number of belt strands, cross section, effective length and the "JB" signifying joined band construction. For example; part number 3/5M1000JB represents 3 strands joined together, 5mm top width for each belt strand, effective length of 1000mm and joined band (JB) construction.

Manufacturing lead times may apply to matched sets and to rib configurations other than those listed. Minimum order quantities do not apply for belt lengths listed. Contact Customer Service for details.



Product No. Series 8911

3M

Nominal Strand Width 1/8"



Part No.	Product No.	Effective Length (In.)
2/3M175JB	8911-2175	6.74
3/3M175JB	8911-3175	6.74
2/3M180JB	8911-2180	6.94
3/3M180JB	8911-3180	6.94
2/3M185JB	8911-2185	7.13
3/3M185JB	8911-3185	7.13
2/3M190JB	8911-2190	7.33
3/3M190JB	8911-3190	7.33
2/3M195JB	8911-2195	7.53
3/3M195JB	8911-3195	7.53
2/3M200JB	8911-2200	7.72
3/3M200JB	8911-3200	7.72
2/3M206JB	8911-2206	7.96
3/3M206JB	8911-3206	7.96
2/3M212JB	8911-2212	8.20
3/3M212JB	8911-3212	8.20
2/3M218JB	8911-2218	8.43
3/3M218JB	8911-3218	8.43
2/3M224JB	8911-2224	8.67
3/3M224JB	8911-3224	8.67
2/3M230JB	8911-2230	8.91
3/3M230JB	8911-3230	8.91
2/3M236JB	8911-2236	9.14
3/3M236JB	8911-3236	9.14
2/3M243JB	8911-2243	9.42
3/3M243JB	8911-3243	9.42
2/3M250JB	8911-2250	9.69
3/3M250JB	8911-3250	9.69

Part No.	Product No.	Effective Length (In.)
2/3M258JB	8911-2258	10.01
3/3M258JB	8911-3258	10.01
2/3M265JB	8911-2265	10.28
3/3M265JB	8911-3265	10.28
2/3M272JB	8911-2272	10.56
3/3M272JB	8911-3272	10.56
2/3M280JB	8911-2280	10.87
3/3M280JB	8911-3280	10.87
2/3M290JB	8911-2290	11.27
3/3M290JB	8911-3290	11.27
2/3M300JB	8911-2300	11.66
3/3M300JB	8911-3300	11.66
2/3M307JB	8911-2307	11.94
3/3M307JB	8911-3307	11.94
2/3M315JB	8911-2315	12.25
3/3M315JB	8911-3315	12.25
2/3M325JB	8911-2325	12.65
3/3M325JB	8911-3325	12.65
2/3M335JB	8911-2335	13.04
3/3M335JB	8911-3335	13.04
2/3M345JB	8911-2345	13.43
3/3M345JB	8911-3345	13.43
2/3M350JB	8911-2350	13.63
3/3M350JB	8911-3350	13.63
2/3M355JB	8911-2355	13.83
3/3M355JB	8911-3355	13.83
2/3M365JB	8911-2365	14.22
3/3M365JB	8911-3365	14.22



Product No. Series 8911 (continued)

3M (continued)

Part No.	Product No.	Effective Length (In.)
2/3M375JB	8911-2375	14.61
3/3M375JB	8911-3375	14.61
2/3M387JB	8911-2387	15.09
3/3M387JB	8911-3387	15.09
2/3M400JB	8911-2400	15.60
3/3M400JB	8911-3400	15.60
2/3M412JB	8911-2412	16.07
3/3M412JB	8911-3412	16.07
2/3M425JB	8911-2425	15.68
3/3M425JB	8911-3425	15.68
2/3M437JB	8911-2437	17.06
3/3M437JB	8911-3437	17.06
2/3M450JB	8911-2450	17.57
3/3M450JB	8911-3450	17.57
2/3M462JB	8911-2462	18.04
3/3M462JB	8911-3462	18.04
2/3M475JB	8911-2475	18.55
3/3M475JB	8911-3475	18.55
2/3M487JB	8911-2487	19.02
3/3M487JB	8911-3487	19.02
2/3M500JB	8911-2500	19.54
3/3M500JB	8911-3500	19.54
2/3M515JB	8911-2515	20.13
3/3M515JB	8911-3515	20.13
2/3M530JB	8911-2530	20.72

Part No.	Product No.	Effective Length (In.)
3/3M530JB	8911-3530	20.72
2/3M545JB	8911-2545	21.31
3/3M545JB	8911-3545	21.31
2/3M560JB	8911-2560	21.90
3/3M560JB	8911-3560	21.90
2/3M580JB	8911-2580	22.69
3/3M580JB	8911-3580	22.69
2/3M600JB	8911-2600	23.47
3/3M600JB	8911-3600	23.47
2/3M615JB	8911-2615	24.06
3/3M615JB	8911-3615	24.06
2/3M630JB	8911-2630	24.65
3/3M630JB	8911-3630	24.65
2/3M650JB	8911-2650	25.44
3/3M650JB	8911-3650	25.44
2/3M670JB	8911-2670	26.23
3/3M670JB	8911-3670	26.23
2/3M690JB	8911-2690	27.01
3/3M690JB	8911-3690	27.01
2/3M710JB	8911-2710	27.80
3/3M710JB	8911-3710	27.80
2/3M730JB	8911-2730	28.59
3/3M730JB	8911-3730	28.59
2/3M750JB	8911-2750	29.38
3/3M750JB	8911-3750	29.38

Product No. Series 8912

5M

Nominal Strand Width 3/16"



Part No.	Product No.	Effective Length (In.)
2/5M280JB	8912-2280	11.02
3/5M280JB	8912-3280	11.02
4/5M280JB	8912-4280	11.02
5/5M280JB	8912-5280	11.02
2/5M290JB	8912-2290	11.42
3/5M290JB	8912-3290	11.42
4/5M290JB	8912-4290	11.42
5/5M290JB	8912-5290	11.42
2/5M300JB	8912-2300	11.81
3/5M300JB	8912-3300	11.81
4/5M300JB	8912-4300	11.81
5/5M300JB	8912-5300	11.81
2/5M307JB	8912-2307	12.09
3/5M307JB	8912-3307	12.09
4/5M307JB	8912-4307	12.09
5/5M307JB	8912-5307	12.09
2/5M315JB	8912-2315	12.40
3/5M315JB	8912-3315	12.40
4/5M315JB	8912-4315	12.40
5/5M315JB	8912-5315	12.40
2/5M325JB	8912-2325	12.80
3/5M325JB	8912-3325	12.80
4/5M325JB	8912-4325	12.80
5/5M325JB	8912-5325	12.80
2/5M335JB	8912-2335	13.19
3/5M335JB	8912-3335	13.19
4/5M335JB	8912-4335	13.19
5/5M335JB	8912-5335	13.19
2/5M345JB	8912-2345	13.58

Part No.	Product No.	Effective Length (In.)
3/5M345JB	8912-3345	13.58
4/5M345JB	8912-4345	13.58
5/5M345JB	8912-5345	13.58
2/5M355JB	8912-2355	13.98
3/5M355JB	8912-3355	13.98
4/5M355JB	8912-4355	13.98
5/5M355JB	8912-5355	13.98
2/5M365JB	8912-2365	14.37
3/5M365JB	8912-3365	14.37
4/5M365JB	8912-4365	14.37
5/5M365JB	8912-5365	14.37
2/5M375JB	8912-2375	14.76
3/5M375JB	8912-3375	14.76
4/5M375JB	8912-4375	14.76
5/5M375JB	8912-5375	14.76
2/5M387JB	8912-2387	15.24
3/5M387JB	8912-3387	15.24
4/5M387JB	8912-4387	15.24
5/5M387JB	8912-5387	15.24
2/5M400JB	8912-2400	15.75
3/5M400JB	8912-3400	15.75
4/5M400JB	8912-4400	15.75
5/5M400JB	8912-5400	15.75
2/5M412JB	8912-2412	16.22
3/5M412JB	8912-3412	16.22
4/5M412JB	8912-4412	16.22
5/5M412JB	8912-5412	16.22
2/5M425JB	8912-2425	16.73
3/5M425JB	8912-3425	16.73



Polyflex® JB® Belts

Product No. Series 8912 (continued)

5M (continued)

Part No.	Product No.	Effective Length (In.)
4/5M425JB	8912-4425	16.73
5/5M425JB	8912-5425	16.73
2/5M437JB	8912-2437	17.20
3/5M437JB	8912-3437	17.20
4/5M437JB	8912-4437	17.20
5/5M437JB	8912-5437	17.20
2/5M450JB	8912-2450	17.72
3/5M450JB	8912-3450	17.72
4/5M450JB	8912-4450	17.72
5/5M450JB	8912-5450	17.72
2/5M462JB	8912-2462	18.19
3/5M462JB	8912-3462	18.19
4/5M462JB	8912-4462	18.19
5/5M462JB	8912-5462	18.19
2/5M475JB	8912-2475	18.70
3/5M475JB	8912-3475	18.70
4/5M475JB	8912-4475	18.70
5/5M475JB	8912-5475	18.70
2/5M487JB	8912-2487	19.17
3/5M487JB	8912-3487	19.17
4/5M487JB	8912-4487	19.17
5/5M487JB	8912-5487	19.17
2/5M500JB	8912-2500	19.69
3/5M500JB	8912-3500	19.69
4/5M500JB	8912-4500	19.69
5/5M500JB	8912-5500	19.69
2/5M515JB	8912-2515	20.28
3/5M515JB	8912-3515	20.28
4/5M515JB	8912-4515	20.28
5/5M515JB	8912-5515	20.28
2/5M530JB	8912-2530	20.87
3/5M530JB	8912-3530	20.87
4/5M530JB	8912-4530	20.87
5/5M530JB	8912-5530	20.87
2/5M545JB	8912-2545	21.46
3/5M545JB	8912-3545	21.46
4/5M545JB	8912-4545	21.46
5/5M545JB	8912-5545	21.46
2/5M560JB	8912-2560	22.05
3/5M560JB	8912-3560	22.05
4/5M560JB	8912-4560	22.05
5/5M560JB	8912-5560	22.05
2/5M580JB	8912-2580	22.83
3/5M580JB	8912-3580	22.83
4/5M580JB	8912-4580	22.83
5/5M580JB	8912-5580	22.83
2/5M600JB	8912-2600	23.62
3/5M600JB	8912-3600	23.62
4/5M600JB	8912-4600	23.62
5/5M600JB	8912-5600	23.62
2/5M615JB	8912-2615	24.21
3/5M615JB	8912-3615	24.21
4/5M615JB	8912-4615	24.21
5/5M615JB	8912-5615	24.21
2/5M630JB	8912-2630	24.80
3/5M630JB	8912-3630	24.80
4/5M630JB	8912-4630	24.80
5/5M630JB	8912-5630	24.80
2/5M650JB	8912-2650	25.59
3/5M650JB	8912-3650	25.59
4/5M650JB	8912-4650	25.59
5/5M650JB	8912-5650	25.59

Part No.	Product No.	Effective Length (In.)
2/5M670JB	8912-2670	26.38
3/5M670JB	8912-3670	26.38
4/5M670JB	8912-4670	26.38
5/5M670JB	8912-5670	26.38
2/5M690JB	8912-2690	27.17
3/5M690JB	8912-3690	27.17
4/5M690JB	8912-4690	27.17
5/5M690JB	8912-5690	27.17
2/5M710JB	8912-2710	27.95
3/5M710JB	8912-3710	27.95
4/5M710JB	8912-4710	27.95
5/5M710JB	8912-5710	27.95
2/5M730JB	8912-2730	28.74
3/5M730JB	8912-3730	28.74
4/5M730JB	8912-4730	28.74
5/5M730JB	8912-5730	28.74
2/5M750JB	8912-2750	29.53
3/5M750JB	8912-3750	29.53
4/5M750JB	8912-4750	29.53
5/5M750JB	8912-5750	29.53
2/5M775JB	8912-2775	30.51
3/5M775JB	8912-3775	30.51
4/5M775JB	8912-4775	30.51
5/5M775JB	8912-5775	30.51
2/5M800JB	8912-2800	31.50
3/5M800JB	8912-3800	31.50
4/5M800JB	8912-4800	31.50
5/5M800JB	8912-5800	31.50
2/5M825JB	8912-2825	32.48
3/5M825JB	8912-3825	32.48
4/5M825JB	8912-4825	32.48
5/5M825JB	8912-5825	32.48
2/5M850JB	8912-2850	33.46
3/5M850JB	8912-3850	33.46
4/5M850JB	8912-4850	33.46
5/5M850JB	8912-5850	33.46
2/5M875JB	8912-2875	34.45
3/5M875JB	8912-3875	34.45
4/5M875JB	8912-4875	34.45
5/5M875JB	8912-5875	34.45
2/5M900JB	8912-2900	35.43
3/5M900JB	8912-3900	35.43
4/5M900JB	8912-4900	35.43
5/5M900JB	8912-5900	35.43
2/5M925JB	8912-2925	36.42
3/5M925JB	8912-3925	36.42
4/5M925JB	8912-4925	36.42
5/5M925JB	8912-5925	36.42
2/5M950JB	8912-2950	37.40
3/5M950JB	8912-3950	37.40
4/5M950JB	8912-4950	37.40
5/5M950JB	8912-5950	37.40
2/5M975JB	8912-2975	38.39
3/5M975JB	8912-3975	38.39
4/5M975JB	8912-4975	38.39
5/5M975JB	8912-5975	38.39
2/5M1000JB	8912-2100	39.37
3/5M1000JB	8912-3100	39.37
4/5M1000JB	8912-4100	39.37
5/5M1000JB	8912-5100	39.37
2/5M1030JB	8912-2103	40.55
3/5M1030JB	8912-3103	40.55



Product No. Series 8912 (continued)

5M (continued)

Part No.	Product No.	Effective Length (In.)
4/5M1030JB	8912-4103	40.55
5/5M1030JB	8912-5103	40.55
2/5M1060JB	8912-2106	41.73
3/5M1060JB	8912-3106	41.73
4/5M1060JB	8912-4106	41.73
5/5M1060JB	8912-5106	41.73
2/5M1090JB	8912-2109	42.91
3/5M1090JB	8912-3109	42.91
4/5M1090JB	8912-4109	42.91
5/5M1090JB	8912-5109	42.91
2/5M1120JB	8912-2112	44.09
3/5M1120JB	8912-3112	44.09
4/5M1120JB	8912-4112	44.09
5/5M1120JB	8912-5112	44.09
2/5M1150JB	8912-2115	45.28
3/5M1150JB	8912-3115	45.28
4/5M1150JB	8912-4115	45.28
5/5M1150JB	8912-5115	45.28
2/5M1180JB	8912-2118	46.46
3/5M1180JB	8912-3118	46.46
4/5M1180JB	8912-4118	46.46
5/5M1180JB	8912-5118	46.46
2/5M1220JB	8912-2122	48.03
3/5M1220JB	8912-3122	48.03
4/5M1220JB	8912-4122	48.03
5/5M1220JB	8912-5122	48.03
2/5M1250JB	8912-2125	49.21

Part No.	Product No.	Effective Length (In.)
3/5M1250JB	8912-3125	49.21
4/5M1250JB	8912-4125	49.21
5/5M1250JB	8912-5125	49.21
2/5M1280JB	8912-2128	50.39
3/5M1280JB	8912-3128	50.39
4/5M1280JB	8912-4128	50.39
5/5M1280JB	8912-5128	50.39
2/5M1320JB	8912-2132	51.97
3/5M1320JB	8912-3132	51.97
4/5M1320JB	8912-4132	51.97
5/5M1320JB	8912-5132	51.97
2/5M1360JB	8912-2136	53.54
3/5M1360JB	8912-3136	53.54
4/5M1360JB	8912-4136	53.54
5/5M1360JB	8912-5136	53.54
2/5M1400JB	8912-2140	55.12
3/5M1400JB	8912-3140	55.12
4/5M1400JB	8912-4140	55.12
5/5M1400JB	8912-5140	55.12
2/5M1450JB	8912-2145	57.09
3/5M1450JB	8912-3145	57.09
4/5M1450JB	8912-4145	57.09
5/5M1450JB	8912-5145	57.09
2/5M1500JB	8912-2150	59.06
3/5M1500JB	8912-3150	59.06
4/5M1500JB	8912-4150	59.06
5/5M1500JB	8912-5150	59.06

Product No. Series 8913

7M

Part No.	Product No.	Effective Length (In.)
2/7M500JB	8913-2500	19.30
3/7M500JB	8913-3500	19.30
4/7M500JB	8913-4500	19.30
5/7M500JB	8913-5500	19.30
2/7M515JB	8913-2515	19.90
3/7M515JB	8913-3515	19.90
4/7M515JB	8913-4515	19.90
5/7M515JB	8913-5515	19.90
2/7M530JB	8913-2530	20.50
3/7M530JB	8913-3530	20.50
4/7M530JB	8913-4530	20.50
5/7M530JB	8913-5530	20.50
2/7M545JB	8913-2545	21.10
3/7M545JB	8913-3545	21.10
4/7M545JB	8913-4545	21.10
5/7M545JB	8913-5545	21.10
2/7M560JB	8913-2560	21.60
3/7M560JB	8913-3560	21.60
4/7M560JB	8913-4560	21.60
5/7M560JB	8913-5560	21.60
2/7M580JB	8913-2580	22.40
3/7M580JB	8913-3580	22.40
4/7M580JB	8913-4580	22.40
5/7M580JB	8913-5580	22.40
2/7M600JB	8913-2600	23.20
3/7M600JB	8913-3600	23.20
4/7M600JB	8913-4600	23.20

Nominal Strand Width 3/32"



Part No.	Product No.	Effective Length (In.)
5/7M600JB	8913-5600	23.20
2/7M615JB	8913-2615	23.80
3/7M615JB	8913-3615	23.80
4/7M615JB	8913-4615	23.80
5/7M615JB	8913-5615	23.80
2/7M630JB	8913-2630	24.40
3/7M630JB	8913-3630	24.40
4/7M630JB	8913-4630	24.40
5/7M630JB	8913-5630	24.40
2/7M650JB	8913-2650	25.20
3/7M650JB	8913-3650	25.20
4/7M650JB	8913-4650	25.20
5/7M650JB	8913-5650	25.20
2/7M670JB	8913-2670	26.00
3/7M670JB	8913-3670	26.00
4/7M670JB	8913-4670	26.00
5/7M670JB	8913-5670	26.00
2/7M690JB	8913-2690	26.80
3/7M690JB	8913-3690	26.80
4/7M690JB	8913-4690	26.80
5/7M690JB	8913-5690	26.80
2/7M710JB	8913-2710	27.70
3/7M710JB	8913-3710	27.70
4/7M710JB	8913-4710	27.70
5/7M710JB	8913-5710	27.70
2/7M730JB	8913-2730	28.50
3/7M730JB	8913-3730	28.50



Polyflex® JB® Belts

Product No. Series 8913 (continued)

7M (continued)

Part No.	Product No.	Effective Length (In.)
4/7M730JB	8913-4730	28.50
5/7M730JB	8913-5730	28.50
2/7M750JB	8913-2750	29.30
3/7M750JB	8913-3750	29.30
4/7M750JB	8913-4750	29.30
5/7M750JB	8913-5750	29.30
2/7M775JB	8913-2775	30.30
3/7M775JB	8913-3775	30.30
4/7M775JB	8913-4775	30.30
5/7M775JB	8913-5775	30.30
2/7M800JB	8913-2800	31.20
3/7M800JB	8913-3800	31.20
4/7M800JB	8913-4800	31.20
5/7M800JB	8913-5800	31.20
2/7M825JB	8913-2825	32.20
3/7M825JB	8913-3825	32.20
4/7M825JB	8913-4825	32.20
5/7M825JB	8913-5825	32.20
2/7M850JB	8913-2850	33.20
3/7M850JB	8913-3850	33.20
4/7M850JB	8913-4850	33.20
5/7M850JB	8913-5850	33.20
2/7M875JB	8913-2875	34.20
3/7M875JB	8913-3875	34.20
4/7M875JB	8913-4875	34.20
5/7M875JB	8913-5875	34.20
2/7M900JB	8913-2900	35.20
3/7M900JB	8913-3900	35.20
4/7M900JB	8913-4900	35.20
5/7M900JB	8913-5900	35.20
2/7M925JB	8913-2925	36.20
3/7M925JB	8913-3925	36.20
4/7M925JB	8913-4925	36.20
5/7M925JB	8913-5925	36.20
2/7M950JB	8913-2950	37.20
3/7M950JB	8913-3950	37.20
4/7M950JB	8913-4950	37.20
5/7M950JB	8913-5950	37.20
2/7M975JB	8913-2975	38.10
3/7M975JB	8913-3975	38.10
4/7M975JB	8913-4975	38.10
5/7M975JB	8913-5975	38.10
2/7M1000JB	8913-2100	39.10
3/7M1000JB	8913-3100	39.10
4/7M1000JB	8913-4100	39.10
5/7M1000JB	8913-5100	39.10
2/7M1030JB	8913-2103	40.30
3/7M1030JB	8913-3103	40.30
4/7M1030JB	8913-4103	40.30
5/7M1030JB	8913-5103	40.30
2/7M1060JB	8913-2106	41.50
3/7M1060JB	8913-3106	41.50
4/7M1060JB	8913-4106	41.50
5/7M1060JB	8913-5106	41.50
2/7M1090JB	8913-2109	42.70
3/7M1090JB	8913-3109	42.70
4/7M1090JB	8913-4109	42.70
5/7M1090JB	8913-5109	42.70
2/7M1120JB	8913-2112	43.80
3/7M1120JB	8913-3112	43.80
4/7M1120JB	8913-4112	43.80
5/7M1120JB	8913-5112	43.80

Part No.	Product No.	Effective Length (In.)
2/7M1150JB	8913-2115	45.00
3/7M1150JB	8913-3115	45.00
4/7M1150JB	8913-4115	45.00
5/7M1150JB	8913-5115	45.00
2/7M1180JB	8913-2118	46.20
3/7M1180JB	8913-3118	46.20
4/7M1180JB	8913-4118	46.20
5/7M1180JB	8913-5118	46.20
2/7M1220JB	8913-2122	47.80
3/7M1220JB	8913-3122	47.80
4/7M1220JB	8913-4122	47.80
5/7M1220JB	8913-5122	47.80
2/7M1250JB	8913-2125	49.00
3/7M1250JB	8913-3125	49.00
4/7M1250JB	8913-4125	49.00
5/7M1250JB	8913-5125	49.00
2/7M1280JB	8913-2128	50.10
3/7M1280JB	8913-3128	50.10
4/7M1280JB	8913-4128	50.10
5/7M1280JB	8913-5128	50.10
2/7M1320JB	8913-2132	51.70
3/7M1320JB	8913-3132	51.70
4/7M1320JB	8913-4132	51.70
5/7M1320JB	8913-5132	51.70
2/7M1360JB	8913-2136	53.30
3/7M1360JB	8913-3136	53.30
4/7M1360JB	8913-4136	53.30
5/7M1360JB	8913-5136	53.30
2/7M1400JB	8913-2140	54.90
3/7M1400JB	8913-3140	54.90
4/7M1400JB	8913-4140	54.90
5/7M1400JB	8913-5140	54.90
2/7M1450JB	8913-2145	56.80
3/7M1450JB	8913-3145	56.80
4/7M1450JB	8913-4145	56.80
5/7M1450JB	8913-5145	56.80
2/7M1500JB	8913-2150	58.80
3/7M1500JB	8913-3150	58.80
4/7M1500JB	8913-4150	58.80
5/7M1500JB	8913-5150	58.80
2/7M1550JB	8913-2155	60.80
3/7M1550JB	8913-3155	60.80
4/7M1550JB	8913-4155	60.80
5/7M1550JB	8913-5155	60.80
2/7M1600JB	8913-2160	62.70
3/7M1600JB	8913-3160	62.70
4/7M1600JB	8913-4160	62.70
5/7M1600JB	8913-5160	62.70
2/7M1650JB	8913-2165	64.70
3/7M1650JB	8913-3165	64.70
4/7M1650JB	8913-4165	64.70
5/7M1650JB	8913-5165	64.70
2/7M1700JB	8913-2170	66.70
3/7M1700JB	8913-3170	66.70
4/7M1700JB	8913-4170	66.70
5/7M1700JB	8913-5170	66.70
2/7M1750JB	8913-2175	68.60
3/7M1750JB	8913-3175	68.60
4/7M1750JB	8913-4175	68.60
5/7M1750JB	8913-5175	68.60
2/7M1800JB	8913-2180	70.60
3/7M1800JB	8913-3180	70.60



Product No. Series 8913 (continued)

7M (continued)

Part No.	Product No.	Effective Length (In.)
4/7M1800JB	8913-4180	70.60
5/7M1800JB	8913-5180	70.60
2/7M1850JB	8913-2185	72.60
3/7M1850JB	8913-3185	72.60
4/7M1850JB	8913-4185	72.60
5/7M1850JB	8913-5185	72.60
2/7M1900JB	8913-2190	74.60
3/7M1900JB	8913-3190	74.60
4/7M1900JB	8913-4190	74.60
5/7M1900JB	8913-5190	74.60
2/7M1950JB	8913-2195	76.50
3/7M1950JB	8913-3195	76.50
4/7M1950JB	8913-4195	76.50
5/7M1950JB	8913-5195	76.50
2/7M2000JB	8913-2200	78.50
3/7M2000JB	8913-3200	78.50
4/7M2000JB	8913-4200	78.50
5/7M2000JB	8913-5200	78.50
2/7M2060JB	8913-2206	80.90

Part No.	Product No.	Effective Length (In.)
3/7M2060JB	8913-3206	80.90
4/7M2060JB	8913-4206	80.90
5/7M2060JB	8913-5206	80.90
2/7M2120JB	8913-2212	83.20
3/7M2120JB	8913-3212	83.20
4/7M2120JB	8913-4212	83.20
5/7M2120JB	8913-5212	83.20
2/7M2180JB	8913-2218	85.60
3/7M2180JB	8913-3218	85.60
4/7M2180JB	8913-4218	85.60
5/7M2180JB	8913-5218	85.60
2/7M2240JB	8913-2224	87.90
3/7M2240JB	8913-3224	87.90
4/7M2240JB	8913-4224	87.90
5/7M2240JB	8913-5224	87.90
2/7M2300JB	8913-2230	90.30
3/7M2300JB	8913-3230	90.30
4/7M2300JB	8913-4230	90.30
5/7M2300JB	8913-5230	90.30

Product No. Series 8914

11M

Part No.	Product No.	Effective Length (In.)
2/11M710JB	8914-2710	27.30
3/11M710JB	8914-3710	27.30
2/11M730JB	8914-2730	28.00
3/11M730JB	8914-3730	28.00
2/11M750JB	8914-2750	28.80
3/11M750JB	8914-3750	28.80
2/11M775JB	8914-2775	29.80
3/11M775JB	8914-3775	29.80
2/11M800JB	8914-2800	30.80
3/11M800JB	8914-3800	30.80
2/11M825JB	8914-2825	31.80
3/11M825JB	8914-3825	31.80
2/11M850JB	8914-2850	32.80
3/11M850JB	8914-3850	32.80
2/11M875JB	8914-2875	33.70
3/11M875JB	8914-3875	33.70
2/11M900JB	8914-2900	34.70
3/11M900JB	8914-3900	34.70
2/11M925JB	8914-2925	35.70
3/11M925JB	8914-3925	35.70
2/11M950JB	8914-2950	36.70
3/11M950JB	8914-3950	36.70
2/11M975JB	8914-2975	37.70
3/11M975JB	8914-3975	37.70
2/11M1000JB	8914-2100	38.70
3/11M1000JB	8914-3100	38.70
2/11M1030JB	8914-2103	39.90
3/11M1030JB	8914-3103	39.90
2/11M1060JB	8914-2106	41.00
3/11M1060JB	8914-3106	41.00
2/11M1090JB	8914-2109	42.20
3/11M1090JB	8914-3109	42.20
2/11M1120JB	8914-2112	43.40
3/11M1120JB	8914-3112	43.40
2/11M1150JB	8914-2115	44.60

Nominal Strand Width 7/16"



Part No.	Product No.	Effective Length (In.)
3/11M1150JB	8914-3115	44.60
2/11M1180JB	8914-2118	45.80
3/11M1180JB	8914-3118	45.80
2/11M1220JB	8914-2122	47.30
3/11M1220JB	8914-3122	47.30
2/11M1250JB	8914-2125	48.50
3/11M1250JB	8914-3125	48.50
2/11M1280JB	8914-2128	49.70
3/11M1280JB	8914-3128	49.70
2/11M1320JB	8914-2132	51.30
3/11M1320JB	8914-3132	51.30
2/11M1360JB	8914-2136	52.80
3/11M1360JB	8914-3136	52.80
2/11M1400JB	8914-2140	54.40
3/11M1400JB	8914-3140	54.40
2/11M1450JB	8914-2145	56.40
3/11M1450JB	8914-3145	56.40
2/11M1500JB	8914-2150	58.40
3/11M1500JB	8914-3150	58.40
2/11M1550JB	8914-2155	60.30
3/11M1550JB	8914-3155	60.30
2/11M1600JB	8914-2160	62.30
3/11M1600JB	8914-3160	62.30
2/11M1650JB	8914-2165	64.30
3/11M1650JB	8914-3165	64.30
2/11M1700JB	8914-2170	66.20
3/11M1700JB	8914-3170	66.20
2/11M1750JB	8914-2175	68.20
3/11M1750JB	8914-3175	68.20
2/11M1800JB	8914-2180	70.20
3/11M1800JB	8914-3180	70.20
2/11M1850JB	8914-2185	72.10
3/11M1850JB	8914-3185	72.10
2/11M1900JB	8914-2190	74.10
3/11M1900JB	8914-3190	74.10



Polyflex® JB® Belts

Product No. Series 8914 (continued)

11M (continued)

Part No.	Product No.	Effective Length (In.)
2/11M1950JB	8914-2195	76.10
3/11M1950JB	8914-3195	76.10
2/11M2000JB	8914-2200	78.00
3/11M2000JB	8914-3200	78.00
2/11M2060JB	8914-2206	80.40
3/11M2060JB	8914-3206	80.40
2/11M2120JB	8914-2212	82.80

Part No.	Product No.	Effective Length (In.)
3/11M2120JB	8914-3212	82.80
2/11M2180JB	8914-2218	85.10
3/11M2180JB	8914-3218	85.10
2/11M2240JB	8914-2224	87.50
3/11M2240JB	8914-3224	87.50
2/11M2300JB	8914-2230	89.90
3/11M2300JB	8914-3230	89.90

